

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033897

Luminaire Tested: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033897
REPORT IS A COMBINATION OF REPORTS P999987 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5760.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033897

CATALOG NUMBER: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033897

CATALOG NUMBER: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	39	36
6	67	55	47	41	64	53	45	39	48	42	37	44	38	34	40	35	32
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	33	29	26
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14554	14554	14554
5°	14556	14122	14123
10°	14432	13676	13513
15°	14233	13122	12794
20°	13973	12489	11974
25°	13649	11806	11172
30°	13332	11110	10273
35°	12983	10404	9394
40°	12568	9645	8490
45°	12178	8891	7595
50°	11734	8068	6687
55°	11256	7225	5749
60°	10724	6328	4824
65°	10212	5301	3932
70°	9482	4219	3005
75°	8547	3070	2101
80°	7140	1884	1511
85°	5370	1086	830

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12178 cd/sqm

TEST NUMBER: P1033897

CATALOG NUMBER: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.8	2.9
10°-20°	467.9	8.1
20°-30°	675.6	11.7
30°-40°	765.7	13.3
40°-50°	739.3	12.8
50°-60°	614.6	10.7
60°-70°	424.2	7.4
70°-80°	214.4	3.7
80°-90°	55.7	1.0
90°-100°	38.4	0.7
100°-110°	115.0	2.0
110°-120°	195.4	3.4
120°-130°	257.7	4.5
130°-140°	289.5	5.0
140°-150°	284.5	4.9
150°-160°	239.3	4.2
160°-170°	159.2	2.8
170°-180°	55.7	1.0
0°-30°	1311.4	22.8
0°-40°	2077.1	36.1
0°-60°	3431.0	59.6
0°-90°	4125.3	71.6
90°-120°	348.8	6.1
90°-150°	1180.5	20.5
90°-180°	1635.0	28.4
0°-180°	5760.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1785	1785	1785	1785	1785	
5°	1782	1777	1760	1774	1771	169
15°	1697	1685	1651	1648	1639	478
25°	1535	1510	1454	1431	1417	707
35°	1327	1283	1215	1168	1144	829
45°	1082	1032	950	883	858	835
55°	820	765	676	605	579	734
65°	558	499	411	353	336	551
75°	297	246	182	150	142	313
85°	74	46	42	40	40	81
90°	1	6	10	13	14	6
95°	27	31	35	36	36	30
105°	106	107	108	110	111	113
115°	199	199	198	197	197	196
125°	289	289	289	288	287	258
135°	373	376	376	375	374	289
145°	453	455	456	455	454	284
155°	520	520	519	521	519	239
165°	566	564	563	566	564	159
175°	588	586	586	589	586	56
180°	589	589	589	589	589	

TEST NUMBER: P1033897

CATALOG NUMBER: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.8	1784.8	1784.8	1784.8	1784.8
2.5°	1790.3	1784.8	1769.8	1784.8	1783.4
5°	1782.1	1776.6	1760.2	1773.9	1771.1
7.5°	1769.8	1764.3	1743.8	1753.4	1749.3
10°	1750.6	1743.8	1719.2	1724.7	1719.2
12.5°	1726.0	1717.8	1687.8	1690.5	1682.3
15°	1697.3	1685.0	1650.9	1648.2	1638.6
17.5°	1664.5	1646.8	1607.2	1600.3	1586.7
20°	1624.9	1607.2	1560.7	1549.8	1532.0
22.5°	1581.2	1560.7	1510.1	1492.4	1478.7
25°	1534.7	1510.1	1454.1	1430.9	1417.2
27.5°	1486.9	1456.8	1398.1	1370.7	1351.6
30°	1436.3	1402.2	1337.9	1303.8	1281.9
32.5°	1383.0	1343.4	1276.4	1235.4	1214.9
35°	1327.0	1283.3	1214.9	1168.5	1143.9
37.5°	1268.2	1223.1	1148.0	1097.4	1072.8
40°	1205.4	1160.3	1082.4	1025.0	1000.4
42.5°	1145.2	1097.4	1015.4	956.6	930.7
45°	1082.4	1031.8	949.8	882.8	858.2
47.5°	1018.1	966.2	881.5	811.8	784.4
50°	952.5	899.2	811.8	743.4	717.5
52.5°	885.6	833.6	743.4	673.7	646.4
55°	820.0	765.3	676.5	605.4	579.4
57.5°	755.7	698.3	610.9	538.5	519.3
60°	686.0	631.4	543.9	472.9	451.0
62.5°	623.2	565.8	475.6	411.4	395.0
65°	557.6	498.8	411.4	352.6	336.2
67.5°	489.3	433.2	351.2	299.3	280.2
70°	425.0	367.6	289.7	244.6	231.0
72.5°	356.7	306.1	233.7	196.8	184.5
75°	296.6	246.0	181.8	150.3	142.1
77.5°	233.7	190.0	135.3	113.4	110.7
80°	173.6	133.9	92.9	88.8	87.5
82.5°	121.6	86.1	67.0	64.2	62.9
85°	73.8	46.5	42.4	39.6	39.6
87.5°	31.4	20.5	19.1	17.8	19.1
90°	1.4	6.4	10.0	12.8	13.7
92.5°	11.8	17.8	20.0	21.4	21.9
95°	27.3	31.4	34.6	36.0	36.0
97.5°	43.7	47.4	51.0	52.9	52.9
100°	63.8	65.6	69.7	70.6	70.6
102.5°	84.8	85.2	88.9	90.2	90.7
105°	106.2	106.6	108.4	109.8	111.2
107.5°	128.5	129.0	129.4	131.2	130.8
110°	151.3	152.2	151.7	150.8	152.2

TEST NUMBER: P1033897

CATALOG NUMBER: S124RDIW-B1020D470UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.0	175.0	174.1	174.1	174.1
115°	198.7	198.7	197.8	197.3	196.8
117.5°	221.0	221.0	220.5	219.2	217.8
120°	243.3	245.1	243.8	241.5	242.4
122.5°	266.6	267.0	266.6	265.2	262.9
125°	289.3	289.3	288.9	288.0	287.1
127.5°	309.9	311.2	310.3	309.4	308.9
130°	331.7	333.1	333.1	332.2	330.4
132.5°	354.1	355.0	354.5	353.6	353.1
135°	373.2	375.9	375.9	375.0	373.6
137.5°	394.6	396.0	396.9	395.5	396.0
140°	416.0	416.9	416.9	416.5	416.0
142.5°	435.6	436.5	436.1	436.1	436.1
145°	453.4	455.2	455.7	455.2	453.8
147.5°	471.6	473.9	473.4	473.0	472.5
150°	488.0	489.8	489.8	489.8	489.4
152.5°	503.5	504.4	504.9	506.2	504.9
155°	519.5	519.5	519.0	520.8	519.0
157.5°	533.1	532.2	532.2	533.6	532.2
160°	545.0	544.5	544.1	545.4	543.2
162.5°	555.9	554.5	554.1	556.8	554.5
165°	565.5	564.1	563.2	565.9	564.1
167.5°	573.2	571.4	571.4	574.1	571.4
170°	579.6	577.3	577.8	580.5	577.3
172.5°	584.2	582.3	582.3	585.5	582.3
175°	588.3	586.0	585.5	588.7	585.5
177.5°	590.1	587.8	587.8	591.0	587.4
180°	589.2	589.2	589.2	589.2	589.2

(END OF REPORT)