

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034382

Luminaire Tested: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034382
REPORT IS A COMBINATION OF REPORTS P1003003 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7396.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034382

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034382

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	98	93	89	85	91	86	83	79	74	71	69	62	60	59	52	50	49
2	89	81	74	69	82	75	69	65	64	60	56	54	51	48	45	43	41
3	81	71	63	57	75	66	59	54	56	51	47	48	44	40	40	37	34
4	74	63	54	48	68	58	51	45	50	44	40	42	38	34	35	32	29
5	68	56	47	41	62	52	44	39	45	39	34	38	33	30	32	28	25
6	62	50	42	36	58	47	39	34	40	34	30	34	30	26	29	25	22
7	58	45	37	31	53	42	35	29	36	30	26	31	26	23	26	23	20
8	53	41	33	27	49	38	31	26	33	27	23	28	24	20	24	20	18
9	50	37	30	24	46	35	28	23	30	25	21	26	22	18	22	19	16
10	47	34	27	22	43	32	25	21	28	22	19	24	20	17	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8807	8807	8807
5°	8821	8622	8643
10°	8755	8446	8422
15°	8648	8241	8150
20°	8504	7994	7880
25°	8334	7731	7554
30°	8127	7445	7257
35°	7935	7180	6984
40°	7738	6902	6708
45°	7517	6661	6460
50°	7304	6399	6236
55°	7049	6149	5976
60°	6770	5864	5709
65°	6477	5564	5409
70°	6142	5162	5097
75°	5615	4765	4716
80°	4922	4282	4295
85°	4237	3899	4073

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7517 cd/sqm

TEST NUMBER: P1034382

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	1.8
10°-20°	369.2	5.0
20°-30°	549.1	7.4
30°-40°	650.3	8.8
40°-50°	672.3	9.1
50°-60°	619.3	8.4
60°-70°	500.6	6.8
70°-80°	335.0	4.5
80°-90°	174.7	2.4
90°-100°	132.2	1.8
100°-110°	302.3	4.1
110°-120°	463.1	6.3
120°-130°	559.9	7.6
130°-140°	584.8	7.9
140°-150°	540.0	7.3
150°-160°	434.9	5.9
160°-170°	281.3	3.8
170°-180°	97.0	1.3
0°-30°	1048.4	14.2
0°-40°	1698.6	23.0
0°-60°	2990.2	40.4
0°-90°	4000.4	54.1
90°-120°	897.6	12.1
90°-150°	2582.4	34.9
90°-180°	3396.0	45.9
0°-180°	7396.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1374	1372	1362	1373	1372	130
15°	1312	1314	1304	1312	1307	370
25°	1193	1197	1188	1194	1187	549
35°	1032	1042	1038	1042	1042	646
45°	850	865	872	881	883	656
55°	654	675	697	712	717	584
65°	450	481	513	534	539	447
75°	248	283	326	353	360	263
85°	74	119	166	195	206	77
90°	22	72	123	157	169	17
95°	61	94	110	144	153	67
105°	235	259	300	327	335	249
115°	426	439	475	496	500	422
125°	600	604	630	649	654	535
135°	744	747	755	771	773	573
145°	860	861	861	868	869	538
155°	946	942	943	945	939	436
165°	998	994	995	999	993	282
175°	1021	1016	1017	1023	1016	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1034382

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.5	1374.5	1374.5	1374.5	1374.5
2.5°	1378.6	1375.9	1366.4	1375.9	1374.5
5°	1374.5	1371.8	1362.4	1373.2	1371.8
7.5°	1365.1	1363.7	1354.3	1363.7	1362.4
10°	1351.6	1351.6	1340.8	1350.3	1348.9
12.5°	1332.7	1334.1	1326.0	1332.7	1328.7
15°	1312.5	1313.9	1304.4	1312.5	1307.1
17.5°	1286.9	1289.6	1280.2	1286.9	1282.9
20°	1258.6	1261.3	1251.9	1255.9	1255.9
22.5°	1226.3	1231.7	1220.9	1226.3	1222.2
25°	1192.6	1196.6	1188.5	1193.9	1187.2
27.5°	1156.2	1161.6	1152.2	1156.2	1153.5
30°	1114.4	1122.5	1114.4	1117.1	1115.8
32.5°	1076.7	1083.4	1078.0	1080.7	1079.4
35°	1032.2	1041.7	1037.6	1041.7	1041.7
37.5°	989.1	997.2	995.8	1001.2	999.9
40°	944.6	955.4	954.1	959.5	962.2
42.5°	896.1	911.0	915.0	921.7	921.7
45°	850.3	865.1	871.9	881.3	882.7
47.5°	803.1	816.6	827.4	840.9	843.6
50°	754.6	769.5	784.3	799.1	803.1
52.5°	703.4	722.3	741.2	757.3	760.0
55°	653.6	675.1	696.7	711.5	716.9
57.5°	602.4	628.0	652.2	668.4	672.4
60°	551.2	578.1	605.1	625.3	629.3
62.5°	501.3	528.2	557.9	580.8	586.2
65°	450.1	481.1	513.4	533.6	539.0
67.5°	402.9	432.6	464.9	489.2	495.9
70°	350.4	381.4	416.4	442.0	450.1
72.5°	299.2	331.5	370.6	398.9	404.3
75°	248.0	283.0	326.1	353.1	359.8
77.5°	198.1	238.5	278.9	308.6	314.0
80°	152.3	192.7	238.5	268.2	273.6
82.5°	110.5	153.6	200.8	229.1	239.9
85°	74.1	118.6	165.8	195.4	206.2
87.5°	47.2	90.3	136.1	167.1	176.5
90°	22.4	71.5	122.6	157.4	169.1
92.5°	33.3	65.5	117.2	150.7	160.9
95°	60.6	93.5	110.5	143.9	153.4
97.5°	97.2	134.0	106.6	136.4	146.6
100°	141.2	171.8	217.9	133.4	138.5
102.5°	186.1	214.7	258.0	286.4	230.9
105°	234.6	259.3	299.7	326.7	335.3
107.5°	284.8	303.6	344.2	372.0	377.0
110°	333.4	349.6	388.8	412.1	422.4

TEST NUMBER: P1034382

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.3	394.8	431.8	453.1	461.0
115°	425.9	439.1	475.0	496.1	499.7
117.5°	473.7	480.5	517.2	535.6	543.5
120°	519.1	522.5	555.7	577.1	581.4
122.5°	557.9	563.0	593.5	613.5	617.0
125°	599.6	603.5	630.5	649.0	653.5
127.5°	638.3	640.8	662.9	681.6	683.6
130°	674.6	677.1	696.8	713.3	716.3
132.5°	709.6	714.2	725.4	744.2	745.8
135°	743.7	746.8	754.8	770.8	773.0
137.5°	775.5	778.6	782.5	798.7	800.3
140°	805.1	806.6	807.3	823.6	824.5
142.5°	833.1	832.6	834.1	846.2	847.1
145°	860.4	860.6	860.6	868.1	868.9
147.5°	883.3	883.3	884.1	887.5	884.9
150°	906.0	904.5	906.0	907.5	902.8
152.5°	928.0	924.2	925.7	927.2	921.9
155°	946.1	941.6	943.1	945.4	939.3
157.5°	960.5	958.2	958.2	960.5	954.5
160°	975.6	971.1	971.9	974.9	968.8
162.5°	987.8	983.2	984.0	988.5	981.7
165°	998.4	993.8	994.6	999.1	993.1
167.5°	1006.7	1002.1	1002.9	1008.2	1001.4
170°	1013.5	1008.2	1009.0	1015.0	1008.2
172.5°	1018.0	1012.7	1014.2	1019.5	1012.7
175°	1021.1	1016.5	1017.3	1023.3	1016.5
177.5°	1023.3	1018.8	1019.5	1024.8	1018.8
180°	1021.1	1021.1	1021.1	1021.1	1021.1

(END OF REPORT)