

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034386

Luminaire Tested: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034386
REPORT IS A COMBINATION OF REPORTS P1003009 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7540.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034386

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034386

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45
3	83	73	66	60	77	68	62	56	60	55	50	52	48	44	44	41	39
4	76	65	57	50	70	61	53	48	53	47	43	46	42	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26
7	59	47	39	33	55	44	37	31	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1034386

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.1
10°-20°	452.1	6.0
20°-30°	667.5	8.9
30°-40°	778.8	10.3
40°-50°	782.2	10.4
50°-60°	686.6	9.1
60°-70°	511.4	6.8
70°-80°	292.1	3.9
80°-90°	85.8	1.1
90°-100°	34.5	0.5
100°-110°	229.5	3.0
110°-120°	413.3	5.5
120°-130°	530.4	7.0
130°-140°	570.5	7.6
140°-150°	535.5	7.1
150°-160°	433.1	5.7
160°-170°	280.1	3.7
170°-180°	96.6	1.3
0°-30°	1279.7	17.0
0°-40°	2058.4	27.3
0°-60°	3527.2	46.8
0°-90°	4416.5	58.6
90°-120°	677.3	9.0
90°-150°	2313.7	30.7
90°-180°	3124.0	41.4
0°-180°	7540.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	7	12	16	18	7
95°	43	41	12	16	16	53
105°	222	225	225	225	224	235
115°	416	420	421	418	413	412
125°	592	597	597	594	592	529
135°	738	742	741	739	735	569
145°	856	857	857	858	853	535
155°	942	938	939	942	935	434
165°	994	990	990	995	989	281
175°	1017	1012	1013	1019	1012	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1034386

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	0.8	6.8	12.1	15.8	18.1
92.5°	14.3	7.5	12.1	15.8	16.6
95°	43.0	40.7	12.1	15.8	15.8
97.5°	80.7	85.2	13.6	15.1	15.8
100°	125.9	128.1	131.2	18.8	15.8
102.5°	171.9	174.9	176.4	177.9	114.6
105°	221.6	224.6	224.6	224.6	223.9
107.5°	272.9	272.9	274.4	275.1	272.1
110°	322.6	322.6	324.1	321.9	322.6



TEST NUMBER: P1034386

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	369.3	371.6	372.4	369.3	367.8
115°	416.1	419.8	420.6	417.6	413.1
117.5°	465.1	465.1	468.1	463.6	462.1
120°	510.3	509.5	511.8	510.3	506.5
122.5°	550.2	554.0	554.8	553.3	548.7
125°	591.7	597.0	597.0	594.0	591.7
127.5°	631.7	635.4	634.7	633.2	627.1
130°	667.8	671.6	672.4	670.1	666.3
132.5°	704.0	708.5	706.3	706.3	702.5
135°	737.9	742.5	741.0	739.4	734.9
137.5°	769.6	774.1	772.6	772.6	768.8
140°	800.5	802.0	801.3	802.8	798.2
142.5°	828.4	829.1	830.7	830.7	826.1
145°	855.5	857.0	857.0	857.8	853.3
147.5°	879.6	879.6	880.4	881.2	875.9
150°	902.3	900.8	902.3	903.8	897.7
152.5°	924.1	920.3	921.9	923.4	918.1
155°	942.2	937.7	939.2	941.5	935.4
157.5°	956.5	954.3	954.3	956.5	950.5
160°	971.6	967.1	967.8	970.9	964.8
162.5°	983.7	979.1	979.9	984.4	977.6
165°	994.2	989.7	990.4	995.0	988.9
167.5°	1002.5	998.0	998.7	1004.0	997.2
170°	1009.3	1004.0	1004.8	1010.8	1004.0
172.5°	1013.8	1008.5	1010.0	1015.3	1008.5
175°	1016.8	1012.3	1013.1	1019.1	1012.3
177.5°	1019.1	1014.6	1015.3	1020.6	1014.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)