

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034387

Luminaire Tested: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034387
REPORT IS A COMBINATION OF REPORTS P1003010 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7572.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034387

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034387

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45
3	83	73	66	60	77	68	62	56	60	55	50	52	48	44	44	41	39
4	76	65	57	50	70	61	53	48	53	47	43	46	42	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26
7	59	47	39	33	55	44	37	31	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10915	10915	10915
5°	10916	10662	10682
10°	10825	10417	10384
15°	10683	10125	10034
20°	10491	9786	9632
25°	10285	9416	9202
30°	10036	9031	8749
35°	9769	8627	8241
40°	9495	8200	7789
45°	9198	7784	7309
50°	8871	7313	6750
55°	8547	6792	6235
60°	8162	6243	5637
65°	7700	5608	5018
70°	7229	4878	4305
75°	6440	4017	3480
80°	5487	3000	2560
85°	4237	1775	1410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9198 cd/sqm

TEST NUMBER: P1034387

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.1
10°-20°	454.1	6.0
20°-30°	670.4	8.9
30°-40°	782.1	10.3
40°-50°	785.5	10.4
50°-60°	689.5	9.1
60°-70°	513.6	6.8
70°-80°	293.3	3.9
80°-90°	86.2	1.1
90°-100°	34.7	0.5
100°-110°	230.4	3.0
110°-120°	415.0	5.5
120°-130°	532.7	7.0
130°-140°	572.9	7.6
140°-150°	537.7	7.1
150°-160°	434.9	5.7
160°-170°	281.3	3.7
170°-180°	97.0	1.3
0°-30°	1285.2	17.0
0°-40°	2067.3	27.3
0°-60°	3542.4	46.8
0°-90°	4435.5	58.6
90°-120°	680.1	9.0
90°-150°	2323.3	30.7
90°-180°	3136.0	41.4
0°-180°	7572.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1704	1704	1704	1704	1704	
5°	1701	1698	1685	1697	1696	161
15°	1621	1617	1602	1609	1609	457
25°	1472	1465	1448	1450	1446	677
35°	1271	1266	1247	1240	1229	795
45°	1040	1035	1019	1003	999	802
55°	792	788	770	757	748	707
65°	535	532	518	505	500	531
75°	284	282	275	271	266	303
85°	74	76	76	74	71	81
90°	1	7	12	16	18	7
95°	43	41	12	16	16	53
105°	222	226	226	226	225	236
115°	418	422	422	419	415	414
125°	594	600	600	596	594	531
135°	741	746	744	742	738	571
145°	859	861	861	861	857	537
155°	946	942	943	945	939	436
165°	998	994	995	999	993	282
175°	1021	1016	1017	1023	1016	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1034387

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1703.6	1703.6	1703.6	1703.6	1703.6
2.5°	1709.0	1704.9	1691.5	1704.9	1703.6
5°	1700.9	1698.2	1684.7	1696.8	1695.5
7.5°	1688.8	1686.1	1671.2	1683.4	1682.0
10°	1671.2	1668.5	1653.7	1664.5	1663.1
12.5°	1649.7	1644.3	1630.8	1638.9	1638.9
15°	1621.4	1617.3	1602.5	1609.2	1609.2
17.5°	1591.7	1585.0	1570.2	1578.2	1571.5
20°	1552.6	1549.9	1532.4	1541.8	1535.1
22.5°	1513.5	1508.2	1492.0	1497.4	1493.3
25°	1471.8	1465.0	1447.5	1450.2	1446.2
27.5°	1423.2	1419.2	1401.7	1403.0	1399.0
30°	1376.1	1372.0	1351.8	1349.1	1345.1
32.5°	1324.9	1318.1	1300.6	1295.2	1287.1
35°	1270.9	1265.6	1246.7	1239.9	1229.2
37.5°	1215.7	1208.9	1191.4	1182.0	1175.3
40°	1159.1	1152.3	1133.5	1121.3	1117.3
42.5°	1098.4	1093.0	1074.2	1063.4	1056.7
45°	1040.5	1035.1	1018.9	1002.7	998.7
47.5°	977.1	978.5	958.3	942.1	932.7
50°	916.5	912.4	896.3	878.7	869.3
52.5°	854.5	851.8	834.3	819.4	808.7
55°	792.5	788.4	769.6	757.4	748.0
57.5°	726.4	725.1	708.9	692.8	688.7
60°	664.5	659.1	644.2	630.8	621.3
62.5°	599.8	595.7	583.6	568.8	562.0
65°	535.1	532.4	517.5	505.4	500.0
67.5°	471.7	466.3	455.5	444.8	442.1
70°	412.4	405.7	393.5	385.5	380.1
72.5°	347.7	343.7	336.9	327.5	322.1
75°	284.4	281.7	274.9	270.9	265.5
77.5°	225.1	223.7	219.7	217.0	212.9
80°	169.8	169.8	167.1	165.8	163.1
82.5°	121.3	118.6	118.6	115.9	115.9
85°	74.1	75.5	75.5	74.1	71.4
87.5°	36.4	36.4	35.0	35.0	32.3
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.1	40.9	12.1	15.9	15.9
97.5°	81.0	85.5	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.6	177.1	178.6	115.0
105°	222.5	225.6	225.6	225.6	224.8
107.5°	274.0	274.0	275.5	276.3	273.2
110°	324.0	324.0	325.5	323.2	324.0

TEST NUMBER: P1034387

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.9	373.2	373.9	370.9	369.4
115°	417.8	421.6	422.4	419.3	414.8
117.5°	467.0	467.0	470.0	465.5	464.0
120°	512.4	511.7	513.9	512.4	508.6
122.5°	552.5	556.3	557.1	555.6	551.0
125°	594.2	599.5	599.5	596.4	594.2
127.5°	634.3	638.1	637.3	635.8	629.7
130°	670.6	674.4	675.2	672.9	669.1
132.5°	706.9	711.5	709.2	709.2	705.4
135°	741.0	745.5	744.0	742.5	738.0
137.5°	772.8	777.3	775.8	775.8	772.0
140°	803.8	805.3	804.6	806.1	801.6
142.5°	831.8	832.6	834.1	834.1	829.6
145°	859.1	860.6	860.6	861.4	856.8
147.5°	883.3	883.3	884.1	884.8	879.5
150°	906.0	904.5	906.0	907.5	901.5
152.5°	928.0	924.2	925.7	927.2	921.9
155°	946.1	941.6	943.1	945.4	939.3
157.5°	960.5	958.2	958.2	960.5	954.5
160°	975.6	971.1	971.9	974.9	968.8
162.5°	987.8	983.2	984.0	988.5	981.7
165°	998.4	993.8	994.6	999.1	993.1
167.5°	1006.7	1002.1	1002.9	1008.2	1001.4
170°	1013.5	1008.2	1009.0	1015.0	1008.2
172.5°	1018.0	1012.7	1014.2	1019.5	1012.7
175°	1021.1	1016.5	1017.3	1023.3	1016.5
177.5°	1023.3	1018.8	1019.5	1024.8	1018.8
180°	1021.1	1021.1	1021.1	1021.1	1021.1

(END OF REPORT)