

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033924

Luminaire Tested: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033924
REPORT IS A COMBINATION OF REPORTS P1000042 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9005.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033924

CATALOG NUMBER: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033924

CATALOG NUMBER: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	63	62	60	53	52	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	60	54	48	52	47	43	45	40	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16898	16898	16898
5°	16899	16395	16397
10°	16756	15878	15689
15°	16525	15234	14854
20°	16223	14500	13902
25°	15847	13707	12972
30°	15479	12899	11927
35°	15073	12079	10906
40°	14590	11197	9857
45°	14138	10322	8818
50°	13624	9367	7764
55°	13068	8387	6675
60°	12451	7347	5600
65°	11856	6154	4565
70°	11010	4899	3488
75°	9922	3563	2440
80°	8287	2188	1753
85°	6236	1261	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14138 cd/sqm

TEST NUMBER: P1033924

CATALOG NUMBER: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	2.2
10°-20°	543.3	6.0
20°-30°	784.4	8.7
30°-40°	889.0	9.9
40°-50°	858.3	9.5
50°-60°	713.6	7.9
60°-70°	492.5	5.5
70°-80°	248.9	2.8
80°-90°	66.0	0.7
90°-100°	45.2	0.5
100°-110°	297.7	3.3
110°-120°	568.5	6.3
120°-130°	721.7	8.0
130°-140°	772.1	8.6
140°-150°	721.9	8.0
150°-160°	582.2	6.5
160°-170°	375.5	4.2
170°-180°	129.4	1.4
0°-30°	1522.5	16.9
0°-40°	2411.5	26.8
0°-60°	3983.4	44.2
0°-90°	4790.8	53.2
90°-120°	911.4	10.1
90°-150°	3127.1	34.7
90°-180°	4214.0	46.8
0°-180°	9005.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2072	2072	2072	2072	2072	
5°	2069	2063	2044	2060	2056	196
15°	1971	1956	1917	1914	1902	555
25°	1782	1753	1688	1661	1645	821
35°	1541	1490	1410	1357	1328	963
45°	1257	1198	1103	1025	996	969
55°	952	888	785	703	673	852
65°	647	579	478	409	390	639
75°	344	286	211	174	165	363
85°	86	54	49	46	46	94
90°	3	14	22	28	31	8
95°	56	21	22	28	30	69
105°	307	313	318	327	290	321
115°	572	576	574	576	576	563
125°	805	809	807	810	811	719
135°	998	997	1001	1003	1005	769
145°	1151	1154	1154	1155	1157	719
155°	1262	1263	1260	1264	1261	582
165°	1331	1326	1326	1334	1325	376
175°	1362	1356	1357	1366	1354	130
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P1033924

CATALOG NUMBER: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2072.2	2072.2	2072.2	2072.2	2072.2
2.5°	2078.5	2072.2	2054.7	2072.2	2070.6
5°	2069.0	2062.7	2043.6	2059.5	2056.3
7.5°	2054.7	2048.4	2024.6	2035.7	2030.9
10°	2032.5	2024.6	1996.0	2002.4	1996.0
12.5°	2004.0	1994.4	1959.5	1962.7	1953.2
15°	1970.6	1956.4	1916.7	1913.5	1902.4
17.5°	1932.6	1911.9	1865.9	1858.0	1842.1
20°	1886.5	1865.9	1812.0	1799.3	1778.7
22.5°	1835.8	1812.0	1753.3	1732.6	1716.8
25°	1781.8	1753.3	1688.2	1661.2	1645.4
27.5°	1726.3	1691.4	1623.2	1591.4	1569.2
30°	1667.6	1627.9	1553.3	1513.7	1488.3
32.5°	1605.7	1559.7	1481.9	1434.3	1410.5
35°	1540.7	1489.9	1410.5	1356.6	1328.0
37.5°	1472.4	1420.1	1332.8	1274.1	1245.5
40°	1399.4	1347.1	1256.6	1190.0	1161.4
42.5°	1329.6	1274.1	1178.9	1110.7	1080.5
45°	1256.6	1197.9	1102.7	1025.0	996.4
47.5°	1182.1	1121.8	1023.4	942.5	910.7
50°	1105.9	1044.0	942.5	863.1	833.0
52.5°	1028.2	967.9	863.1	782.2	750.5
55°	952.0	888.5	785.4	702.9	672.7
57.5°	877.4	810.8	709.2	625.1	602.9
60°	796.5	733.0	631.5	549.0	523.6
62.5°	723.5	656.9	552.2	477.6	458.5
65°	647.4	579.1	477.6	409.4	390.3
67.5°	568.0	503.0	407.8	347.5	325.3
70°	493.5	426.8	336.4	284.0	268.1
72.5°	414.1	355.4	271.3	228.5	214.2
75°	344.3	285.6	211.0	174.5	165.0
77.5°	271.3	220.5	157.1	131.7	128.5
80°	201.5	155.5	107.9	103.1	101.5
82.5°	141.2	100.0	77.7	74.6	73.0
85°	85.7	53.9	49.2	46.0	46.0
87.5°	36.5	23.8	22.2	20.6	22.2
90°	3.1	14.3	22.4	28.5	30.6
92.5°	15.3	13.2	21.4	27.5	27.5
95°	56.0	21.4	22.4	28.5	29.5
97.5°	107.0	129.4	22.4	27.5	28.5
100°	167.1	185.4	44.8	27.5	28.5
102.5°	234.3	246.5	258.7	29.5	29.5
105°	306.6	312.7	317.8	327.0	290.3
107.5°	372.8	375.9	383.0	388.1	392.2
110°	440.0	443.1	449.2	451.2	454.3

TEST NUMBER: P1033924

CATALOG NUMBER: S124RDIW-B1195D1050UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	505.2	511.3	513.4	512.4	516.4
115°	572.5	575.5	574.5	576.5	576.5
117.5°	632.6	636.6	639.7	638.7	638.7
120°	693.7	697.8	696.7	698.8	696.7
122.5°	750.7	752.8	754.8	755.8	753.8
125°	804.7	808.8	806.7	809.8	810.8
127.5°	856.7	857.7	862.8	861.8	860.7
130°	906.6	907.6	910.6	911.7	911.7
132.5°	952.4	954.4	958.5	959.5	958.5
135°	998.2	997.2	1001.3	1003.3	1005.4
137.5°	1039.0	1039.0	1044.1	1046.1	1045.1
140°	1078.7	1080.8	1082.8	1085.9	1086.9
142.5°	1114.4	1118.4	1119.5	1121.5	1121.5
145°	1151.0	1154.1	1154.1	1155.1	1157.2
147.5°	1179.6	1185.7	1184.7	1185.7	1186.7
150°	1211.1	1215.2	1214.2	1214.2	1215.2
152.5°	1237.6	1240.7	1238.6	1240.7	1239.7
155°	1262.1	1263.1	1260.0	1264.1	1261.1
157.5°	1283.5	1283.5	1279.4	1284.5	1279.4
160°	1301.8	1298.7	1297.7	1303.8	1297.7
162.5°	1318.1	1314.0	1313.0	1319.1	1312.0
165°	1331.3	1326.2	1326.2	1334.4	1325.2
167.5°	1342.5	1337.4	1336.4	1345.6	1335.4
170°	1351.7	1345.6	1346.6	1354.8	1344.6
172.5°	1357.8	1351.7	1352.7	1360.9	1349.7
175°	1361.9	1355.8	1356.8	1366.0	1353.7
177.5°	1365.0	1357.8	1359.9	1368.0	1355.8
180°	1361.9	1361.9	1361.9	1361.9	1361.9

(END OF REPORT)