

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034399

Luminaire Tested: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034399
REPORT IS A COMBINATION OF REPORTS P1003072 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8489.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034399

CATALOG NUMBER: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034399

CATALOG NUMBER: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	29	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12168	11886	11908
10°	12068	11613	11577
15°	11910	11287	11186
20°	11695	10909	10738
25°	11465	10497	10258
30°	11187	10068	9753
35°	10891	9618	9186
40°	10585	9142	8683
45°	10254	8678	8148
50°	9889	8152	7525
55°	9529	7571	6951
60°	9098	6960	6284
65°	8583	6253	5594
70°	8060	5438	4798
75°	7178	4478	3880
80°	6117	3345	2854
85°	4723	1977	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10254 cd/sqm

TEST NUMBER: P1034399

CATALOG NUMBER: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	2.1
10°-20°	506.2	6.0
20°-30°	747.3	8.8
30°-40°	871.9	10.3
40°-50°	875.7	10.3
50°-60°	768.7	9.1
60°-70°	572.6	6.7
70°-80°	327.0	3.9
80°-90°	96.4	1.1
90°-100°	84.4	1.0
100°-110°	250.9	3.0
110°-120°	425.4	5.0
120°-130°	560.1	6.6
130°-140°	627.6	7.4
140°-150°	615.2	7.2
150°-160°	516.7	6.1
160°-170°	343.5	4.0
170°-180°	120.2	1.4
0°-30°	1432.7	16.9
0°-40°	2304.6	27.1
0°-60°	3949.0	46.5
0°-90°	4945.0	58.3
90°-120°	760.7	9.0
90°-150°	2563.6	30.2
90°-180°	3544.0	41.7
0°-180°	8489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	90
90°	1	9	16	21	24	10
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	628	626	626	557
135°	808	814	815	815	811	623
145°	979	983	986	986	983	612
155°	1121	1121	1122	1126	1121	516
165°	1218	1216	1218	1221	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1034399

CATALOG NUMBER: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.6	34.6	43.5	50.4	52.4
95°	64.2	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.6	119.6	120.6
100°	138.3	138.3	151.2	160.1	162.1
102.5°	180.8	185.8	190.7	200.6	203.6
105°	225.3	230.3	236.2	242.1	245.1
107.5°	273.7	278.7	283.6	286.6	286.6
110°	324.1	329.1	332.0	335.0	334.0



TEST NUMBER: P1034399

CATALOG NUMBER: S125DIW-B1270D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.5	377.5	381.4	382.4	380.5
115°	425.9	429.9	431.8	430.9	429.9
117.5°	477.3	478.3	480.3	481.3	477.3
120°	524.7	529.7	530.7	530.7	526.7
122.5°	576.1	577.1	580.1	579.1	576.1
125°	621.6	627.5	628.5	626.5	625.5
127.5°	672.0	674.9	675.9	674.9	673.0
130°	716.4	721.4	723.4	722.4	720.4
132.5°	760.9	769.8	768.8	767.8	764.9
135°	808.4	814.3	815.3	815.3	811.3
137.5°	852.8	858.7	860.7	861.7	856.8
140°	895.3	900.3	903.2	905.2	900.3
142.5°	937.8	941.8	945.7	946.7	941.8
145°	979.3	983.3	986.2	986.2	983.3
147.5°	1017.8	1020.8	1022.8	1025.8	1017.8
150°	1056.4	1055.4	1059.4	1059.4	1057.4
152.5°	1088.0	1090.0	1091.0	1093.9	1090.0
155°	1120.6	1120.6	1121.6	1125.6	1120.6
157.5°	1150.3	1148.3	1149.3	1153.2	1146.3
160°	1176.0	1173.0	1174.0	1177.9	1173.0
162.5°	1198.7	1196.7	1196.7	1201.7	1195.7
165°	1218.5	1216.5	1217.5	1221.4	1215.5
167.5°	1236.2	1232.3	1232.3	1238.2	1232.3
170°	1250.1	1246.1	1246.1	1252.1	1245.1
172.5°	1260.0	1256.0	1256.0	1261.9	1256.0
175°	1266.9	1262.9	1262.9	1268.9	1261.9
177.5°	1271.8	1267.9	1266.9	1272.8	1265.9
180°	1269.8	1269.8	1269.8	1269.8	1269.8

(END OF REPORT)