

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034418

Luminaire Tested: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034418
REPORT IS A COMBINATION OF REPORTS P1003144 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10107.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034418

CATALOG NUMBER: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034418

CATALOG NUMBER: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12168	11886	11908
10°	12068	11613	11577
15°	11910	11287	11186
20°	11695	10909	10738
25°	11465	10497	10258
30°	11187	10068	9753
35°	10891	9618	9186
40°	10585	9142	8683
45°	10254	8678	8148
50°	9889	8152	7525
55°	9529	7571	6951
60°	9098	6960	6284
65°	8583	6253	5594
70°	8060	5438	4798
75°	7178	4478	3880
80°	6117	3345	2854
85°	4723	1977	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10254 cd/sqm

TEST NUMBER: P1034418

CATALOG NUMBER: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	1.8
10°-20°	506.2	5.0
20°-30°	747.3	7.4
30°-40°	871.9	8.6
40°-50°	875.7	8.7
50°-60°	768.7	7.6
60°-70°	572.6	5.7
70°-80°	327.0	3.2
80°-90°	96.9	1.0
90°-100°	57.0	0.6
100°-110°	379.2	3.8
110°-120°	682.9	6.8
120°-130°	876.6	8.7
130°-140°	942.8	9.3
140°-150°	884.8	8.8
150°-160°	715.7	7.1
160°-170°	462.9	4.6
170°-180°	159.6	1.6
0°-30°	1432.7	14.2
0°-40°	2304.6	22.8
0°-60°	3949.0	39.1
0°-90°	4945.5	48.9
90°-120°	1119.2	11.1
90°-150°	3823.3	37.8
90°-180°	5162.0	51.1
0°-180°	10107.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	90
90°	1	11	20	26	30	9
95°	71	67	20	26	26	87
105°	366	371	371	371	370	388
115°	688	694	695	690	683	682
125°	978	986	986	982	978	873
135°	1219	1227	1224	1222	1214	940
145°	1414	1416	1416	1418	1410	884
155°	1557	1550	1552	1556	1546	717
165°	1643	1636	1637	1644	1634	464
175°	1680	1673	1674	1684	1673	160
180°	1680	1680	1680	1680	1680	

TEST NUMBER: P1034418

CATALOG NUMBER: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	1.2	11.2	19.9	26.2	29.9
92.5°	23.7	12.5	19.9	26.2	27.4
95°	71.0	67.3	19.9	26.2	26.2
97.5°	133.3	140.8	22.4	24.9	26.2
100°	208.0	211.7	216.7	31.1	26.2
102.5°	284.0	289.0	291.5	294.0	189.3
105°	366.2	371.2	371.2	371.2	369.9
107.5°	450.9	450.9	453.4	454.6	449.7
110°	533.1	533.1	535.6	531.9	533.1

TEST NUMBER: P1034418

CATALOG NUMBER: S125DIW-B1270D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	610.3	614.1	615.3	610.3	607.8
115°	687.6	693.8	695.0	690.1	682.6
117.5°	768.5	768.5	773.5	766.0	763.5
120°	843.3	842.0	845.8	843.3	837.0
122.5°	909.3	915.5	916.8	914.3	906.8
125°	977.8	986.5	986.5	981.5	977.8
127.5°	1043.8	1050.0	1048.8	1046.3	1036.3
130°	1103.6	1109.8	1111.1	1107.3	1101.1
132.5°	1163.4	1170.8	1167.1	1167.1	1160.9
135°	1219.4	1226.9	1224.4	1221.9	1214.4
137.5°	1271.7	1279.2	1276.7	1276.7	1270.5
140°	1322.8	1325.3	1324.1	1326.5	1319.1
142.5°	1368.9	1370.1	1372.6	1372.6	1365.2
145°	1413.7	1416.2	1416.2	1417.5	1410.0
147.5°	1453.6	1453.6	1454.8	1456.1	1447.4
150°	1491.0	1488.5	1491.0	1493.5	1483.5
152.5°	1527.1	1520.9	1523.4	1525.8	1517.1
155°	1557.0	1549.5	1552.0	1555.7	1545.8
157.5°	1580.6	1576.9	1576.9	1580.6	1570.7
160°	1605.6	1598.1	1599.3	1604.3	1594.3
162.5°	1625.5	1618.0	1619.3	1626.7	1615.5
165°	1642.9	1635.5	1636.7	1644.2	1634.2
167.5°	1656.6	1649.2	1650.4	1659.1	1647.9
170°	1667.8	1659.1	1660.4	1670.3	1659.1
172.5°	1675.3	1666.6	1669.1	1677.8	1666.6
175°	1680.3	1672.8	1674.1	1684.0	1672.8
177.5°	1684.0	1676.6	1677.8	1686.5	1676.6
180°	1680.3	1680.3	1680.3	1680.3	1680.3

(END OF REPORT)