

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033952

Luminaire Tested: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033952
REPORT IS A COMBINATION OF REPORTS P1000112 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10245.1 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033952

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033952

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46
2	89	82	76	71	82	75	70	66	64	60	56	53	50	48	42	41	39
3	81	72	65	59	74	67	60	55	56	52	48	47	43	40	38	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	41	45	40	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	22
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17116	17116	17116
5°	17118	16608	16610
10°	16973	16084	15893
15°	16740	15431	15046
20°	16434	14687	14082
25°	16052	13885	13139
30°	15679	13066	12082
35°	15268	12236	11047
40°	14780	11342	9985
45°	14321	10456	8933
50°	13800	9489	7864
55°	13237	8496	6762
60°	12612	7443	5673
65°	12008	6234	4624
70°	11150	4961	3534
75°	10052	3611	2471
80°	8394	2217	1777
85°	6316	1276	977

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14321 cd/sqm

TEST NUMBER: P1033952

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.4	1.9
10°-20°	550.3	5.4
20°-30°	794.5	7.8
30°-40°	900.5	8.8
40°-50°	869.4	8.5
50°-60°	722.8	7.1
60°-70°	498.9	4.9
70°-80°	252.1	2.5
80°-90°	67.6	0.7
90°-100°	57.8	0.6
100°-110°	380.9	3.7
110°-120°	727.3	7.1
120°-130°	923.3	9.0
130°-140°	987.7	9.6
140°-150°	923.6	9.0
150°-160°	744.8	7.3
160°-170°	480.4	4.7
170°-180°	165.5	1.6
0°-30°	1542.2	15.1
0°-40°	2442.7	23.8
0°-60°	4035.0	39.4
0°-90°	4853.6	47.4
90°-120°	1166.1	11.4
90°-150°	4000.7	39.1
90°-180°	5391.0	52.6
0°-180°	10245.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2099	2099	2099	2099	2099	
5°	2096	2089	2070	2086	2083	199
15°	1996	1982	1942	1938	1927	563
25°	1805	1776	1710	1683	1667	832
35°	1561	1509	1429	1374	1345	975
45°	1273	1213	1117	1038	1009	982
55°	964	900	796	712	682	863
65°	656	587	484	415	395	648
75°	349	289	214	177	167	368
85°	87	55	50	47	47	95
90°	4	18	29	36	39	9
95°	72	27	29	36	38	88
105°	392	400	407	418	371	411
115°	732	736	735	738	738	721
125°	1030	1035	1032	1036	1037	919
135°	1277	1276	1281	1284	1286	984
145°	1473	1476	1476	1478	1480	920
155°	1615	1616	1612	1617	1613	744
165°	1703	1697	1697	1707	1695	481
175°	1742	1734	1736	1748	1732	166
180°	1742	1742	1742	1742	1742	

TEST NUMBER: P1033952

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2099.0	2099.0	2099.0	2099.0	2099.0
2.5°	2105.4	2099.0	2081.3	2099.0	2097.4
5°	2095.8	2089.4	2070.1	2086.2	2082.9
7.5°	2081.3	2074.9	2050.8	2062.1	2057.2
10°	2058.8	2050.8	2021.9	2028.3	2021.9
12.5°	2029.9	2020.3	1984.9	1988.1	1978.5
15°	1996.2	1981.7	1941.5	1938.3	1927.0
17.5°	1957.6	1936.7	1890.1	1882.0	1866.0
20°	1911.0	1890.1	1835.4	1822.6	1801.7
22.5°	1859.5	1835.4	1776.0	1755.1	1739.0
25°	1804.9	1776.0	1710.1	1682.7	1666.7
27.5°	1748.6	1713.3	1644.2	1612.0	1589.5
30°	1689.2	1649.0	1573.5	1533.3	1507.6
32.5°	1626.5	1579.9	1501.1	1452.9	1428.8
35°	1560.6	1509.2	1428.8	1374.2	1345.2
37.5°	1491.5	1438.5	1350.1	1290.6	1261.7
40°	1417.6	1364.5	1272.9	1205.4	1176.5
42.5°	1346.8	1290.6	1194.2	1125.0	1094.5
45°	1272.9	1213.4	1117.0	1038.3	1009.3
47.5°	1197.4	1136.3	1036.7	954.7	922.5
50°	1120.2	1057.5	954.7	874.3	843.8
52.5°	1041.5	980.4	874.3	792.4	760.2
55°	964.3	900.0	795.6	712.0	681.5
57.5°	888.8	821.3	718.4	633.2	610.7
60°	806.8	742.5	639.7	556.1	530.4
62.5°	732.9	665.4	559.3	483.8	464.5
65°	655.7	586.6	483.8	414.7	395.4
67.5°	575.4	509.5	413.1	352.0	329.5
70°	499.8	432.3	340.7	287.7	271.6
72.5°	419.5	360.0	274.8	231.4	217.0
75°	348.8	289.3	213.8	176.8	167.1
77.5°	274.8	223.4	159.1	133.4	130.2
80°	204.1	157.5	109.3	104.5	102.9
82.5°	143.0	101.3	78.8	75.5	73.9
85°	86.8	54.6	49.8	46.6	46.6
87.5°	37.0	24.1	22.5	20.9	22.5
90°	3.9	18.2	28.7	36.5	39.1
92.5°	19.5	16.9	27.4	35.2	35.2
95°	71.7	27.4	28.7	36.5	37.8
97.5°	136.8	165.5	28.7	35.2	36.5
100°	213.7	237.2	57.3	35.2	36.5
102.5°	299.7	315.4	331.0	37.8	37.8
105°	392.3	400.1	406.6	418.3	371.4
107.5°	477.0	480.9	490.0	496.5	501.7
110°	563.0	566.9	574.7	577.3	581.2

TEST NUMBER: P1033952

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	646.4	654.2	656.8	655.5	660.7
115°	732.4	736.3	735.0	737.6	737.6
117.5°	809.3	814.5	818.4	817.1	817.1
120°	887.5	892.7	891.4	894.0	891.4
122.5°	960.4	963.0	965.6	967.0	964.3
125°	1029.5	1034.7	1032.1	1036.0	1037.3
127.5°	1096.0	1097.3	1103.8	1102.5	1101.2
130°	1159.8	1161.1	1165.0	1166.3	1166.3
132.5°	1218.5	1221.1	1226.3	1227.6	1226.3
135°	1277.1	1275.8	1281.0	1283.6	1286.2
137.5°	1329.2	1329.2	1335.7	1338.4	1337.1
140°	1380.1	1382.7	1385.3	1389.2	1390.5
142.5°	1425.7	1430.9	1432.2	1434.8	1434.8
145°	1472.6	1476.5	1476.5	1477.8	1480.4
147.5°	1509.1	1516.9	1515.6	1516.9	1518.2
150°	1549.5	1554.7	1553.4	1553.4	1554.7
152.5°	1583.3	1587.3	1584.7	1587.3	1586.0
155°	1614.6	1615.9	1612.0	1617.2	1613.3
157.5°	1642.0	1642.0	1636.8	1643.3	1636.8
160°	1665.4	1661.5	1660.2	1668.1	1660.2
162.5°	1686.3	1681.1	1679.8	1687.6	1678.5
165°	1703.2	1696.7	1696.7	1707.2	1695.4
167.5°	1717.6	1711.1	1709.8	1721.5	1708.5
170°	1729.3	1721.5	1722.8	1733.2	1720.2
172.5°	1737.1	1729.3	1730.6	1741.0	1726.7
175°	1742.3	1734.5	1735.8	1747.5	1731.9
177.5°	1746.2	1737.1	1739.7	1750.2	1734.5
180°	1742.3	1742.3	1742.3	1742.3	1742.3

(END OF REPORT)