

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033953

Luminaire Tested: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033953
REPORT IS A COMBINATION OF REPORTS P1000113 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9528.0 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033953

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033953

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	65	60	75	67	61	56	58	53	49	49	45	42	40	38	36
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	46	41	46	41	36	39	35	32	33	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17116	17116	17116
5°	17118	16608	16610
10°	16973	16084	15893
15°	16740	15431	15046
20°	16434	14687	14082
25°	16052	13885	13139
30°	15679	13066	12082
35°	15268	12236	11047
40°	14780	11342	9985
45°	14321	10456	8933
50°	13800	9489	7864
55°	13237	8496	6762
60°	12612	7443	5673
65°	12008	6234	4624
70°	11150	4961	3534
75°	10052	3611	2471
80°	8394	2217	1777
85°	6316	1276	977

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14321 cd/sqm

TEST NUMBER: P1033953

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.4	2.1
10°-20°	550.3	5.8
20°-30°	794.5	8.3
30°-40°	900.5	9.5
40°-50°	869.4	9.1
50°-60°	722.8	7.6
60°-70°	498.9	5.2
70°-80°	252.1	2.6
80°-90°	67.6	0.7
90°-100°	109.8	1.2
100°-110°	328.9	3.5
110°-120°	558.8	5.9
120°-130°	736.9	7.7
130°-140°	827.7	8.7
140°-150°	813.5	8.5
150°-160°	684.2	7.2
160°-170°	455.2	4.8
170°-180°	159.4	1.7
0°-30°	1542.2	16.2
0°-40°	2442.7	25.6
0°-60°	4035.0	42.3
0°-90°	4853.6	50.9
90°-120°	997.5	10.5
90°-150°	3375.5	35.4
90°-180°	4674.0	49.1
0°-180°	9528.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2099	2099	2099	2099	2099	
5°	2096	2089	2070	2086	2083	199
15°	1996	1982	1942	1938	1927	563
25°	1805	1776	1710	1683	1667	832
35°	1561	1509	1429	1374	1345	975
45°	1273	1213	1117	1038	1009	982
55°	964	900	796	712	682	863
65°	656	587	484	415	395	648
75°	349	289	214	177	167	368
85°	87	55	50	47	47	95
90°	4	18	29	36	39	11
95°	78	90	99	103	103	85
105°	304	305	310	314	318	322
115°	568	568	566	564	563	560
125°	827	827	826	824	821	738
135°	1067	1075	1075	1072	1068	826
145°	1296	1302	1303	1302	1298	811
155°	1485	1485	1484	1489	1484	684
165°	1617	1613	1610	1618	1613	456
175°	1682	1676	1674	1683	1674	160
180°	1685	1685	1685	1685	1685	

TEST NUMBER: P1033953

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2099.0	2099.0	2099.0	2099.0	2099.0
2.5°	2105.4	2099.0	2081.3	2099.0	2097.4
5°	2095.8	2089.4	2070.1	2086.2	2082.9
7.5°	2081.3	2074.9	2050.8	2062.1	2057.2
10°	2058.8	2050.8	2021.9	2028.3	2021.9
12.5°	2029.9	2020.3	1984.9	1988.1	1978.5
15°	1996.2	1981.7	1941.5	1938.3	1927.0
17.5°	1957.6	1936.7	1890.1	1882.0	1866.0
20°	1911.0	1890.1	1835.4	1822.6	1801.7
22.5°	1859.5	1835.4	1776.0	1755.1	1739.0
25°	1804.9	1776.0	1710.1	1682.7	1666.7
27.5°	1748.6	1713.3	1644.2	1612.0	1589.5
30°	1689.2	1649.0	1573.5	1533.3	1507.6
32.5°	1626.5	1579.9	1501.1	1452.9	1428.8
35°	1560.6	1509.2	1428.8	1374.2	1345.2
37.5°	1491.5	1438.5	1350.1	1290.6	1261.7
40°	1417.6	1364.5	1272.9	1205.4	1176.5
42.5°	1346.8	1290.6	1194.2	1125.0	1094.5
45°	1272.9	1213.4	1117.0	1038.3	1009.3
47.5°	1197.4	1136.3	1036.7	954.7	922.5
50°	1120.2	1057.5	954.7	874.3	843.8
52.5°	1041.5	980.4	874.3	792.4	760.2
55°	964.3	900.0	795.6	712.0	681.5
57.5°	888.8	821.3	718.4	633.2	610.7
60°	806.8	742.5	639.7	556.1	530.4
62.5°	732.9	665.4	559.3	483.8	464.5
65°	655.7	586.6	483.8	414.7	395.4
67.5°	575.4	509.5	413.1	352.0	329.5
70°	499.8	432.3	340.7	287.7	271.6
72.5°	419.5	360.0	274.8	231.4	217.0
75°	348.8	289.3	213.8	176.8	167.1
77.5°	274.8	223.4	159.1	133.4	130.2
80°	204.1	157.5	109.3	104.5	102.9
82.5°	143.0	101.3	78.8	75.5	73.9
85°	86.8	54.6	49.8	46.6	46.6
87.5°	37.0	24.1	22.5	20.9	22.5
90°	3.9	18.2	28.7	36.5	39.1
92.5°	33.9	50.8	57.3	61.2	62.5
95°	78.2	89.9	99.0	102.9	102.9
97.5°	125.1	135.5	145.9	151.1	151.1
100°	182.4	187.6	199.3	202.0	202.0
102.5°	242.3	243.6	254.1	258.0	259.3
105°	303.6	304.9	310.1	314.0	317.9
107.5°	367.4	368.7	370.0	375.2	373.9
110°	432.6	435.2	433.9	431.3	435.2



TEST NUMBER: P1033953

CATALOG NUMBER: S124RDIW-B1195D1340UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	500.3	500.3	497.7	497.7	497.7
115°	568.1	568.1	565.5	564.2	562.9
117.5°	631.9	631.9	630.6	626.7	622.8
120°	695.8	701.0	697.1	690.6	693.2
122.5°	762.2	763.5	762.2	758.3	751.8
125°	827.4	827.4	826.1	823.5	820.8
127.5°	886.0	889.9	887.3	884.7	883.4
130°	948.5	952.4	952.4	949.8	944.6
132.5°	1012.4	1015.0	1013.7	1011.1	1009.8
135°	1067.1	1074.9	1074.9	1072.3	1068.4
137.5°	1128.3	1132.2	1134.9	1130.9	1132.2
140°	1189.6	1192.2	1192.2	1190.9	1189.6
142.5°	1245.6	1248.2	1246.9	1246.9	1246.9
145°	1296.4	1301.6	1302.9	1301.6	1297.7
147.5°	1348.5	1355.0	1353.7	1352.4	1351.1
150°	1395.4	1400.7	1400.7	1400.7	1399.3
152.5°	1439.7	1442.3	1443.6	1447.6	1443.6
155°	1485.3	1485.3	1484.0	1489.3	1484.0
157.5°	1524.4	1521.8	1521.8	1525.7	1521.8
160°	1558.3	1557.0	1555.7	1559.6	1553.1
162.5°	1589.6	1585.7	1584.4	1592.2	1585.7
165°	1616.9	1613.0	1610.4	1618.2	1613.0
167.5°	1639.1	1633.9	1633.9	1641.7	1633.9
170°	1657.3	1650.8	1652.1	1659.9	1650.8
172.5°	1670.4	1665.1	1665.1	1674.3	1665.1
175°	1682.1	1675.6	1674.3	1683.4	1674.3
177.5°	1687.3	1680.8	1680.8	1689.9	1679.5
180°	1684.7	1684.7	1684.7	1684.7	1684.7

(END OF REPORT)