

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034424

Luminaire Tested: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034424
REPORT IS A COMBINATION OF REPORTS P1003197 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10027.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034424

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034424

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	88	84	80	77	69	67	64	56	54	53	44	43	42
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35
3	79	70	62	56	72	64	57	52	53	48	44	43	40	37	34	31	29
4	72	61	53	47	66	56	49	44	47	42	37	38	34	31	30	27	25
5	66	55	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	49	41	35	56	45	38	32	38	32	28	31	27	23	24	21	19
7	56	44	36	30	51	41	33	28	34	28	24	28	24	21	22	19	17
8	52	40	32	27	48	37	30	25	31	26	22	26	21	18	20	17	15
9	49	36	29	24	44	34	27	22	28	23	19	23	19	16	19	16	14
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9818	9818	9818
5°	9834	9612	9636
10°	9760	9416	9389
15°	9642	9188	9086
20°	9481	8913	8786
25°	9291	8619	8421
30°	9061	8300	8091
35°	8846	8005	7785
40°	8627	7695	7478
45°	8380	7426	7201
50°	8143	7133	6952
55°	7858	6855	6662
60°	7546	6537	6365
65°	7220	6203	6031
70°	6847	5755	5683
75°	6258	5313	5258
80°	5487	4774	4788
85°	4723	4345	4541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8380 cd/sqm

TEST NUMBER: P1034424

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	1.4
10°-20°	411.6	4.1
20°-30°	612.1	6.1
30°-40°	724.9	7.2
40°-50°	749.5	7.5
50°-60°	690.4	6.9
60°-70°	558.1	5.6
70°-80°	373.4	3.7
80°-90°	196.0	2.0
90°-100°	234.4	2.3
100°-110°	453.7	4.5
110°-120°	687.1	6.9
120°-130°	864.3	8.6
130°-140°	947.8	9.5
140°-150°	918.6	9.2
150°-160°	769.4	7.7
160°-170°	511.5	5.1
170°-180°	179.0	1.8
0°-30°	1168.8	11.7
0°-40°	1893.7	18.9
0°-60°	3333.6	33.2
0°-90°	4461.1	44.5
90°-120°	1375.2	13.7
90°-150°	4106.0	40.9
90°-180°	5566.0	55.5
0°-180°	10027.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1532	1532	1532	1532	1532	
5°	1532	1529	1519	1531	1529	145
15°	1463	1465	1454	1463	1457	412
25°	1330	1334	1325	1331	1324	612
35°	1151	1161	1157	1161	1161	720
45°	948	964	972	982	984	731
55°	729	753	777	793	799	651
65°	502	536	572	595	601	498
75°	276	316	364	394	401	293
85°	83	132	185	218	230	86
90°	26	85	147	189	204	23
95°	115	157	223	266	280	115
105°	349	380	434	473	488	372
115°	643	660	702	727	735	636
125°	932	939	970	992	998	834
135°	1207	1214	1226	1245	1247	930
145°	1460	1464	1468	1476	1478	912
155°	1669	1669	1670	1676	1669	769
165°	1814	1811	1813	1819	1810	512
175°	1886	1880	1880	1889	1879	179
180°	1891	1891	1891	1891	1891	

TEST NUMBER: P1034424

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1532.4	1532.4	1532.4	1532.4	1532.4
2.5°	1536.9	1533.9	1523.4	1533.9	1532.4
5°	1532.4	1529.4	1518.8	1530.9	1529.4
7.5°	1521.8	1520.3	1509.8	1520.3	1518.8
10°	1506.8	1506.8	1494.8	1505.3	1503.8
12.5°	1485.8	1487.3	1478.3	1485.8	1481.3
15°	1463.3	1464.8	1454.2	1463.3	1457.2
17.5°	1434.7	1437.7	1427.2	1434.7	1430.2
20°	1403.2	1406.2	1395.7	1400.2	1400.2
22.5°	1367.1	1373.1	1361.1	1367.1	1362.6
25°	1329.6	1334.1	1325.0	1331.1	1323.5
27.5°	1289.0	1295.0	1284.5	1289.0	1286.0
30°	1242.4	1251.4	1242.4	1245.4	1243.9
32.5°	1200.4	1207.9	1201.9	1204.9	1203.4
35°	1150.8	1161.3	1156.8	1161.3	1161.3
37.5°	1102.7	1111.7	1110.2	1116.2	1114.7
40°	1053.1	1065.1	1063.6	1069.7	1072.7
42.5°	999.0	1015.6	1020.1	1027.6	1027.6
45°	948.0	964.5	972.0	982.5	984.0
47.5°	895.4	910.4	922.4	937.4	940.5
50°	841.3	857.8	874.3	890.9	895.4
52.5°	784.2	805.2	826.3	844.3	847.3
55°	728.6	752.7	776.7	793.2	799.2
57.5°	671.5	700.1	727.1	745.2	749.7
60°	614.4	644.5	674.5	697.1	701.6
62.5°	558.9	588.9	622.0	647.5	653.5
65°	501.8	536.3	572.4	594.9	600.9
67.5°	449.2	482.2	518.3	545.3	552.9
70°	390.6	425.2	464.2	492.8	501.8
72.5°	333.5	369.6	413.1	444.7	450.7
75°	276.4	315.5	363.6	393.6	401.1
77.5°	220.8	265.9	311.0	344.0	350.0
80°	169.8	214.8	265.9	299.0	305.0
82.5°	123.2	171.3	223.8	255.4	267.4
85°	82.6	132.2	184.8	217.8	229.9
87.5°	52.6	100.7	151.7	186.3	196.8
90°	25.5	85.3	146.7	188.6	203.6
92.5°	65.1	116.1	181.9	225.2	238.7
95°	115.1	157.2	223.0	266.3	279.7
97.5°	165.1	202.7	272.9	313.2	325.2
100°	222.5	254.1	321.2	366.1	378.0
102.5°	284.3	320.2	374.1	418.9	432.3
105°	349.0	380.4	434.3	473.2	488.1
107.5°	419.6	448.0	498.9	533.4	542.4
110°	493.1	518.5	565.0	598.0	607.0

TEST NUMBER: P1034424

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	569.6	586.1	632.6	661.0	668.7
115°	643.2	659.6	701.6	727.1	734.7
117.5°	718.2	727.2	767.7	794.7	799.3
120°	788.8	800.7	836.8	862.3	865.4
122.5°	863.8	866.8	904.3	926.9	931.4
125°	931.5	938.9	970.4	991.5	997.5
127.5°	1005.1	1008.0	1035.0	1056.1	1062.1
130°	1071.3	1077.1	1101.1	1120.7	1125.3
132.5°	1136.0	1149.2	1162.8	1182.4	1184.0
135°	1206.6	1214.0	1225.9	1245.4	1247.1
137.5°	1272.8	1280.2	1289.1	1308.6	1307.2
140°	1334.6	1342.0	1347.9	1367.3	1366.0
142.5°	1397.9	1402.3	1408.2	1423.1	1421.8
145°	1459.7	1464.1	1468.5	1476.0	1477.6
147.5°	1515.6	1520.0	1522.9	1530.4	1521.6
150°	1573.0	1571.5	1577.4	1577.4	1575.9
152.5°	1620.1	1623.0	1624.5	1628.9	1623.0
155°	1668.6	1668.6	1670.1	1676.0	1668.6
157.5°	1712.8	1709.8	1711.3	1717.2	1706.9
160°	1751.0	1746.6	1748.1	1754.0	1746.6
162.5°	1784.9	1781.9	1781.9	1789.3	1780.4
165°	1814.3	1811.3	1812.8	1818.7	1809.9
167.5°	1840.8	1834.9	1834.9	1843.7	1834.9
170°	1861.4	1855.5	1855.5	1864.3	1854.0
172.5°	1876.1	1870.2	1870.2	1879.0	1870.2
175°	1886.4	1880.5	1880.5	1889.3	1879.0
177.5°	1893.7	1887.9	1886.4	1895.2	1884.9
180°	1890.8	1890.8	1890.8	1890.8	1890.8

(END OF REPORT)