

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034425

Luminaire Tested: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034425
REPORT IS A COMBINATION OF REPORTS P1003199 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11172.9 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034425

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034425

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	95	91	87	83	87	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	73	67	78	72	67	62	59	55	52	47	44	42	36	34	33
3	79	69	62	56	71	63	57	51	52	47	43	41	38	35	32	29	27
4	72	61	53	47	65	56	49	43	46	41	37	37	33	30	28	26	24
5	66	54	46	40	60	50	42	37	41	36	31	33	29	26	25	23	20
6	61	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	40	32	26	47	36	29	25	30	25	21	25	21	18	19	16	14
9	48	36	29	23	44	33	26	22	28	22	19	23	19	16	18	15	13
10	45	33	26	21	41	30	24	20	25	20	17	21	17	14	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10124	10124	10124
5°	10140	9912	9936
10°	10065	9710	9682
15°	9942	9475	9370
20°	9776	9191	9059
25°	9581	8889	8684
30°	9344	8559	8343
35°	9122	8255	8028
40°	8897	7935	7711
45°	8641	7657	7426
50°	8397	7356	7169
55°	8103	7068	6870
60°	7782	6741	6564
65°	7445	6396	6219
70°	7061	5934	5859
75°	6453	5478	5421
80°	5658	4923	4937
85°	4871	4479	4682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8641 cd/sqm

TEST NUMBER: P1034425

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	1.3
10°-20°	424.5	3.8
20°-30°	631.2	5.6
30°-40°	747.5	6.7
40°-50°	772.8	6.9
50°-60°	711.9	6.4
60°-70°	575.5	5.2
70°-80°	385.1	3.4
80°-90°	202.1	1.8
90°-100°	181.4	1.6
100°-110°	543.7	4.9
110°-120°	885.5	7.9
120°-130°	1097.0	9.8
130°-140°	1159.8	10.4
140°-150°	1078.4	9.7
150°-160°	870.1	7.8
160°-170°	562.7	5.0
170°-180°	194.1	1.7
0°-30°	1205.2	10.8
0°-40°	1952.7	17.5
0°-60°	3437.5	30.8
0°-90°	4600.2	41.2
90°-120°	1610.7	14.4
90°-150°	4945.8	44.3
90°-180°	6573.0	58.8
0°-180°	11172.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1577	1566	1579	1577	150
15°	1509	1510	1500	1509	1503	425
25°	1371	1376	1366	1373	1365	631
35°	1187	1198	1193	1198	1198	743
45°	978	995	1002	1013	1015	754
55°	751	776	801	818	824	672
65°	517	553	590	614	620	513
75°	285	325	375	406	414	302
85°	85	136	190	225	237	89
90°	26	88	151	194	210	22
95°	106	142	137	179	190	122
105°	459	490	536	568	577	486
115°	845	864	905	927	927	838
125°	1195	1204	1235	1254	1257	1067
135°	1486	1493	1501	1518	1517	1145
145°	1720	1722	1722	1731	1728	1076
155°	1893	1884	1887	1891	1879	872
165°	1997	1988	1990	1999	1987	564
175°	2043	2034	2035	2047	2034	195
180°	2043	2043	2043	2043	2043	

TEST NUMBER: P1034425

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.1	1580.1	1580.1	1580.1	1580.1
2.5°	1584.8	1581.7	1570.8	1581.7	1580.1
5°	1580.1	1577.0	1566.2	1578.6	1577.0
7.5°	1569.3	1567.7	1556.9	1567.7	1566.2
10°	1553.8	1553.8	1541.4	1552.3	1550.7
12.5°	1532.1	1533.7	1524.4	1532.1	1527.5
15°	1508.9	1510.4	1499.6	1508.9	1502.7
17.5°	1479.4	1482.5	1471.7	1479.4	1474.8
20°	1446.9	1450.0	1439.2	1443.8	1443.8
22.5°	1409.7	1415.9	1403.5	1409.7	1405.1
25°	1371.0	1375.7	1366.4	1372.6	1364.8
27.5°	1329.2	1335.4	1324.5	1329.2	1326.1
30°	1281.2	1290.4	1281.2	1284.3	1282.7
32.5°	1237.8	1245.5	1239.3	1242.4	1240.9
35°	1186.7	1197.5	1192.9	1197.5	1197.5
37.5°	1137.1	1146.4	1144.8	1151.0	1149.5
40°	1086.0	1098.4	1096.8	1103.0	1106.1
42.5°	1030.2	1047.2	1051.9	1059.6	1059.6
45°	977.5	994.6	1002.3	1013.1	1014.7
47.5°	923.3	938.8	951.2	966.7	969.8
50°	867.5	884.6	901.6	918.7	923.3
52.5°	808.7	830.3	852.0	870.6	873.7
55°	751.3	776.1	800.9	818.0	824.2
57.5°	692.5	721.9	749.8	768.4	773.0
60°	633.6	664.6	695.6	718.8	723.5
62.5°	576.3	607.3	641.4	667.7	673.9
65°	517.4	553.0	590.2	613.5	619.7
67.5°	463.2	497.3	534.5	562.3	570.1
70°	402.8	438.4	478.7	508.1	517.4
72.5°	343.9	381.1	426.0	458.6	464.7
75°	285.0	325.3	374.9	405.9	413.6
77.5°	227.7	274.2	320.7	354.8	361.0
80°	175.1	221.5	274.2	308.3	314.5
82.5°	127.0	176.6	230.8	263.4	275.8
85°	85.2	136.3	190.5	224.6	237.0
87.5°	54.2	103.8	156.5	192.1	202.9
90°	26.3	88.0	151.2	194.5	209.8
92.5°	50.5	81.7	145.0	186.7	199.1
95°	106.4	142.2	137.3	179.0	189.8
97.5°	180.6	226.9	134.2	169.7	182.1
100°	269.9	307.0	362.6	169.6	172.8
102.5°	360.8	396.2	447.2	481.3	363.4
105°	459.1	490.0	536.5	567.5	576.7
107.5°	560.6	582.3	630.2	662.7	666.0
110°	658.9	677.5	723.9	748.8	761.2

TEST NUMBER: P1034425

CATALOG NUMBER: S125DIW-B1270D1560UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	752.8	771.3	814.7	836.5	844.3
115°	845.2	863.6	905.4	927.2	927.4
117.5°	942.0	949.8	994.6	1011.9	1019.7
120°	1032.9	1036.1	1076.2	1099.6	1101.3
122.5°	1111.6	1120.7	1156.3	1178.1	1178.3
125°	1194.9	1203.9	1234.9	1253.7	1256.9
127.5°	1273.6	1279.6	1304.4	1324.7	1321.9
130°	1346.3	1352.3	1375.5	1392.7	1392.8
132.5°	1417.4	1426.5	1437.5	1459.2	1457.8
135°	1485.6	1493.1	1500.9	1518.0	1516.7
137.5°	1549.2	1556.7	1559.8	1578.4	1577.1
140°	1609.7	1612.7	1612.8	1632.8	1629.9
142.5°	1665.7	1665.7	1668.7	1682.6	1679.8
145°	1720.2	1721.7	1721.7	1731.0	1728.1
147.5°	1767.2	1767.2	1768.7	1773.3	1765.8
150°	1812.6	1809.6	1812.6	1815.6	1805.0
152.5°	1856.5	1848.9	1852.0	1855.0	1844.4
155°	1892.9	1883.8	1886.8	1891.3	1879.2
157.5°	1921.6	1917.1	1917.1	1921.6	1909.5
160°	1951.9	1942.8	1944.3	1950.4	1938.3
162.5°	1976.1	1967.1	1968.6	1977.7	1964.0
165°	1997.3	1988.3	1989.8	1998.9	1986.7
167.5°	2014.0	2004.9	2006.4	2017.0	2003.4
170°	2027.6	2017.0	2018.5	2030.7	2017.0
172.5°	2036.7	2026.1	2029.1	2039.7	2026.1
175°	2042.8	2033.7	2035.2	2047.3	2033.7
177.5°	2047.3	2038.2	2039.7	2050.3	2038.2
180°	2042.8	2042.8	2042.8	2042.8	2042.8

(END OF REPORT)