

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034457

Luminaire Tested: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034457
REPORT IS A COMBINATION OF REPORTS P1003333 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8097.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034457

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034457

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	94	90	86	92	87	84	80	76	73	70	65	62	61	54	53	52
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43
3	81	71	64	57	75	67	60	54	58	52	48	49	45	42	42	39	36
4	74	63	55	48	69	59	51	46	51	45	41	44	39	36	37	34	31
5	68	56	48	41	63	52	45	39	46	40	35	39	35	31	33	30	27
6	63	50	42	36	58	47	40	34	41	35	30	35	31	27	30	26	23
7	58	45	37	31	54	43	35	30	37	31	27	32	27	24	28	24	21
8	54	41	33	28	50	39	31	26	34	28	24	29	25	21	25	21	19
9	50	38	30	25	47	35	28	24	31	25	21	27	22	19	23	20	17
10	47	35	27	22	44	33	26	21	29	23	19	25	20	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10256	10256	10256
5°	10273	10042	10066
10°	10196	9837	9809
15°	10072	9599	9492
20°	9904	9311	9178
25°	9706	9004	8798
30°	9466	8671	8452
35°	9241	8362	8133
40°	9013	8038	7812
45°	8754	7757	7523
50°	8507	7452	7263
55°	8210	7161	6960
60°	7884	6830	6649
65°	7543	6479	6301
70°	7152	6011	5936
75°	6539	5549	5492
80°	5729	4988	5002
85°	4934	4538	4743

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8754 cd/sqm

TEST NUMBER: P1034457

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	1.9
10°-20°	430.0	5.3
20°-30°	639.5	7.9
30°-40°	757.3	9.4
40°-50°	782.9	9.7
50°-60°	721.2	8.9
60°-70°	583.0	7.2
70°-80°	390.1	4.8
80°-90°	203.2	2.5
90°-100°	148.2	1.8
100°-110°	314.2	3.9
110°-120°	471.0	5.8
120°-130°	564.4	7.0
130°-140°	586.8	7.2
140°-150°	540.4	6.7
150°-160°	434.9	5.4
160°-170°	281.3	3.5
170°-180°	97.0	1.2
0°-30°	1221.0	15.1
0°-40°	1978.3	24.4
0°-60°	3482.4	43.0
0°-90°	4658.8	57.5
90°-120°	933.4	11.5
90°-150°	2625.0	32.4
90°-180°	3438.0	42.5
0°-180°	8097.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1601	1601	1601	1601	1601	
5°	1601	1598	1587	1599	1598	152
15°	1529	1530	1519	1529	1522	431
25°	1389	1394	1384	1390	1383	639
35°	1202	1213	1208	1213	1213	753
45°	990	1008	1015	1026	1028	764
55°	761	786	811	829	835	680
65°	524	560	598	622	628	520
75°	289	330	380	411	419	306
85°	86	138	193	228	240	90
90°	26	82	141	181	194	20
95°	64	102	127	165	176	69
105°	237	265	312	343	354	251
115°	427	442	484	509	514	424
125°	600	604	636	658	663	536
135°	744	747	757	776	779	574
145°	861	861	861	869	871	538
155°	946	942	943	945	939	436
165°	998	994	995	999	993	282
175°	1021	1016	1017	1023	1016	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1034457

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1600.8	1600.8	1600.8	1600.8	1600.8
2.5°	1605.5	1602.4	1591.4	1602.4	1600.8
5°	1600.8	1597.7	1586.7	1599.2	1597.7
7.5°	1589.8	1588.2	1577.3	1588.2	1586.7
10°	1574.1	1574.1	1561.6	1572.6	1571.0
12.5°	1552.1	1553.7	1544.3	1552.1	1547.4
15°	1528.6	1530.2	1519.2	1528.6	1522.3
17.5°	1498.8	1501.9	1490.9	1498.8	1494.1
20°	1465.8	1469.0	1458.0	1462.7	1462.7
22.5°	1428.2	1434.4	1421.9	1428.2	1423.5
25°	1388.9	1393.6	1384.2	1390.5	1382.7
27.5°	1346.6	1352.8	1341.8	1346.6	1343.4
30°	1297.9	1307.3	1297.9	1301.0	1299.5
32.5°	1254.0	1261.8	1255.5	1258.7	1257.1
35°	1202.2	1213.2	1208.4	1213.2	1213.2
37.5°	1151.9	1161.4	1159.8	1166.1	1164.5
40°	1100.2	1112.7	1111.1	1117.4	1120.6
42.5°	1043.7	1060.9	1065.6	1073.5	1073.5
45°	990.3	1007.6	1015.4	1026.4	1028.0
47.5°	935.4	951.1	963.6	979.3	982.5
50°	878.9	896.1	913.4	930.7	935.4
52.5°	819.2	841.2	863.2	882.0	885.1
55°	761.2	786.3	811.4	828.6	834.9
57.5°	701.5	731.3	759.6	778.4	783.1
60°	641.9	673.3	704.7	728.2	732.9
62.5°	583.8	615.2	649.7	676.4	682.7
65°	524.2	560.3	597.9	621.5	627.8
67.5°	469.3	503.8	541.4	569.7	577.5
70°	408.0	444.1	484.9	514.8	524.2
72.5°	348.4	386.1	431.6	464.5	470.8
75°	288.8	329.6	379.8	411.2	419.0
77.5°	230.7	277.8	324.9	359.4	365.7
80°	177.3	224.4	277.8	312.3	318.6
82.5°	128.7	178.9	233.8	266.8	279.4
85°	86.3	138.1	193.0	227.6	240.1
87.5°	54.9	105.2	158.5	194.6	205.6
90°	25.9	82.1	140.8	180.7	194.0
92.5°	36.4	75.1	134.5	172.8	184.6
95°	63.5	102.1	126.7	165.0	176.0
97.5°	99.8	142.0	121.9	156.3	168.1
100°	143.7	178.9	232.1	152.3	158.7
102.5°	188.3	221.1	271.3	304.2	250.0
105°	236.6	264.8	311.9	343.3	353.5
107.5°	286.6	308.5	355.5	387.7	394.0
110°	335.0	353.8	399.3	426.8	438.6



TEST NUMBER: P1034457

CATALOG NUMBER: S125DIW-B1270D770UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.9	398.3	441.4	466.6	476.1
115°	427.2	442.0	483.6	508.8	513.7
117.5°	474.8	482.7	524.9	547.1	556.6
120°	520.2	524.3	562.6	587.7	593.3
122.5°	558.8	564.1	599.5	623.1	627.9
125°	600.5	604.2	635.6	657.6	663.3
127.5°	639.0	641.2	667.1	689.2	692.5
130°	675.3	677.5	700.3	720.0	724.0
132.5°	710.0	714.6	728.0	750.0	752.5
135°	744.1	747.1	756.6	775.5	778.8
137.5°	775.9	778.9	783.6	802.5	805.0
140°	805.4	806.9	807.7	826.5	828.3
142.5°	833.4	832.6	834.1	848.2	850.0
145°	860.7	860.6	860.6	869.2	870.9
147.5°	883.3	883.3	884.1	887.9	885.8
150°	906.0	904.5	906.0	907.5	903.1
152.5°	928.0	924.2	925.7	927.2	921.9
155°	946.1	941.6	943.1	945.4	939.3
157.5°	960.5	958.2	958.2	960.5	954.5
160°	975.6	971.1	971.9	974.9	968.8
162.5°	987.8	983.2	984.0	988.5	981.7
165°	998.4	993.8	994.6	999.1	993.1
167.5°	1006.7	1002.1	1002.9	1008.2	1001.4
170°	1013.5	1008.2	1009.0	1015.0	1008.2
172.5°	1018.0	1012.7	1014.2	1019.5	1012.7
175°	1021.1	1016.5	1017.3	1023.3	1016.5
177.5°	1023.3	1018.8	1019.5	1024.8	1018.8
180°	1021.1	1021.1	1021.1	1021.1	1021.1

(END OF REPORT)