

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034046

Luminaire Tested: S124RDIW-B350D1340UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034046
REPORT IS A COMBINATION OF REPORTS P1000326 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B350D1340UB30-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6762.0 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034046

CATALOG NUMBER: S124RDIW-B350D1340UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034046

CATALOG NUMBER: S124RDIW-B350D1340UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	40	39	26	25	25
2	83	76	70	66	73	68	63	59	51	48	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	15
5	64	53	45	39	56	47	40	35	36	31	28	26	23	21	16	15	14
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4906	4906	4906
5°	4906	4760	4761
10°	4865	4610	4555
15°	4798	4422	4312
20°	4710	4209	4036
25°	4601	3979	3766
30°	4493	3744	3463
35°	4376	3507	3166
40°	4236	3251	2862
45°	4104	2996	2560
50°	3956	2719	2254
55°	3794	2435	1938
60°	3614	2133	1626
65°	3441	1786	1325
70°	3197	1423	1012
75°	2882	1035	708
80°	2406	635	510
85°	1812	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4104 cd/sqm

TEST NUMBER: P1034046

CATALOG NUMBER: S124RDIW-B350D1340UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	0.8
10°-20°	157.7	2.3
20°-30°	227.7	3.4
30°-40°	258.1	3.8
40°-50°	249.2	3.7
50°-60°	207.2	3.1
60°-70°	143.0	2.1
70°-80°	72.3	1.1
80°-90°	21.9	0.3
90°-100°	57.6	0.9
100°-110°	379.3	5.6
110°-120°	724.2	10.7
120°-130°	919.4	13.6
130°-140°	983.6	14.5
140°-150°	919.7	13.6
150°-160°	741.6	11.0
160°-170°	478.3	7.1
170°-180°	164.8	2.4
0°-30°	442.0	6.5
0°-40°	700.1	10.4
0°-60°	1156.4	17.1
0°-90°	1393.6	20.6
90°-120°	1161.0	17.2
90°-150°	3983.6	58.9
90°-180°	5368.0	79.4
0°-180°	6762.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	602	602	602	602	602	
5°	601	599	593	598	597	57
15°	572	568	556	556	552	161
25°	517	509	490	482	478	238
35°	447	432	410	394	386	280
45°	365	348	320	298	289	281
55°	276	258	228	204	195	247
65°	188	168	139	119	113	186
75°	100	83	61	51	48	105
85°	25	16	14	13	13	27
90°	4	18	28	36	39	5
95°	71	27	28	36	38	88
105°	391	398	405	416	370	409
115°	729	733	732	734	734	718
125°	1025	1030	1028	1032	1033	915
135°	1272	1270	1276	1278	1281	980
145°	1466	1470	1470	1472	1474	916
155°	1608	1609	1605	1610	1606	741
165°	1696	1690	1690	1700	1688	479
175°	1735	1727	1728	1740	1724	165
180°	1735	1735	1735	1735	1735	

TEST NUMBER: P1034046

CATALOG NUMBER: S124RDIW-B350D1340UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	601.6	601.6	601.6	601.6	601.6
2.5°	603.4	601.6	596.5	601.6	601.1
5°	600.7	598.8	593.3	597.9	597.0
7.5°	596.5	594.7	587.8	591.0	589.6
10°	590.1	587.8	579.5	581.3	579.5
12.5°	581.8	579.0	568.9	569.8	567.0
15°	572.1	567.9	556.4	555.5	552.3
17.5°	561.0	555.1	541.7	539.4	534.8
20°	547.7	541.7	526.0	522.3	516.4
22.5°	532.9	526.0	509.0	503.0	498.4
25°	517.3	509.0	490.1	482.3	477.7
27.5°	501.2	491.0	471.2	462.0	455.6
30°	484.1	472.6	450.9	439.4	432.1
32.5°	466.2	452.8	430.2	416.4	409.5
35°	447.3	432.5	409.5	393.8	385.5
37.5°	427.5	412.3	386.9	369.9	361.6
40°	406.3	391.1	364.8	345.5	337.2
42.5°	386.0	369.9	342.2	322.4	313.7
45°	364.8	347.8	320.1	297.6	289.3
47.5°	343.2	325.7	297.1	273.6	264.4
50°	321.1	303.1	273.6	250.6	241.8
52.5°	298.5	281.0	250.6	227.1	217.9
55°	276.4	257.9	228.0	204.1	195.3
57.5°	254.7	235.4	205.9	181.5	175.0
60°	231.2	212.8	183.3	159.4	152.0
62.5°	210.0	190.7	160.3	138.6	133.1
65°	187.9	168.1	138.6	118.8	113.3
67.5°	164.9	146.0	118.4	100.9	94.4
70°	143.3	123.9	97.7	82.5	77.8
72.5°	120.2	103.2	78.8	66.3	62.2
75°	100.0	82.9	61.3	50.7	47.9
77.5°	78.8	64.0	45.6	38.2	37.3
80°	58.5	45.1	31.3	29.9	29.5
82.5°	41.0	29.0	22.6	21.6	21.2
85°	24.9	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.4	6.0	6.4
90°	3.9	18.2	28.5	36.3	38.9
92.5°	19.5	16.9	27.2	35.0	35.0
95°	71.4	27.2	28.5	36.3	37.6
97.5°	136.2	164.8	28.5	35.0	36.3
100°	212.8	236.2	57.1	35.0	36.3
102.5°	298.5	314.0	329.6	37.6	37.6
105°	390.6	398.4	404.9	416.5	369.8
107.5°	474.9	478.8	487.9	494.4	499.6
110°	560.6	564.5	572.2	574.8	578.7

TEST NUMBER: P1034046

CATALOG NUMBER: S124RDIW-B350D1340UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	643.6	651.4	654.0	652.7	657.9
115°	729.3	733.2	731.9	734.4	734.4
117.5°	805.8	811.0	814.9	813.6	813.6
120°	883.7	888.9	887.6	890.2	887.6
122.5°	956.3	958.9	961.5	962.8	960.2
125°	1025.1	1030.3	1027.7	1031.6	1032.9
127.5°	1091.3	1092.6	1099.1	1097.8	1096.5
130°	1154.9	1156.2	1160.1	1161.4	1161.4
132.5°	1213.3	1215.9	1221.1	1222.4	1221.1
135°	1271.7	1270.4	1275.6	1278.1	1280.7
137.5°	1323.6	1323.6	1330.1	1332.6	1331.4
140°	1374.2	1376.8	1379.4	1383.3	1384.6
142.5°	1419.6	1424.8	1426.1	1428.7	1428.7
145°	1466.3	1470.2	1470.2	1471.5	1474.1
147.5°	1502.6	1510.4	1509.1	1510.4	1511.7
150°	1542.9	1548.1	1546.8	1546.8	1548.1
152.5°	1576.6	1580.5	1577.9	1580.5	1579.2
155°	1607.7	1609.0	1605.1	1610.3	1606.4
157.5°	1635.0	1635.0	1629.8	1636.3	1629.8
160°	1658.3	1654.5	1653.2	1660.9	1653.2
162.5°	1679.1	1673.9	1672.6	1680.4	1671.3
165°	1696.0	1689.5	1689.5	1699.9	1688.2
167.5°	1710.3	1703.8	1702.5	1714.1	1701.2
170°	1721.9	1714.1	1715.4	1725.8	1712.8
172.5°	1729.7	1721.9	1723.2	1733.6	1719.3
175°	1734.9	1727.1	1728.4	1740.1	1724.5
177.5°	1738.8	1729.7	1732.3	1742.7	1727.1
180°	1734.9	1734.9	1734.9	1734.9	1734.9

(END OF REPORT)