

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034490

Luminaire Tested: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034490
REPORT IS A COMBINATION OF REPORTS P1003470 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6791.0 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034490

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034490

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25
2	83	76	70	65	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	54	67	59	54	49	45	41	38	33	30	28	21	19	18
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	16	15	13
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12
7	54	42	34	29	47	38	31	26	29	24	21	21	18	16	14	12	10
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	11	9
9	46	34	27	23	41	31	25	20	24	20	16	18	15	12	11	10	8
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3611	3528	3534
10°	3581	3446	3436
15°	3534	3350	3320
20°	3471	3238	3187
25°	3402	3115	3045
30°	3321	2988	2894
35°	3232	2855	2726
40°	3142	2713	2577
45°	3043	2575	2418
50°	2935	2419	2233
55°	2828	2247	2063
60°	2700	2065	1865
65°	2547	1855	1660
70°	2391	1614	1424
75°	2131	1330	1151
80°	1816	993	848
85°	1401	588	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3043 cd/sqm

TEST NUMBER: P1034490

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	0.8
10°-20°	150.2	2.2
20°-30°	221.8	3.3
30°-40°	258.8	3.8
40°-50°	259.9	3.8
50°-60°	228.1	3.4
60°-70°	169.9	2.5
70°-80°	97.1	1.4
80°-90°	30.6	0.5
90°-100°	58.8	0.9
100°-110°	391.0	5.8
110°-120°	704.1	10.4
120°-130°	903.7	13.3
130°-140°	972.0	14.3
140°-150°	912.2	13.4
150°-160°	737.9	10.9
160°-170°	477.2	7.0
170°-180°	164.6	2.4
0°-30°	425.2	6.3
0°-40°	684.0	10.1
0°-60°	1172.0	17.3
0°-90°	1469.6	21.6
90°-120°	1153.8	17.0
90°-150°	3941.7	58.0
90°-180°	5321.0	78.4
0°-180°	6791.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	27
90°	1	12	20	27	31	5
95°	73	69	20	27	27	90
105°	378	383	383	383	381	400
115°	709	715	717	711	704	703
125°	1008	1017	1017	1012	1008	900
135°	1257	1265	1262	1260	1252	969
145°	1458	1460	1460	1461	1454	912
155°	1605	1598	1600	1604	1594	740
165°	1694	1686	1687	1695	1685	478
175°	1732	1725	1726	1736	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1034490

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	1.3	11.6	20.5	27.0	30.8
92.5°	24.4	12.8	20.5	27.0	28.3
95°	73.2	69.3	20.5	27.0	27.0
97.5°	137.4	145.1	23.1	25.7	27.0
100°	214.5	218.3	223.4	32.1	27.0
102.5°	292.8	297.9	300.5	303.1	195.2
105°	377.5	382.7	382.7	382.7	381.4
107.5°	464.9	464.9	467.4	468.7	463.6
110°	549.6	549.6	552.2	548.3	549.6

TEST NUMBER: P1034490

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	629.2	633.1	634.4	629.2	626.7
115°	708.9	715.3	716.6	711.4	703.7
117.5°	792.3	792.3	797.5	789.8	787.2
120°	869.4	868.1	872.0	869.4	863.0
122.5°	937.4	943.9	945.2	942.6	934.9
125°	1008.1	1017.1	1017.1	1011.9	1008.1
127.5°	1076.1	1082.6	1081.3	1078.7	1068.4
130°	1137.8	1144.2	1145.5	1141.6	1135.2
132.5°	1199.4	1207.1	1203.3	1203.3	1196.9
135°	1257.2	1264.9	1262.3	1259.8	1252.1
137.5°	1311.1	1318.9	1316.3	1316.3	1309.9
140°	1363.8	1366.4	1365.1	1367.6	1359.9
142.5°	1411.3	1412.6	1415.2	1415.2	1407.5
145°	1457.5	1460.1	1460.1	1461.4	1453.7
147.5°	1498.6	1498.6	1499.9	1501.2	1492.2
150°	1537.2	1534.6	1537.2	1539.7	1529.5
152.5°	1574.4	1568.0	1570.5	1573.1	1564.1
155°	1605.2	1597.5	1600.1	1603.9	1593.7
157.5°	1629.6	1625.8	1625.8	1629.6	1619.3
160°	1655.3	1647.6	1648.9	1654.0	1643.7
162.5°	1675.9	1668.1	1669.4	1677.1	1665.6
165°	1693.8	1686.1	1687.4	1695.1	1684.8
167.5°	1708.0	1700.3	1701.5	1710.5	1699.0
170°	1719.5	1710.5	1711.8	1722.1	1710.5
172.5°	1727.2	1718.2	1720.8	1729.8	1718.2
175°	1732.4	1724.7	1725.9	1736.2	1724.7
177.5°	1736.2	1728.5	1729.8	1738.8	1728.5
180°	1732.4	1732.4	1732.4	1732.4	1732.4

(END OF REPORT)