

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034520

Luminaire Tested: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034520
REPORT IS A COMBINATION OF REPORTS P1003602 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3347.0 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034520

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034520

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	45	43	43
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	57	73	65	59	53	54	49	45	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3611	3528	3534
10°	3581	3446	3436
15°	3534	3350	3320
20°	3471	3238	3187
25°	3402	3115	3045
30°	3321	2988	2894
35°	3232	2855	2726
40°	3142	2713	2577
45°	3043	2575	2418
50°	2935	2419	2233
55°	2828	2247	2063
60°	2700	2065	1865
65°	2547	1855	1660
70°	2391	1614	1424
75°	2131	1330	1151
80°	1816	993	848
85°	1401	588	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3043 cd/sqm

TEST NUMBER: P1034520

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	1.6
10°-20°	150.2	4.5
20°-30°	221.8	6.6
30°-40°	258.8	7.7
40°-50°	259.9	7.8
50°-60°	228.1	6.8
60°-70°	169.9	5.1
70°-80°	97.1	2.9
80°-90°	28.9	0.9
90°-100°	20.8	0.6
100°-110°	138.1	4.1
110°-120°	248.6	7.4
120°-130°	319.1	9.5
130°-140°	343.2	10.3
140°-150°	322.1	9.6
150°-160°	260.6	7.8
160°-170°	168.5	5.0
170°-180°	58.1	1.7
0°-30°	425.2	12.7
0°-40°	684.0	20.4
0°-60°	1172.0	35.0
0°-90°	1467.9	43.9
90°-120°	407.4	12.2
90°-150°	1391.9	41.6
90°-180°	1879.0	56.1
0°-180°	3347.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	27
90°	0	4	7	10	11	3
95°	26	24	7	10	10	32
105°	133	135	135	135	135	141
115°	250	253	253	251	248	248
125°	356	359	359	357	356	318
135°	444	447	446	445	442	342
145°	515	516	516	516	513	322
155°	567	564	565	566	563	261
165°	598	595	596	599	595	169
175°	612	609	610	613	609	58
180°	612	612	612	612	612	

TEST NUMBER: P1034520

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	0.5	4.1	7.3	9.5	10.9
92.5°	8.6	4.5	7.3	9.5	10.0
95°	25.8	24.5	7.3	9.5	9.5
97.5°	48.5	51.2	8.2	9.1	9.5
100°	75.7	77.1	78.9	11.3	9.5
102.5°	103.4	105.2	106.1	107.0	68.9
105°	133.3	135.1	135.1	135.1	134.7
107.5°	164.2	164.2	165.1	165.5	163.7
110°	194.1	194.1	195.0	193.6	194.1



TEST NUMBER: P1034520

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.2	223.6	224.0	222.2	221.3
115°	250.3	252.6	253.0	251.2	248.5
117.5°	279.8	279.8	281.6	278.9	278.0
120°	307.0	306.5	307.9	307.0	304.7
122.5°	331.0	333.3	333.8	332.8	330.1
125°	356.0	359.1	359.1	357.3	356.0
127.5°	380.0	382.3	381.8	380.9	377.3
130°	401.8	404.0	404.5	403.1	400.9
132.5°	423.5	426.3	424.9	424.9	422.6
135°	443.9	446.7	445.8	444.9	442.1
137.5°	463.0	465.7	464.8	464.8	462.5
140°	481.6	482.5	482.0	482.9	480.2
142.5°	498.4	498.8	499.7	499.7	497.0
145°	514.7	515.6	515.6	516.0	513.3
147.5°	529.2	529.2	529.6	530.1	526.9
150°	542.8	541.9	542.8	543.7	540.1
152.5°	555.9	553.7	554.6	555.5	552.3
155°	566.8	564.1	565.0	566.4	562.8
157.5°	575.4	574.1	574.1	575.4	571.8
160°	584.5	581.8	582.3	584.1	580.4
162.5°	591.8	589.1	589.5	592.2	588.1
165°	598.1	595.4	595.9	598.6	594.9
167.5°	603.1	600.4	600.8	604.0	599.9
170°	607.2	604.0	604.5	608.1	604.0
172.5°	609.9	606.7	607.6	610.8	606.7
175°	611.7	609.0	609.5	613.1	609.0
177.5°	613.1	610.4	610.8	614.0	610.4
180°	611.7	611.7	611.7	611.7	611.7

(END OF REPORT)