

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034521

Luminaire Tested: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034521
REPORT IS A COMBINATION OF REPORTS P1003603 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3376.0 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034521

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034521

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	45	43	43
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	57	73	65	59	53	54	49	45	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1034521

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.6
10°-20°	151.6	4.5
20°-30°	223.8	6.6
30°-40°	261.1	7.7
40°-50°	262.2	7.8
50°-60°	230.2	6.8
60°-70°	171.4	5.1
70°-80°	97.9	2.9
80°-90°	29.2	0.9
90°-100°	20.9	0.6
100°-110°	139.2	4.1
110°-120°	250.7	7.4
120°-130°	321.8	9.5
130°-140°	346.1	10.3
140°-150°	324.9	9.6
150°-160°	262.8	7.8
160°-170°	170.0	5.0
170°-180°	58.6	1.7
0°-30°	429.0	12.7
0°-40°	690.0	20.4
0°-60°	1182.4	35.0
0°-90°	1480.9	43.9
90°-120°	410.9	12.2
90°-150°	1403.8	41.6
90°-180°	1895.0	56.1
0°-180°	3376.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	0	4	7	10	11	3
95°	26	25	7	10	10	32
105°	134	136	136	136	136	142
115°	252	255	255	253	251	250
125°	359	362	362	360	359	321
135°	448	450	450	449	446	345
145°	519	520	520	520	518	325
155°	572	569	570	571	568	263
165°	603	600	601	604	600	170
175°	617	614	615	618	614	59
180°	617	617	617	617	617	

TEST NUMBER: P1034521

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.1	24.7	7.3	9.6	9.6
97.5°	48.9	51.7	8.2	9.1	9.6
100°	76.4	77.7	79.6	11.4	9.6
102.5°	104.3	106.1	107.0	107.9	69.5
105°	134.5	136.3	136.3	136.3	135.8
107.5°	165.6	165.6	166.5	166.9	165.1
110°	195.7	195.7	196.6	195.3	195.7

TEST NUMBER: P1034521

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	224.1	225.5	225.9	224.1	223.2
115°	252.4	254.7	255.2	253.4	250.6
117.5°	282.2	282.2	284.0	281.3	280.3
120°	309.6	309.2	310.5	309.6	307.3
122.5°	333.8	336.1	336.6	335.7	332.9
125°	359.0	362.2	362.2	360.4	359.0
127.5°	383.2	385.5	385.1	384.2	380.5
130°	405.2	407.5	407.9	406.6	404.3
132.5°	427.1	429.9	428.5	428.5	426.2
135°	447.7	450.5	449.6	448.6	445.9
137.5°	466.9	469.7	468.8	468.8	466.5
140°	485.7	486.6	486.1	487.1	484.3
142.5°	502.6	503.1	504.0	504.0	501.2
145°	519.1	520.0	520.0	520.4	517.7
147.5°	533.7	533.7	534.2	534.6	531.4
150°	547.4	546.5	547.4	548.3	544.7
152.5°	560.7	558.4	559.3	560.2	557.0
155°	571.7	568.9	569.8	571.2	567.5
157.5°	580.3	579.0	579.0	580.3	576.7
160°	589.5	586.7	587.2	589.0	585.4
162.5°	596.8	594.1	594.5	597.3	593.2
165°	603.2	600.5	600.9	603.7	600.0
167.5°	608.2	605.5	606.0	609.2	605.0
170°	612.4	609.2	609.6	613.3	609.2
172.5°	615.1	611.9	612.8	616.0	611.9
175°	616.9	614.2	614.6	618.3	614.2
177.5°	618.3	615.6	616.0	619.2	615.6
180°	616.9	616.9	616.9	616.9	616.9

(END OF REPORT)