

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034097

Luminaire Tested: S124RDIW-B350D470UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034097
REPORT IS A COMBINATION OF REPORTS P1000433 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B350D470UB50-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2919.0 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034097

CATALOG NUMBER: S124RDIW-B350D470UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1034097

CATALOG NUMBER: S124RDIW-B350D470UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46		
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	47	46	45	39		
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	40	38	33		
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	28		
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	30	28	25		
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21		
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19		
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17		
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14		
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1034097

CATALOG NUMBER: S124RDIW-B350D470UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.9
10°-20°	151.7	5.2
20°-30°	219.0	7.5
30°-40°	248.2	8.5
40°-50°	239.7	8.2
50°-60°	199.3	6.8
60°-70°	137.5	4.7
70°-80°	69.5	2.4
80°-90°	18.9	0.6
90°-100°	37.1	1.3
100°-110°	111.2	3.8
110°-120°	189.0	6.5
120°-130°	249.2	8.5
130°-140°	279.9	9.6
140°-150°	275.1	9.4
150°-160°	231.4	7.9
160°-170°	153.9	5.3
170°-180°	53.9	1.8
0°-30°	425.2	14.6
0°-40°	673.4	23.1
0°-60°	1112.3	38.1
0°-90°	1338.2	45.8
90°-120°	337.3	11.6
90°-150°	1141.5	39.1
90°-180°	1581.0	54.2
0°-180°	2919.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	1	6	10	12	13	3
95°	26	30	34	35	35	29
105°	103	103	105	106	108	109
115°	192	192	191	191	190	189
125°	280	280	279	278	278	249
135°	361	364	364	363	361	279
145°	438	440	441	440	439	274
155°	502	502	502	504	502	231
165°	547	546	545	547	546	154
175°	569	567	566	569	566	54
180°	570	570	570	570	570	

TEST NUMBER: P1034097

CATALOG NUMBER: S124RDIW-B350D470UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	1.3	6.2	9.7	12.3	13.2
92.5°	11.5	17.2	19.4	20.7	21.1
95°	26.4	30.4	33.5	34.8	34.8
97.5°	42.3	45.8	49.3	51.1	51.1
100°	61.7	63.4	67.4	68.3	68.3
102.5°	82.0	82.4	85.9	87.2	87.7
105°	102.7	103.1	104.9	106.2	107.5
107.5°	124.3	124.7	125.1	126.9	126.5
110°	146.3	147.2	146.7	145.8	147.2



TEST NUMBER: P1034097

CATALOG NUMBER: S124RDIW-B350D470UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.2	169.2	168.3	168.3	168.3
115°	192.1	192.1	191.2	190.8	190.3
117.5°	213.7	213.7	213.3	211.9	210.6
120°	235.3	237.1	235.7	233.5	234.4
122.5°	257.8	258.2	257.8	256.4	254.2
125°	279.8	279.8	279.4	278.5	277.6
127.5°	299.6	300.9	300.1	299.2	298.7
130°	320.8	322.1	322.1	321.2	319.5
132.5°	342.4	343.2	342.8	341.9	341.5
135°	360.9	363.5	363.5	362.6	361.3
137.5°	381.6	382.9	383.8	382.5	382.9
140°	402.3	403.2	403.2	402.7	402.3
142.5°	421.2	422.1	421.7	421.7	421.7
145°	438.4	440.2	440.6	440.2	438.9
147.5°	456.0	458.2	457.8	457.4	456.9
150°	471.9	473.7	473.7	473.7	473.2
152.5°	486.9	487.8	488.2	489.5	488.2
155°	502.3	502.3	501.9	503.6	501.9
157.5°	515.5	514.6	514.6	516.0	514.6
160°	527.0	526.5	526.1	527.4	525.2
162.5°	537.6	536.2	535.8	538.4	536.2
165°	546.8	545.5	544.6	547.3	545.5
167.5°	554.3	552.5	552.5	555.2	552.5
170°	560.5	558.3	558.7	561.4	558.3
172.5°	564.9	563.1	563.1	566.2	563.1
175°	568.8	566.6	566.2	569.3	566.2
177.5°	570.6	568.4	568.4	571.5	568.0
180°	569.7	569.7	569.7	569.7	569.7

(END OF REPORT)