

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034567

Luminaire Tested: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034567
REPORT IS A COMBINATION OF REPORTS P1003802 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7893.0 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034567

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034567

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6154	6154	6154
5°	6154	6012	6023
10°	6104	5873	5855
15°	6024	5708	5657
20°	5915	5517	5431
25°	5799	5309	5188
30°	5659	5092	4933
35°	5509	4864	4646
40°	5353	4624	4392
45°	5186	4389	4121
50°	5001	4123	3805
55°	4819	3829	3515
60°	4601	3520	3178
65°	4341	3162	2829
70°	4076	2751	2427
75°	3630	2265	1962
80°	3093	1691	1443
85°	2390	1002	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5186 cd/sqm

TEST NUMBER: P1034567

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.1
10°-20°	256.0	3.2
20°-30°	378.0	4.8
30°-40°	441.0	5.6
40°-50°	442.9	5.6
50°-60°	388.8	4.9
60°-70°	289.6	3.7
70°-80°	165.4	2.1
80°-90°	50.4	0.6
90°-100°	59.5	0.8
100°-110°	396.0	5.0
110°-120°	713.2	9.0
120°-130°	915.4	11.6
130°-140°	984.6	12.5
140°-150°	924.1	11.7
150°-160°	747.5	9.5
160°-170°	483.4	6.1
170°-180°	166.7	2.1
0°-30°	724.6	9.2
0°-40°	1165.6	14.8
0°-60°	1997.3	25.3
0°-90°	2502.6	31.7
90°-120°	1168.8	14.8
90°-150°	3992.8	50.6
90°-180°	5390.0	68.3
0°-180°	7893.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	958	950	957	956	91
15°	914	912	904	907	907	258
25°	830	826	816	818	815	382
35°	717	714	703	699	693	448
45°	587	584	574	565	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	43	43	42	40	46
90°	1	12	21	27	31	7
95°	74	70	21	27	27	91
105°	382	388	388	388	386	405
115°	718	725	726	721	713	712
125°	1021	1030	1030	1025	1021	912
135°	1274	1281	1279	1276	1268	982
145°	1476	1479	1479	1480	1472	923
155°	1626	1618	1621	1625	1614	749
165°	1716	1708	1709	1717	1707	485
175°	1755	1747	1748	1759	1747	167
180°	1755	1755	1755	1755	1755	

TEST NUMBER: P1034567

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	960.5	960.5	960.5	960.5	960.5
2.5°	963.6	961.3	953.7	961.3	960.5
5°	959.0	957.5	949.9	956.7	956.0
7.5°	952.2	950.6	942.3	949.1	948.4
10°	942.3	940.8	932.4	938.5	937.7
12.5°	930.1	927.1	919.5	924.0	924.0
15°	914.2	911.9	903.5	907.3	907.3
17.5°	897.4	893.6	885.3	889.8	886.1
20°	875.4	873.9	864.0	869.3	865.5
22.5°	853.4	850.3	841.2	844.3	842.0
25°	829.8	826.0	816.1	817.7	815.4
27.5°	802.5	800.2	790.3	791.1	788.8
30°	775.9	773.6	762.2	760.7	758.4
32.5°	747.0	743.2	733.3	730.3	725.7
35°	716.6	713.6	702.9	699.1	693.0
37.5°	685.4	681.6	671.8	666.4	662.6
40°	653.5	649.7	639.1	632.2	630.0
42.5°	619.3	616.3	605.6	599.6	595.8
45°	586.6	583.6	574.5	565.4	563.1
47.5°	550.9	551.7	540.3	531.2	525.9
50°	516.7	514.5	505.3	495.5	490.1
52.5°	481.8	480.3	470.4	462.0	455.9
55°	446.8	444.5	433.9	427.1	421.7
57.5°	409.6	408.8	399.7	390.6	388.3
60°	374.6	371.6	363.2	355.6	350.3
62.5°	338.2	335.9	329.0	320.7	316.9
65°	301.7	300.2	291.8	285.0	281.9
67.5°	266.0	262.9	256.8	250.8	249.2
70°	232.5	228.7	221.9	217.3	214.3
72.5°	196.1	193.8	190.0	184.7	181.6
75°	160.3	158.8	155.0	152.7	149.7
77.5°	126.9	126.1	123.9	122.3	120.1
80°	95.7	95.7	94.2	93.5	91.9
82.5°	68.4	66.9	66.9	65.4	65.4
85°	41.8	42.6	42.6	41.8	40.3
87.5°	20.5	20.5	19.8	19.8	18.2
90°	1.3	11.7	20.8	27.3	31.2
92.5°	24.7	13.0	20.8	27.3	28.6
95°	74.1	70.2	20.8	27.3	27.3
97.5°	139.2	147.0	23.4	26.0	27.3
100°	217.2	221.1	226.3	32.5	27.3
102.5°	296.6	301.8	304.4	307.0	197.7
105°	382.4	387.6	387.6	387.6	386.3
107.5°	470.9	470.9	473.5	474.8	469.6
110°	556.8	556.8	559.4	555.5	556.8

TEST NUMBER: P1034567

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	637.4	641.3	642.6	637.4	634.8
115°	718.1	724.6	725.9	720.7	712.8
117.5°	802.6	802.6	807.8	800.0	797.4
120°	880.7	879.4	883.3	880.7	874.2
122.5°	949.6	956.1	957.4	954.8	947.0
125°	1021.1	1030.3	1030.3	1025.0	1021.1
127.5°	1090.1	1096.6	1095.3	1092.7	1082.3
130°	1152.5	1159.0	1160.3	1156.4	1149.9
132.5°	1215.0	1222.8	1218.9	1218.9	1212.4
135°	1273.5	1281.3	1278.7	1276.1	1268.3
137.5°	1328.1	1335.9	1333.3	1333.3	1326.8
140°	1381.5	1384.1	1382.8	1385.4	1377.6
142.5°	1429.6	1430.9	1433.5	1433.5	1425.7
145°	1476.4	1479.0	1479.0	1480.3	1472.5
147.5°	1518.1	1518.1	1519.4	1520.7	1511.6
150°	1557.1	1554.5	1557.1	1559.7	1549.3
152.5°	1594.8	1588.3	1590.9	1593.5	1584.4
155°	1626.0	1618.2	1620.8	1624.7	1614.3
157.5°	1650.7	1646.8	1646.8	1650.7	1640.3
160°	1676.8	1669.0	1670.3	1675.5	1665.1
162.5°	1697.6	1689.8	1691.1	1698.9	1687.2
165°	1715.8	1708.0	1709.3	1717.1	1706.7
167.5°	1730.1	1722.3	1723.6	1732.7	1721.0
170°	1741.8	1732.7	1734.0	1744.4	1732.7
172.5°	1749.6	1740.5	1743.1	1752.2	1740.5
175°	1754.8	1747.0	1748.3	1758.7	1747.0
177.5°	1758.7	1750.9	1752.2	1761.3	1750.9
180°	1754.8	1754.8	1754.8	1754.8	1754.8

(END OF REPORT)