

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034605

Luminaire Tested: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034605
REPORT IS A COMBINATION OF REPORTS P1003991 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5468.2 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034605

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034605

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	52	47	44	42	36	34	32
3	79	69	62	56	71	63	57	51	52	47	43	41	38	35	32	29	27
4	72	61	53	47	65	56	49	43	46	41	36	37	33	30	28	25	23
5	66	54	46	40	60	49	42	37	41	35	31	33	29	26	25	22	20
6	60	48	40	34	55	44	37	32	37	31	27	30	25	22	23	20	18
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	32	26	47	36	29	25	30	25	21	24	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	22	18	16	18	15	13
10	45	33	26	21	41	30	24	20	25	20	17	21	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4902	4902	4902
5°	4910	4799	4811
10°	4873	4701	4688
15°	4814	4588	4537
20°	4733	4450	4386
25°	4639	4303	4205
30°	4524	4144	4039
35°	4416	3996	3887
40°	4307	3842	3733
45°	4184	3708	3596
50°	4065	3561	3471
55°	3924	3423	3326
60°	3768	3264	3178
65°	3604	3097	3011
70°	3418	2874	2837
75°	3125	2652	2625
80°	2740	2384	2391
85°	2361	2170	2268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4184 cd/sqm

TEST NUMBER: P1034605

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.3
10°-20°	205.5	3.8
20°-30°	305.6	5.6
30°-40°	361.9	6.6
40°-50°	374.2	6.8
50°-60°	344.7	6.3
60°-70°	278.7	5.1
70°-80°	186.5	3.4
80°-90°	97.9	1.8
90°-100°	88.5	1.6
100°-110°	267.6	4.9
110°-120°	436.5	8.0
120°-130°	541.1	9.9
130°-140°	572.2	10.5
140°-150°	532.1	9.7
150°-160°	429.4	7.9
160°-170°	277.7	5.1
170°-180°	95.8	1.8
0°-30°	583.5	10.7
0°-40°	945.4	17.3
0°-60°	1664.3	30.4
0°-90°	2227.3	40.7
90°-120°	792.6	14.5
90°-150°	2438.0	44.6
90°-180°	3241.0	59.3
0°-180°	5468.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	765	765	765	765	765	
5°	765	764	758	764	764	73
15°	731	731	726	731	728	206
25°	664	666	662	664	661	306
35°	574	580	578	580	580	360
45°	473	482	485	490	491	365
55°	364	376	388	396	399	325
65°	250	268	286	297	300	249
75°	138	158	182	196	200	146
85°	41	66	92	109	115	43
90°	13	43	74	94	102	10
95°	52	70	67	87	92	60
105°	226	242	264	279	283	240
115°	417	426	446	457	457	413
125°	590	594	609	618	620	527
135°	733	737	741	749	748	565
145°	849	850	850	854	853	531
155°	934	930	931	933	927	430
165°	986	981	982	986	980	278
175°	1008	1004	1004	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1034605

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	765.1	765.1	765.1	765.1	765.1
2.5°	767.3	765.8	760.6	765.8	765.1
5°	765.1	763.6	758.3	764.3	763.6
7.5°	759.8	759.1	753.8	759.1	758.3
10°	752.3	752.3	746.3	751.6	750.8
12.5°	741.8	742.6	738.1	741.8	739.6
15°	730.6	731.3	726.1	730.6	727.6
17.5°	716.3	717.8	712.5	716.3	714.0
20°	700.5	702.0	696.8	699.0	699.0
22.5°	682.5	685.5	679.5	682.5	680.3
25°	663.8	666.0	661.5	664.5	660.8
27.5°	643.5	646.5	641.3	643.5	642.0
30°	620.3	624.8	620.3	621.8	621.0
32.5°	599.3	603.0	600.0	601.5	600.8
35°	574.5	579.8	577.5	579.8	579.8
37.5°	550.5	555.0	554.3	557.3	556.5
40°	525.8	531.8	531.0	534.0	535.5
42.5°	498.8	507.0	509.3	513.0	513.0
45°	473.3	481.5	485.3	490.5	491.3
47.5°	447.0	454.5	460.5	468.0	469.5
50°	420.0	428.3	436.5	444.8	447.0
52.5°	391.5	402.0	412.5	421.5	423.0
55°	363.8	375.8	387.8	396.0	399.0
57.5°	335.3	349.5	363.0	372.0	374.3
60°	306.8	321.8	336.8	348.0	350.3
62.5°	279.0	294.0	310.5	323.3	326.3
65°	250.5	267.8	285.8	297.0	300.0
67.5°	224.3	240.8	258.8	272.3	276.0
70°	195.0	212.3	231.8	246.0	250.5
72.5°	166.5	184.5	206.3	222.0	225.0
75°	138.0	157.5	181.5	196.5	200.3
77.5°	110.3	132.8	155.3	171.8	174.8
80°	84.8	107.3	132.8	149.3	152.3
82.5°	61.5	85.5	111.8	127.5	133.5
85°	41.3	66.0	92.3	108.8	114.8
87.5°	26.3	50.3	75.8	93.0	98.3
90°	12.7	42.7	73.5	94.5	101.9
92.5°	24.7	39.8	70.5	90.7	96.7
95°	52.4	69.7	66.8	87.0	92.2
97.5°	89.0	111.4	65.3	82.4	88.5
100°	133.1	151.0	178.0	82.5	84.0
102.5°	177.9	195.2	219.9	236.4	178.1
105°	226.5	241.5	264.0	279.0	283.4
107.5°	276.5	287.0	310.3	326.0	327.6
110°	325.1	334.1	356.6	368.6	374.6

TEST NUMBER: P1034605

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.5	380.4	401.4	412.0	415.7
115°	417.0	426.0	446.3	456.8	456.8
117.5°	464.9	468.6	490.3	498.6	502.4
120°	509.7	511.1	530.7	541.9	542.7
122.5°	548.5	553.0	570.3	580.8	580.8
125°	589.6	594.1	609.1	618.1	619.6
127.5°	628.5	631.4	643.5	653.2	651.7
130°	664.4	667.3	678.6	686.8	686.9
132.5°	699.4	703.9	709.2	719.7	718.9
135°	733.1	736.8	740.6	748.9	748.1
137.5°	764.4	768.2	769.7	778.7	778.0
140°	794.4	795.9	795.8	805.6	804.1
142.5°	822.0	822.0	823.5	830.3	828.8
145°	848.9	849.6	849.6	854.2	852.7
147.5°	872.0	872.0	872.8	875.0	871.3
150°	894.5	893.0	894.5	896.0	890.8
152.5°	916.1	912.4	913.9	915.4	910.2
155°	934.1	929.6	931.1	933.3	927.3
157.5°	948.3	946.0	946.0	948.3	942.3
160°	963.2	958.7	959.5	962.5	956.5
162.5°	975.2	970.7	971.4	975.9	969.2
165°	985.6	981.1	981.9	986.4	980.4
167.5°	993.8	989.4	990.1	995.3	988.6
170°	1000.6	995.3	996.1	1002.1	995.3
172.5°	1005.1	999.8	1001.3	1006.6	999.8
175°	1008.0	1003.6	1004.3	1010.3	1003.6
177.5°	1010.3	1005.8	1006.6	1011.8	1005.8
180°	1008.0	1008.0	1008.0	1008.0	1008.0

(END OF REPORT)