

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034606

Luminaire Tested: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034606
REPORT IS A COMBINATION OF REPORTS P1003992 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5516.0 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034606

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034606

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	52	47	44	42	36	34	32
3	79	69	62	56	71	63	57	51	52	47	43	41	38	35	32	29	27
4	72	61	53	47	65	56	49	43	46	41	36	37	33	30	28	25	23
5	66	54	46	40	60	49	42	37	41	35	31	33	29	26	25	22	20
6	60	48	40	34	55	44	37	32	37	31	27	30	25	22	23	20	18
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	32	26	47	36	29	25	30	25	21	24	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	22	18	16	18	15	13
10	45	33	26	21	41	30	24	20	25	20	17	21	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4945	4945	4945
5°	4953	4841	4853
10°	4916	4743	4730
15°	4856	4628	4577
20°	4776	4489	4425
25°	4680	4342	4242
30°	4564	4181	4075
35°	4455	4032	3921
40°	4345	3876	3767
45°	4221	3740	3627
50°	4102	3593	3502
55°	3958	3453	3356
60°	3801	3293	3206
65°	3636	3124	3038
70°	3448	2898	2862
75°	3152	2675	2648
80°	2763	2404	2411
85°	2378	2189	2288

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4221 cd/sqm

TEST NUMBER: P1034606

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.3
10°-20°	207.3	3.8
20°-30°	308.3	5.6
30°-40°	365.1	6.6
40°-50°	377.5	6.8
50°-60°	347.7	6.3
60°-70°	281.1	5.1
70°-80°	188.1	3.4
80°-90°	98.7	1.8
90°-100°	89.3	1.6
100°-110°	269.9	4.9
110°-120°	440.3	8.0
120°-130°	545.8	9.9
130°-140°	577.2	10.5
140°-150°	536.8	9.7
150°-160°	433.1	7.9
160°-170°	280.1	5.1
170°-180°	96.6	1.8
0°-30°	588.7	10.7
0°-40°	953.8	17.3
0°-60°	1679.1	30.4
0°-90°	2247.0	40.7
90°-120°	799.4	14.5
90°-150°	2459.2	44.6
90°-180°	3269.0	59.3
0°-180°	5516.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	772	772	772	772	772	
5°	772	770	765	771	770	73
15°	737	738	732	737	734	208
25°	670	672	667	670	667	308
35°	580	585	583	585	585	363
45°	478	486	490	495	496	368
55°	367	379	391	400	403	328
65°	253	270	288	300	303	251
75°	139	159	183	198	202	148
85°	42	67	93	110	116	43
90°	13	43	74	95	103	11
95°	53	70	67	88	93	60
105°	228	244	266	281	286	242
115°	421	430	450	461	461	417
125°	595	599	614	624	625	531
135°	739	743	747	755	755	570
145°	856	857	857	862	860	535
155°	942	938	939	942	935	434
165°	994	990	990	995	989	281
175°	1017	1012	1013	1019	1012	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1034606

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	771.8	771.8	771.8	771.8	771.8
2.5°	774.1	772.6	767.3	772.6	771.8
5°	771.8	770.3	765.0	771.1	770.3
7.5°	766.5	765.8	760.5	765.8	765.0
10°	759.0	759.0	752.9	758.2	757.5
12.5°	748.4	749.1	744.6	748.4	746.1
15°	737.0	737.8	732.5	737.0	734.0
17.5°	722.6	724.2	718.9	722.6	720.4
20°	706.8	708.3	703.0	705.2	705.2
22.5°	688.6	691.6	685.6	688.6	686.3
25°	669.7	671.9	667.4	670.4	666.7
27.5°	649.2	652.3	647.0	649.2	647.7
30°	625.8	630.3	625.8	627.3	626.5
32.5°	604.6	608.4	605.4	606.9	606.1
35°	579.6	584.9	582.7	584.9	584.9
37.5°	555.4	560.0	559.2	562.2	561.5
40°	530.4	536.5	535.7	538.8	540.3
42.5°	503.2	511.5	513.8	517.6	517.6
45°	477.5	485.8	489.6	494.9	495.6
47.5°	451.0	458.6	464.6	472.2	473.7
50°	423.8	432.1	440.4	448.7	451.0
52.5°	395.0	405.6	416.2	425.3	426.8
55°	367.0	379.1	391.2	399.5	402.6
57.5°	338.2	352.6	366.2	375.3	377.6
60°	309.5	324.6	339.8	351.1	353.4
62.5°	281.5	296.6	313.3	326.1	329.2
65°	252.7	270.1	288.3	299.7	302.7
67.5°	226.3	242.9	261.1	274.7	278.5
70°	196.7	214.1	233.8	248.2	252.7
72.5°	168.0	186.1	208.1	224.0	227.0
75°	139.2	158.9	183.1	198.3	202.0
77.5°	111.2	133.9	156.6	173.3	176.3
80°	85.5	108.2	133.9	150.6	153.6
82.5°	62.0	86.3	112.7	128.6	134.7
85°	41.6	66.6	93.1	109.7	115.8
87.5°	26.5	50.7	76.4	93.8	99.1
90°	12.9	43.1	74.1	95.3	102.9
92.5°	24.9	40.0	71.1	91.5	97.6
95°	52.8	70.2	67.3	87.7	93.0
97.5°	89.8	112.4	65.8	83.2	89.2
100°	134.2	152.3	179.6	83.1	84.7
102.5°	179.5	196.8	221.8	238.4	179.7
105°	228.4	243.5	266.2	281.4	285.9
107.5°	279.0	289.5	313.0	328.8	330.4
110°	327.9	337.0	359.7	371.8	377.8

TEST NUMBER: P1034606

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.6	383.7	404.9	415.5	419.3
115°	420.6	429.6	450.1	460.7	460.8
117.5°	468.9	472.7	494.6	502.9	506.7
120°	514.1	515.6	535.3	546.6	547.4
122.5°	553.2	557.8	575.2	585.8	585.8
125°	594.7	599.3	614.4	623.5	625.0
127.5°	634.0	636.9	649.1	658.9	657.4
130°	670.1	673.1	684.5	692.8	692.8
132.5°	705.5	710.0	715.4	726.0	725.2
135°	739.4	743.3	747.1	755.3	754.6
137.5°	771.1	774.9	776.4	785.5	784.7
140°	801.3	802.8	802.8	812.6	811.1
142.5°	829.2	829.1	830.7	837.5	835.9
145°	856.3	857.0	857.0	861.6	860.1
147.5°	879.6	879.6	880.4	882.7	878.9
150°	902.3	900.8	902.3	903.8	898.5
152.5°	924.1	920.3	921.9	923.4	918.1
155°	942.2	937.7	939.2	941.5	935.4
157.5°	956.5	954.3	954.3	956.5	950.5
160°	971.6	967.1	967.8	970.9	964.8
162.5°	983.7	979.1	979.9	984.4	977.6
165°	994.2	989.7	990.4	995.0	988.9
167.5°	1002.5	998.0	998.7	1004.0	997.2
170°	1009.3	1004.0	1004.8	1010.8	1004.0
172.5°	1013.8	1008.5	1010.0	1015.3	1008.5
175°	1016.8	1012.3	1013.1	1019.1	1012.3
177.5°	1019.1	1014.6	1015.3	1020.6	1014.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)