

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034609

Luminaire Tested: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034609
REPORT IS A COMBINATION OF REPORTS P1003996 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4998.9 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034609

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034609

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5893	5893	5893
5°	5893	5756	5767
10°	5845	5625	5607
15°	5768	5466	5418
20°	5664	5284	5200
25°	5553	5084	4968
30°	5419	4876	4723
35°	5275	4658	4449
40°	5127	4428	4206
45°	4966	4203	3946
50°	4789	3948	3645
55°	4615	3667	3367
60°	4406	3371	3044
65°	4157	3028	2710
70°	3904	2634	2324
75°	3476	2168	1880
80°	2963	1619	1381
85°	2287	959	763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4966 cd/sqm

TEST NUMBER: P1034609

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.7
10°-20°	245.2	4.9
20°-30°	361.9	7.2
30°-40°	422.3	8.4
40°-50°	424.1	8.5
50°-60°	372.3	7.4
60°-70°	277.3	5.5
70°-80°	158.4	3.2
80°-90°	47.2	0.9
90°-100°	62.0	1.2
100°-110°	184.3	3.7
110°-120°	312.5	6.3
120°-130°	411.4	8.2
130°-140°	461.1	9.2
140°-150°	451.9	9.0
150°-160°	379.6	7.6
160°-170°	252.3	5.0
170°-180°	88.3	1.8
0°-30°	693.9	13.9
0°-40°	1116.2	22.3
0°-60°	1912.6	38.3
0°-90°	2395.5	47.9
90°-120°	558.8	11.2
90°-150°	1883.3	37.7
90°-180°	2603.0	52.1
0°-180°	4998.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	918	917	910	916	915	87
15°	875	873	865	869	869	247
25°	795	791	782	783	781	366
35°	686	683	673	670	664	429
45°	562	559	550	541	539	433
55°	428	426	416	409	404	382
65°	289	287	279	273	270	287
75°	154	152	148	146	143	163
85°	40	41	41	40	39	44
90°	1	6	12	15	17	6
95°	47	49	56	61	62	49
105°	166	169	174	178	180	176
115°	313	316	317	316	316	310
125°	457	461	462	460	460	409
135°	594	598	599	599	596	458
145°	719	722	724	724	722	450
155°	823	823	824	827	823	379
165°	895	894	894	897	893	253
175°	931	928	928	932	927	88
180°	933	933	933	933	933	

TEST NUMBER: P1034609

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	919.8	919.8	919.8	919.8	919.8
2.5°	922.7	920.5	913.2	920.5	919.8
5°	918.3	916.9	909.6	916.2	915.4
7.5°	911.8	910.3	902.3	908.9	908.2
10°	902.3	900.9	892.9	898.7	898.0
12.5°	890.7	887.8	880.5	884.9	884.9
15°	875.4	873.2	865.2	868.9	868.9
17.5°	859.4	855.8	847.8	852.1	848.5
20°	838.3	836.8	827.4	832.5	828.8
22.5°	817.2	814.3	805.5	808.5	806.3
25°	794.6	791.0	781.5	783.0	780.8
27.5°	768.4	766.3	756.8	757.5	755.3
30°	743.0	740.8	729.9	728.4	726.2
32.5°	715.3	711.7	702.2	699.3	694.9
35°	686.2	683.3	673.1	669.5	663.6
37.5°	656.4	652.7	643.3	638.2	634.5
40°	625.8	622.2	612.0	605.4	603.3
42.5°	593.1	590.2	580.0	574.1	570.5
45°	561.8	558.9	550.1	541.4	539.2
47.5°	527.6	528.3	517.4	508.7	503.6
50°	494.8	492.6	483.9	474.5	469.4
52.5°	461.4	459.9	450.4	442.4	436.6
55°	427.9	425.7	415.5	409.0	403.9
57.5°	392.2	391.5	382.8	374.0	371.8
60°	358.7	355.8	347.8	340.6	335.5
62.5°	323.8	321.6	315.1	307.1	303.4
65°	288.9	287.4	279.4	272.9	270.0
67.5°	254.7	251.8	246.0	240.1	238.7
70°	222.7	219.0	212.5	208.1	205.2
72.5°	187.7	185.6	181.9	176.8	173.9
75°	153.5	152.1	148.4	146.3	143.4
77.5°	121.5	120.8	118.6	117.2	115.0
80°	91.7	91.7	90.2	89.5	88.0
82.5°	65.5	64.0	64.0	62.6	62.6
85°	40.0	40.8	40.8	40.0	38.6
87.5°	19.6	19.6	18.9	18.9	17.5
90°	0.7	6.5	11.6	15.2	17.4
92.5°	21.8	25.4	31.9	37.0	38.5
95°	47.2	48.6	55.9	61.0	62.4
97.5°	72.6	73.3	83.5	87.8	88.6
100°	101.6	101.6	111.1	117.6	119.1
102.5°	132.9	136.5	140.1	147.4	149.5
105°	165.5	169.1	173.5	177.9	180.0
107.5°	201.1	204.7	208.4	210.5	210.5
110°	238.1	241.7	243.9	246.1	245.4

TEST NUMBER: P1034609

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	275.9	277.3	280.2	280.9	279.5
115°	312.9	315.8	317.2	316.5	315.8
117.5°	350.6	351.4	352.8	353.5	350.6
120°	385.5	389.1	389.8	389.8	386.9
122.5°	423.2	424.0	426.1	425.4	423.2
125°	456.6	461.0	461.7	460.3	459.5
127.5°	493.7	495.8	496.6	495.8	494.4
130°	526.3	530.0	531.4	530.7	529.2
132.5°	559.0	565.5	564.8	564.1	561.9
135°	593.8	598.2	598.9	598.9	596.0
137.5°	626.5	630.9	632.3	633.0	629.4
140°	657.7	661.4	663.5	665.0	661.4
142.5°	688.9	691.8	694.7	695.5	691.8
145°	719.4	722.3	724.5	724.5	722.3
147.5°	747.7	749.9	751.4	753.6	747.7
150°	776.1	775.3	778.2	778.2	776.8
152.5°	799.3	800.7	801.5	803.6	800.7
155°	823.2	823.2	824.0	826.9	823.2
157.5°	845.0	843.6	844.3	847.2	842.1
160°	863.9	861.7	862.4	865.3	861.7
162.5°	880.6	879.1	879.1	882.8	878.4
165°	895.1	893.7	894.4	897.3	892.9
167.5°	908.2	905.3	905.3	909.6	905.3
170°	918.3	915.4	915.4	919.8	914.7
172.5°	925.6	922.7	922.7	927.1	922.7
175°	930.7	927.8	927.8	932.1	927.1
177.5°	934.3	931.4	930.7	935.0	930.0
180°	932.9	932.9	932.9	932.9	932.9

(END OF REPORT)