

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034613

Luminaire Tested: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034613
REPORT IS A COMBINATION OF REPORTS P1004002 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5399.0 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034613

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034613

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	40	38	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	33	31
4	73	62	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5893	5893	5893
5°	5893	5756	5767
10°	5845	5625	5607
15°	5768	5466	5418
20°	5664	5284	5200
25°	5553	5084	4968
30°	5419	4876	4723
35°	5275	4658	4449
40°	5127	4428	4206
45°	4966	4203	3946
50°	4789	3948	3645
55°	4615	3667	3367
60°	4406	3371	3044
65°	4157	3028	2710
70°	3904	2634	2324
75°	3476	2168	1880
80°	2963	1619	1381
85°	2287	959	763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4966 cd/sqm

TEST NUMBER: P1034613

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.6
10°-20°	245.2	4.5
20°-30°	361.9	6.7
30°-40°	422.3	7.8
40°-50°	424.1	7.9
50°-60°	372.3	6.9
60°-70°	277.3	5.1
70°-80°	158.4	2.9
80°-90°	47.2	0.9
90°-100°	33.2	0.6
100°-110°	220.7	4.1
110°-120°	397.4	7.4
120°-130°	510.1	9.4
130°-140°	548.6	10.2
140°-150°	514.9	9.5
150°-160°	416.5	7.7
160°-170°	269.4	5.0
170°-180°	92.9	1.7
0°-30°	693.9	12.9
0°-40°	1116.2	20.7
0°-60°	1912.6	35.4
0°-90°	2395.5	44.4
90°-120°	651.2	12.1
90°-150°	2224.8	41.2
90°-180°	3004.0	55.6
0°-180°	5399.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	918	917	910	916	915	87
15°	875	873	865	869	869	247
25°	795	791	782	783	781	366
35°	686	683	673	670	664	429
45°	562	559	550	541	539	433
55°	428	426	416	409	404	382
65°	289	287	279	273	270	287
75°	154	152	148	146	143	163
85°	40	41	41	40	39	44
90°	1	6	12	15	17	5
95°	41	39	12	15	15	51
105°	213	216	216	216	215	226
115°	400	404	404	402	397	397
125°	569	574	574	571	569	508
135°	710	714	712	711	707	547
145°	823	824	824	825	820	515
155°	906	902	903	905	900	417
165°	956	952	952	957	951	270
175°	978	973	974	980	973	93
180°	978	978	978	978	978	

TEST NUMBER: P1034613

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	919.8	919.8	919.8	919.8	919.8
2.5°	922.7	920.5	913.2	920.5	919.8
5°	918.3	916.9	909.6	916.2	915.4
7.5°	911.8	910.3	902.3	908.9	908.2
10°	902.3	900.9	892.9	898.7	898.0
12.5°	890.7	887.8	880.5	884.9	884.9
15°	875.4	873.2	865.2	868.9	868.9
17.5°	859.4	855.8	847.8	852.1	848.5
20°	838.3	836.8	827.4	832.5	828.8
22.5°	817.2	814.3	805.5	808.5	806.3
25°	794.6	791.0	781.5	783.0	780.8
27.5°	768.4	766.3	756.8	757.5	755.3
30°	743.0	740.8	729.9	728.4	726.2
32.5°	715.3	711.7	702.2	699.3	694.9
35°	686.2	683.3	673.1	669.5	663.6
37.5°	656.4	652.7	643.3	638.2	634.5
40°	625.8	622.2	612.0	605.4	603.3
42.5°	593.1	590.2	580.0	574.1	570.5
45°	561.8	558.9	550.1	541.4	539.2
47.5°	527.6	528.3	517.4	508.7	503.6
50°	494.8	492.6	483.9	474.5	469.4
52.5°	461.4	459.9	450.4	442.4	436.6
55°	427.9	425.7	415.5	409.0	403.9
57.5°	392.2	391.5	382.8	374.0	371.8
60°	358.7	355.8	347.8	340.6	335.5
62.5°	323.8	321.6	315.1	307.1	303.4
65°	288.9	287.4	279.4	272.9	270.0
67.5°	254.7	251.8	246.0	240.1	238.7
70°	222.7	219.0	212.5	208.1	205.2
72.5°	187.7	185.6	181.9	176.8	173.9
75°	153.5	152.1	148.4	146.3	143.4
77.5°	121.5	120.8	118.6	117.2	115.0
80°	91.7	91.7	90.2	89.5	88.0
82.5°	65.5	64.0	64.0	62.6	62.6
85°	40.0	40.8	40.8	40.0	38.6
87.5°	19.6	19.6	18.9	18.9	17.5
90°	0.7	6.5	11.6	15.2	17.4
92.5°	13.8	7.2	11.6	15.2	15.9
95°	41.3	39.1	11.6	15.2	15.2
97.5°	77.6	81.9	13.0	14.5	15.2
100°	121.0	123.2	126.1	18.1	15.2
102.5°	165.3	168.2	169.6	171.1	110.2
105°	213.1	216.0	216.0	216.0	215.3
107.5°	262.4	262.4	263.8	264.6	261.7
110°	310.2	310.2	311.7	309.5	310.2

TEST NUMBER: P1034613

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.2	357.3	358.1	355.2	353.7
115°	400.1	403.7	404.5	401.6	397.2
117.5°	447.2	447.2	450.1	445.8	444.3
120°	490.7	490.0	492.2	490.7	487.1
122.5°	529.1	532.7	533.5	532.0	527.7
125°	569.0	574.1	574.1	571.2	569.0
127.5°	607.4	611.0	610.3	608.9	603.1
130°	642.2	645.8	646.5	644.4	640.7
132.5°	677.0	681.3	679.2	679.2	675.5
135°	709.6	713.9	712.5	711.1	706.7
137.5°	740.0	744.4	742.9	742.9	739.3
140°	769.8	771.2	770.5	771.9	767.6
142.5°	796.6	797.3	798.8	798.8	794.4
145°	822.7	824.1	824.1	824.8	820.5
147.5°	845.9	845.9	846.6	847.3	842.2
150°	867.6	866.2	867.6	869.1	863.3
152.5°	888.6	885.0	886.5	887.9	882.8
155°	906.0	901.7	903.1	905.3	899.5
157.5°	919.8	917.6	917.6	919.8	914.0
160°	934.3	929.9	930.7	933.6	927.8
162.5°	945.9	941.5	942.3	946.6	940.1
165°	956.0	951.7	952.4	956.8	951.0
167.5°	964.0	959.7	960.4	965.5	958.9
170°	970.5	965.5	966.2	972.0	965.5
172.5°	974.9	969.8	971.3	976.3	969.8
175°	977.8	973.4	974.2	980.0	973.4
177.5°	980.0	975.6	976.3	981.4	975.6
180°	977.8	977.8	977.8	977.8	977.8

(END OF REPORT)