

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034156

Luminaire Tested: S124RDIW-B575D1340UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034156
REPORT IS A COMBINATION OF REPORTS P1000564 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D1340UB50-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7414.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034156

CATALOG NUMBER: S124RDIW-B575D1340UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034156

CATALOG NUMBER: S124RDIW-B575D1340UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	32
2	85	78	72	67	76	70	66	61	56	52	50	42	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7937	7937	7937
5°	7937	7701	7702
10°	7870	7459	7370
15°	7762	7156	6977
20°	7620	6811	6530
25°	7444	6439	6093
30°	7271	6059	5603
35°	7080	5674	5123
40°	6853	5260	4630
45°	6641	4849	4142
50°	6400	4400	3647
55°	6139	3940	3136
60°	5848	3451	2630
65°	5569	2890	2144
70°	5171	2301	1639
75°	4660	1674	1146
80°	3895	1028	824
85°	2925	592	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6641 cd/sqm

TEST NUMBER: P1034156

CATALOG NUMBER: S124RDIW-B575D1340UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.2
10°-20°	255.2	3.4
20°-30°	368.4	5.0
30°-40°	417.6	5.6
40°-50°	403.2	5.4
50°-60°	335.2	4.5
60°-70°	231.3	3.1
70°-80°	116.9	1.6
80°-90°	33.1	0.4
90°-100°	55.4	0.7
100°-110°	364.6	4.9
110°-120°	696.3	9.4
120°-130°	883.9	11.9
130°-140°	945.6	12.8
140°-150°	884.2	11.9
150°-160°	713.1	9.6
160°-170°	459.9	6.2
170°-180°	158.5	2.1
0°-30°	715.2	9.6
0°-40°	1132.7	15.3
0°-60°	1871.1	25.2
0°-90°	2252.4	30.4
90°-120°	1116.3	15.1
90°-150°	3830.1	51.7
90°-180°	5162.0	69.6
0°-180°	7414.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	973	973	973	973	973	
5°	972	969	960	967	966	92
15°	926	919	900	899	894	261
25°	837	824	793	780	773	386
35°	724	700	663	637	624	452
45°	590	563	518	482	468	455
55°	447	417	369	330	316	400
65°	304	272	224	192	183	300
75°	162	134	99	82	78	171
85°	40	25	23	22	22	44
90°	4	18	27	35	37	6
95°	69	26	27	35	36	85
105°	376	383	389	400	356	393
115°	701	705	704	706	706	690
125°	986	991	988	992	993	880
135°	1223	1221	1226	1229	1231	942
145°	1410	1414	1414	1415	1417	881
155°	1546	1547	1543	1548	1544	713
165°	1631	1624	1624	1634	1623	461
175°	1668	1661	1662	1673	1658	159
180°	1668	1668	1668	1668	1668	

TEST NUMBER: P1034156

CATALOG NUMBER: S124RDIW-B575D1340UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	973.3	973.3	973.3	973.3	973.3
2.5°	976.3	973.3	965.1	973.3	972.6
5°	971.8	968.9	959.9	967.4	965.9
7.5°	965.1	962.2	951.0	956.2	954.0
10°	954.7	951.0	937.6	940.5	937.6
12.5°	941.3	936.8	920.4	921.9	917.4
15°	925.6	918.9	900.3	898.8	893.6
17.5°	907.8	898.1	876.5	872.7	865.3
20°	886.1	876.5	851.1	845.1	835.5
22.5°	862.3	851.1	823.5	813.8	806.4
25°	837.0	823.5	793.0	780.3	772.9
27.5°	810.9	794.5	762.4	747.5	737.1
30°	783.3	764.7	729.6	711.0	699.1
32.5°	754.2	732.6	696.1	673.7	662.6
35°	723.7	699.8	662.6	637.2	623.8
37.5°	691.6	667.0	626.0	598.5	585.0
40°	657.3	632.7	590.3	559.0	545.5
42.5°	624.5	598.5	553.7	521.7	507.5
45°	590.3	562.7	518.0	481.5	468.0
47.5°	555.2	526.9	480.7	442.7	427.8
50°	519.5	490.4	442.7	405.4	391.3
52.5°	482.9	454.6	405.4	367.4	352.5
55°	447.2	417.4	368.9	330.2	316.0
57.5°	412.1	380.8	333.1	293.6	283.2
60°	374.1	344.3	296.6	257.9	245.9
62.5°	339.8	308.5	259.4	224.3	215.4
65°	304.1	272.0	224.3	192.3	183.3
67.5°	266.8	236.3	191.5	163.2	152.8
70°	231.8	200.5	158.0	133.4	126.0
72.5°	194.5	166.9	127.4	107.3	100.6
75°	161.7	134.2	99.1	82.0	77.5
77.5°	127.4	103.6	73.8	61.9	60.4
80°	94.7	73.0	50.7	48.4	47.7
82.5°	66.3	47.0	36.5	35.0	34.3
85°	40.2	25.3	23.1	21.6	21.6
87.5°	17.1	11.2	10.4	9.7	10.4
90°	3.7	17.5	27.4	34.9	37.4
92.5°	18.7	16.2	26.2	33.7	33.7
95°	68.6	26.2	27.4	34.9	36.2
97.5°	131.0	158.4	27.4	33.7	34.9
100°	204.6	227.1	54.9	33.7	34.9
102.5°	287.0	301.9	316.9	36.2	36.2
105°	375.5	383.0	389.3	400.5	355.6
107.5°	456.6	460.4	469.1	475.3	480.3
110°	539.0	542.7	550.2	552.7	556.4

TEST NUMBER: P1034156

CATALOG NUMBER: S124RDIW-B575D1340UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	618.8	626.3	628.8	627.5	632.5
115°	701.2	704.9	703.7	706.1	706.1
117.5°	774.8	779.8	783.5	782.3	782.3
120°	849.6	854.6	853.4	855.9	853.4
122.5°	919.5	922.0	924.5	925.7	923.2
125°	985.6	990.6	988.1	991.9	993.1
127.5°	1049.2	1050.5	1056.7	1055.5	1054.2
130°	1110.4	1111.6	1115.4	1116.6	1116.6
132.5°	1166.5	1169.0	1174.0	1175.3	1174.0
135°	1222.7	1221.4	1226.4	1228.9	1231.4
137.5°	1272.6	1272.6	1278.8	1281.3	1280.0
140°	1321.2	1323.7	1326.2	1330.0	1331.2
142.5°	1364.9	1369.9	1371.1	1373.6	1373.6
145°	1409.8	1413.5	1413.5	1414.8	1417.3
147.5°	1444.7	1452.2	1451.0	1452.2	1453.5
150°	1483.4	1488.4	1487.2	1487.2	1488.4
152.5°	1515.8	1519.6	1517.1	1519.6	1518.3
155°	1545.8	1547.0	1543.3	1548.3	1544.5
157.5°	1572.0	1572.0	1567.0	1573.2	1567.0
160°	1594.4	1590.7	1589.5	1596.9	1589.5
162.5°	1614.4	1609.4	1608.2	1615.7	1606.9
165°	1630.6	1624.4	1624.4	1634.4	1623.1
167.5°	1644.4	1638.1	1636.9	1648.1	1635.6
170°	1655.6	1648.1	1649.3	1659.3	1646.8
172.5°	1663.1	1655.6	1656.8	1666.8	1653.1
175°	1668.1	1660.6	1661.8	1673.0	1658.1
177.5°	1671.8	1663.1	1665.6	1675.5	1660.6
180°	1668.1	1668.1	1668.1	1668.1	1668.1

(END OF REPORT)