

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034621

Luminaire Tested: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034621
REPORT IS A COMBINATION OF REPORTS P1004058 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7552.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034621

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034621

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	91	87	83	87	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	52	47	44	42	36	34	33
3	79	69	62	56	71	63	57	51	52	47	43	41	38	35	32	29	27
4	72	61	53	47	65	56	49	43	46	41	37	37	33	30	28	26	23
5	66	54	46	40	60	50	42	37	41	35	31	33	29	26	25	23	20
6	61	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	32	26	47	36	29	25	30	25	21	25	21	18	19	16	14
9	48	36	29	23	44	33	26	22	28	22	19	23	19	16	18	15	13
10	45	33	26	21	41	30	24	20	25	20	17	21	17	14	16	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6823	6823	6823
5°	6834	6680	6697
10°	6783	6544	6525
15°	6700	6385	6315
20°	6589	6194	6106
25°	6457	5991	5853
30°	6297	5768	5623
35°	6147	5563	5411
40°	5996	5348	5197
45°	5824	5161	5005
50°	5659	4957	4832
55°	5462	4764	4630
60°	5245	4543	4424
65°	5017	4311	4191
70°	4759	3999	3949
75°	4350	3692	3654
80°	3813	3318	3327
85°	3282	3019	3155

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5824 cd/sqm

TEST NUMBER: P1034621

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.3
10°-20°	286.1	3.8
20°-30°	425.4	5.6
30°-40°	503.8	6.7
40°-50°	520.9	6.9
50°-60°	479.8	6.4
60°-70°	387.9	5.1
70°-80°	259.5	3.4
80°-90°	136.2	1.8
90°-100°	122.5	1.6
100°-110°	368.0	4.9
110°-120°	599.7	7.9
120°-130°	743.0	9.8
130°-140°	785.7	10.4
140°-150°	730.6	9.7
150°-160°	589.5	7.8
160°-170°	381.2	5.0
170°-180°	131.5	1.7
0°-30°	812.3	10.8
0°-40°	1316.1	17.4
0°-60°	2316.7	30.7
0°-90°	3100.3	41.1
90°-120°	1090.2	14.4
90°-150°	3349.5	44.4
90°-180°	4452.0	59.0
0°-180°	7552.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1065	1065	1065	1065	1065	
5°	1065	1063	1056	1064	1063	101
15°	1017	1018	1011	1017	1013	287
25°	924	927	921	925	920	425
35°	800	807	804	807	807	501
45°	659	670	676	683	684	508
55°	506	523	540	551	555	453
65°	349	373	398	413	418	346
75°	192	219	253	274	279	204
85°	57	92	128	151	160	60
90°	18	59	102	131	142	15
95°	72	96	93	121	128	82
105°	311	332	363	384	390	329
115°	573	585	613	628	628	568
125°	810	816	836	849	851	723
135°	1006	1012	1017	1028	1027	776
145°	1165	1166	1166	1173	1171	729
155°	1282	1276	1278	1281	1273	591
165°	1353	1347	1348	1354	1346	382
175°	1384	1378	1379	1387	1378	132
180°	1384	1384	1384	1384	1384	

TEST NUMBER: P1034621

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.9	1064.9	1064.9	1064.9	1064.9
2.5°	1068.1	1066.0	1058.7	1066.0	1064.9
5°	1064.9	1062.9	1055.5	1063.9	1062.9
7.5°	1057.6	1056.6	1049.3	1056.6	1055.5
10°	1047.2	1047.2	1038.8	1046.1	1045.1
12.5°	1032.6	1033.6	1027.4	1032.6	1029.4
15°	1016.9	1018.0	1010.6	1016.9	1012.7
17.5°	997.1	999.2	991.9	997.1	993.9
20°	975.2	977.2	969.9	973.1	973.1
22.5°	950.1	954.3	945.9	950.1	947.0
25°	924.0	927.1	920.9	925.0	919.8
27.5°	895.8	900.0	892.7	895.8	893.7
30°	863.4	869.7	863.4	865.5	864.5
32.5°	834.2	839.4	835.2	837.3	836.3
35°	799.7	807.1	803.9	807.1	807.1
37.5°	766.3	772.6	771.6	775.7	774.7
40°	731.9	740.2	739.2	743.4	745.5
42.5°	694.3	705.8	708.9	714.1	714.1
45°	658.8	670.3	675.5	682.8	683.9
47.5°	622.3	632.7	641.1	651.5	653.6
50°	584.7	596.2	607.6	619.1	622.3
52.5°	545.0	559.6	574.2	586.8	588.8
55°	506.4	523.1	539.8	551.3	555.4
57.5°	466.7	486.5	505.3	517.9	521.0
60°	427.0	447.9	468.8	484.4	487.6
62.5°	388.4	409.3	432.2	450.0	454.2
65°	348.7	372.7	397.8	413.4	417.6
67.5°	312.2	335.1	360.2	379.0	384.2
70°	271.5	295.5	322.6	342.5	348.7
72.5°	231.8	256.8	287.1	309.0	313.2
75°	192.1	219.3	252.7	273.5	278.8
77.5°	153.5	184.8	216.1	239.1	243.3
80°	118.0	149.3	184.8	207.8	211.9
82.5°	85.6	119.0	155.6	177.5	185.8
85°	57.4	91.9	128.4	151.4	159.7
87.5°	36.5	70.0	105.5	129.5	136.8
90°	17.7	59.3	102.0	131.1	141.5
92.5°	34.1	55.2	97.8	125.9	134.3
95°	72.1	96.1	92.6	120.7	128.0
97.5°	122.3	153.5	90.5	114.5	122.8
100°	182.8	207.8	245.3	114.3	116.5
102.5°	244.3	268.3	302.6	325.6	245.7
105°	311.0	331.8	363.1	384.0	390.3
107.5°	379.8	394.4	426.6	448.5	450.7
110°	446.4	458.9	490.2	506.9	515.3

TEST NUMBER: P1034621

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	510.0	522.4	551.7	566.4	571.6
115°	572.6	585.0	613.1	627.8	628.0
117.5°	638.1	643.3	673.6	685.2	690.4
120°	699.7	701.9	728.9	744.6	745.8
122.5°	753.1	759.2	783.2	797.9	798.0
125°	809.5	815.6	836.5	849.1	851.2
127.5°	862.8	866.9	883.6	897.2	895.3
130°	912.0	916.1	931.8	943.3	943.3
132.5°	960.2	966.4	973.7	988.3	987.4
135°	1006.4	1011.5	1016.8	1028.3	1027.3
137.5°	1049.5	1054.5	1056.7	1069.2	1068.3
140°	1090.4	1092.5	1092.6	1106.1	1104.1
142.5°	1128.4	1128.4	1130.5	1139.9	1137.9
145°	1165.3	1166.4	1166.4	1172.6	1170.7
147.5°	1197.2	1197.2	1198.2	1201.3	1196.2
150°	1227.9	1225.9	1227.9	1230.0	1222.8
152.5°	1257.7	1252.6	1254.6	1256.7	1249.5
155°	1282.3	1276.2	1278.2	1281.3	1273.1
157.5°	1301.8	1298.7	1298.7	1301.8	1293.6
160°	1322.3	1316.2	1317.2	1321.3	1313.1
162.5°	1338.7	1332.6	1333.6	1339.8	1330.5
165°	1353.1	1346.9	1348.0	1354.1	1345.9
167.5°	1364.4	1358.2	1359.2	1366.4	1357.2
170°	1373.6	1366.4	1367.5	1375.7	1366.4
172.5°	1379.8	1372.6	1374.6	1381.8	1372.6
175°	1383.9	1377.7	1378.7	1386.9	1377.7
177.5°	1386.9	1380.8	1381.8	1389.0	1380.8
180°	1383.9	1383.9	1383.9	1383.9	1383.9

(END OF REPORT)