

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034169

Luminaire Tested: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034169
REPORT IS A COMBINATION OF REPORTS P1000597 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7866.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034169

CATALOG NUMBER: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1034169

CATALOG NUMBER: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	86	82	84	80	77	74	63	61	59	48	47	45	34	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27
3	78	69	62	56	70	62	56	51	49	45	42	37	35	32	26	25	23
4	71	61	53	48	64	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	21	19	18
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	19	17	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8290	8290	8290
5°	8291	8044	8044
10°	8221	7790	7698
15°	8108	7474	7287
20°	7959	7114	6820
25°	7775	6724	6364
30°	7594	6328	5852
35°	7394	5926	5350
40°	7159	5493	4836
45°	6936	5064	4326
50°	6684	4596	3809
55°	6412	4115	3275
60°	6109	3604	2748
65°	5816	3019	2240
70°	5401	2403	1712
75°	4867	1748	1198
80°	4068	1073	860
85°	3056	618	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6936 cd/sqm

TEST NUMBER: P1034169

CATALOG NUMBER: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	1.2
10°-20°	266.5	3.4
20°-30°	384.8	4.9
30°-40°	436.1	5.5
40°-50°	421.1	5.4
50°-60°	350.1	4.5
60°-70°	241.6	3.1
70°-80°	122.1	1.6
80°-90°	35.2	0.4
90°-100°	129.5	1.6
100°-110°	387.9	4.9
110°-120°	659.0	8.4
120°-130°	869.1	11.0
130°-140°	976.1	12.4
140°-150°	959.4	12.2
150°-160°	806.9	10.3
160°-170°	536.9	6.8
170°-180°	188.0	2.4
0°-30°	747.0	9.5
0°-40°	1183.1	15.0
0°-60°	1954.3	24.8
0°-90°	2353.3	29.9
90°-120°	1176.4	15.0
90°-150°	3981.0	50.6
90°-180°	5513.0	70.1
0°-180°	7866.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1017	1017	1017	1017	1017	
5°	1015	1012	1003	1010	1009	96
15°	967	960	940	939	933	272
25°	874	860	828	815	807	403
35°	756	731	692	666	652	472
45°	616	588	541	503	489	475
55°	467	436	385	345	330	418
65°	318	284	234	201	192	314
75°	169	140	104	86	81	178
85°	42	26	24	23	23	46
90°	5	22	34	43	46	9
95°	92	106	117	121	121	100
105°	358	360	366	370	375	380
115°	670	670	667	665	664	661
125°	976	976	974	971	968	870
135°	1258	1268	1268	1265	1260	974
145°	1529	1535	1537	1535	1530	957
155°	1752	1752	1750	1756	1750	806
165°	1907	1902	1899	1908	1902	538
175°	1984	1976	1974	1985	1974	188
180°	1987	1987	1987	1987	1987	

TEST NUMBER: P1034169

CATALOG NUMBER: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1019.7	1016.6	1008.1	1016.6	1015.8
5°	1015.1	1011.9	1002.6	1010.4	1008.8
7.5°	1008.1	1004.9	993.3	998.7	996.4
10°	997.2	993.3	979.3	982.4	979.3
12.5°	983.1	978.5	961.3	962.9	958.2
15°	966.8	959.8	940.3	938.8	933.3
17.5°	948.1	938.0	915.4	911.5	903.7
20°	925.5	915.4	889.0	882.7	872.6
22.5°	900.6	889.0	860.2	850.0	842.3
25°	874.2	860.2	828.2	815.0	807.2
27.5°	846.9	829.8	796.3	780.8	769.9
30°	818.1	798.7	762.1	742.6	730.2
32.5°	787.8	765.2	727.0	703.7	692.0
35°	755.8	730.9	692.0	665.5	651.5
37.5°	722.4	696.7	653.9	625.1	611.1
40°	686.6	660.9	616.5	583.8	569.8
42.5°	652.3	625.1	578.4	544.9	530.1
45°	616.5	587.7	541.0	502.9	488.8
47.5°	579.9	550.3	502.1	462.4	446.8
50°	542.6	512.2	462.4	423.5	408.7
52.5°	504.4	474.8	423.5	383.8	368.2
55°	467.1	435.9	385.3	344.8	330.1
57.5°	430.5	397.8	348.0	306.7	295.8
60°	390.8	359.6	309.8	269.3	256.9
62.5°	355.0	322.3	270.9	234.3	225.0
65°	317.6	284.1	234.3	200.8	191.5
67.5°	278.7	246.8	200.1	170.5	159.6
70°	242.1	209.4	165.0	139.3	131.6
72.5°	203.2	174.4	133.1	112.1	105.1
75°	168.9	140.1	103.5	85.6	81.0
77.5°	133.1	108.2	77.1	64.6	63.1
80°	98.9	76.3	52.9	50.6	49.8
82.5°	69.3	49.0	38.1	36.6	35.8
85°	42.0	26.5	24.1	22.6	22.6
87.5°	17.9	11.7	10.9	10.1	10.9
90°	4.6	21.5	33.8	43.0	46.1
92.5°	40.0	59.9	67.6	72.2	73.8
95°	92.2	106.0	116.8	121.4	121.4
97.5°	147.5	159.8	172.1	178.2	178.2
100°	215.1	221.3	235.1	238.2	238.2
102.5°	285.8	287.3	299.6	304.2	305.8
105°	358.0	359.6	365.7	370.3	374.9
107.5°	433.3	434.9	436.4	442.5	441.0
110°	510.2	513.2	511.7	508.6	513.2

TEST NUMBER: P1034169

CATALOG NUMBER: S124RDIW-B575D1560UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.1	590.1	587.0	587.0	587.0
115°	670.0	670.0	666.9	665.4	663.8
117.5°	745.3	745.3	743.7	739.1	734.5
120°	820.6	826.7	822.1	814.4	817.5
122.5°	898.9	900.5	898.9	894.3	886.6
125°	975.7	975.7	974.2	971.1	968.1
127.5°	1044.9	1049.5	1046.4	1043.4	1041.8
130°	1118.7	1123.3	1123.3	1120.2	1114.0
132.5°	1193.9	1197.0	1195.5	1192.4	1190.9
135°	1258.5	1267.7	1267.7	1264.6	1260.0
137.5°	1330.7	1335.3	1338.4	1333.8	1335.3
140°	1402.9	1406.0	1406.0	1404.5	1402.9
142.5°	1469.0	1472.1	1470.5	1470.5	1470.5
145°	1528.9	1535.1	1536.6	1535.1	1530.5
147.5°	1590.4	1598.1	1596.5	1595.0	1593.5
150°	1645.7	1651.9	1651.9	1651.9	1650.3
152.5°	1698.0	1701.0	1702.6	1707.2	1702.6
155°	1751.7	1751.7	1750.2	1756.3	1750.2
157.5°	1797.8	1794.8	1794.8	1799.4	1794.8
160°	1837.8	1836.3	1834.7	1839.3	1831.6
162.5°	1874.7	1870.1	1868.5	1877.7	1870.1
165°	1906.9	1902.3	1899.3	1908.5	1902.3
167.5°	1933.1	1926.9	1926.9	1936.1	1926.9
170°	1954.6	1946.9	1948.4	1957.6	1946.9
172.5°	1969.9	1963.8	1963.8	1974.5	1963.8
175°	1983.8	1976.1	1974.5	1985.3	1974.5
177.5°	1989.9	1982.2	1982.2	1993.0	1980.7
180°	1986.8	1986.8	1986.8	1986.8	1986.8

(END OF REPORT)