

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034624

Luminaire Tested: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034624
REPORT IS A COMBINATION OF REPORTS P1004062 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6849.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034624

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034624

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55			48
1	97	93	89	86	89	86	82	79	72	70	67	60	58	56	48	47	46			41
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39			34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33			29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28			25
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25			21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22			19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19			17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17			15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16			13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	16	20	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8131	8131	8131
5°	8131	7942	7957
10°	8064	7760	7735
15°	7958	7542	7475
20°	7815	7289	7175
25°	7662	7014	6855
30°	7476	6727	6517
35°	7278	6427	6138
40°	7073	6109	5802
45°	6852	5799	5445
50°	6608	5448	5028
55°	6367	5060	4645
60°	6080	4651	4199
65°	5735	4178	3738
70°	5385	3635	3206
75°	4796	2992	2593
80°	4088	2235	1907
85°	3156	1321	1051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6852 cd/sqm

TEST NUMBER: P1034624

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.7
10°-20°	338.2	4.9
20°-30°	499.4	7.3
30°-40°	582.6	8.5
40°-50°	585.2	8.5
50°-60°	513.6	7.5
60°-70°	382.6	5.6
70°-80°	218.5	3.2
80°-90°	65.1	0.9
90°-100°	84.4	1.2
100°-110°	250.9	3.7
110°-120°	425.4	6.2
120°-130°	560.1	8.2
130°-140°	627.6	9.2
140°-150°	615.2	9.0
150°-160°	516.7	7.5
160°-170°	343.5	5.0
170°-180°	120.2	1.8
0°-30°	957.4	14.0
0°-40°	1540.0	22.5
0°-60°	2638.8	38.5
0°-90°	3305.0	48.3
90°-120°	760.7	11.1
90°-150°	2563.6	37.4
90°-180°	3544.0	51.7
0°-180°	6849.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1267	1265	1255	1264	1263	120
15°	1208	1205	1194	1199	1199	341
25°	1096	1091	1078	1080	1077	504
35°	947	943	929	924	916	592
45°	775	771	759	747	744	597
55°	590	587	573	564	557	527
65°	399	397	386	376	372	395
75°	212	210	205	202	198	226
85°	55	56	56	55	53	60
90°	1	9	16	21	24	8
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	628	626	626	557
135°	808	814	815	815	811	623
145°	979	983	986	986	983	612
155°	1121	1121	1122	1126	1121	516
165°	1218	1216	1218	1221	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1034624

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.0	1269.0	1269.0	1269.0	1269.0
2.5°	1273.1	1270.0	1260.0	1270.0	1269.0
5°	1267.0	1265.0	1255.0	1264.0	1263.0
7.5°	1258.0	1256.0	1244.9	1254.0	1253.0
10°	1244.9	1242.9	1231.9	1239.9	1238.9
12.5°	1228.9	1224.9	1214.8	1220.8	1220.8
15°	1207.8	1204.8	1193.7	1198.8	1198.8
17.5°	1185.7	1180.7	1169.6	1175.7	1170.6
20°	1156.6	1154.6	1141.5	1148.6	1143.5
22.5°	1127.5	1123.5	1111.4	1115.4	1112.4
25°	1096.4	1091.3	1078.3	1080.3	1077.3
27.5°	1060.2	1057.2	1044.1	1045.2	1042.1
30°	1025.1	1022.1	1007.0	1005.0	1002.0
32.5°	986.9	981.9	968.8	964.8	958.8
35°	946.8	942.7	928.7	923.7	915.6
37.5°	905.6	900.6	887.5	880.5	875.5
40°	863.4	858.4	844.4	835.3	832.3
42.5°	818.2	814.2	800.2	792.1	787.1
45°	775.1	771.1	759.0	747.0	744.0
47.5°	727.9	728.9	713.8	701.8	694.8
50°	682.7	679.7	667.7	654.6	647.6
52.5°	636.5	634.5	621.5	610.4	602.4
55°	590.3	587.3	573.3	564.2	557.2
57.5°	541.1	540.1	528.1	516.0	513.0
60°	495.0	490.9	479.9	469.9	462.8
62.5°	446.8	443.8	434.7	423.7	418.7
65°	398.6	396.6	385.5	376.5	372.5
67.5°	351.4	347.4	339.3	331.3	329.3
70°	307.2	302.2	293.2	287.1	283.1
72.5°	259.0	256.0	251.0	244.0	240.0
75°	211.8	209.8	204.8	201.8	197.8
77.5°	167.7	166.7	163.6	161.6	158.6
80°	126.5	126.5	124.5	123.5	121.5
82.5°	90.4	88.4	88.4	86.3	86.3
85°	55.2	56.2	56.2	55.2	53.2
87.5°	27.1	27.1	26.1	26.1	24.1
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.6	34.6	43.5	50.4	52.4
95°	64.2	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.6	119.6	120.6
100°	138.3	138.3	151.2	160.1	162.1
102.5°	180.8	185.8	190.7	200.6	203.6
105°	225.3	230.3	236.2	242.1	245.1
107.5°	273.7	278.7	283.6	286.6	286.6
110°	324.1	329.1	332.0	335.0	334.0

TEST NUMBER: P1034624

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.5	377.5	381.4	382.4	380.5
115°	425.9	429.9	431.8	430.9	429.9
117.5°	477.3	478.3	480.3	481.3	477.3
120°	524.7	529.7	530.7	530.7	526.7
122.5°	576.1	577.1	580.1	579.1	576.1
125°	621.6	627.5	628.5	626.5	625.5
127.5°	672.0	674.9	675.9	674.9	673.0
130°	716.4	721.4	723.4	722.4	720.4
132.5°	760.9	769.8	768.8	767.8	764.9
135°	808.4	814.3	815.3	815.3	811.3
137.5°	852.8	858.7	860.7	861.7	856.8
140°	895.3	900.3	903.2	905.2	900.3
142.5°	937.8	941.8	945.7	946.7	941.8
145°	979.3	983.3	986.2	986.2	983.3
147.5°	1017.8	1020.8	1022.8	1025.8	1017.8
150°	1056.4	1055.4	1059.4	1059.4	1057.4
152.5°	1088.0	1090.0	1091.0	1093.9	1090.0
155°	1120.6	1120.6	1121.6	1125.6	1120.6
157.5°	1150.3	1148.3	1149.3	1153.2	1146.3
160°	1176.0	1173.0	1174.0	1177.9	1173.0
162.5°	1198.7	1196.7	1196.7	1201.7	1195.7
165°	1218.5	1216.5	1217.5	1221.4	1215.5
167.5°	1236.2	1232.3	1232.3	1238.2	1232.3
170°	1250.1	1246.1	1246.1	1252.1	1245.1
172.5°	1260.0	1256.0	1256.0	1261.9	1256.0
175°	1266.9	1262.9	1262.9	1268.9	1261.9
177.5°	1271.8	1267.9	1266.9	1272.8	1265.9
180°	1269.8	1269.8	1269.8	1269.8	1269.8

(END OF REPORT)