Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034201

Luminaire Tested: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1034201
	REPORT IS A COMBINATION OF REPORTS P1000676 AND P1007351
Test Lab:	INNOVATION CENTER
Issue Date:	5/7/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	NEO-RAY
Catalog Number:	S124RDIW-B575D770UB30-4F0-XX-W2A-A1
Description:	Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5142.0 lumens
Efficiency:	N/A
Efficacy:	108.9 lumens/watt
Spacing Criteria (0/90/45):	1.22 / 1.27 / 1.38
Luminous Opening:	Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type:	General Diffuse

Input Watts (W):	47.2
Input Voltage (V):	
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	52	44	38	58	48	41	36	41	36	32	35	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7842	7842	7842	7842
5°	7842	8861	7855	6773
10°	7800	10214	7794	5890
15°	7708	11496	7708	4932
20°	7611	12465	7570	4342
25°	7491	12517	7457	3922
30°	7365	10644	7308	3633
35°	7187	8031	7096	3417
40°	6989	5820	6851	3249
45°	6661	4423	6495	3100
50°	6272	3575	6100	2882
55°	5850	2960	5660	2591
60°	5427	2503	5185	2155
65°	4895	2040	4739	1713
70°	4408	1654	4201	1391
75°	3864	1192	3596	1020
80°	3187	789	2900	750
85°	2314	407	1914	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°
Vertical Angle: 45°
Luminance: 9817 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	1.8
10°-20°	281.2	5.5
20°-30°	440.5	8.6
30°-40°	489.1	9.5
40°-50°	433.5	8.4
50°-60°	337.8	6.6
60°-70°	221.0	4.3
70°-80°	108.4	2.1
80°-90°	28.5	0.6
90°-100°	63.6	1.2
100°-110°	190.6	3.7
110°-120°	323.8	6.3
120°-130°	427.1	8.3
130°-140°	479.7	9.3
140°-150°	471.4	9.2
150°-160°	396.5	7.7
160°-170°	263.8	5.1
170°-180°	92.4	1.8
0°-30°	814.8	15.8
0°-40°	1304.0	25.4
0°-60°	2075.2	40.4
0°-90°	2433.1	47.3
90°-120°	578.0	11.2
90°-150°	1956.2	38.0
90°-180°	2709.0	52.7
0°-180°	5142.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	960	1111	962	849	960	91
15°	919	1472	919	632	919	259
25°	842	1588	838	498	842	388
35°	735	978	725	416	735	459
45°	592	500	577	350	592	457
55°	426	298	412	261	426	381
65°	267	174	259	146	267	267
75°	134	81	125	69	134	142
85°	32	19	26	19	32	36
90°	2	23	2	23	2	5
95°	45	60	45	60	45	49
105°	176	184	176	184	176	187
115°	329	326	329	326	329	325
125°	480	476	480	476	480	427
135°	618	619	618	619	618	478
145°	751	752	751	752	751	470
155°	861	860	861	860	861	396
165°	937	935	937	935	937	264
175°	975	970	975	970	975	93
180°	976	976	976	976	976	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	963.2	971.7	976.4	980.3	988.0	991.1	997.3	998.9	1005.1	1004.3	1002.0
5°	960.1	974.8	985.7	997.3	1011.3	1019.0	1027.5	1039.9	1046.1	1054.7	1060.1
7.5°	954.7	974.8	992.7	1010.5	1033.0	1045.4	1056.2	1075.6	1091.9	1105.8	1121.3
10°	946.2	971.7	998.1	1022.1	1053.1	1067.8	1084.1	1112.8	1135.3	1154.6	1179.4
12.5°	933.0	968.6	998.1	1030.6	1070.2	1090.3	1112.0	1146.1	1172.5	1204.2	1235.2
15°	919.1	958.6	997.3	1039.9	1084.9	1108.1	1129.8	1175.6	1215.8	1252.3	1286.4
17.5°	903.6	947.0	989.6	1036.8	1091.1	1119.8	1145.3	1200.3	1244.5	1291.8	1325.9
20°	885.0	932.2	981.0	1033.7	1095.0	1126.7	1155.4	1218.2	1267.0	1318.1	1360.8
22.5°	*864.8*	*916.0*	*969.4*	*1026.8*	*1090.3*	*1125.2*	*1158.5*	*1225.9*	*1282.5*	*1329.8*	*1387.1*
25°	842.3	896.6	951.6	1012.0	1083.3	1121.3	1155.4	1222.0	1282.5	1344.5	1400.3
27.5°	819.1	874.9	932.2	995.8	1068.6	1105.8	1144.6	1208.9	1279.4	1346.8	1403.4
30°	793.5	847.8	908.2	968.6	1046.1	1083.3	1122.9	1192.6	1269.3	1336.7	1398.0
32.5°	765.6	821.4	878.8	941.5	1017.5	1057.8	1094.2	1173.2	1251.5	1318.1	1375.5
35°	734.6	787.3	841.6	905.9	981.0	1017.5	1060.9	1143.0	1222.0	1292.6	1329.8
37.5°	701.3	751.7	802.0	865.6	937.7	981.8	1024.4	1107.4	1191.1	1238.3	1257.7
40°	670.3	714.5	758.6	819.9	892.7	938.4	981.8	1067.8	1141.5	1177.9	1163.2
42.5°	630.8	676.5	716.0	772.6	846.2	888.8	933.0	1022.1	1081.8	1096.5	1060.1
45°	592.0	630.0	668.0	723.0	800.5	836.9	884.2	967.1	1016.7	1003.5	950.1
47.5°	554.1	585.1	620.7	674.2	743.9	787.3	831.5	903.6	938.4	919.8	845.4
50°	509.1	540.1	577.3	623.8	691.2	733.1	767.9	834.6	860.9	815.2	725.3
52.5°	466.5	493.6	525.4	568.8	633.1	671.1	709.1	766.4	774.9	722.2	627.7
55°	426.2	447.9	481.2	516.1	575.0	615.3	641.6	690.5	688.1	622.3	540.9
57.5°	384.4	404.5	427.0	463.4	519.2	549.4	578.1	620.7	598.2	542.4	461.9
60°	347.2	358.8	381.3	416.1	463.4	489.7	512.2	535.5	516.1	455.7	393.7
62.5°	306.1	319.3	335.5	363.4	405.3	430.1	446.4	456.4	436.3	389.8	333.2
65°	267.3	279.0	296.0	320.8	352.6	371.2	379.7	386.7	375.8	323.1	278.2
67.5°	232.5	240.2	255.7	272.0	306.1	310.7	322.4	325.5	303.8	263.5	227.8
70°	197.6	205.4	212.3	231.7	247.2	255.7	258.0	258.0	236.4	210.0	180.6
72.5°	165.1	169.7	176.7	189.9	198.4	204.6	207.7	203.8	183.7	162.0	140.3
75°	134.1	136.4	142.6	151.1	158.1	155.8	155.0	150.3	135.6	120.1	107.7
77.5°	103.1	104.6	111.6	113.9	113.9	116.2	113.1	108.5	96.1	84.5	79.0
80°	77.5	79.8	80.6	82.1	80.6	80.6	78.3	70.5	64.3	58.9	55.0
82.5°	53.5	55.0	55.8	53.5	55.0	52.7	48.8	43.4	39.5	38.7	37.2
85°	31.8	32.5	31.8	31.8	29.4	28.7	25.6	24.8	23.2	23.2	22.5
87.5°	15.5	14.7	13.2	11.6	11.6	10.8	11.6	10.1	11.6	10.8	10.1
90°	2.3	4.1	6.0	7.8	9.7	10.6	11.3	12.6	13.9	15.3	16.6
92.5°	19.6	21.8	24.0	26.1	28.3	29.4	29.8	30.7	31.5	32.4	33.2
95°	45.3	46.8	48.3	49.8	51.3	52.1	52.7	53.9	55.0	56.2	57.4
97.5°	72.5	73.8	75.2	76.5	77.8	78.5	79.2	80.5	81.9	83.2	84.6
100°	105.7	106.4	107.0	107.7	108.4	108.7	109.5	111.0	112.5	114.0	115.5
102.5°	140.4	140.6	140.8	140.9	141.1	141.2	141.9	143.2	144.5	145.9	147.2
105°	175.9	176.1	176.3	176.4	176.6	176.7	177.0	177.7	178.4	179.0	179.7
107.5°	212.9	213.1	213.3	213.4	213.6	213.7	213.8	213.9	214.1	214.2	214.4
110°	250.7	251.0	251.4	251.7	252.0	252.2	252.1	251.9	251.8	251.6	251.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	289.9	289.9	289.9	289.9	289.9	289.9	289.7	289.4	289.1	288.7	288.4
115°	329.2	329.2	329.2	329.2	329.2	329.2	329.0	328.7	328.4	328.0	327.7
117.5°	366.2	366.2	366.2	366.2	366.2	366.2	366.1	366.0	365.8	365.7	365.5
120°	403.2	403.9	404.5	405.2	405.9	406.2	406.0	405.5	405.0	404.5	404.0
122.5°	441.7	441.9	442.1	442.2	442.4	442.5	442.4	442.2	442.1	441.9	441.7
125°	479.5	479.5	479.5	479.5	479.5	479.5	479.4	479.2	479.1	478.9	478.7
127.5°	513.5	514.0	514.5	515.0	515.5	515.7	515.5	515.2	514.9	514.5	514.2
130°	549.7	550.2	550.7	551.2	551.7	552.0	552.0	552.0	552.0	552.0	552.0
132.5°	586.7	587.0	587.4	587.7	588.0	588.2	588.1	587.9	587.8	587.6	587.4
135°	618.4	619.4	620.4	621.4	622.4	622.9	622.9	622.9	622.9	622.9	622.9
137.5°	653.9	654.4	654.9	655.4	655.9	656.2	656.4	656.7	657.0	657.4	657.7
140°	689.4	689.7	690.1	690.4	690.7	690.9	690.9	690.9	690.9	690.9	690.9
142.5°	721.9	722.2	722.6	722.9	723.2	723.4	723.3	723.1	723.0	722.8	722.6
145°	751.3	752.0	752.6	753.3	754.0	754.3	754.4	754.6	754.7	754.9	755.1
147.5°	781.5	782.3	783.2	784.0	784.9	785.3	785.2	785.0	784.9	784.7	784.5
150°	808.7	809.4	810.0	810.7	811.4	811.7	811.7	811.7	811.7	811.7	811.7
152.5°	834.4	834.7	835.1	835.4	835.7	835.9	836.0	836.1	836.3	836.4	836.6
155°	860.8	860.8	860.8	860.8	860.8	860.8	860.7	860.5	860.4	860.2	860.0
157.5°	883.4	883.1	882.7	882.4	882.1	881.9	881.9	881.9	881.9	881.9	881.9
160°	903.1	902.9	902.7	902.6	902.4	902.3	902.2	902.1	901.9	901.8	901.6
162.5°	921.2	920.7	920.2	919.7	919.2	918.9	918.8	918.7	918.5	918.4	918.2
165°	937.1	936.6	936.1	935.6	935.1	934.8	934.6	934.3	934.0	933.6	933.3
167.5°	949.9	949.2	948.6	947.9	947.2	946.9	946.9	946.9	946.9	946.9	946.9
170°	960.5	959.7	958.8	958.0	957.1	956.7	956.8	956.9	957.1	957.2	957.4
172.5°	968.0	967.3	966.7	966.0	965.3	965.0	965.0	965.0	965.0	965.0	965.0
175°	974.8	974.0	973.1	972.3	971.4	971.0	970.9	970.8	970.6	970.5	970.3
177.5°	977.8	977.0	976.1	975.3	974.4	974.0	974.0	974.0	974.0	974.0	974.0
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	*961.7*	961.7	961.7
2.5°	1008.2	1016.7	1017.5	1025.2	1022.9	1019.0	1026.0	1021.3	*1030.6*	1027.5	1031.4
5°	1067.1	1078.7	1088.8	1095.0	1105.8	1103.5	1115.1	1111.2	*1119.8*	1111.2	1122.1
7.5°	1136.0	1155.4	1165.5	1181.8	1186.4	1187.2	1201.1	1204.2	*1209.6*	1204.2	1210.4
10°	1203.4	1226.7	1249.9	1263.1	1271.6	1283.3	1295.7	1301.1	*1305.0*	1299.5	1303.4
12.5°	1264.7	1301.1	1326.7	1353.0	1359.2	1369.3	1382.5	1380.9	*1396.4*	1393.3	1400.3
15°	1321.2	1361.5	1392.5	1413.5	1430.5	1439.0	1463.8	1465.4	*1464.6*	1472.3	1467.7
17.5°	1371.6	1405.7	1449.9	1477.0	1497.9	1497.9	1511.9	1540.5	*1538.2*	1537.4	1542.1
20°	1412.7	1451.4	1492.5	1538.2	1555.3	1558.4	1577.7	1592.5	*1594.8*	1594.8	1594.8
22.5°	*1443.7*	*1489.4*	*1533.6*	*1566.1*	*1579.3*	*1590.1*	*1607.2*	*1616.5*	*1619.6*	*1618.0*	*1619.6*
25°	1459.2	1502.6	1547.5	1577.0	1584.7	1590.9	1592.5	1597.9	*1597.1*	1587.8	1593.2
27.5°	1462.3	1504.1	1533.6	1541.3	1537.4	1533.6	1508.8	1511.1	*1504.1*	1490.2	1495.6
30°	1448.3	1470.8	1470.0	1446.0	1439.0	1422.8	1400.3	1367.0	*1339.8*	1328.2	1332.1
32.5°	1398.0	1398.0	1370.1	1315.8	1291.8	1262.3	1222.0	1191.8	*1156.2*	1148.4	1163.2
35°	1328.2	1288.7	1237.5	1166.3	1129.8	1108.1	1038.4	1016.7	*986.5*	977.9	984.9
37.5°	1219.7	1153.9	1079.5	1012.8	981.8	943.1	881.9	850.9	*829.2*	814.4	821.4
40°	1098.1	1018.2	940.8	858.6	824.5	792.7	747.0	719.1	*684.3*	685.8	688.1
42.5°	981.8	888.1	801.3	725.3	692.8	666.4	634.7	600.6	*588.2*	584.3	580.4
45°	858.6	758.6	677.3	620.7	591.3	566.5	537.0	517.6	*502.9*	499.8	503.7
47.5°	742.4	657.9	580.4	527.7	503.7	491.3	468.1	450.2	*440.9*	433.2	437.8
50°	637.0	557.9	495.9	451.8	434.7	426.2	404.5	395.2	*385.9*	383.6	382.8
52.5°	550.2	482.8	429.3	393.7	380.5	375.8	359.6	346.4	*338.6*	341.0	342.5
55°	471.2	413.8	372.0	343.3	332.4	327.0	315.4	306.1	*300.7*	298.3	299.9
57.5°	401.4	351.8	321.6	298.3	289.8	287.5	275.1	272.0	*268.1*	265.8	265.8
60°	337.9	303.0	275.1	261.9	252.6	250.3	241.0	237.1	*236.4*	234.0	232.5
62.5°	284.4	255.7	236.4	222.4	218.5	217.8	211.6	206.9	*204.6*	203.0	203.0
65°	237.9	217.0	200.7	190.6	187.5	186.0	179.0	177.5	*175.9*	174.4	173.6
67.5°	198.4	179.8	168.2	161.2	157.3	158.1	154.2	151.1	*151.1*	150.3	149.6
70°	160.4	148.8	138.7	134.8	133.3	131.7	130.2	127.9	*127.1*	127.1	127.1
72.5°	126.3	118.6	113.1	110.8	109.3	107.7	106.2	106.2	*106.2*	105.4	105.4
75°	96.9	93.8	89.9	87.6	87.6	89.1	86.8	84.5	*82.1*	80.6	81.4
77.5°	72.8	71.3	69.0	65.1	65.9	64.3	64.3	62.8	*63.5*	63.5	62.0
80°	53.5	51.1	50.4	48.0	48.8	48.0	47.3	47.3	*45.7*	45.7	45.7
82.5°	37.2	34.9	34.9	34.1	33.3	33.3	32.5	32.5	*33.3*	31.8	31.8
85°	22.5	21.7	21.7	20.1	20.1	20.1	20.1	20.9	*20.1*	19.4	19.4
87.5°	10.1	10.8	10.1	9.3	9.3	9.3	8.5	8.5	*7.7*	8.5	8.5
90°	17.6	18.6	19.6	20.6	21.1	21.3	21.6	22.0	*22.3*	22.7	22.3
92.5°	33.7	34.2	34.7	35.2	35.5	35.6	35.7	35.9	*36.0*	36.2	36.0
95°	57.9	58.4	58.9	59.4	59.7	59.7	59.7	59.7	*59.7*	59.7	59.7
97.5°	85.3	85.9	86.6	87.3	87.6	87.6	87.6	87.6	*87.6*	87.6	87.6
100°	115.8	116.2	116.5	116.8	117.0	117.0	117.0	117.0	*117.0*	117.0	117.0
102.5°	147.7	148.2	148.7	149.2	149.5	149.6	149.8	149.9	*150.1*	150.3	150.1
105°	180.2	180.7	181.2	181.7	182.0	182.2	182.7	183.2	*183.7*	184.2	183.7
107.5°	215.1	215.8	216.5	217.2	217.5	217.4	217.2	217.1	*216.9*	216.7	216.9
110°	251.1	250.7	250.4	250.1	249.9	250.2	250.7	251.2	*251.7*	252.2	251.7

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	*288.4*	288.4	288.4
115°	327.5	327.3	327.2	327.0	326.9	326.8	326.7	326.5	*326.4*	326.2	326.4
117.5°	365.0	364.5	364.0	363.5	363.2	362.9	362.4	361.9	*361.4*	360.9	361.4
120°	403.2	402.3	401.5	400.6	400.2	400.4	400.7	401.0	*401.4*	401.7	401.4
122.5°	441.2	440.7	440.2	439.7	439.5	439.1	438.2	437.4	*436.5*	435.7	436.5
125°	478.4	478.0	477.7	477.4	477.2	477.0	476.7	476.4	*476.0*	475.7	476.0
127.5°	513.9	513.5	513.2	512.9	512.7	512.6	512.4	512.3	*512.1*	511.9	512.1
130°	551.7	551.3	551.0	550.7	550.5	550.2	549.5	548.8	*548.1*	547.4	548.1
132.5°	587.1	586.7	586.4	586.1	585.9	585.8	585.7	585.5	*585.4*	585.2	585.4
135°	622.6	622.2	621.9	621.6	621.4	621.2	620.7	620.2	*619.7*	619.2	619.7
137.5°	657.2	656.7	656.2	655.7	655.4	655.5	655.7	655.8	*656.0*	656.2	656.0
140°	690.7	690.5	690.4	690.2	690.1	690.0	689.9	689.7	*689.6*	689.4	689.6
142.5°	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	*722.6*	722.6	722.6
145°	754.9	754.7	754.6	754.4	754.3	754.1	753.6	753.1	*752.6*	752.1	752.6
147.5°	784.3	784.2	784.0	783.9	783.8	783.7	783.5	783.4	*783.2*	783.0	783.2
150°	811.7	811.7	811.7	811.7	811.7	811.6	811.5	811.3	*811.2*	811.0	811.2
152.5°	837.1	837.6	838.1	838.6	838.9	838.6	838.1	837.6	*837.1*	836.6	837.1
155°	860.7	861.4	862.1	862.8	863.1	862.8	862.1	861.4	*860.7*	860.0	860.7
157.5°	882.4	882.9	883.4	883.9	884.2	883.9	883.4	882.9	*882.4*	881.9	882.4
160°	902.1	902.6	903.1	903.6	903.8	903.4	902.6	901.7	*900.9*	900.1	900.9
162.5°	919.2	920.2	921.2	922.2	922.7	922.3	921.4	920.6	*919.7*	918.9	919.7
165°	934.3	935.3	936.3	937.3	937.8	937.5	936.8	936.1	*935.5*	934.8	935.5
167.5°	947.9	948.9	949.9	950.9	951.4	950.9	949.9	948.9	*947.9*	946.9	947.9
170°	958.4	959.4	960.5	961.5	962.0	961.4	960.2	959.1	*957.9*	956.7	957.9
172.5°	966.2	967.4	968.5	969.7	970.3	969.7	968.5	967.4	*966.2*	965.0	966.2
175°	971.5	972.7	973.8	975.0	975.6	975.0	973.8	972.7	*971.5*	970.3	971.5
177.5°	975.2	976.4	977.5	978.7	979.3	978.6	977.3	976.0	*974.6*	973.3	974.6
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	*976.3*	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	1033.7	1028.3	1027.5	1027.5	1019.0	1023.7	1014.4	1004.3	999.6	999.6	991.1
5°	1119.8	1114.3	1108.9	1100.4	1100.4	1095.7	1081.0	1066.3	1055.4	1046.1	1036.1
7.5°	1208.1	1202.7	1187.2	1178.7	1183.3	1174.0	1154.6	1129.8	1111.2	1096.5	1075.6
10°	1304.2	1289.5	1281.7	1277.1	1260.8	1250.7	1228.2	1191.8	1168.6	1149.2	1122.1
12.5°	1382.5	1387.1	1357.7	1360.0	1343.7	1329.8	1294.9	1260.0	1225.1	1198.0	1157.7
15°	1466.9	1453.0	1435.1	1421.2	1415.8	1398.7	1369.3	1322.8	1284.8	1242.2	1196.5
17.5°	1533.6	1522.7	1505.7	1492.5	1480.9	1439.8	1415.0	1373.9	1322.0	1280.2	1224.4
20°	1590.1	1580.1	1556.0	1547.5	1526.6	1497.1	1461.5	1398.0	1351.5	1305.7	1251.5
22.5°	*1614.2*	*1604.1*	*1583.2*	*1572.3*	*1559.1*	*1530.5*	*1496.4*	*1435.9*	*1378.6*	*1321.2*	*1263.9*
25°	1594.0	1594.0	1583.9	1580.1	1568.4	1542.9	1508.0	1456.8	1395.6	1333.6	1265.4
27.5°	1496.4	1515.7	1522.7	1526.6	1526.6	1527.4	1503.3	1453.7	1394.1	1333.6	1262.3
30°	1355.3	1387.9	1416.6	1425.1	1439.8	1456.1	1466.1	1442.1	1388.7	1325.1	1253.8
32.5°	1177.9	1219.7	1273.2	1286.4	1306.5	1355.3	1382.5	1392.5	1363.1	1307.3	1231.3
35°	1001.2	1053.9	1086.4	1126.7	1145.3	1217.4	1277.8	1314.3	1307.3	1274.0	1205.0
37.5°	847.0	877.2	916.7	959.3	996.5	1065.5	1140.7	1211.2	1239.9	1223.6	1171.7
40°	699.0	734.6	781.9	816.8	842.3	911.3	1004.3	1081.0	1143.8	1153.9	1122.1
42.5°	594.4	630.0	658.7	696.7	716.8	783.4	865.6	961.7	1036.1	1075.6	1061.6
45°	513.8	535.5	558.7	580.4	605.2	664.1	740.0	845.4	929.1	984.9	990.3
47.5°	443.3	462.6	482.8	502.9	516.9	562.6	632.3	718.3	809.8	886.5	916.7
50°	393.7	403.0	417.7	429.3	445.6	485.1	540.9	615.3	712.2	795.1	834.6
52.5°	344.8	356.5	368.1	378.2	389.0	416.9	468.1	532.4	616.1	701.3	750.1
55°	303.8	313.1	323.9	330.9	337.1	361.9	400.6	450.2	522.3	602.9	663.3
57.5°	270.4	274.3	283.6	287.5	294.5	314.6	342.5	386.7	444.8	523.1	572.7
60°	234.0	241.8	248.7	251.8	257.3	271.2	290.6	331.7	382.0	439.4	495.9
62.5°	204.6	207.7	213.1	217.0	220.9	235.6	251.8	282.8	320.8	368.9	420.8
65°	177.5	179.0	182.1	187.5	189.9	200.7	210.0	232.5	268.1	304.5	356.5
67.5°	149.6	151.1	155.0	158.1	160.4	167.4	177.5	193.7	213.1	253.4	282.1
70°	127.9	127.9	130.2	131.7	134.1	137.2	142.6	155.0	172.8	198.4	224.7
72.5°	106.9	106.9	106.9	109.3	109.3	111.6	114.7	123.2	135.6	155.8	172.8
75°	82.9	83.7	85.2	85.2	86.0	89.1	91.4	93.8	100.0	113.1	128.6
77.5°	62.8	64.3	65.1	63.5	65.1	65.1	68.2	71.3	74.4	78.3	89.9
80°	46.5	47.3	45.7	46.5	46.5	48.0	49.6	48.8	50.4	55.0	58.1
82.5°	31.0	31.8	31.8	31.8	31.8	34.1	34.1	33.3	34.1	34.9	35.6
85°	19.4	18.6	18.6	19.4	18.6	18.6	19.4	20.1	19.4	20.1	20.9
87.5°	8.5	8.5	8.5	8.5	7.7	7.7	8.5	7.7	8.5	7.7	7.0
90°	22.0	21.6	21.3	21.1	20.6	19.6	18.6	17.6	16.6	15.3	13.9
92.5°	35.9	35.7	35.6	35.5	35.2	34.7	34.2	33.7	33.2	32.4	31.5
95°	59.7	59.7	59.7	59.7	59.4	58.9	58.4	57.9	57.4	56.2	55.0
97.5°	87.6	87.6	87.6	87.6	87.3	86.6	85.9	85.3	84.6	83.2	81.9
100°	117.0	117.0	117.0	117.0	116.8	116.5	116.2	115.8	115.5	114.0	112.5
102.5°	149.9	149.8	149.6	149.5	149.2	148.7	148.2	147.7	147.2	145.9	144.5
105°	183.2	182.7	182.2	182.0	181.7	181.2	180.7	180.2	179.7	179.0	178.4
107.5°	217.1	217.2	217.4	217.5	217.2	216.5	215.8	215.1	214.4	214.2	214.1
110°	251.2	250.7	250.2	249.9	250.1	250.4	250.7	251.1	251.4	251.6	251.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.7	289.1
115°	326.5	326.7	326.8	326.9	327.0	327.2	327.3	327.5	327.7	328.0	328.4
117.5°	361.9	362.4	362.9	363.2	363.5	364.0	364.5	365.0	365.5	365.7	365.8
120°	401.0	400.7	400.4	400.2	400.6	401.5	402.3	403.2	404.0	404.5	405.0
122.5°	437.4	438.2	439.1	439.5	439.7	440.2	440.7	441.2	441.7	441.9	442.1
125°	476.4	476.7	477.0	477.2	477.4	477.7	478.0	478.4	478.7	478.9	479.1
127.5°	512.3	512.4	512.6	512.7	512.9	513.2	513.5	513.9	514.2	514.5	514.9
130°	548.8	549.5	550.2	550.5	550.7	551.0	551.3	551.7	552.0	552.0	552.0
132.5°	585.5	585.7	585.8	585.9	586.1	586.4	586.7	587.1	587.4	587.6	587.8
135°	620.2	620.7	621.2	621.4	621.6	621.9	622.2	622.6	622.9	622.9	622.9
137.5°	655.8	655.7	655.5	655.4	655.7	656.2	656.7	657.2	657.7	657.4	657.0
140°	689.7	689.9	690.0	690.1	690.2	690.4	690.5	690.7	690.9	690.9	690.9
142.5°	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.8	723.0
145°	753.1	753.6	754.1	754.3	754.4	754.6	754.7	754.9	755.1	754.9	754.7
147.5°	783.4	783.5	783.7	783.8	783.9	784.0	784.2	784.3	784.5	784.7	784.9
150°	811.3	811.5	811.6	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7
152.5°	837.6	838.1	838.6	838.9	838.6	838.1	837.6	837.1	836.6	836.4	836.3
155°	861.4	862.1	862.8	863.1	862.8	862.1	861.4	860.7	860.0	860.2	860.4
157.5°	882.9	883.4	883.9	884.2	883.9	883.4	882.9	882.4	881.9	881.9	881.9
160°	901.7	902.6	903.4	903.8	903.6	903.1	902.6	902.1	901.6	901.8	901.9
162.5°	920.6	921.4	922.3	922.7	922.2	921.2	920.2	919.2	918.2	918.4	918.5
165°	936.1	936.8	937.5	937.8	937.3	936.3	935.3	934.3	933.3	933.6	934.0
167.5°	948.9	949.9	950.9	951.4	950.9	949.9	948.9	947.9	946.9	946.9	946.9
170°	959.1	960.2	961.4	962.0	961.5	960.5	959.4	958.4	957.4	957.2	957.1
172.5°	967.4	968.5	969.7	970.3	969.7	968.5	967.4	966.2	965.0	965.0	965.0
175°	972.7	973.8	975.0	975.6	975.0	973.8	972.7	971.5	970.3	970.5	970.6
177.5°	976.0	977.3	978.6	979.3	978.7	977.5	976.4	975.2	974.0	974.0	974.0
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	986.5	982.6	980.3	979.5	972.5	968.6	966.3	964.8	962.4	956.2	950.8
5°	1023.7	1012.8	1007.4	1001.2	990.3	977.9	967.9	961.7	953.9	941.5	929.9
7.5°	1058.5	1042.3	1031.4	1022.9	1004.3	984.1	967.9	954.7	940.0	922.9	906.7
10°	1095.0	1068.6	1054.7	1041.5	1014.4	988.0	964.8	945.4	924.5	902.0	884.2
12.5°	1123.6	1088.8	1073.3	1054.7	1021.3	990.3	960.9	934.6	907.4	883.4	857.8
15°	1157.0	1113.6	1095.7	1071.7	1026.0	985.7	947.7	919.1	891.2	855.5	828.4
17.5°	1176.3	1126.0	1100.4	1079.5	1029.9	981.0	936.9	901.2	868.7	833.0	804.4
20°	1195.7	1138.4	1109.7	1080.2	1021.3	969.4	922.9	880.3	846.2	807.5	778.0
22.5°	*1201.9*	*1135.3*	*1105.0*	*1077.9*	*1015.9*	*957.8*	*904.3*	*860.9*	*821.4*	*782.7*	*749.3*
25°	1201.9	1134.5	1098.8	1064.0	998.9	939.2	885.7	838.5	794.3	755.5	722.2
27.5°	1189.5	1119.0	1081.8	1050.0	982.6	918.3	863.3	811.3	768.7	730.0	692.0
30°	1174.0	1096.5	1059.3	1021.3	956.2	895.0	835.4	787.3	742.4	698.2	664.1
32.5°	1154.6	1072.5	1031.4	992.7	923.7	860.2	805.1	757.9	715.3	669.5	631.6
35°	1126.7	1036.8	991.1	957.0	890.4	824.5	771.8	725.3	684.3	637.0	595.9
37.5°	1091.1	1004.3	957.8	916.0	847.0	786.5	736.9	692.0	651.7	608.3	562.6
40°	1049.2	958.6	918.3	874.1	801.3	743.9	697.4	657.1	616.8	575.8	531.6
42.5°	1002.0	912.1	867.1	824.5	754.8	698.2	654.8	618.4	581.2	543.2	495.9
45°	945.4	860.9	817.5	777.2	709.8	651.7	612.2	577.3	545.5	506.8	465.0
47.5°	881.9	808.2	764.1	720.7	654.8	604.4	565.7	536.2	509.1	470.4	432.4
50°	819.9	747.0	711.4	667.2	606.8	559.5	520.0	495.2	474.3	436.3	402.2
52.5°	741.6	686.6	652.5	614.5	556.4	508.3	477.4	455.7	430.9	401.4	371.2
55°	672.6	621.5	594.4	558.7	501.4	458.8	432.4	412.3	392.9	366.5	342.5
57.5°	594.4	562.6	535.5	504.5	447.9	411.5	388.2	371.2	353.4	331.7	312.3
60°	512.2	497.5	471.2	446.4	398.3	366.5	347.2	331.7	314.6	296.8	280.5
62.5°	439.4	430.9	415.4	396.0	351.0	323.9	304.5	292.9	280.5	264.2	248.7
65°	370.4	366.5	351.8	337.9	306.9	282.8	265.8	258.8	244.9	232.5	218.5
67.5°	309.2	304.5	296.0	289.8	263.5	241.0	232.5	223.2	211.6	202.3	190.6
70°	247.2	246.4	241.0	233.3	219.3	203.0	194.5	188.3	176.7	169.7	161.2
72.5°	192.2	196.1	191.4	188.3	179.0	167.4	159.6	155.8	146.5	141.0	134.8
75°	143.4	146.5	148.8	143.4	141.0	135.6	128.6	124.8	120.1	112.4	110.0
77.5°	97.6	104.6	104.6	106.2	106.9	103.8	98.4	95.3	89.9	88.3	85.2
80°	64.3	70.5	71.3	72.8	75.2	75.2	71.3	70.5	65.1	64.3	62.0
82.5°	37.2	42.6	45.7	48.0	47.3	50.4	47.3	46.5	43.4	43.4	41.8
85°	20.1	20.9	22.5	24.0	25.6	27.1	27.1	26.3	25.6	24.8	23.2
87.5°	7.7	7.7	8.5	7.7	8.5	10.1	10.8	10.8	10.1	9.3	7.7
90°	12.6	11.3	10.6	9.7	7.8	6.0	4.1	2.3	4.1	6.0	7.8
92.5°	30.7	29.8	29.4	28.3	26.1	24.0	21.8	19.6	21.8	24.0	26.1
95°	53.9	52.7	52.1	51.3	49.8	48.3	46.8	45.3	46.8	48.3	49.8
97.5°	80.5	79.2	78.5	77.8	76.5	75.2	73.8	72.5	73.8	75.2	76.5
100°	111.0	109.5	108.7	108.4	107.7	107.0	106.4	105.7	106.4	107.0	107.7
102.5°	143.2	141.9	141.2	141.1	140.9	140.8	140.6	140.4	140.6	140.8	140.9
105°	177.7	177.0	176.7	176.6	176.4	176.3	176.1	175.9	176.1	176.3	176.4
107.5°	213.9	213.8	213.7	213.6	213.4	213.3	213.1	212.9	213.1	213.3	213.4
110°	251.9	252.1	252.2	252.0	251.7	251.4	251.0	250.7	251.0	251.4	251.7

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	289.4	289.7	289.9	289.9	289.9	289.9	289.9	289.9	289.9	289.9	289.9
115°	328.7	329.0	329.2	329.2	329.2	329.2	329.2	329.2	329.2	329.2	329.2
117.5°	366.0	366.1	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2
120°	405.5	406.0	406.2	405.9	405.2	404.5	403.9	403.2	403.9	404.5	405.2
122.5°	442.2	442.4	442.5	442.4	442.2	442.1	441.9	441.7	441.9	442.1	442.2
125°	479.2	479.4	479.5	479.5	479.5	479.5	479.5	479.5	479.5	479.5	479.5
127.5°	515.2	515.5	515.7	515.5	515.0	514.5	514.0	513.5	514.0	514.5	515.0
130°	552.0	552.0	552.0	551.7	551.2	550.7	550.2	549.7	550.2	550.7	551.2
132.5°	587.9	588.1	588.2	588.0	587.7	587.4	587.0	586.7	587.0	587.4	587.7
135°	622.9	622.9	622.9	622.4	621.4	620.4	619.4	618.4	619.4	620.4	621.4
137.5°	656.7	656.4	656.2	655.9	655.4	654.9	654.4	653.9	654.4	654.9	655.4
140°	690.9	690.9	690.9	690.7	690.4	690.1	689.7	689.4	689.7	690.1	690.4
142.5°	723.1	723.3	723.4	723.2	722.9	722.6	722.2	721.9	722.2	722.6	722.9
145°	754.6	754.4	754.3	754.0	753.3	752.6	752.0	751.3	752.0	752.6	753.3
147.5°	785.0	785.2	785.3	784.9	784.0	783.2	782.3	781.5	782.3	783.2	784.0
150°	811.7	811.7	811.7	811.4	810.7	810.0	809.4	808.7	809.4	810.0	810.7
152.5°	836.1	836.0	835.9	835.7	835.4	835.1	834.7	834.4	834.7	835.1	835.4
155°	860.5	860.7	860.8	860.8	860.8	860.8	860.8	860.8	860.8	860.8	860.8
157.5°	881.9	881.9	881.9	882.1	882.4	882.7	883.1	883.4	883.1	882.7	882.4
160°	902.1	902.2	902.3	902.4	902.6	902.7	902.9	903.1	902.9	902.7	902.6
162.5°	918.7	918.8	918.9	919.2	919.7	920.2	920.7	921.2	920.7	920.2	919.7
165°	934.3	934.6	934.8	935.1	935.6	936.1	936.6	937.1	936.6	936.1	935.6
167.5°	946.9	946.9	946.9	947.2	947.9	948.6	949.2	949.9	949.2	948.6	947.9
170°	956.9	956.8	956.7	957.1	958.0	958.8	959.7	960.5	959.7	958.8	958.0
172.5°	965.0	965.0	965.0	965.3	966.0	966.7	967.3	968.0	967.3	966.7	966.0
175°	970.8	970.9	971.0	971.4	972.3	973.1	974.0	974.8	974.0	973.1	972.3
177.5°	974.0	974.0	974.0	974.4	975.3	976.1	977.0	977.8	977.0	976.1	975.3
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	946.2	944.6	943.1	936.9	931.5	922.2	914.4	911.3	910.5	911.3	909.0
5°	919.1	918.3	912.9	902.0	891.9	881.1	873.3	865.6	860.9	860.9	855.5
7.5°	893.5	888.1	883.4	869.5	857.8	843.1	831.5	824.5	820.6	812.1	812.1
10°	866.4	858.6	852.4	839.2	822.2	807.5	792.7	784.2	777.2	771.0	768.7
12.5°	839.2	833.0	821.4	807.5	790.4	771.8	756.3	750.1	733.8	720.7	721.4
15°	813.7	799.7	794.3	774.1	754.0	736.2	713.7	695.9	682.7	674.2	663.3
17.5°	785.0	771.0	761.0	743.9	717.6	689.7	668.0	644.0	630.8	616.1	609.1
20°	753.2	741.6	733.8	706.7	675.0	641.6	617.6	602.9	588.2	577.3	571.1
22.5°	*726.1*	*711.4*	*702.1*	*665.7*	*630.8*	*597.5*	*578.9*	*566.5*	*554.1*	*544.8*	*541.7*
25°	691.2	682.7	660.2	628.5	585.8	563.4	547.1	530.8	523.8	517.6	510.7
27.5°	662.6	641.6	626.1	584.3	557.9	532.4	516.1	503.7	495.2	489.0	483.5
30°	626.9	607.5	585.8	551.0	526.9	502.9	488.2	478.1	468.8	465.0	460.3
32.5°	589.7	571.9	551.0	523.1	493.6	475.0	463.4	452.6	446.4	442.5	437.1
35°	556.4	533.9	520.0	493.6	469.6	448.7	437.8	428.5	421.6	420.0	419.2
37.5°	520.7	503.7	490.5	463.4	443.3	425.4	415.4	405.3	401.4	400.6	397.5
40°	489.7	475.0	462.6	437.1	415.4	399.1	391.3	385.1	381.3	381.3	380.5
42.5°	462.6	447.1	434.7	411.5	392.1	377.4	368.9	362.7	361.1	361.9	361.1
45°	432.4	419.2	406.8	382.8	366.5	355.7	346.4	343.3	341.0	341.7	342.5
47.5°	403.7	392.9	380.5	361.1	342.5	330.9	325.5	322.4	322.4	322.4	323.9
50°	378.2	365.8	354.9	334.8	317.7	308.4	303.8	299.9	300.7	301.4	302.2
52.5°	347.9	337.1	329.3	309.2	296.8	285.2	279.7	280.5	279.7	279.7	281.3
55°	321.6	310.7	303.0	284.4	272.0	264.2	259.6	257.3	258.0	256.5	259.6
57.5°	292.1	282.8	277.4	259.6	248.7	241.8	237.9	234.0	235.6	234.8	234.0
60°	266.6	255.7	247.2	234.8	225.5	217.0	214.7	210.8	212.3	210.8	210.0
62.5°	237.1	228.6	222.4	210.0	202.3	195.3	189.9	187.5	186.8	184.4	182.1
65°	207.7	203.0	196.8	184.4	176.7	171.3	168.2	165.8	165.1	158.9	151.9
67.5°	180.6	177.5	171.3	162.0	155.0	149.6	144.9	141.0	136.4	131.7	127.9
70°	155.0	150.3	146.5	137.9	131.7	126.3	121.7	117.0	114.7	110.0	108.5
72.5°	130.2	125.5	121.7	113.9	108.5	103.1	101.5	96.1	93.8	93.0	93.0
75°	104.6	100.7	98.4	91.4	86.8	82.9	80.6	79.0	77.5	75.9	73.6
77.5°	79.8	77.5	75.9	71.3	67.4	65.1	64.3	58.9	57.3	55.8	54.2
80°	58.1	57.3	55.8	51.9	50.4	44.9	44.9	43.4	42.6	42.6	42.6
82.5°	39.5	38.0	37.2	33.3	32.5	31.8	31.0	30.2	31.0	30.2	31.0
85°	20.9	20.1	19.4	19.4	19.4	19.4	19.4	19.4	19.4	18.6	19.4
87.5°	7.7	7.7	7.7	7.7	7.0	7.7	7.7	7.0	7.7	7.7	7.7
90°	9.7	10.6	11.3	12.6	13.9	15.3	16.6	17.6	18.6	19.6	20.6
92.5°	28.3	29.4	29.8	30.7	31.5	32.4	33.2	33.7	34.2	34.7	35.2
95°	51.3	52.1	52.7	53.9	55.0	56.2	57.4	57.9	58.4	58.9	59.4
97.5°	77.8	78.5	79.2	80.5	81.9	83.2	84.6	85.3	85.9	86.6	87.3
100°	108.4	108.7	109.5	111.0	112.5	114.0	115.5	115.8	116.2	116.5	116.8
102.5°	141.1	141.2	141.9	143.2	144.5	145.9	147.2	147.7	148.2	148.7	149.2
105°	176.6	176.7	177.0	177.7	178.4	179.0	179.7	180.2	180.7	181.2	181.7
107.5°	213.6	213.7	213.8	213.9	214.1	214.2	214.4	215.1	215.8	216.5	217.2
110°	252.0	252.2	252.1	251.9	251.8	251.6	251.4	251.1	250.7	250.4	250.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	289.9	289.9	289.7	289.4	289.1	288.7	288.4	288.4	288.4	288.4	288.4
115°	329.2	329.2	329.0	328.7	328.4	328.0	327.7	327.5	327.3	327.2	327.0
117.5°	366.2	366.2	366.1	366.0	365.8	365.7	365.5	365.0	364.5	364.0	363.5
120°	405.9	406.2	406.0	405.5	405.0	404.5	404.0	403.2	402.3	401.5	400.6
122.5°	442.4	442.5	442.4	442.2	442.1	441.9	441.7	441.2	440.7	440.2	439.7
125°	479.5	479.5	479.4	479.2	479.1	478.9	478.7	478.4	478.0	477.7	477.4
127.5°	515.5	515.7	515.5	515.2	514.9	514.5	514.2	513.9	513.5	513.2	512.9
130°	551.7	552.0	552.0	552.0	552.0	552.0	552.0	551.7	551.3	551.0	550.7
132.5°	588.0	588.2	588.1	587.9	587.8	587.6	587.4	587.1	586.7	586.4	586.1
135°	622.4	622.9	622.9	622.9	622.9	622.9	622.9	622.6	622.2	621.9	621.6
137.5°	655.9	656.2	656.4	656.7	657.0	657.4	657.7	657.2	656.7	656.2	655.7
140°	690.7	690.9	690.9	690.9	690.9	690.9	690.9	690.7	690.5	690.4	690.2
142.5°	723.2	723.4	723.3	723.1	723.0	722.8	722.6	722.6	722.6	722.6	722.6
145°	754.0	754.3	754.4	754.6	754.7	754.9	755.1	754.9	754.7	754.6	754.4
147.5°	784.9	785.3	785.2	785.0	784.9	784.7	784.5	784.3	784.2	784.0	783.9
150°	811.4	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7
152.5°	835.7	835.9	836.0	836.1	836.3	836.4	836.6	837.1	837.6	838.1	838.6
155°	860.8	860.8	860.7	860.5	860.4	860.2	860.0	860.7	861.4	862.1	862.8
157.5°	882.1	881.9	881.9	881.9	881.9	881.9	881.9	882.4	882.9	883.4	883.9
160°	902.4	902.3	902.2	902.1	901.9	901.8	901.6	902.1	902.6	903.1	903.6
162.5°	919.2	918.9	918.8	918.7	918.5	918.4	918.2	919.2	920.2	921.2	922.2
165°	935.1	934.8	934.6	934.3	934.0	933.6	933.3	934.3	935.3	936.3	937.3
167.5°	947.2	946.9	946.9	946.9	946.9	946.9	946.9	947.9	948.9	949.9	950.9
170°	957.1	956.7	956.8	956.9	957.1	957.2	957.4	958.4	959.4	960.5	961.5
172.5°	965.3	965.0	965.0	965.0	965.0	965.0	965.0	966.2	967.4	968.5	969.7
175°	971.4	971.0	970.9	970.8	970.6	970.5	970.3	971.5	972.7	973.8	975.0
177.5°	974.4	974.0	974.0	974.0	974.0	974.0	974.0	975.2	976.4	977.5	978.7
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	909.0	912.1	908.2	910.5	905.1	904.3	905.1	905.1	905.9	906.7	907.4
5°	857.8	857.1	852.4	849.3	847.0	849.3	850.9	852.4	850.9	852.4	853.2
7.5°	809.8	807.5	805.1	799.7	801.3	799.7	804.4	802.0	802.0	805.9	809.0
10°	767.2	762.5	761.0	754.8	750.1	749.3	754.8	757.1	759.4	761.0	767.2
12.5°	712.2	705.2	699.8	702.1	688.9	694.3	695.9	692.8	702.1	712.9	706.7
15°	653.3	654.0	643.2	639.3	628.5	631.6	632.3	640.1	647.8	647.1	656.4
17.5°	609.9	605.2	595.9	595.1	590.5	592.8	592.0	598.2	595.9	599.8	607.5
20°	569.6	566.5	558.7	555.6	557.2	555.6	556.4	557.2	559.5	568.0	566.5
22.5°	*537.8*	*533.9*	*533.9*	*530.0*	*525.4*	*523.8*	*527.7*	*530.0*	*533.1*	*534.7*	*538.6*
25°	509.9	506.8	502.9	500.6	496.7	497.5	499.8	502.9	505.2	508.3	511.4
27.5°	481.2	481.2	477.4	476.6	475.0	474.3	477.4	478.9	478.9	481.2	484.3
30°	458.8	458.8	454.9	454.1	453.3	453.3	455.7	456.4	457.2	459.5	461.1
32.5°	437.1	436.3	434.7	435.5	434.7	435.5	435.5	436.3	437.8	438.6	441.7
35°	416.9	417.7	416.1	416.1	415.4	416.1	417.7	418.5	419.2	420.8	420.8
37.5°	397.5	399.1	398.3	400.6	400.6	400.6	400.6	402.2	402.2	402.2	401.4
40°	380.5	380.5	379.7	381.3	382.8	382.8	383.6	383.6	384.4	384.4	383.6
42.5°	361.1	362.7	365.0	365.8	367.3	366.5	368.9	368.1	368.9	367.3	365.8
45°	343.3	343.3	346.4	349.5	350.3	350.3	350.3	351.8	350.3	347.9	347.2
47.5°	323.9	325.5	327.0	330.9	331.7	331.7	331.7	331.7	330.1	330.1	330.1
50°	304.5	305.3	306.1	307.6	310.0	309.2	309.2	309.2	312.3	309.2	310.0
52.5°	281.3	282.1	282.8	285.9	285.2	285.2	285.9	285.9	288.3	287.5	285.9
55°	258.0	258.0	259.6	259.6	259.6	261.1	261.9	263.5	262.7	263.5	264.2
57.5°	234.8	233.3	232.5	232.5	234.8	234.0	234.8	234.8	237.9	239.4	240.2
60°	207.7	207.7	206.9	202.3	202.3	201.5	203.8	205.4	206.9	213.9	213.1
62.5°	179.8	176.7	173.6	174.4	169.7	172.0	170.5	172.0	176.7	182.1	182.9
65°	151.9	149.6	146.5	145.7	144.1	146.5	145.7	146.5	148.8	151.9	155.8
67.5°	127.1	126.3	124.8	124.0	124.0	124.0	125.5	125.5	126.3	128.6	131.0
70°	108.5	107.7	108.5	106.9	107.7	106.9	107.7	108.5	109.3	110.0	112.4
72.5°	91.4	91.4	91.4	89.9	91.4	90.7	90.7	91.4	92.2	93.0	94.5
75°	72.8	71.3	69.7	68.2	67.4	69.0	69.7	69.0	71.3	74.4	74.4
77.5°	55.0	54.2	54.2	54.2	55.0	54.2	55.8	55.0	55.8	55.8	57.3
80°	42.6	41.8	42.6	42.6	41.8	43.4	42.6	42.6	43.4	44.2	43.4
82.5°	31.0	31.8	31.0	31.0	31.0	32.5	31.0	31.0	31.0	31.8	31.8
85°	19.4	19.4	19.4	19.4	20.1	19.4	20.1	19.4	20.9	20.1	20.1
87.5°	7.0	7.7	8.5	8.5	8.5	8.5	7.7	8.5	9.3	8.5	9.3
90°	21.1	21.3	21.6	22.0	22.3	22.7	22.3	22.0	21.6	21.3	21.1
92.5°	35.5	35.6	35.7	35.9	36.0	36.2	36.0	35.9	35.7	35.6	35.5
95°	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7
97.5°	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6	87.6
100°	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0
102.5°	149.5	149.6	149.8	149.9	150.1	150.3	150.1	149.9	149.8	149.6	149.5
105°	182.0	182.2	182.7	183.2	183.7	184.2	183.7	183.2	182.7	182.2	182.0
107.5°	217.5	217.4	217.2	217.1	216.9	216.7	216.9	217.1	217.2	217.4	217.5
110°	249.9	250.2	250.7	251.2	251.7	252.2	251.7	251.2	250.7	250.2	249.9

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4	288.4
115°	326.9	326.8	326.7	326.5	326.4	326.2	326.4	326.5	326.7	326.8	326.9
117.5°	363.2	362.9	362.4	361.9	361.4	360.9	361.4	361.9	362.4	362.9	363.2
120°	400.2	400.4	400.7	401.0	401.4	401.7	401.4	401.0	400.7	400.4	400.2
122.5°	439.5	439.1	438.2	437.4	436.5	435.7	436.5	437.4	438.2	439.1	439.5
125°	477.2	477.0	476.7	476.4	476.0	475.7	476.0	476.4	476.7	477.0	477.2
127.5°	512.7	512.6	512.4	512.3	512.1	511.9	512.1	512.3	512.4	512.6	512.7
130°	550.5	550.2	549.5	548.8	548.1	547.4	548.1	548.8	549.5	550.2	550.5
132.5°	585.9	585.8	585.7	585.5	585.4	585.2	585.4	585.5	585.7	585.8	585.9
135°	621.4	621.2	620.7	620.2	619.7	619.2	619.7	620.2	620.7	621.2	621.4
137.5°	655.4	655.5	655.7	655.8	656.0	656.2	656.0	655.8	655.7	655.5	655.4
140°	690.1	690.0	689.9	689.7	689.6	689.4	689.6	689.7	689.9	690.0	690.1
142.5°	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6	722.6
145°	754.3	754.1	753.6	753.1	752.6	752.1	752.6	753.1	753.6	754.1	754.3
147.5°	783.8	783.7	783.5	783.4	783.2	783.0	783.2	783.4	783.5	783.7	783.8
150°	811.7	811.6	811.5	811.3	811.2	811.0	811.2	811.3	811.5	811.6	811.7
152.5°	838.9	838.6	838.1	837.6	837.1	836.6	837.1	837.6	838.1	838.6	838.9
155°	863.1	862.8	862.1	861.4	860.7	860.0	860.7	861.4	862.1	862.8	863.1
157.5°	884.2	883.9	883.4	882.9	882.4	881.9	882.4	882.9	883.4	883.9	884.2
160°	903.8	903.4	902.6	901.7	900.9	900.1	900.9	901.7	902.6	903.4	903.8
162.5°	922.7	922.3	921.4	920.6	919.7	918.9	919.7	920.6	921.4	922.3	922.7
165°	937.8	937.5	936.8	936.1	935.5	934.8	935.5	936.1	936.8	937.5	937.8
167.5°	951.4	950.9	949.9	948.9	947.9	946.9	947.9	948.9	949.9	950.9	951.4
170°	962.0	961.4	960.2	959.1	957.9	956.7	957.9	959.1	960.2	961.4	962.0
172.5°	970.3	969.7	968.5	967.4	966.2	965.0	966.2	967.4	968.5	969.7	970.3
175°	975.6	975.0	973.8	972.7	971.5	970.3	971.5	972.7	973.8	975.0	975.6
177.5°	979.3	978.6	977.3	976.0	974.6	973.3	974.6	976.0	977.3	978.6	979.3
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	910.5	914.4	912.9	907.4	909.8	914.4	919.1	925.3	929.1	932.2	933.8
5°	857.1	864.0	862.5	862.5	865.6	873.3	881.1	894.3	898.9	904.3	912.1
7.5°	809.8	815.2	819.9	821.4	826.1	836.1	846.2	860.9	872.6	878.8	883.4
10°	767.9	771.8	778.8	782.7	787.3	799.7	814.4	829.9	841.6	852.4	858.6
12.5°	714.5	730.0	739.3	745.5	751.7	770.3	781.9	798.9	812.9	823.0	832.3
15°	654.8	673.4	678.8	702.9	718.3	733.1	750.9	771.0	784.2	795.8	808.2
17.5°	604.4	617.6	623.8	649.4	662.6	685.8	711.4	736.9	757.1	765.6	778.0
20°	572.7	579.6	592.0	600.6	614.5	641.6	669.5	700.5	730.7	739.3	751.7
22.5°	*540.1*	*549.4*	*557.9*	*569.6*	*580.4*	*599.0*	*626.9*	*661.0*	*693.6*	*709.1*	*723.8*
25°	510.7	520.0	525.4	537.8	547.9	566.5	585.8	620.7	659.5	672.6	695.9
27.5°	487.4	492.8	502.1	507.6	519.2	536.2	554.1	580.4	618.4	640.9	663.3
30°	464.2	468.1	475.8	483.5	492.1	503.7	523.8	549.4	584.3	603.7	626.1
32.5°	440.9	447.1	451.8	457.2	466.5	480.4	494.4	519.2	547.1	568.8	591.3
35°	421.6	423.9	430.1	436.3	442.5	454.9	469.6	493.6	518.4	535.5	555.6
37.5°	400.6	404.5	409.2	411.5	421.6	429.3	444.8	463.4	492.8	503.7	523.8
40°	384.4	383.6	388.2	392.1	396.8	409.2	418.5	438.6	461.9	478.9	491.3
42.5°	364.2	364.2	365.8	370.4	376.6	384.4	395.2	412.3	436.3	448.7	463.4
45°	347.9	345.6	346.4	349.5	353.4	361.1	372.0	386.7	410.7	420.8	436.3
47.5°	328.6	326.2	326.2	329.3	332.4	337.9	346.4	363.4	382.8	396.0	407.6
50°	306.9	307.6	306.9	309.2	310.7	316.2	325.5	339.4	357.2	368.1	381.3
52.5°	286.7	285.2	284.4	285.9	289.0	292.9	303.0	315.4	332.4	343.3	354.9
55°	261.9	263.5	263.5	263.5	268.1	269.7	277.4	289.8	306.9	315.4	326.2
57.5°	239.4	238.7	240.2	239.4	243.3	248.7	254.9	264.2	281.3	289.8	299.9
60°	214.7	215.4	216.2	216.2	219.3	224.7	231.7	240.2	254.2	262.7	272.0
62.5°	184.4	188.3	192.2	193.7	198.4	202.3	206.9	216.2	228.6	234.8	243.3
65°	155.8	161.2	166.6	170.5	173.6	177.5	183.7	192.2	202.3	208.5	217.0
67.5°	131.0	134.8	141.8	145.7	151.9	156.5	160.4	167.4	179.8	182.1	189.1
70°	113.1	114.7	117.8	120.9	127.9	131.7	136.4	143.4	152.7	158.1	162.0
72.5°	95.3	96.1	97.6	100.7	103.8	108.5	113.9	120.1	128.6	131.0	136.4
75°	75.9	80.6	80.6	82.9	85.2	87.6	92.2	98.4	103.8	107.7	110.8
77.5°	56.6	58.9	60.4	64.3	67.4	69.7	72.8	77.5	80.6	83.7	86.0
80°	44.2	44.9	45.7	45.7	47.3	50.4	53.5	56.6	60.4	62.0	64.3
82.5°	32.5	32.5	32.5	34.1	34.9	35.6	35.6	37.2	41.1	42.6	44.9
85°	20.9	20.9	20.9	20.9	21.7	22.5	23.2	24.0	24.0	24.0	25.6
87.5°	8.5	10.1	9.3	10.1	10.1	10.1	10.1	10.8	10.8	11.6	11.6
90°	20.6	19.6	18.6	17.6	16.6	15.3	13.9	12.6	11.3	10.6	9.7
92.5°	35.2	34.7	34.2	33.7	33.2	32.4	31.5	30.7	29.8	29.4	28.3
95°	59.4	58.9	58.4	57.9	57.4	56.2	55.0	53.9	52.7	52.1	51.3
97.5°	87.3	86.6	85.9	85.3	84.6	83.2	81.9	80.5	79.2	78.5	77.8
100°	116.8	116.5	116.2	115.8	115.5	114.0	112.5	111.0	109.5	108.7	108.4
102.5°	149.2	148.7	148.2	147.7	147.2	145.9	144.5	143.2	141.9	141.2	141.1
105°	181.7	181.2	180.7	180.2	179.7	179.0	178.4	177.7	177.0	176.7	176.6
107.5°	217.2	216.5	215.8	215.1	214.4	214.2	214.1	213.9	213.8	213.7	213.6
110°	250.1	250.4	250.7	251.1	251.4	251.6	251.8	251.9	252.1	252.2	252.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	288.4	288.4	288.4	288.4	288.4	288.7	289.1	289.4	289.7	289.9	289.9
115°	327.0	327.2	327.3	327.5	327.7	328.0	328.4	328.7	329.0	329.2	329.2
117.5°	363.5	364.0	364.5	365.0	365.5	365.7	365.8	366.0	366.1	366.2	366.2
120°	400.6	401.5	402.3	403.2	404.0	404.5	405.0	405.5	406.0	406.2	405.9
122.5°	439.7	440.2	440.7	441.2	441.7	441.9	442.1	442.2	442.4	442.5	442.4
125°	477.4	477.7	478.0	478.4	478.7	478.9	479.1	479.2	479.4	479.5	479.5
127.5°	512.9	513.2	513.5	513.9	514.2	514.5	514.9	515.2	515.5	515.7	515.5
130°	550.7	551.0	551.3	551.7	552.0	552.0	552.0	552.0	552.0	552.0	551.7
132.5°	586.1	586.4	586.7	587.1	587.4	587.6	587.8	587.9	588.1	588.2	588.0
135°	621.6	621.9	622.2	622.6	622.9	622.9	622.9	622.9	622.9	622.9	622.4
137.5°	655.7	656.2	656.7	657.2	657.7	657.4	657.0	656.7	656.4	656.2	655.9
140°	690.2	690.4	690.5	690.7	690.9	690.9	690.9	690.9	690.9	690.9	690.7
142.5°	722.6	722.6	722.6	722.6	722.6	722.8	723.0	723.1	723.3	723.4	723.2
145°	754.4	754.6	754.7	754.9	755.1	754.9	754.7	754.6	754.4	754.3	754.0
147.5°	783.9	784.0	784.2	784.3	784.5	784.7	784.9	785.0	785.2	785.3	784.9
150°	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.7	811.4
152.5°	838.6	838.1	837.6	837.1	836.6	836.4	836.3	836.1	836.0	835.9	835.7
155°	862.8	862.1	861.4	860.7	860.0	860.2	860.4	860.5	860.7	860.8	860.8
157.5°	883.9	883.4	882.9	882.4	881.9	881.9	881.9	881.9	881.9	881.9	882.1
160°	903.6	903.1	902.6	902.1	901.6	901.8	901.9	902.1	902.2	902.3	902.4
162.5°	922.2	921.2	920.2	919.2	918.2	918.4	918.5	918.7	918.8	918.9	919.2
165°	937.3	936.3	935.3	934.3	933.3	933.6	934.0	934.3	934.6	934.8	935.1
167.5°	950.9	949.9	948.9	947.9	946.9	946.9	946.9	946.9	946.9	946.9	947.2
170°	961.5	960.5	959.4	958.4	957.4	957.2	957.1	956.9	956.8	956.7	957.1
172.5°	969.7	968.5	967.4	966.2	965.0	965.0	965.0	965.0	965.0	965.0	965.3
175°	975.0	973.8	972.7	971.5	970.3	970.5	970.6	970.8	970.9	971.0	971.4
177.5°	978.7	977.5	976.4	975.2	974.0	974.0	974.0	974.0	974.0	974.0	974.4
180°	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3	976.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	961.7	961.7	961.7	961.7
2.5°	940.0	944.6	952.4	963.2
5°	918.3	931.5	943.9	960.1
7.5°	898.9	914.4	931.5	954.7
10°	876.4	895.8	917.5	946.2
12.5°	850.1	877.2	902.0	933.0
15°	830.7	850.9	882.6	919.1
17.5°	803.6	830.7	862.5	903.6
20°	778.0	806.7	842.3	885.0
22.5°	*750.9*	*783.4*	*819.1*	*864.8*
25°	723.0	757.9	793.5	842.3
27.5°	697.4	729.2	769.5	819.1
30°	666.4	702.9	741.6	793.5
32.5°	636.2	674.2	713.7	765.6
35°	603.7	641.6	685.0	734.6
37.5°	571.9	613.7	653.3	701.3
40°	537.0	580.4	621.5	670.3
42.5°	502.9	547.9	588.9	630.8
45°	471.2	515.3	552.5	592.0
47.5°	440.9	480.4	518.4	554.1
50°	411.5	444.8	479.7	509.1
52.5°	380.5	412.3	440.2	466.5
55°	352.6	377.4	402.2	426.2
57.5°	319.3	344.1	365.8	384.4
60°	291.4	306.9	327.8	347.2
62.5°	259.6	277.4	293.7	306.1
65°	228.6	244.1	256.5	267.3
67.5°	202.3	211.6	220.9	232.5
70°	170.5	178.2	189.1	197.6
72.5°	143.4	149.6	155.0	165.1
75°	116.2	121.7	124.8	134.1
77.5°	89.9	95.3	97.6	103.1
80°	69.0	69.7	72.8	77.5
82.5°	47.3	48.8	49.6	53.5
85°	27.1	31.0	30.2	31.8
87.5°	11.6	12.4	13.9	15.5
90°	7.8	6.0	4.1	2.3
92.5°	26.1	24.0	21.8	19.6
95°	49.8	48.3	46.8	45.3
97.5°	76.5	75.2	73.8	72.5
100°	107.7	107.0	106.4	105.7
102.5°	140.9	140.8	140.6	140.4
105°	176.4	176.3	176.1	175.9
107.5°	213.4	213.3	213.1	212.9
110°	251.7	251.4	251.0	250.7

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1034201
CATALOG NUMBER: S124RDIW-B575D770UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	289.9	289.9	289.9	289.9
115°	329.2	329.2	329.2	329.2
117.5°	366.2	366.2	366.2	366.2
120°	405.2	404.5	403.9	403.2
122.5°	442.2	442.1	441.9	441.7
125°	479.5	479.5	479.5	479.5
127.5°	515.0	514.5	514.0	513.5
130°	551.2	550.7	550.2	549.7
132.5°	587.7	587.4	587.0	586.7
135°	621.4	620.4	619.4	618.4
137.5°	655.4	654.9	654.4	653.9
140°	690.4	690.1	689.7	689.4
142.5°	722.9	722.6	722.2	721.9
145°	753.3	752.6	752.0	751.3
147.5°	784.0	783.2	782.3	781.5
150°	810.7	810.0	809.4	808.7
152.5°	835.4	835.1	834.7	834.4
155°	860.8	860.8	860.8	860.8
157.5°	882.4	882.7	883.1	883.4
160°	902.6	902.7	902.9	903.1
162.5°	919.7	920.2	920.7	921.2
165°	935.6	936.1	936.6	937.1
167.5°	947.9	948.6	949.2	949.9
170°	958.0	958.8	959.7	960.5
172.5°	966.0	966.7	967.3	968.0
175°	972.3	973.1	974.0	974.8
177.5°	975.3	976.1	977.0	977.8
180°	976.3	976.3	976.3	976.3

(END OF REPORT)