

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034666

Luminaire Tested: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034666
REPORT IS A COMBINATION OF REPORTS P1004256 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5195.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034666

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034666

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60		
1	99	94	90	86	92	88	84	81	77	74	71	66	64	62	56	55	53	48		
2	90	82	75	70	84	77	71	66	67	62	58	57	54	51	49	46	44	40		
3	82	72	64	58	76	67	60	55	58	53	49	50	46	43	43	40	37	33		
4	75	63	55	49	69	59	52	46	52	46	41	45	40	36	38	35	32	28		
5	69	56	48	42	64	53	45	39	46	40	35	40	35	31	34	31	28	24		
6	63	51	42	36	59	47	40	34	42	35	31	36	31	27	31	27	24	21		
7	58	46	37	32	54	43	35	30	38	32	27	33	28	24	28	24	21	19		
8	54	41	33	28	50	39	32	27	34	28	24	30	25	22	26	22	19	17		
9	50	38	30	25	47	36	29	24	32	26	22	28	23	19	24	20	17	15		
10	47	35	27	22	44	33	26	21	29	23	19	26	21	18	22	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6823	6823	6823
5°	6834	6680	6697
10°	6783	6544	6525
15°	6700	6385	6315
20°	6589	6194	6106
25°	6457	5991	5853
30°	6297	5768	5623
35°	6147	5563	5411
40°	5996	5348	5197
45°	5824	5161	5005
50°	5659	4957	4832
55°	5462	4764	4630
60°	5245	4543	4424
65°	5017	4311	4191
70°	4759	3999	3949
75°	4350	3692	3654
80°	3813	3318	3327
85°	3282	3019	3155

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5824 cd/sqm

TEST NUMBER: P1034666

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.9
10°-20°	286.1	5.5
20°-30°	425.4	8.2
30°-40°	503.8	9.7
40°-50°	520.9	10.0
50°-60°	479.8	9.2
60°-70°	387.9	7.5
70°-80°	259.5	5.0
80°-90°	135.1	2.6
90°-100°	96.5	1.9
100°-110°	194.9	3.8
110°-120°	288.0	5.5
120°-130°	342.9	6.6
130°-140°	355.4	6.8
140°-150°	326.7	6.3
150°-160°	262.8	5.1
160°-170°	170.0	3.3
170°-180°	58.6	1.1
0°-30°	812.3	15.6
0°-40°	1316.1	25.3
0°-60°	2316.7	44.6
0°-90°	3099.2	59.7
90°-120°	579.4	11.2
90°-150°	1604.5	30.9
90°-180°	2096.0	40.3
0°-180°	5195.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1065	1065	1065	1065	1065	
5°	1065	1063	1056	1064	1063	101
15°	1017	1018	1011	1017	1013	287
25°	924	927	921	925	920	425
35°	800	807	804	807	807	501
45°	659	670	676	683	684	508
55°	506	523	540	551	555	453
65°	349	373	398	413	418	346
75°	192	219	253	274	279	204
85°	57	92	128	151	160	60
90°	17	54	93	119	128	13
95°	40	65	84	109	116	43
105°	144	162	194	215	221	152
115°	259	268	296	313	316	256
125°	363	365	386	401	405	324
135°	450	452	458	470	473	347
145°	520	520	520	526	527	325
155°	572	569	570	571	568	263
165°	603	600	601	604	600	170
175°	617	614	615	618	614	59
180°	617	617	617	617	617	

TEST NUMBER: P1034666

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.9	1064.9	1064.9	1064.9	1064.9
2.5°	1068.1	1066.0	1058.7	1066.0	1064.9
5°	1064.9	1062.9	1055.5	1063.9	1062.9
7.5°	1057.6	1056.6	1049.3	1056.6	1055.5
10°	1047.2	1047.2	1038.8	1046.1	1045.1
12.5°	1032.6	1033.6	1027.4	1032.6	1029.4
15°	1016.9	1018.0	1010.6	1016.9	1012.7
17.5°	997.1	999.2	991.9	997.1	993.9
20°	975.2	977.2	969.9	973.1	973.1
22.5°	950.1	954.3	945.9	950.1	947.0
25°	924.0	927.1	920.9	925.0	919.8
27.5°	895.8	900.0	892.7	895.8	893.7
30°	863.4	869.7	863.4	865.5	864.5
32.5°	834.2	839.4	835.2	837.3	836.3
35°	799.7	807.1	803.9	807.1	807.1
37.5°	766.3	772.6	771.6	775.7	774.7
40°	731.9	740.2	739.2	743.4	745.5
42.5°	694.3	705.8	708.9	714.1	714.1
45°	658.8	670.3	675.5	682.8	683.9
47.5°	622.3	632.7	641.1	651.5	653.6
50°	584.7	596.2	607.6	619.1	622.3
52.5°	545.0	559.6	574.2	586.8	588.8
55°	506.4	523.1	539.8	551.3	555.4
57.5°	466.7	486.5	505.3	517.9	521.0
60°	427.0	447.9	468.8	484.4	487.6
62.5°	388.4	409.3	432.2	450.0	454.2
65°	348.7	372.7	397.8	413.4	417.6
67.5°	312.2	335.1	360.2	379.0	384.2
70°	271.5	295.5	322.6	342.5	348.7
72.5°	231.8	256.8	287.1	309.0	313.2
75°	192.1	219.3	252.7	273.5	278.8
77.5°	153.5	184.8	216.1	239.1	243.3
80°	118.0	149.3	184.8	207.8	211.9
82.5°	85.6	119.0	155.6	177.5	185.8
85°	57.4	91.9	128.4	151.4	159.7
87.5°	36.5	70.0	105.5	129.5	136.8
90°	17.2	54.2	92.9	119.2	127.9
92.5°	23.3	49.5	88.7	114.0	121.8
95°	39.7	65.4	83.5	108.8	116.1
97.5°	61.4	89.3	80.2	103.1	110.9
100°	87.9	111.1	146.4	100.1	104.6
102.5°	114.7	136.4	169.6	191.4	159.3
105°	143.9	162.4	193.7	214.6	221.4
107.5°	174.0	188.6	219.7	241.0	245.5
110°	203.0	215.5	245.7	264.2	271.9



TEST NUMBER: P1034666

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	231.4	242.2	270.8	287.8	294.2
115°	258.7	268.3	295.9	312.9	316.4
117.5°	287.4	292.6	320.5	335.6	341.9
120°	314.8	317.6	342.9	359.7	363.7
122.5°	338.0	341.3	364.8	380.6	384.1
125°	363.2	365.3	386.2	401.1	404.9
127.5°	386.3	387.6	404.9	419.7	422.3
130°	408.3	409.6	424.6	437.9	440.8
132.5°	429.2	432.0	441.0	455.6	457.5
135°	449.8	451.5	458.0	470.5	473.0
137.5°	469.0	470.7	474.0	486.5	488.4
140°	486.7	487.6	488.2	500.7	502.0
142.5°	503.6	503.1	504.0	513.4	514.8
145°	520.1	520.0	520.0	525.6	527.1
147.5°	533.7	533.7	534.2	536.7	535.6
150°	547.4	546.5	547.4	548.3	545.7
152.5°	560.7	558.4	559.3	560.2	557.0
155°	571.7	568.9	569.8	571.2	567.5
157.5°	580.3	579.0	579.0	580.3	576.7
160°	589.5	586.7	587.2	589.0	585.4
162.5°	596.8	594.1	594.5	597.3	593.2
165°	603.2	600.5	600.9	603.7	600.0
167.5°	608.2	605.5	606.0	609.2	605.0
170°	612.4	609.2	609.6	613.3	609.2
172.5°	615.1	611.9	612.8	616.0	611.9
175°	616.9	614.2	614.6	618.3	614.2
177.5°	618.3	615.6	616.0	619.2	615.6
180°	616.9	616.9	616.9	616.9	616.9

(END OF REPORT)