

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034272

Luminaire Tested: S124RDIW-B795D1560UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034272
REPORT IS A COMBINATION OF REPORTS P1000828 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1560UB50-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9194.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034272

CATALOG NUMBER: S124RDIW-B795D1560UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034272

CATALOG NUMBER: S124RDIW-B795D1560UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	82	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	33	31	30
3	79	69	62	57	71	63	57	52	51	46	43	39	37	34	29	27	26
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	23	21	19
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1034272

CATALOG NUMBER: S124RDIW-B795D1560UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.4
10°-20°	352.1	3.8
20°-30°	508.3	5.5
30°-40°	576.1	6.3
40°-50°	556.3	6.1
50°-60°	462.5	5.0
60°-70°	319.2	3.5
70°-80°	161.3	1.8
80°-90°	45.0	0.5
90°-100°	65.3	0.7
100°-110°	430.0	4.7
110°-120°	821.2	8.9
120°-130°	1042.4	11.3
130°-140°	1115.2	12.1
140°-150°	1042.8	11.3
150°-160°	840.9	9.1
160°-170°	542.3	5.9
170°-180°	186.9	2.0
0°-30°	986.7	10.7
0°-40°	1562.8	17.0
0°-60°	2581.6	28.1
0°-90°	3107.1	33.8
90°-120°	1316.5	14.3
90°-150°	4516.8	49.1
90°-180°	6087.0	66.2
0°-180°	9194.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	4	21	32	41	44	7
95°	81	31	32	41	43	100
105°	443	452	459	472	419	463
115°	827	831	830	833	833	814
125°	1162	1168	1165	1170	1171	1038
135°	1442	1440	1446	1449	1452	1111
145°	1663	1667	1667	1668	1671	1039
155°	1823	1824	1820	1826	1822	841
165°	1923	1916	1916	1927	1914	543
175°	1967	1958	1960	1973	1955	187
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1034272

CATALOG NUMBER: S124RDIW-B795D1560UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	4.4	20.6	32.4	41.2	44.1
92.5°	22.1	19.1	30.9	39.7	39.7
95°	80.9	30.9	32.4	41.2	42.7
97.5°	154.5	186.9	32.4	39.7	41.2
100°	241.3	267.8	64.7	39.7	41.2
102.5°	338.4	356.1	373.7	42.7	42.7
105°	442.9	451.7	459.0	472.3	419.3
107.5°	538.5	542.9	553.2	560.6	566.4
110°	635.6	640.0	648.8	651.8	656.2

TEST NUMBER: P1034272

CATALOG NUMBER: S124RDIW-B795D1560UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	729.8	738.6	741.5	740.1	745.9
115°	826.9	831.3	829.8	832.7	832.7
117.5°	913.7	919.6	924.0	922.5	922.5
120°	1001.9	1007.8	1006.4	1009.3	1006.4
122.5°	1084.3	1087.3	1090.2	1091.7	1088.8
125°	1162.3	1168.2	1165.3	1169.7	1171.1
127.5°	1237.4	1238.8	1246.2	1244.7	1243.2
130°	1309.4	1310.9	1315.3	1316.8	1316.8
132.5°	1375.7	1378.6	1384.5	1386.0	1384.5
135°	1441.9	1440.4	1446.3	1449.2	1452.2
137.5°	1500.7	1500.7	1508.1	1511.0	1509.5
140°	1558.1	1561.0	1564.0	1568.4	1569.9
142.5°	1609.6	1615.5	1616.9	1619.9	1619.9
145°	1662.6	1667.0	1667.0	1668.4	1671.4
147.5°	1703.8	1712.6	1711.1	1712.6	1714.1
150°	1749.4	1755.2	1753.8	1753.8	1755.2
152.5°	1787.6	1792.0	1789.1	1792.0	1790.6
155°	1822.9	1824.4	1820.0	1825.9	1821.5
157.5°	1853.8	1853.8	1847.9	1855.3	1847.9
160°	1880.3	1875.9	1874.4	1883.2	1874.4
162.5°	1903.8	1898.0	1896.5	1905.3	1895.0
165°	1923.0	1915.6	1915.6	1927.4	1914.1
167.5°	1939.2	1931.8	1930.3	1943.6	1928.9
170°	1952.4	1943.6	1945.0	1956.8	1942.1
172.5°	1961.2	1952.4	1953.9	1965.6	1949.5
175°	1967.1	1958.3	1959.8	1973.0	1955.3
177.5°	1971.5	1961.2	1964.2	1975.9	1958.3
180°	1967.1	1967.1	1967.1	1967.1	1967.1

(END OF REPORT)