

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034672

Luminaire Tested: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034672
REPORT IS A COMBINATION OF REPORTS P1004264 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5354.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034672

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034672

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	96	92	89	95	91	87	84	80	77	75	70	68	67	61	60	59
2	92	84	78	73	86	79	74	69	70	66	62	62	58	55	54	51	49
3	84	74	66	60	78	70	63	58	62	57	52	55	50	47	48	45	42
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	38	44	39	35	38	35	31
6	65	53	44	38	61	50	42	37	44	38	34	40	34	31	35	31	28
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7157 cd/sqm

TEST NUMBER: P1034672

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.3
10°-20°	353.3	6.6
20°-30°	521.6	9.7
30°-40°	608.6	11.4
40°-50°	611.2	11.4
50°-60°	536.5	10.0
60°-70°	399.6	7.5
70°-80°	228.2	4.3
80°-90°	66.8	1.2
90°-100°	21.0	0.4
100°-110°	139.8	2.6
110°-120°	251.8	4.7
120°-130°	323.2	6.0
130°-140°	347.6	6.5
140°-150°	326.2	6.1
150°-160°	263.9	4.9
160°-170°	170.7	3.2
170°-180°	58.9	1.1
0°-30°	1000.0	18.7
0°-40°	1608.5	30.0
0°-60°	2756.3	51.5
0°-90°	3450.9	64.5
90°-120°	412.6	7.7
90°-150°	1409.7	26.3
90°-180°	1903.0	35.5
0°-180°	5354.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	0	4	7	10	11	5
95°	26	25	7	10	10	32
105°	135	137	137	137	136	143
115°	254	256	256	254	252	251
125°	360	364	364	362	360	322
135°	450	452	451	450	448	347
145°	521	522	522	523	520	326
155°	574	571	572	574	570	265
165°	606	603	604	606	602	171
175°	620	617	617	621	617	59
180°	620	620	620	620	620	

TEST NUMBER: P1034672

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.2	24.8	7.3	9.6	9.6
97.5°	49.1	51.9	8.3	9.2	9.6
100°	76.7	78.1	79.9	11.5	9.6
102.5°	104.7	106.5	107.5	108.4	69.8
105°	135.0	136.9	136.9	136.9	136.4
107.5°	166.3	166.3	167.2	167.6	165.8
110°	196.6	196.6	197.5	196.1	196.6

TEST NUMBER: P1034672

CATALOG NUMBER: S125DIW-B850D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.0	226.4	226.9	225.0	224.1
115°	253.5	255.8	256.3	254.4	251.7
117.5°	283.4	283.4	285.2	282.4	281.5
120°	310.9	310.5	311.8	310.9	308.6
122.5°	335.3	337.6	338.0	337.1	334.3
125°	360.5	363.7	363.7	361.9	360.5
127.5°	384.9	387.2	386.7	385.8	382.1
130°	406.9	409.2	409.7	408.3	406.0
132.5°	428.9	431.7	430.3	430.3	428.0
135°	449.6	452.4	451.4	450.5	447.8
137.5°	468.9	471.7	470.7	470.7	468.4
140°	487.7	488.6	488.2	489.1	486.4
142.5°	504.7	505.2	506.1	506.1	503.3
145°	521.3	522.2	522.2	522.6	519.9
147.5°	536.0	536.0	536.4	536.9	533.7
150°	549.7	548.8	549.7	550.6	547.0
152.5°	563.0	560.8	561.7	562.6	559.4
155°	574.1	571.3	572.2	573.6	569.9
157.5°	582.8	581.4	581.4	582.8	579.1
160°	592.0	589.2	589.7	591.5	587.8
162.5°	599.3	596.6	597.0	599.8	595.7
165°	605.8	603.0	603.5	606.2	602.5
167.5°	610.8	608.1	608.5	611.7	607.6
170°	614.9	611.7	612.2	615.9	611.7
172.5°	617.7	614.5	615.4	618.6	614.5
175°	619.5	616.8	617.2	620.9	616.8
177.5°	620.9	618.2	618.6	621.8	618.2
180°	619.5	619.5	619.5	619.5	619.5

(END OF REPORT)