

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034689

Luminaire Tested: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034689
REPORT IS A COMBINATION OF REPORTS P1005925 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7618.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	51	51	51
2	91	83	77	72	84	78	72	68	67	63	59	57	54	51	47	45	44	44	44	44
3	83	74	66	61	77	69	62	57	59	54	50	50	47	44	42	40	38	38	38	38
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	33	33	33
5	70	58	50	45	65	55	47	42	47	42	38	41	36	33	34	31	29	29	29	29
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	25	25	25
7	60	47	40	34	55	44	37	32	39	33	29	34	29	26	29	25	23	23	23	23
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	20	20	20
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	18	18	18
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	22	19	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10061	11349	10061	8723
10°	10005	12754	9972	7541
15°	9897	13493	9829	6566
20°	9766	14566	9678	5935
25°	9594	16487	9486	5386
30°	9420	17525	9279	4994
35°	9195	14412	9066	4628
40°	8795	9787	8721	4300
45°	8270	7036	8259	3976
50°	7732	5410	7769	3677
55°	7126	4400	7112	3389
60°	6561	3605	6529	3008
65°	5905	3005	5941	2422
70°	5360	2411	5338	2017
75°	4529	1827	4529	1658
80°	3671	1115	3629	1115
85°	2584	587	2510	664

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14334 cd/sqm

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	2.0
10°-20°	441.9	5.8
20°-30°	700.6	9.2
30°-40°	846.6	11.1
40°-50°	753.8	9.9
50°-60°	578.0	7.6
60°-70°	375.4	4.9
70°-80°	182.2	2.4
80°-90°	44.8	0.6
90°-100°	84.4	1.1
100°-110°	250.9	3.3
110°-120°	425.4	5.6
120°-130°	560.1	7.4
130°-140°	627.6	8.2
140°-150°	615.2	8.1
150°-160°	516.7	6.8
160°-170°	343.5	4.5
170°-180°	120.2	1.6
0°-30°	1293.2	17.0
0°-40°	2139.8	28.1
0°-60°	3471.6	45.6
0°-90°	4074.0	53.5
90°-120°	760.7	10.0
90°-150°	2563.6	33.7
90°-180°	3544.0	46.5
0°-180°	7618.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1568	1801	1568	1385	1568	149
15°	1502	2164	1492	1053	1502	424
25°	1373	2591	1358	846	1373	633
35°	1196	2150	1179	690	1196	745
45°	936	961	934	543	936	722
55°	661	528	659	406	661	592
65°	410	299	413	241	410	410
75°	200	139	200	126	200	214
85°	45	30	44	34	45	51
90°	1	24	1	24	1	7
95°	64	85	64	85	64	67
105°	225	245	225	245	225	240
115°	426	430	426	430	426	421
125°	622	626	622	626	622	557
135°	808	811	808	811	808	623
145°	979	983	979	983	979	612
155°	1121	1121	1121	1121	1121	516
165°	1218	1216	1218	1216	1218	344
175°	1267	1262	1267	1262	1267	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1573.0	1585.9	1589.8	1600.1	1611.7	1614.3	1620.8	1629.8	1634.9	1633.7	1633.7
5°	1567.8	1589.8	1605.3	1623.3	1645.3	1654.3	1662.0	1681.4	1696.9	1705.9	1721.4
7.5°	1558.8	1591.1	1616.9	1644.0	1677.5	1693.0	1709.8	1736.9	1765.3	1783.3	1800.1
10°	1544.6	1585.9	1622.0	1662.0	1707.2	1730.4	1751.1	1792.4	1827.2	1850.4	1889.2
12.5°	1524.0	1575.6	1625.9	1678.8	1735.6	1760.1	1788.5	1833.7	1882.7	1916.3	1948.5
15°	1502.0	1564.0	1618.2	1681.4	1749.8	1787.2	1823.3	1871.1	1915.0	1952.4	1989.8
17.5°	1476.2	1542.0	1609.1	1681.4	1758.8	1796.3	1827.2	1884.0	1930.5	1967.9	2001.4
20°	1445.3	1518.8	1594.9	1675.0	1753.7	1788.5	1818.2	1880.1	1921.4	1961.4	2009.2
22.5°	1411.7	1491.7	1573.0	1651.7	1729.1	1766.6	1801.4	1855.6	1900.8	1955.0	2016.9
25°	1373.0	1460.7	1543.3	1622.0	1695.6	1730.4	1761.4	1820.8	1884.0	1952.4	2022.1
27.5°	1334.3	1419.5	1499.5	1571.7	1651.7	1684.0	1715.0	1789.8	1864.6	1936.9	2032.4
30°	1291.7	1378.2	1447.8	1514.9	1592.4	1625.9	1664.6	1749.8	1835.0	1933.0	2049.2
32.5°	1244.0	1322.7	1387.2	1456.9	1526.6	1567.8	1616.9	1709.8	1807.9	1925.3	2073.7
35°	1196.2	1259.4	1318.8	1384.6	1468.5	1512.4	1560.1	1658.2	1780.8	1921.4	2094.3
37.5°	1135.6	1196.2	1242.7	1309.8	1396.2	1447.8	1495.6	1609.1	1748.5	1912.4	2093.0
40°	1073.6	1125.2	1169.1	1238.8	1333.0	1380.7	1432.4	1556.2	1715.0	1886.6	2062.1
42.5°	1006.5	1050.4	1098.1	1165.2	1256.9	1303.3	1362.7	1507.2	1668.5	1850.4	1982.1
45°	935.5	978.1	1018.1	1087.8	1179.4	1229.8	1294.3	1442.7	1611.7	1774.3	1853.0
47.5°	865.9	903.3	945.9	1006.5	1099.4	1154.9	1220.7	1379.4	1535.6	1672.4	1678.8
50°	798.8	828.4	864.6	926.5	1023.3	1076.2	1144.6	1293.0	1445.3	1539.5	1476.2
52.5°	729.1	756.2	793.6	847.8	938.1	1000.1	1059.4	1207.8	1335.6	1398.8	1282.7
55°	660.7	683.9	722.6	783.3	862.0	909.7	970.4	1108.5	1220.7	1222.0	1095.6
57.5°	593.6	614.2	646.5	700.7	774.2	829.7	885.2	1005.2	1081.4	1059.4	918.8
60°	534.2	547.1	576.8	629.7	698.1	738.1	797.5	898.1	948.5	908.4	757.5
62.5°	472.3	485.2	508.4	551.0	615.5	658.1	695.5	778.1	813.0	752.3	628.4
65°	410.4	425.8	442.6	476.2	536.8	565.2	598.8	659.4	692.9	622.0	514.9
67.5°	356.2	363.9	380.7	415.5	458.1	483.9	507.1	548.4	554.9	498.1	410.4
70°	305.8	308.4	323.9	344.5	376.8	392.3	411.6	436.2	436.2	389.7	320.0
72.5°	249.0	252.9	264.5	286.5	305.8	313.6	320.0	335.5	332.9	290.3	242.6
75°	200.0	202.6	211.6	222.0	229.7	243.9	249.0	246.5	245.2	209.0	181.9
77.5°	154.8	156.1	162.6	171.6	172.9	178.1	174.2	174.2	162.6	141.9	127.8
80°	113.6	114.8	117.4	120.0	120.0	120.0	120.0	113.6	105.8	92.9	89.0
82.5°	76.1	76.1	77.4	80.0	78.7	76.1	73.6	67.1	61.9	58.1	55.5
85°	45.2	45.2	46.5	45.2	40.0	38.7	36.1	34.8	33.6	32.3	32.3
87.5°	21.9	20.6	18.1	15.5	15.5	15.5	15.5	15.5	15.5	14.2	14.2
90°	1.0	2.8	4.5	6.3	8.0	8.9	9.7	11.2	12.7	14.3	15.8
92.5°	29.6	30.7	31.8	32.9	34.0	34.6	35.6	37.6	39.5	41.5	43.5
95°	64.2	64.6	65.1	65.5	66.0	66.2	67.3	69.5	71.7	73.9	76.1
97.5°	98.8	99.0	99.2	99.5	99.7	99.8	101.3	104.4	107.5	110.5	113.6
100°	138.3	138.3	138.3	138.3	138.3	138.3	139.7	142.6	145.5	148.3	151.2
102.5°	180.8	181.9	183.0	184.1	185.2	185.8	186.3	187.4	188.5	189.6	190.7
105°	225.3	226.4	227.5	228.6	229.7	230.3	231.0	232.3	233.6	234.9	236.2
107.5°	273.7	274.8	275.9	277.0	278.1	278.7	279.2	280.3	281.4	282.5	283.6
110°	324.1	325.2	326.3	327.4	328.5	329.1	329.4	330.1	330.7	331.4	332.0



TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	375.5	375.9	376.4	376.8	377.3	377.5	377.9	378.8	379.7	380.5	381.4
115°	425.9	426.8	427.7	428.6	429.5	429.9	430.1	430.5	431.0	431.4	431.8
117.5°	477.3	477.5	477.7	478.0	478.2	478.3	478.5	479.0	479.4	479.9	480.3
120°	524.7	525.8	526.9	528.0	529.1	529.7	529.8	530.0	530.3	530.5	530.7
122.5°	576.1	576.3	576.5	576.8	577.0	577.1	577.4	578.1	578.8	579.4	580.1
125°	621.6	622.9	624.2	625.5	626.8	627.5	627.6	627.8	628.1	628.3	628.5
127.5°	672.0	672.6	673.3	673.9	674.6	674.9	675.0	675.2	675.5	675.7	675.9
130°	716.4	717.5	718.6	719.7	720.8	721.4	721.6	722.1	722.5	723.0	723.4
132.5°	760.9	762.9	764.9	766.8	768.8	769.8	769.7	769.5	769.2	769.0	768.8
135°	808.4	809.7	811.0	812.3	813.6	814.3	814.4	814.6	814.9	815.1	815.3
137.5°	852.8	854.1	855.4	856.7	858.0	858.7	858.9	859.4	859.8	860.3	860.7
140°	895.3	896.4	897.5	898.6	899.7	900.3	900.6	901.3	901.9	902.6	903.2
142.5°	937.8	938.7	939.6	940.5	941.4	941.8	942.2	943.1	944.0	944.8	945.7
145°	979.3	980.2	981.1	982.0	982.9	983.3	983.6	984.3	984.9	985.6	986.2
147.5°	1017.8	1018.5	1019.1	1019.8	1020.5	1020.8	1021.0	1021.5	1021.9	1022.4	1022.8
150°	1056.4	1056.2	1056.0	1055.7	1055.5	1055.4	1055.8	1056.7	1057.6	1058.5	1059.4
152.5°	1088.0	1088.4	1088.9	1089.3	1089.8	1090.0	1090.1	1090.3	1090.6	1090.8	1091.0
155°	1120.6	1120.6	1120.6	1120.6	1120.6	1120.6	1120.7	1120.9	1121.2	1121.4	1121.6
157.5°	1150.3	1149.9	1149.4	1149.0	1148.5	1148.3	1148.4	1148.6	1148.9	1149.1	1149.3
160°	1176.0	1175.3	1174.7	1174.0	1173.3	1173.0	1173.1	1173.3	1173.6	1173.8	1174.0
162.5°	1198.7	1198.3	1197.8	1197.4	1196.9	1196.7	1196.7	1196.7	1196.7	1196.7	1196.7
165°	1218.5	1218.1	1217.6	1217.2	1216.7	1216.5	1216.6	1216.8	1217.1	1217.3	1217.5
167.5°	1236.2	1235.3	1234.5	1233.6	1232.7	1232.3	1232.3	1232.3	1232.3	1232.3	1232.3
170°	1250.1	1249.2	1248.3	1247.4	1246.5	1246.1	1246.1	1246.1	1246.1	1246.1	1246.1
172.5°	1260.0	1259.1	1258.2	1257.3	1256.4	1256.0	1256.0	1256.0	1256.0	1256.0	1256.0
175°	1266.9	1266.0	1265.1	1264.2	1263.3	1262.9	1262.9	1262.9	1262.9	1262.9	1262.9
177.5°	1271.8	1270.9	1270.1	1269.2	1268.3	1267.9	1267.8	1267.6	1267.3	1267.1	1266.9
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1640.1	1649.1	1656.9	1653.0	1668.5	1667.2	1669.8	1675.0	1676.2	1673.7	1668.5
5°	1729.1	1742.1	1764.0	1775.6	1773.0	1783.3	1788.5	1796.3	1804.0	1801.4	1801.4
7.5°	1828.5	1846.6	1868.5	1898.2	1902.1	1911.1	1926.6	1926.6	1935.6	1931.7	1930.5
10°	1915.0	1936.9	1971.7	1995.0	2005.3	2010.5	2025.9	2031.1	2041.4	2042.7	2042.7
12.5°	1985.9	2024.7	2047.9	2071.1	2076.3	2084.0	2095.6	2103.4	2107.2	2107.2	2103.4
15°	2023.4	2054.3	2081.4	2105.9	2120.1	2126.6	2138.2	2147.2	2152.4	2164.0	2166.6
17.5°	2038.8	2076.3	2120.1	2155.0	2179.5	2186.0	2209.2	2216.9	2227.2	2232.4	2238.9
20°	2060.8	2115.0	2167.9	2210.5	2233.7	2250.5	2275.0	2311.1	2321.4	2321.4	2317.6
22.5°	2080.1	2149.8	2222.1	2290.5	2309.8	2343.4	2388.5	2427.3	2442.7	2449.2	2444.0
25°	2103.4	2198.9	2293.1	2378.2	2431.1	2455.6	2516.3	2562.8	2580.8	2591.1	2593.7
27.5°	2143.4	2263.4	2383.4	2491.8	2546.0	2574.4	2637.6	2677.6	2699.5	2708.6	2702.1
30°	2188.5	2335.6	2475.0	2571.8	2607.9	2642.8	2684.1	2699.5	2694.4	2694.4	2713.7
32.5°	2235.0	2387.3	2511.1	2574.4	2587.3	2582.1	2565.3	2518.9	2491.8	2491.8	2508.6
35°	2260.8	2392.4	2455.6	2435.0	2384.7	2355.0	2263.4	2211.8	2153.7	2149.8	2169.2
37.5°	2246.6	2303.4	2277.6	2142.1	2073.7	2016.9	1873.7	1816.9	1774.3	1715.0	1806.6
40°	2147.2	2127.9	1993.7	1798.8	1722.7	1642.7	1529.1	1472.4	1413.0	1404.0	1425.9
42.5°	1979.5	1864.6	1668.5	1480.1	1402.7	1345.9	1259.4	1204.0	1166.5	1151.0	1176.9
45°	1770.4	1589.8	1393.6	1244.0	1158.8	1129.1	1050.4	1001.4	973.0	961.4	979.4
47.5°	1514.9	1333.0	1147.2	1020.7	970.4	940.7	887.8	845.2	820.7	813.0	820.7
50°	1286.5	1099.4	943.3	862.0	816.8	792.3	748.4	721.3	702.0	696.8	709.7
52.5°	1089.1	918.8	800.1	727.8	698.1	677.5	646.5	623.3	611.7	606.5	615.5
55°	912.3	774.2	678.8	616.8	594.9	582.0	554.9	542.0	529.1	527.8	536.8
57.5°	756.2	660.7	572.9	529.1	522.6	503.3	480.0	468.4	462.0	460.7	464.5
60°	629.7	544.6	491.6	452.9	443.9	428.4	415.5	407.8	400.0	397.4	400.0
62.5°	523.9	456.8	414.2	388.4	375.5	371.6	357.4	348.4	347.1	347.1	349.7
65°	432.3	375.5	348.4	327.8	318.7	314.9	304.5	298.1	299.4	299.4	300.7
67.5°	352.3	311.0	286.5	276.1	268.4	267.1	256.8	254.2	251.6	251.6	254.2
70°	280.0	254.2	236.1	231.0	229.7	220.7	216.8	215.5	211.6	212.9	212.9
72.5°	219.4	202.6	192.3	184.5	185.8	180.7	175.5	175.5	172.9	176.8	176.8
75°	162.6	154.8	147.1	144.5	147.1	144.5	140.7	139.4	140.7	139.4	139.4
77.5°	120.0	116.1	113.6	112.3	112.3	107.1	104.5	107.1	101.9	104.5	104.5
80°	83.9	78.7	77.4	74.8	76.1	72.3	73.6	71.0	71.0	71.0	71.0
82.5°	52.9	51.6	51.6	51.6	50.3	50.3	50.3	50.3	50.3	50.3	49.0
85°	32.3	31.0	31.0	31.0	29.7	29.7	29.7	29.7	29.7	29.7	29.7
87.5°	12.9	14.2	14.2	15.5	14.2	12.9	12.9	12.9	14.2	14.2	12.9
90°	16.9	18.0	19.1	20.2	20.8	21.1	21.8	22.4	23.1	23.7	23.1
92.5°	45.0	46.6	48.1	49.6	50.4	50.6	51.1	51.5	52.0	52.4	52.0
95°	77.6	79.2	80.7	82.2	83.0	83.2	83.7	84.1	84.6	85.0	84.6
97.5°	114.9	116.3	117.6	118.9	119.6	119.7	119.9	120.2	120.4	120.6	120.4
100°	153.2	155.2	157.1	159.1	160.1	160.3	160.8	161.2	161.7	162.1	161.7
102.5°	192.9	195.1	197.3	199.5	200.6	200.9	201.6	202.3	202.9	203.6	202.9
105°	237.5	238.8	240.1	241.4	242.1	242.4	243.1	243.8	244.4	245.1	244.4
107.5°	284.3	284.9	285.6	286.3	286.6	286.6	286.6	286.6	286.6	286.6	286.6
110°	332.7	333.3	334.0	334.7	335.0	334.9	334.7	334.4	334.2	334.0	334.2



TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	381.6	381.8	382.1	382.3	382.4	382.2	381.8	381.3	380.9	380.5	380.9
115°	431.6	431.4	431.2	431.0	430.9	430.8	430.6	430.3	430.1	429.9	430.1
117.5°	480.5	480.7	481.0	481.2	481.3	480.9	480.0	479.1	478.2	477.3	478.2
120°	530.7	530.7	530.7	530.7	530.7	530.3	529.4	528.5	527.6	526.7	527.6
122.5°	579.9	579.7	579.4	579.2	579.1	578.8	578.1	577.4	576.8	576.1	576.8
125°	628.1	627.6	627.2	626.7	626.5	626.4	626.2	625.9	625.7	625.5	625.7
127.5°	675.7	675.5	675.2	675.0	674.9	674.7	674.3	673.8	673.4	673.0	673.4
130°	723.2	723.0	722.7	722.5	722.4	722.2	721.7	721.3	720.8	720.4	720.8
132.5°	768.6	768.4	768.1	767.9	767.8	767.5	766.8	766.2	765.5	764.9	765.5
135°	815.3	815.3	815.3	815.3	815.3	814.9	814.0	813.1	812.2	811.3	812.2
137.5°	860.9	861.1	861.4	861.6	861.7	861.2	860.1	859.0	857.9	856.8	857.9
140°	903.6	904.1	904.5	905.0	905.2	904.7	903.6	902.5	901.4	900.3	901.4
142.5°	945.9	946.1	946.4	946.6	946.7	946.2	945.1	944.0	942.9	941.8	942.9
145°	986.2	986.2	986.2	986.2	986.2	985.9	985.2	984.6	983.9	983.3	983.9
147.5°	1023.5	1024.1	1024.8	1025.5	1025.8	1024.9	1023.1	1021.4	1019.6	1017.8	1019.6
150°	1059.4	1059.4	1059.4	1059.4	1059.4	1059.2	1058.7	1058.3	1057.8	1057.4	1057.8
152.5°	1091.6	1092.3	1092.9	1093.6	1093.9	1093.5	1092.6	1091.7	1090.9	1090.0	1090.9
155°	1122.5	1123.4	1124.3	1125.2	1125.6	1125.0	1123.9	1122.8	1121.7	1120.6	1121.7
157.5°	1150.2	1151.0	1151.9	1152.8	1153.2	1152.4	1150.9	1149.4	1147.8	1146.3	1147.8
160°	1174.9	1175.7	1176.6	1177.5	1177.9	1177.4	1176.3	1175.2	1174.1	1173.0	1174.1
162.5°	1197.8	1198.9	1200.0	1201.1	1201.7	1201.0	1199.7	1198.4	1197.0	1195.7	1197.0
165°	1218.4	1219.2	1220.1	1221.0	1221.4	1220.7	1219.4	1218.1	1216.8	1215.5	1216.8
167.5°	1233.6	1234.9	1236.2	1237.5	1238.2	1237.5	1236.2	1234.9	1233.6	1232.3	1233.6
170°	1247.4	1248.8	1250.1	1251.4	1252.1	1251.3	1249.8	1248.2	1246.7	1245.1	1246.7
172.5°	1257.3	1258.6	1259.9	1261.2	1261.9	1261.2	1259.9	1258.6	1257.3	1256.0	1257.3
175°	1264.2	1265.6	1266.9	1268.2	1268.9	1268.1	1266.6	1265.0	1263.5	1261.9	1263.5
177.5°	1268.2	1269.5	1270.8	1272.1	1272.8	1272.0	1270.5	1269.0	1267.4	1265.9	1267.4
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1675.0	1665.9	1669.8	1665.9	1662.0	1658.2	1649.1	1636.2	1625.9	1618.2	1616.9
5°	1804.0	1792.4	1784.6	1780.8	1773.0	1762.7	1745.9	1726.6	1703.3	1694.3	1676.2
7.5°	1922.7	1918.8	1900.8	1898.2	1893.0	1873.7	1845.3	1819.5	1789.8	1765.3	1742.1
10°	2035.0	2025.9	2013.0	1995.0	1992.4	1967.9	1940.8	1904.6	1865.9	1842.7	1801.4
12.5°	2104.7	2094.3	2080.1	2068.5	2062.1	2046.6	2009.2	1973.0	1938.2	1895.6	1859.5
15°	2155.0	2142.1	2116.3	2107.2	2099.5	2078.8	2051.8	2014.3	1967.9	1938.2	1886.6
17.5°	2223.4	2207.9	2182.1	2165.3	2151.1	2118.9	2080.1	2029.8	1985.9	1952.4	1905.9
20°	2302.1	2278.9	2245.3	2223.4	2202.7	2165.3	2111.1	2051.8	1988.5	1947.2	1899.5
22.5°	2432.4	2388.5	2335.6	2304.7	2276.3	2211.8	2147.2	2073.7	2002.7	1940.8	1882.7
25°	2558.9	2515.0	2449.2	2406.6	2362.7	2287.9	2202.7	2100.8	2010.5	1938.2	1862.1
27.5°	2676.3	2631.1	2570.5	2518.9	2476.3	2364.0	2251.8	2136.9	2022.1	1922.7	1845.3
30°	2703.4	2684.1	2637.6	2592.4	2553.7	2450.5	2320.2	2174.3	2036.3	1908.5	1822.1
32.5°	2539.5	2587.3	2598.9	2592.4	2567.9	2494.4	2374.4	2220.8	2056.9	1902.1	1783.3
35°	2198.9	2285.3	2374.4	2422.1	2445.3	2455.6	2384.7	2244.0	2071.1	1891.7	1757.5
37.5°	1823.3	1907.2	2047.9	2118.9	2197.6	2300.8	2329.2	2238.9	2064.7	1884.0	1716.2
40°	1498.2	1605.3	1721.4	1785.9	1854.3	2040.1	2180.8	2170.5	2044.0	1855.6	1684.0
42.5°	1219.4	1286.5	1388.5	1459.5	1543.3	1751.1	1939.5	2032.4	1982.1	1820.8	1642.7
45°	1016.8	1068.5	1140.7	1213.0	1264.6	1453.0	1676.2	1828.5	1876.3	1758.8	1579.5
47.5°	856.8	895.5	958.8	1003.9	1059.4	1207.8	1401.4	1615.6	1716.2	1671.1	1512.4
50°	734.2	765.2	815.5	843.9	893.0	1020.7	1167.8	1392.4	1544.6	1549.8	1423.3
52.5°	627.1	658.1	700.7	725.2	754.9	841.3	989.7	1179.4	1354.9	1419.5	1321.4
55°	545.8	563.9	598.8	618.1	645.2	729.1	823.3	984.6	1167.8	1273.6	1211.7
57.5°	471.0	490.4	512.3	527.8	547.1	614.2	699.4	820.7	1002.6	1117.5	1096.8
60°	410.4	422.0	442.6	454.2	472.3	516.2	575.5	696.8	841.3	949.7	961.4
62.5°	353.6	363.9	378.1	388.4	400.0	434.9	478.7	565.2	691.7	809.1	824.6
65°	304.5	313.6	321.3	330.3	339.4	361.3	398.7	465.8	563.9	673.6	707.1
67.5°	260.7	263.2	274.9	276.1	281.3	298.1	325.2	379.4	450.4	538.1	582.0
70°	218.1	223.2	225.8	229.7	234.9	246.5	268.4	296.8	349.7	420.7	462.0
72.5°	176.8	178.1	181.9	184.5	189.7	198.7	209.0	231.0	264.5	316.2	353.6
75°	140.7	141.9	144.5	145.8	149.7	152.3	157.4	172.9	196.1	227.1	254.2
77.5°	105.8	108.4	111.0	111.0	112.3	114.8	117.4	122.6	134.2	154.8	178.1
80°	72.3	73.6	73.6	74.8	73.6	77.4	81.3	87.7	92.9	99.4	111.0
82.5°	50.3	50.3	50.3	51.6	51.6	52.9	52.9	54.2	55.5	59.4	64.5
85°	31.0	31.0	32.3	29.7	31.0	32.3	32.3	31.0	32.3	33.6	34.8
87.5°	12.9	12.9	14.2	14.2	14.2	14.2	12.9	14.2	12.9	14.2	14.2
90°	22.4	21.8	21.1	20.8	20.2	19.1	18.0	16.9	15.8	14.3	12.7
92.5°	51.5	51.1	50.6	50.4	49.6	48.1	46.6	45.0	43.5	41.5	39.5
95°	84.1	83.7	83.2	83.0	82.2	80.7	79.2	77.6	76.1	73.9	71.7
97.5°	120.2	119.9	119.7	119.6	118.9	117.6	116.3	114.9	113.6	110.5	107.5
100°	161.2	160.8	160.3	160.1	159.1	157.1	155.2	153.2	151.2	148.3	145.5
102.5°	202.3	201.6	200.9	200.6	199.5	197.3	195.1	192.9	190.7	189.6	188.5
105°	243.8	243.1	242.4	242.1	241.4	240.1	238.8	237.5	236.2	234.9	233.6
107.5°	286.6	286.6	286.6	286.6	286.3	285.6	284.9	284.3	283.6	282.5	281.4
110°	334.4	334.7	334.9	335.0	334.7	334.0	333.3	332.7	332.0	331.4	330.7

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	381.3	381.8	382.2	382.4	382.3	382.1	381.8	381.6	381.4	380.5	379.7
115°	430.3	430.6	430.8	430.9	431.0	431.2	431.4	431.6	431.8	431.4	431.0
117.5°	479.1	480.0	480.9	481.3	481.2	481.0	480.7	480.5	480.3	479.9	479.4
120°	528.5	529.4	530.3	530.7	530.7	530.7	530.7	530.7	530.7	530.5	530.3
122.5°	577.4	578.1	578.8	579.1	579.2	579.4	579.7	579.9	580.1	579.4	578.8
125°	625.9	626.2	626.4	626.5	626.7	627.2	627.6	628.1	628.5	628.3	628.1
127.5°	673.8	674.3	674.7	674.9	675.0	675.2	675.5	675.7	675.9	675.7	675.5
130°	721.3	721.7	722.2	722.4	722.5	722.7	723.0	723.2	723.4	723.0	722.5
132.5°	766.2	766.8	767.5	767.8	767.9	768.1	768.4	768.6	768.8	769.0	769.2
135°	813.1	814.0	814.9	815.3	815.3	815.3	815.3	815.3	815.3	815.1	814.9
137.5°	859.0	860.1	861.2	861.7	861.6	861.4	861.1	860.9	860.7	860.3	859.8
140°	902.5	903.6	904.7	905.2	905.0	904.5	904.1	903.6	903.2	902.6	901.9
142.5°	944.0	945.1	946.2	946.7	946.6	946.4	946.1	945.9	945.7	944.8	944.0
145°	984.6	985.2	985.9	986.2	986.2	986.2	986.2	986.2	986.2	985.6	984.9
147.5°	1021.4	1023.1	1024.9	1025.8	1025.5	1024.8	1024.1	1023.5	1022.8	1022.4	1021.9
150°	1058.3	1058.7	1059.2	1059.4	1059.4	1059.4	1059.4	1059.4	1059.4	1058.5	1057.6
152.5°	1091.7	1092.6	1093.5	1093.9	1093.6	1092.9	1092.3	1091.6	1091.0	1090.8	1090.6
155°	1122.8	1123.9	1125.0	1125.6	1125.2	1124.3	1123.4	1122.5	1121.6	1121.4	1121.2
157.5°	1149.4	1150.9	1152.4	1153.2	1152.8	1151.9	1151.0	1150.2	1149.3	1149.1	1148.9
160°	1175.2	1176.3	1177.4	1177.9	1177.5	1176.6	1175.7	1174.9	1174.0	1173.8	1173.6
162.5°	1198.4	1199.7	1201.0	1201.7	1201.1	1200.0	1198.9	1197.8	1196.7	1196.7	1196.7
165°	1218.1	1219.4	1220.7	1221.4	1221.0	1220.1	1219.2	1218.4	1217.5	1217.3	1217.1
167.5°	1234.9	1236.2	1237.5	1238.2	1237.5	1236.2	1234.9	1233.6	1232.3	1232.3	1232.3
170°	1248.2	1249.8	1251.3	1252.1	1251.4	1250.1	1248.8	1247.4	1246.1	1246.1	1246.1
172.5°	1258.6	1259.9	1261.2	1261.9	1261.2	1259.9	1258.6	1257.3	1256.0	1256.0	1256.0
175°	1265.0	1266.6	1268.1	1268.9	1268.2	1266.9	1265.6	1264.2	1262.9	1262.9	1262.9
177.5°	1269.0	1270.5	1272.0	1272.8	1272.1	1270.8	1269.5	1268.2	1266.9	1267.1	1267.3
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1613.0	1605.3	1600.1	1598.8	1591.1	1584.6	1576.9	1575.6	1571.7	1561.4	1554.9
5°	1663.3	1645.3	1641.4	1629.8	1610.4	1596.2	1578.2	1567.8	1556.2	1536.9	1521.4
7.5°	1715.0	1690.4	1672.4	1655.6	1628.5	1602.7	1576.9	1556.2	1535.6	1507.2	1484.0
10°	1765.3	1727.9	1705.9	1681.4	1644.0	1605.3	1569.1	1539.5	1505.9	1472.4	1438.8
12.5°	1811.7	1764.0	1731.7	1696.9	1650.4	1602.7	1556.2	1514.9	1480.1	1434.9	1397.5
15°	1840.1	1787.2	1755.0	1721.4	1651.7	1598.8	1544.6	1491.7	1445.3	1397.5	1362.7
17.5°	1856.9	1797.5	1761.4	1730.4	1659.5	1587.2	1517.5	1460.7	1410.4	1353.6	1307.2
20°	1849.2	1791.1	1757.5	1727.9	1645.3	1573.0	1498.2	1432.4	1369.1	1311.1	1262.0
22.5°	1832.4	1771.7	1734.3	1707.2	1633.7	1548.5	1465.9	1394.9	1329.1	1271.1	1215.6
25°	1796.3	1736.9	1704.6	1671.1	1598.8	1517.5	1433.6	1357.5	1287.8	1225.9	1163.9
27.5°	1764.0	1691.7	1658.2	1628.5	1552.4	1480.1	1397.5	1313.6	1242.7	1178.1	1116.2
30°	1726.6	1645.3	1609.1	1569.1	1500.7	1432.4	1349.8	1272.3	1198.8	1130.4	1071.0
32.5°	1686.6	1592.4	1551.1	1505.9	1436.2	1371.7	1302.0	1225.9	1152.3	1085.2	1023.3
35°	1634.9	1534.3	1486.6	1444.0	1371.7	1307.2	1242.7	1179.4	1105.9	1034.9	975.5
37.5°	1585.9	1474.9	1424.6	1375.6	1299.4	1237.5	1184.6	1125.2	1054.3	985.9	929.1
40°	1530.4	1402.7	1351.1	1305.9	1227.2	1158.8	1111.0	1064.6	1002.6	936.8	874.9
42.5°	1480.1	1335.6	1281.4	1234.9	1152.3	1087.8	1042.7	1003.9	949.7	889.1	825.9
45°	1410.4	1263.3	1207.8	1158.8	1074.9	1014.3	967.8	934.3	891.7	834.9	778.1
47.5°	1345.9	1193.6	1133.0	1073.6	997.5	935.5	893.0	867.2	838.8	788.4	730.4
50°	1267.2	1113.6	1051.7	1002.6	916.2	863.3	820.7	802.6	776.8	729.1	682.6
52.5°	1182.0	1036.2	978.1	918.8	838.8	787.1	749.7	729.1	708.4	673.6	629.7
55°	1082.7	949.7	895.5	842.6	762.6	714.9	681.3	659.4	647.8	615.5	583.3
57.5°	987.2	862.0	811.7	762.6	692.9	638.8	616.8	597.5	580.7	557.5	530.4
60°	890.4	776.8	722.6	678.8	618.1	569.1	551.0	531.6	518.7	500.7	481.3
62.5°	779.4	682.6	641.3	600.0	548.4	509.7	489.1	473.6	456.8	445.2	428.4
65°	662.0	593.6	553.6	522.6	473.6	438.7	423.3	412.9	398.7	387.1	374.2
67.5°	552.3	498.1	481.3	447.8	410.4	379.4	367.8	354.9	343.2	336.8	325.2
70°	446.5	407.8	391.0	382.0	340.7	320.0	309.7	304.5	290.3	283.9	276.1
72.5°	345.8	331.6	320.0	308.4	281.3	268.4	256.8	251.6	241.3	236.1	233.6
75°	255.5	246.5	240.0	238.7	227.1	214.2	202.6	200.0	192.3	187.1	184.5
77.5°	179.4	176.8	175.5	176.8	169.0	161.3	158.7	156.1	147.1	145.8	145.8
80°	117.4	123.9	123.9	122.6	120.0	118.7	114.8	112.3	107.1	105.8	107.1
82.5°	72.3	76.1	77.4	80.0	78.7	77.4	74.8	73.6	74.8	72.3	73.6
85°	36.1	38.7	43.9	43.9	45.2	45.2	45.2	43.9	41.3	42.6	41.3
87.5°	14.2	15.5	15.5	15.5	14.2	18.1	19.4	19.4	19.4	16.8	16.8
90°	11.2	9.7	8.9	8.0	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	37.6	35.6	34.6	34.0	32.9	31.8	30.7	29.6	30.7	31.8	32.9
95°	69.5	67.3	66.2	66.0	65.5	65.1	64.6	64.2	64.6	65.1	65.5
97.5°	104.4	101.3	99.8	99.7	99.5	99.2	99.0	98.8	99.0	99.2	99.5
100°	142.6	139.7	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3
102.5°	187.4	186.3	185.8	185.2	184.1	183.0	181.9	180.8	181.9	183.0	184.1
105°	232.3	231.0	230.3	229.7	228.6	227.5	226.4	225.3	226.4	227.5	228.6
107.5°	280.3	279.2	278.7	278.1	277.0	275.9	274.8	273.7	274.8	275.9	277.0
110°	330.1	329.4	329.1	328.5	327.4	326.3	325.2	324.1	325.2	326.3	327.4

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	378.8	377.9	377.5	377.3	376.8	376.4	375.9	375.5	375.9	376.4	376.8
115°	430.5	430.1	429.9	429.5	428.6	427.7	426.8	425.9	426.8	427.7	428.6
117.5°	479.0	478.5	478.3	478.2	478.0	477.7	477.5	477.3	477.5	477.7	478.0
120°	530.0	529.8	529.7	529.1	528.0	526.9	525.8	524.7	525.8	526.9	528.0
122.5°	578.1	577.4	577.1	577.0	576.8	576.5	576.3	576.1	576.3	576.5	576.8
125°	627.8	627.6	627.5	626.8	625.5	624.2	622.9	621.6	622.9	624.2	625.5
127.5°	675.2	675.0	674.9	674.6	673.9	673.3	672.6	672.0	672.6	673.3	673.9
130°	722.1	721.6	721.4	720.8	719.7	718.6	717.5	716.4	717.5	718.6	719.7
132.5°	769.5	769.7	769.8	768.8	766.8	764.9	762.9	760.9	762.9	764.9	766.8
135°	814.6	814.4	814.3	813.6	812.3	811.0	809.7	808.4	809.7	811.0	812.3
137.5°	859.4	858.9	858.7	858.0	856.7	855.4	854.1	852.8	854.1	855.4	856.7
140°	901.3	900.6	900.3	899.7	898.6	897.5	896.4	895.3	896.4	897.5	898.6
142.5°	943.1	942.2	941.8	941.4	940.5	939.6	938.7	937.8	938.7	939.6	940.5
145°	984.3	983.6	983.3	982.9	982.0	981.1	980.2	979.3	980.2	981.1	982.0
147.5°	1021.5	1021.0	1020.8	1020.5	1019.8	1019.1	1018.5	1017.8	1018.5	1019.1	1019.8
150°	1056.7	1055.8	1055.4	1055.5	1055.7	1056.0	1056.2	1056.4	1056.2	1056.0	1055.7
152.5°	1090.3	1090.1	1090.0	1089.8	1089.3	1088.9	1088.4	1088.0	1088.4	1088.9	1089.3
155°	1120.9	1120.7	1120.6	1120.6	1120.6	1120.6	1120.6	1120.6	1120.6	1120.6	1120.6
157.5°	1148.6	1148.4	1148.3	1148.5	1149.0	1149.4	1149.9	1150.3	1149.9	1149.4	1149.0
160°	1173.3	1173.1	1173.0	1173.3	1174.0	1174.7	1175.3	1176.0	1175.3	1174.7	1174.0
162.5°	1196.7	1196.7	1196.7	1196.9	1197.4	1197.8	1198.3	1198.7	1198.3	1197.8	1197.4
165°	1216.8	1216.6	1216.5	1216.7	1217.2	1217.6	1218.1	1218.5	1218.1	1217.6	1217.2
167.5°	1232.3	1232.3	1232.3	1232.7	1233.6	1234.5	1235.3	1236.2	1235.3	1234.5	1233.6
170°	1246.1	1246.1	1246.1	1246.5	1247.4	1248.3	1249.2	1250.1	1249.2	1248.3	1247.4
172.5°	1256.0	1256.0	1256.0	1256.4	1257.3	1258.2	1259.1	1260.0	1259.1	1258.2	1257.3
175°	1262.9	1262.9	1262.9	1263.3	1264.2	1265.1	1266.0	1266.9	1266.0	1265.1	1264.2
177.5°	1267.6	1267.8	1267.9	1268.3	1269.2	1270.1	1270.9	1271.8	1270.9	1270.1	1269.2
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1551.1	1545.9	1542.0	1538.2	1521.4	1503.3	1500.7	1496.9	1489.1	1498.2	1494.3
5°	1511.1	1499.5	1493.0	1476.2	1455.6	1440.1	1427.2	1411.7	1405.3	1400.1	1398.8
7.5°	1462.0	1451.7	1440.1	1423.3	1397.5	1371.7	1352.3	1336.9	1324.0	1317.5	1317.5
10°	1414.3	1401.4	1385.9	1357.5	1333.0	1300.7	1280.1	1264.6	1246.5	1236.2	1227.2
12.5°	1365.3	1351.1	1336.9	1300.7	1272.3	1238.8	1209.1	1189.8	1180.7	1169.1	1153.6
15°	1316.2	1294.3	1280.1	1244.0	1207.8	1174.3	1154.9	1134.3	1113.6	1102.0	1096.8
17.5°	1264.6	1249.1	1225.9	1187.2	1147.2	1117.5	1089.1	1069.7	1045.2	1033.6	1022.0
20°	1218.1	1194.9	1171.7	1133.0	1094.3	1054.3	1025.9	1002.6	987.2	978.1	967.8
22.5°	1162.7	1140.7	1121.4	1080.1	1037.5	1000.1	969.1	954.9	939.4	925.2	914.9
25°	1114.9	1093.0	1073.6	1028.5	982.0	947.2	923.9	905.9	889.1	882.6	872.3
27.5°	1064.6	1043.9	1018.1	973.0	931.7	902.0	877.5	860.7	847.8	834.9	827.2
30°	1016.8	993.6	970.4	921.4	887.8	858.1	834.9	814.2	803.9	797.5	784.6
32.5°	970.4	940.7	921.4	876.2	843.9	815.5	796.2	778.1	765.2	753.6	743.3
35°	920.1	887.8	868.4	831.0	797.5	769.1	752.3	739.4	723.9	713.6	708.4
37.5°	872.3	845.2	825.9	787.1	753.6	730.4	712.3	695.5	689.1	674.9	672.3
40°	820.7	797.5	779.4	742.0	711.0	692.9	673.6	658.1	646.5	640.0	631.0
42.5°	774.2	754.9	735.5	700.7	671.0	649.1	634.9	620.7	610.4	600.0	593.6
45°	731.7	711.0	692.9	659.4	629.7	610.4	596.2	579.4	576.8	562.6	556.2
47.5°	686.5	668.4	652.9	618.1	591.0	571.7	554.9	543.3	531.6	526.5	517.5
50°	642.6	624.6	606.5	575.5	551.0	531.6	514.9	502.0	495.5	487.8	480.0
52.5°	594.9	580.7	566.5	534.2	509.7	492.9	478.7	462.0	455.5	449.1	443.9
55°	554.9	534.2	518.7	491.6	469.7	451.6	436.2	423.3	416.8	411.6	405.2
57.5°	500.7	487.8	474.9	450.4	429.7	411.6	396.2	385.8	378.1	374.2	375.5
60°	454.2	440.0	432.3	406.5	385.8	371.6	357.4	347.1	339.4	335.5	334.2
62.5°	405.2	394.9	380.7	362.6	342.0	329.1	318.7	311.0	298.1	296.8	292.9
65°	357.4	349.7	336.8	320.0	303.2	291.6	280.0	269.7	264.5	258.1	254.2
67.5°	311.0	303.2	291.6	277.4	265.8	254.2	243.9	233.6	224.5	219.4	216.8
70°	265.8	259.4	251.6	234.9	220.7	211.6	203.9	197.4	188.4	185.8	184.5
72.5°	222.0	215.5	211.6	197.4	184.5	176.8	169.0	162.6	158.7	157.4	153.6
75°	181.9	175.5	170.3	157.4	149.7	144.5	136.8	134.2	130.3	129.0	127.8
77.5°	141.9	135.5	134.2	125.2	116.1	113.6	111.0	105.8	105.8	105.8	103.2
80°	101.9	100.7	99.4	90.3	86.5	83.9	82.6	78.7	76.1	73.6	72.3
82.5°	68.4	67.1	65.8	61.9	58.1	56.8	55.5	52.9	52.9	54.2	51.6
85°	41.3	38.7	37.4	36.1	33.6	33.6	34.8	33.6	33.6	33.6	32.3
87.5°	15.5	15.5	15.5	15.5	16.8	14.2	15.5	15.5	14.2	14.2	12.9
90°	8.0	8.9	9.7	11.2	12.7	14.3	15.8	16.9	18.0	19.1	20.2
92.5°	34.0	34.6	35.6	37.6	39.5	41.5	43.5	45.0	46.6	48.1	49.6
95°	66.0	66.2	67.3	69.5	71.7	73.9	76.1	77.6	79.2	80.7	82.2
97.5°	99.7	99.8	101.3	104.4	107.5	110.5	113.6	114.9	116.3	117.6	118.9
100°	138.3	138.3	139.7	142.6	145.5	148.3	151.2	153.2	155.2	157.1	159.1
102.5°	185.2	185.8	186.3	187.4	188.5	189.6	190.7	192.9	195.1	197.3	199.5
105°	229.7	230.3	231.0	232.3	233.6	234.9	236.2	237.5	238.8	240.1	241.4
107.5°	278.1	278.7	279.2	280.3	281.4	282.5	283.6	284.3	284.9	285.6	286.3
110°	328.5	329.1	329.4	330.1	330.7	331.4	332.0	332.7	333.3	334.0	334.7



TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	377.3	377.5	377.9	378.8	379.7	380.5	381.4	381.6	381.8	382.1	382.3
115°	429.5	429.9	430.1	430.5	431.0	431.4	431.8	431.6	431.4	431.2	431.0
117.5°	478.2	478.3	478.5	479.0	479.4	479.9	480.3	480.5	480.7	481.0	481.2
120°	529.1	529.7	529.8	530.0	530.3	530.5	530.7	530.7	530.7	530.7	530.7
122.5°	577.0	577.1	577.4	578.1	578.8	579.4	580.1	579.9	579.7	579.4	579.2
125°	626.8	627.5	627.6	627.8	628.1	628.3	628.5	628.1	627.6	627.2	626.7
127.5°	674.6	674.9	675.0	675.2	675.5	675.7	675.9	675.7	675.5	675.2	675.0
130°	720.8	721.4	721.6	722.1	722.5	723.0	723.4	723.2	723.0	722.7	722.5
132.5°	768.8	769.8	769.7	769.5	769.2	769.0	768.8	768.6	768.4	768.1	767.9
135°	813.6	814.3	814.4	814.6	814.9	815.1	815.3	815.3	815.3	815.3	815.3
137.5°	858.0	858.7	858.9	859.4	859.8	860.3	860.7	860.9	861.1	861.4	861.6
140°	899.7	900.3	900.6	901.3	901.9	902.6	903.2	903.6	904.1	904.5	905.0
142.5°	941.4	941.8	942.2	943.1	944.0	944.8	945.7	945.9	946.1	946.4	946.6
145°	982.9	983.3	983.6	984.3	984.9	985.6	986.2	986.2	986.2	986.2	986.2
147.5°	1020.5	1020.8	1021.0	1021.5	1021.9	1022.4	1022.8	1023.5	1024.1	1024.8	1025.5
150°	1055.5	1055.4	1055.8	1056.7	1057.6	1058.5	1059.4	1059.4	1059.4	1059.4	1059.4
152.5°	1089.8	1090.0	1090.1	1090.3	1090.6	1090.8	1091.0	1091.6	1092.3	1092.9	1093.6
155°	1120.6	1120.6	1120.7	1120.9	1121.2	1121.4	1121.6	1122.5	1123.4	1124.3	1125.2
157.5°	1148.5	1148.3	1148.4	1148.6	1148.9	1149.1	1149.3	1150.2	1151.0	1151.9	1152.8
160°	1173.3	1173.0	1173.1	1173.3	1173.6	1173.8	1174.0	1174.9	1175.7	1176.6	1177.5
162.5°	1196.9	1196.7	1196.7	1196.7	1196.7	1196.7	1196.7	1197.8	1198.9	1200.0	1201.1
165°	1216.7	1216.5	1216.6	1216.8	1217.1	1217.3	1217.5	1218.4	1219.2	1220.1	1221.0
167.5°	1232.7	1232.3	1232.3	1232.3	1232.3	1232.3	1232.3	1233.6	1234.9	1236.2	1237.5
170°	1246.5	1246.1	1246.1	1246.1	1246.1	1246.1	1246.1	1247.4	1248.8	1250.1	1251.4
172.5°	1256.4	1256.0	1256.0	1256.0	1256.0	1256.0	1256.0	1257.3	1258.6	1259.9	1261.2
175°	1263.3	1262.9	1262.9	1262.9	1262.9	1262.9	1262.9	1264.2	1265.6	1266.9	1268.2
177.5°	1268.3	1267.9	1267.8	1267.6	1267.3	1267.1	1266.9	1268.2	1269.5	1270.8	1272.1
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1487.8	1490.4	1484.0	1481.4	1476.2	1482.7	1484.0	1482.7	1494.3	1489.1	1491.7
5°	1401.4	1396.2	1392.4	1383.3	1383.3	1384.6	1388.5	1382.0	1385.9	1394.9	1393.6
7.5°	1305.9	1303.3	1304.6	1294.3	1286.5	1289.1	1286.5	1298.2	1304.6	1302.0	1307.2
10°	1219.4	1224.6	1213.0	1207.8	1202.7	1207.8	1206.5	1209.1	1216.9	1222.0	1231.1
12.5°	1149.8	1148.5	1142.0	1136.9	1127.8	1130.4	1138.1	1135.6	1136.9	1148.5	1147.2
15°	1083.9	1076.2	1071.0	1059.4	1062.0	1053.0	1060.7	1069.7	1073.6	1083.9	1090.4
17.5°	1018.1	1016.8	1010.4	1009.1	994.9	991.0	998.8	1001.4	1005.2	1010.4	1019.4
20°	962.6	961.4	952.3	949.7	938.1	945.9	943.3	948.5	951.0	961.4	965.2
22.5°	912.3	905.9	903.3	899.4	895.5	894.3	899.4	898.1	907.2	911.0	912.3
25°	865.9	860.7	859.4	853.0	850.4	846.5	850.4	854.3	864.6	868.4	873.6
27.5°	823.3	819.4	816.8	811.7	807.8	807.8	810.4	815.5	819.4	822.0	824.6
30°	784.6	782.0	774.2	771.7	767.8	767.8	767.8	770.4	776.8	784.6	788.4
32.5°	744.6	739.4	734.2	734.2	730.4	730.4	731.7	734.2	740.7	742.0	748.4
35°	705.9	700.7	696.8	694.2	695.5	690.4	692.9	696.8	704.6	707.1	711.0
37.5°	668.4	667.1	659.4	655.5	658.1	658.1	656.8	659.4	664.6	669.7	672.3
40°	627.1	624.6	624.6	620.7	622.0	616.8	620.7	623.3	625.8	631.0	634.9
42.5°	591.0	588.4	583.3	584.6	580.7	580.7	583.3	584.6	588.4	594.9	597.5
45°	552.3	552.3	549.7	545.8	547.1	543.3	545.8	547.1	552.3	558.7	556.2
47.5°	514.9	513.6	513.6	508.4	511.0	507.1	511.0	512.3	514.9	518.7	517.5
50°	478.7	474.9	476.2	474.9	473.6	473.6	476.2	476.2	478.7	478.7	482.6
52.5°	441.3	441.3	438.7	440.0	442.6	440.0	443.9	440.0	442.6	443.9	446.5
55°	407.8	405.2	406.5	405.2	410.4	406.5	410.4	407.8	410.4	409.1	411.6
57.5°	371.6	367.8	369.1	367.8	371.6	370.3	374.2	370.3	371.6	372.9	376.8
60°	330.3	330.3	330.3	327.8	331.6	331.6	330.3	330.3	335.5	338.1	336.8
62.5°	291.6	290.3	286.5	285.2	286.5	283.9	289.1	287.8	290.3	292.9	295.5
65°	249.0	246.5	245.2	242.6	242.6	241.3	242.6	247.8	249.0	250.3	256.8
67.5°	214.2	212.9	211.6	207.8	207.8	210.3	210.3	210.3	218.1	214.2	219.4
70°	183.2	180.7	178.1	176.8	176.8	178.1	179.4	180.7	179.4	184.5	185.8
72.5°	153.6	154.8	152.3	152.3	152.3	151.0	151.0	153.6	154.8	153.6	154.8
75°	127.8	127.8	126.5	127.8	127.8	126.5	126.5	129.0	129.0	127.8	131.6
77.5°	103.2	101.9	99.4	96.8	98.1	96.8	98.1	96.8	100.7	104.5	101.9
80°	72.3	71.0	71.0	71.0	72.3	71.0	73.6	71.0	72.3	72.3	73.6
82.5°	51.6	52.9	52.9	51.6	52.9	51.6	52.9	52.9	52.9	51.6	52.9
85°	33.6	33.6	33.6	33.6	32.3	33.6	33.6	33.6	34.8	33.6	34.8
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	15.5	14.2	15.5
90°	20.8	21.1	21.8	22.4	23.1	23.7	23.1	22.4	21.8	21.1	20.8
92.5°	50.4	50.6	51.1	51.5	52.0	52.4	52.0	51.5	51.1	50.6	50.4
95°	83.0	83.2	83.7	84.1	84.6	85.0	84.6	84.1	83.7	83.2	83.0
97.5°	119.6	119.7	119.9	120.2	120.4	120.6	120.4	120.2	119.9	119.7	119.6
100°	160.1	160.3	160.8	161.2	161.7	162.1	161.7	161.2	160.8	160.3	160.1
102.5°	200.6	200.9	201.6	202.3	202.9	203.6	202.9	202.3	201.6	200.9	200.6
105°	242.1	242.4	243.1	243.8	244.4	245.1	244.4	243.8	243.1	242.4	242.1
107.5°	286.6	286.6	286.6	286.6	286.6	286.6	286.6	286.6	286.6	286.6	286.6
110°	335.0	334.9	334.7	334.4	334.2	334.0	334.2	334.4	334.7	334.9	335.0

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	382.4	382.2	381.8	381.3	380.9	380.5	380.9	381.3	381.8	382.2	382.4
115°	430.9	430.8	430.6	430.3	430.1	429.9	430.1	430.3	430.6	430.8	430.9
117.5°	481.3	480.9	480.0	479.1	478.2	477.3	478.2	479.1	480.0	480.9	481.3
120°	530.7	530.3	529.4	528.5	527.6	526.7	527.6	528.5	529.4	530.3	530.7
122.5°	579.1	578.8	578.1	577.4	576.8	576.1	576.8	577.4	578.1	578.8	579.1
125°	626.5	626.4	626.2	625.9	625.7	625.5	625.7	625.9	626.2	626.4	626.5
127.5°	674.9	674.7	674.3	673.8	673.4	673.0	673.4	673.8	674.3	674.7	674.9
130°	722.4	722.2	721.7	721.3	720.8	720.4	720.8	721.3	721.7	722.2	722.4
132.5°	767.8	767.5	766.8	766.2	765.5	764.9	765.5	766.2	766.8	767.5	767.8
135°	815.3	814.9	814.0	813.1	812.2	811.3	812.2	813.1	814.0	814.9	815.3
137.5°	861.7	861.2	860.1	859.0	857.9	856.8	857.9	859.0	860.1	861.2	861.7
140°	905.2	904.7	903.6	902.5	901.4	900.3	901.4	902.5	903.6	904.7	905.2
142.5°	946.7	946.2	945.1	944.0	942.9	941.8	942.9	944.0	945.1	946.2	946.7
145°	986.2	985.9	985.2	984.6	983.9	983.3	983.9	984.6	985.2	985.9	986.2
147.5°	1025.8	1024.9	1023.1	1021.4	1019.6	1017.8	1019.6	1021.4	1023.1	1024.9	1025.8
150°	1059.4	1059.2	1058.7	1058.3	1057.8	1057.4	1057.8	1058.3	1058.7	1059.2	1059.4
152.5°	1093.9	1093.5	1092.6	1091.7	1090.9	1090.0	1090.9	1091.7	1092.6	1093.5	1093.9
155°	1125.6	1125.0	1123.9	1122.8	1121.7	1120.6	1121.7	1122.8	1123.9	1125.0	1125.6
157.5°	1153.2	1152.4	1150.9	1149.4	1147.8	1146.3	1147.8	1149.4	1150.9	1152.4	1153.2
160°	1177.9	1177.4	1176.3	1175.2	1174.1	1173.0	1174.1	1175.2	1176.3	1177.4	1177.9
162.5°	1201.7	1201.0	1199.7	1198.4	1197.0	1195.7	1197.0	1198.4	1199.7	1201.0	1201.7
165°	1221.4	1220.7	1219.4	1218.1	1216.8	1215.5	1216.8	1218.1	1219.4	1220.7	1221.4
167.5°	1238.2	1237.5	1236.2	1234.9	1233.6	1232.3	1233.6	1234.9	1236.2	1237.5	1238.2
170°	1252.1	1251.3	1249.8	1248.2	1246.7	1245.1	1246.7	1248.2	1249.8	1251.3	1252.1
172.5°	1261.9	1261.2	1259.9	1258.6	1257.3	1256.0	1257.3	1258.6	1259.9	1261.2	1261.9
175°	1268.9	1268.1	1266.6	1265.0	1263.5	1261.9	1263.5	1265.0	1266.6	1268.1	1268.9
177.5°	1272.8	1272.0	1270.5	1269.0	1267.4	1265.9	1267.4	1269.0	1270.5	1272.0	1272.8
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1486.6	1493.0	1487.8	1484.0	1494.3	1499.5	1499.5	1508.5	1517.5	1525.3	1526.6
5°	1394.9	1405.3	1407.8	1406.5	1422.0	1429.8	1446.5	1455.6	1468.5	1477.5	1487.8
7.5°	1311.1	1325.3	1326.5	1329.1	1352.3	1365.3	1379.4	1402.7	1420.7	1433.6	1445.3
10°	1227.2	1236.2	1245.2	1256.9	1280.1	1302.0	1322.7	1347.2	1370.4	1383.3	1400.1
12.5°	1163.9	1170.4	1180.7	1188.5	1213.0	1232.3	1259.4	1293.0	1326.5	1336.9	1357.5
15°	1098.1	1102.0	1122.7	1130.4	1151.0	1183.3	1200.1	1232.3	1268.5	1287.8	1311.1
17.5°	1022.0	1045.2	1058.1	1067.2	1093.0	1118.8	1145.9	1179.4	1225.9	1244.0	1260.7
20°	967.8	984.6	998.8	1010.4	1033.6	1072.3	1096.8	1123.9	1167.8	1188.5	1213.0
22.5°	920.1	934.3	947.2	960.1	975.5	1010.4	1038.8	1076.2	1120.1	1139.4	1167.8
25°	874.9	889.1	896.8	912.3	933.0	957.5	991.0	1024.6	1068.5	1090.4	1117.5
27.5°	831.0	845.2	859.4	872.3	886.5	909.7	933.0	975.5	1020.7	1046.5	1069.7
30°	793.6	800.1	813.0	827.2	841.3	863.3	890.4	920.1	971.7	994.9	1023.3
32.5°	752.3	763.9	773.0	783.3	801.3	819.4	843.9	881.3	922.6	944.6	975.5
35°	713.6	723.9	730.4	748.4	760.1	779.4	803.9	837.5	872.3	896.8	923.9
37.5°	676.2	686.5	694.2	704.6	720.0	736.8	762.6	787.1	828.4	849.1	880.1
40°	637.5	646.5	655.5	667.1	681.3	702.0	717.5	748.4	782.0	805.2	828.4
42.5°	600.0	605.2	615.5	628.4	642.6	660.7	682.6	707.1	740.7	761.3	782.0
45°	560.0	569.1	580.7	589.7	602.6	620.7	640.0	662.0	695.5	716.2	738.1
47.5°	522.6	529.1	536.8	551.0	567.8	580.7	601.3	622.0	652.9	672.3	692.9
50°	483.9	490.4	502.0	511.0	523.9	540.7	560.0	582.0	611.7	624.6	645.2
52.5°	447.8	450.4	462.0	471.0	483.9	503.3	518.7	538.1	566.5	580.7	601.3
55°	411.6	414.2	420.7	429.7	443.9	459.4	476.2	498.1	522.6	535.5	554.9
57.5°	374.2	376.8	383.3	389.7	403.9	418.1	437.4	455.5	480.0	491.6	509.7
60°	336.8	336.8	343.2	352.3	362.6	375.5	392.3	414.2	432.3	446.5	459.4
62.5°	296.8	300.7	304.5	311.0	322.6	338.1	352.3	367.8	389.7	400.0	411.6
65°	256.8	260.7	268.4	274.9	283.9	294.2	312.3	325.2	342.0	353.6	363.9
67.5°	222.0	225.8	231.0	238.7	245.2	256.8	269.7	282.6	300.7	308.4	316.2
70°	185.8	189.7	193.6	203.9	210.3	219.4	228.4	241.3	256.8	262.0	268.4
72.5°	157.4	158.7	163.9	166.5	175.5	183.2	193.6	201.3	212.9	219.4	224.5
75°	132.9	132.9	134.2	136.8	141.9	147.1	154.8	162.6	172.9	176.8	183.2
77.5°	104.5	108.4	107.1	109.7	112.3	114.8	121.3	126.5	136.8	139.4	141.9
80°	74.8	76.1	80.0	83.9	83.9	87.7	91.6	92.9	99.4	103.2	103.2
82.5°	54.2	55.5	54.2	55.5	56.8	58.1	61.9	67.1	67.1	68.4	71.0
85°	33.6	33.6	34.8	36.1	36.1	34.8	37.4	36.1	37.4	40.0	40.0
87.5°	16.8	15.5	15.5	15.5	15.5	15.5	16.8	15.5	16.8	16.8	16.8
90°	20.2	19.1	18.0	16.9	15.8	14.3	12.7	11.2	9.7	8.9	8.0
92.5°	49.6	48.1	46.6	45.0	43.5	41.5	39.5	37.6	35.6	34.6	34.0
95°	82.2	80.7	79.2	77.6	76.1	73.9	71.7	69.5	67.3	66.2	66.0
97.5°	118.9	117.6	116.3	114.9	113.6	110.5	107.5	104.4	101.3	99.8	99.7
100°	159.1	157.1	155.2	153.2	151.2	148.3	145.5	142.6	139.7	138.3	138.3
102.5°	199.5	197.3	195.1	192.9	190.7	189.6	188.5	187.4	186.3	185.8	185.2
105°	241.4	240.1	238.8	237.5	236.2	234.9	233.6	232.3	231.0	230.3	229.7
107.5°	286.3	285.6	284.9	284.3	283.6	282.5	281.4	280.3	279.2	278.7	278.1
110°	334.7	334.0	333.3	332.7	332.0	331.4	330.7	330.1	329.4	329.1	328.5

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	382.3	382.1	381.8	381.6	381.4	380.5	379.7	378.8	377.9	377.5	377.3
115°	431.0	431.2	431.4	431.6	431.8	431.4	431.0	430.5	430.1	429.9	429.5
117.5°	481.2	481.0	480.7	480.5	480.3	479.9	479.4	479.0	478.5	478.3	478.2
120°	530.7	530.7	530.7	530.7	530.7	530.5	530.3	530.0	529.8	529.7	529.1
122.5°	579.2	579.4	579.7	579.9	580.1	579.4	578.8	578.1	577.4	577.1	577.0
125°	626.7	627.2	627.6	628.1	628.5	628.3	628.1	627.8	627.6	627.5	626.8
127.5°	675.0	675.2	675.5	675.7	675.9	675.7	675.5	675.2	675.0	674.9	674.6
130°	722.5	722.7	723.0	723.2	723.4	723.0	722.5	722.1	721.6	721.4	720.8
132.5°	767.9	768.1	768.4	768.6	768.8	769.0	769.2	769.5	769.7	769.8	768.8
135°	815.3	815.3	815.3	815.3	815.3	815.1	814.9	814.6	814.4	814.3	813.6
137.5°	861.6	861.4	861.1	860.9	860.7	860.3	859.8	859.4	858.9	858.7	858.0
140°	905.0	904.5	904.1	903.6	903.2	902.6	901.9	901.3	900.6	900.3	899.7
142.5°	946.6	946.4	946.1	945.9	945.7	944.8	944.0	943.1	942.2	941.8	941.4
145°	986.2	986.2	986.2	986.2	986.2	985.6	984.9	984.3	983.6	983.3	982.9
147.5°	1025.5	1024.8	1024.1	1023.5	1022.8	1022.4	1021.9	1021.5	1021.0	1020.8	1020.5
150°	1059.4	1059.4	1059.4	1059.4	1059.4	1058.5	1057.6	1056.7	1055.8	1055.4	1055.5
152.5°	1093.6	1092.9	1092.3	1091.6	1091.0	1090.8	1090.6	1090.3	1090.1	1090.0	1089.8
155°	1125.2	1124.3	1123.4	1122.5	1121.6	1121.4	1121.2	1120.9	1120.7	1120.6	1120.6
157.5°	1152.8	1151.9	1151.0	1150.2	1149.3	1149.1	1148.9	1148.6	1148.4	1148.3	1148.5
160°	1177.5	1176.6	1175.7	1174.9	1174.0	1173.8	1173.6	1173.3	1173.1	1173.0	1173.3
162.5°	1201.1	1200.0	1198.9	1197.8	1196.7	1196.7	1196.7	1196.7	1196.7	1196.7	1196.9
165°	1221.0	1220.1	1219.2	1218.4	1217.5	1217.3	1217.1	1216.8	1216.6	1216.5	1216.7
167.5°	1237.5	1236.2	1234.9	1233.6	1232.3	1232.3	1232.3	1232.3	1232.3	1232.3	1232.7
170°	1251.4	1250.1	1248.8	1247.4	1246.1	1246.1	1246.1	1246.1	1246.1	1246.1	1246.5
172.5°	1261.2	1259.9	1258.6	1257.3	1256.0	1256.0	1256.0	1256.0	1256.0	1256.0	1256.4
175°	1268.2	1266.9	1265.6	1264.2	1262.9	1262.9	1262.9	1262.9	1262.9	1262.9	1263.3
177.5°	1272.1	1270.8	1269.5	1268.2	1266.9	1267.1	1267.3	1267.6	1267.8	1267.9	1268.3
180°	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8	1269.8

TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1535.6	1547.2	1558.8	1573.0
5°	1504.6	1525.3	1547.2	1567.8
7.5°	1471.1	1500.7	1529.1	1558.8
10°	1433.6	1471.1	1503.3	1544.6
12.5°	1392.4	1432.4	1477.5	1524.0
15°	1351.1	1401.4	1449.1	1502.0
17.5°	1312.3	1360.1	1413.0	1476.2
20°	1265.9	1318.8	1378.2	1445.3
22.5°	1216.9	1274.9	1339.4	1411.7
25°	1175.6	1234.9	1296.9	1373.0
27.5°	1130.4	1192.3	1253.0	1334.3
30°	1078.8	1145.9	1207.8	1291.7
32.5°	1029.7	1096.8	1165.2	1244.0
35°	982.0	1047.8	1116.2	1196.2
37.5°	936.8	996.2	1063.3	1135.6
40°	894.3	948.5	1007.8	1073.6
42.5°	840.1	903.3	958.8	1006.5
45°	793.6	845.2	896.8	935.5
47.5°	739.4	791.0	834.9	865.9
50°	694.2	735.5	771.7	798.8
52.5°	640.0	678.8	708.4	729.1
55°	587.1	620.7	646.5	660.7
57.5°	539.4	561.3	580.7	593.6
60°	486.5	503.3	520.0	534.2
62.5°	429.7	447.8	456.8	472.3
65°	379.4	391.0	405.2	410.4
67.5°	330.3	336.8	345.8	356.2
70°	278.7	282.6	291.6	305.8
72.5°	233.6	237.4	243.9	249.0
75°	185.8	189.7	194.9	200.0
77.5°	145.8	147.1	149.7	154.8
80°	105.8	109.7	112.3	113.6
82.5°	73.6	74.8	74.8	76.1
85°	46.5	43.9	43.9	45.2
87.5°	16.8	19.4	19.4	21.9
90°	6.3	4.5	2.8	1.0
92.5°	32.9	31.8	30.7	29.6
95°	65.5	65.1	64.6	64.2
97.5°	99.5	99.2	99.0	98.8
100°	138.3	138.3	138.3	138.3
102.5°	184.1	183.0	181.9	180.8
105°	228.6	227.5	226.4	225.3
107.5°	277.0	275.9	274.8	273.7
110°	327.4	326.3	325.2	324.1



TEST NUMBER: P1034689

CATALOG NUMBER: S125RDIW-B1090D1050UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	376.8	376.4	375.9	375.5
115°	428.6	427.7	426.8	425.9
117.5°	478.0	477.7	477.5	477.3
120°	528.0	526.9	525.8	524.7
122.5°	576.8	576.5	576.3	576.1
125°	625.5	624.2	622.9	621.6
127.5°	673.9	673.3	672.6	672.0
130°	719.7	718.6	717.5	716.4
132.5°	766.8	764.9	762.9	760.9
135°	812.3	811.0	809.7	808.4
137.5°	856.7	855.4	854.1	852.8
140°	898.6	897.5	896.4	895.3
142.5°	940.5	939.6	938.7	937.8
145°	982.0	981.1	980.2	979.3
147.5°	1019.8	1019.1	1018.5	1017.8
150°	1055.7	1056.0	1056.2	1056.4
152.5°	1089.3	1088.9	1088.4	1088.0
155°	1120.6	1120.6	1120.6	1120.6
157.5°	1149.0	1149.4	1149.9	1150.3
160°	1174.0	1174.7	1175.3	1176.0
162.5°	1197.4	1197.8	1198.3	1198.7
165°	1217.2	1217.6	1218.1	1218.5
167.5°	1233.6	1234.5	1235.3	1236.2
170°	1247.4	1248.3	1249.2	1250.1
172.5°	1257.3	1258.2	1259.1	1260.0
175°	1264.2	1265.1	1266.0	1266.9
177.5°	1269.2	1270.1	1270.9	1271.8
180°	1269.8	1269.8	1269.8	1269.8

(END OF REPORT)