

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034703

Luminaire Tested: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034703
REPORT IS A COMBINATION OF REPORTS P1005975 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9236.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	69	66	58	56	55	45	44	44
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28
5	68	57	49	43	62	52	46	40	44	39	35	36	33	30	29	27	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10061	11349	10061	8723
10°	10005	12754	9972	7541
15°	9897	13493	9829	6566
20°	9766	14566	9678	5935
25°	9594	16487	9486	5386
30°	9420	17525	9279	4994
35°	9195	14412	9066	4628
40°	8795	9787	8721	4300
45°	8270	7036	8259	3976
50°	7732	5410	7769	3677
55°	7126	4400	7112	3389
60°	6561	3605	6529	3008
65°	5905	3005	5941	2422
70°	5360	2411	5338	2017
75°	4529	1827	4529	1658
80°	3671	1115	3629	1115
85°	2584	587	2510	664

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14334 cd/sqm

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	1.6
10°-20°	441.9	4.8
20°-30°	700.6	7.6
30°-40°	846.6	9.2
40°-50°	753.8	8.2
50°-60°	578.0	6.3
60°-70°	375.4	4.1
70°-80°	182.2	2.0
80°-90°	45.4	0.5
90°-100°	57.0	0.6
100°-110°	379.2	4.1
110°-120°	682.9	7.4
120°-130°	876.6	9.5
130°-140°	942.8	10.2
140°-150°	884.8	9.6
150°-160°	715.7	7.7
160°-170°	462.9	5.0
170°-180°	159.6	1.7
0°-30°	1293.2	14.0
0°-40°	2139.8	23.2
0°-60°	3471.6	37.6
0°-90°	4074.5	44.1
90°-120°	1119.2	12.1
90°-150°	3823.3	41.4
90°-180°	5162.0	55.9
0°-180°	9236.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1568	1801	1568	1385	1568	149
15°	1502	2164	1492	1053	1502	424
25°	1373	2591	1358	846	1373	633
35°	1196	2150	1179	690	1196	745
45°	936	961	934	543	936	722
55°	661	528	659	406	661	592
65°	410	299	413	241	410	410
75°	200	139	200	126	200	214
85°	45	30	44	34	45	51
90°	1	30	1	30	1	7
95°	71	26	71	26	71	87
105°	366	370	366	370	366	388
115°	688	683	688	683	688	682
125°	978	978	978	978	978	873
135°	1219	1214	1219	1214	1219	940
145°	1414	1410	1414	1410	1414	884
155°	1557	1546	1557	1546	1557	717
165°	1643	1634	1643	1634	1643	464
175°	1680	1673	1680	1673	1680	160
180°	1680	1680	1680	1680	1680	

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1573.0	1585.9	1589.8	1600.1	1611.7	1614.3	1620.8	1629.8	1634.9	1633.7	1633.7
5°	1567.8	1589.8	1605.3	1623.3	1645.3	1654.3	1662.0	1681.4	1696.9	1705.9	1721.4
7.5°	1558.8	1591.1	1616.9	1644.0	1677.5	1693.0	1709.8	1736.9	1765.3	1783.3	1800.1
10°	1544.6	1585.9	1622.0	1662.0	1707.2	1730.4	1751.1	1792.4	1827.2	1850.4	1889.2
12.5°	1524.0	1575.6	1625.9	1678.8	1735.6	1760.1	1788.5	1833.7	1882.7	1916.3	1948.5
15°	1502.0	1564.0	1618.2	1681.4	1749.8	1787.2	1823.3	1871.1	1915.0	1952.4	1989.8
17.5°	1476.2	1542.0	1609.1	1681.4	1758.8	1796.3	1827.2	1884.0	1930.5	1967.9	2001.4
20°	1445.3	1518.8	1594.9	1675.0	1753.7	1788.5	1818.2	1880.1	1921.4	1961.4	2009.2
22.5°	1411.7	1491.7	1573.0	1651.7	1729.1	1766.6	1801.4	1855.6	1900.8	1955.0	2016.9
25°	1373.0	1460.7	1543.3	1622.0	1695.6	1730.4	1761.4	1820.8	1884.0	1952.4	2022.1
27.5°	1334.3	1419.5	1499.5	1571.7	1651.7	1684.0	1715.0	1789.8	1864.6	1936.9	2032.4
30°	1291.7	1378.2	1447.8	1514.9	1592.4	1625.9	1664.6	1749.8	1835.0	1933.0	2049.2
32.5°	1244.0	1322.7	1387.2	1456.9	1526.6	1567.8	1616.9	1709.8	1807.9	1925.3	2073.7
35°	1196.2	1259.4	1318.8	1384.6	1468.5	1512.4	1560.1	1658.2	1780.8	1921.4	2094.3
37.5°	1135.6	1196.2	1242.7	1309.8	1396.2	1447.8	1495.6	1609.1	1748.5	1912.4	2093.0
40°	1073.6	1125.2	1169.1	1238.8	1333.0	1380.7	1432.4	1556.2	1715.0	1886.6	2062.1
42.5°	1006.5	1050.4	1098.1	1165.2	1256.9	1303.3	1362.7	1507.2	1668.5	1850.4	1982.1
45°	935.5	978.1	1018.1	1087.8	1179.4	1229.8	1294.3	1442.7	1611.7	1774.3	1853.0
47.5°	865.9	903.3	945.9	1006.5	1099.4	1154.9	1220.7	1379.4	1535.6	1672.4	1678.8
50°	798.8	828.4	864.6	926.5	1023.3	1076.2	1144.6	1293.0	1445.3	1539.5	1476.2
52.5°	729.1	756.2	793.6	847.8	938.1	1000.1	1059.4	1207.8	1335.6	1398.8	1282.7
55°	660.7	683.9	722.6	783.3	862.0	909.7	970.4	1108.5	1220.7	1222.0	1095.6
57.5°	593.6	614.2	646.5	700.7	774.2	829.7	885.2	1005.2	1081.4	1059.4	918.8
60°	534.2	547.1	576.8	629.7	698.1	738.1	797.5	898.1	948.5	908.4	757.5
62.5°	472.3	485.2	508.4	551.0	615.5	658.1	695.5	778.1	813.0	752.3	628.4
65°	410.4	425.8	442.6	476.2	536.8	565.2	598.8	659.4	692.9	622.0	514.9
67.5°	356.2	363.9	380.7	415.5	458.1	483.9	507.1	548.4	554.9	498.1	410.4
70°	305.8	308.4	323.9	344.5	376.8	392.3	411.6	436.2	436.2	389.7	320.0
72.5°	249.0	252.9	264.5	286.5	305.8	313.6	320.0	335.5	332.9	290.3	242.6
75°	200.0	202.6	211.6	222.0	229.7	243.9	249.0	246.5	245.2	209.0	181.9
77.5°	154.8	156.1	162.6	171.6	172.9	178.1	174.2	174.2	162.6	141.9	127.8
80°	113.6	114.8	117.4	120.0	120.0	120.0	120.0	113.6	105.8	92.9	89.0
82.5°	76.1	76.1	77.4	80.0	78.7	76.1	73.6	67.1	61.9	58.1	55.5
85°	45.2	45.2	46.5	45.2	40.0	38.7	36.1	34.8	33.6	32.3	32.3
87.5°	21.9	20.6	18.1	15.5	15.5	15.5	15.5	15.5	15.5	14.2	14.2
90°	1.2	3.4	5.6	7.9	10.1	11.2	12.2	14.1	16.0	18.0	19.9
92.5°	23.7	21.2	18.7	16.2	13.7	12.5	13.3	15.0	16.6	18.3	19.9
95°	71.0	70.2	69.4	68.5	67.7	67.3	62.0	51.5	41.0	30.4	19.9
97.5°	133.3	135.0	136.6	138.3	140.0	140.8	127.6	101.3	75.0	48.7	22.4
100°	208.0	208.8	209.6	210.5	211.3	211.7	212.3	213.4	214.5	215.6	216.7
102.5°	284.0	285.1	286.2	287.3	288.4	289.0	289.3	289.8	290.4	290.9	291.5
105°	366.2	367.3	368.4	369.5	370.6	371.2	371.2	371.2	371.2	371.2	371.2
107.5°	450.9	450.9	450.9	450.9	450.9	450.9	451.2	451.7	452.3	452.8	453.4
110°	533.1	533.1	533.1	533.1	533.1	533.1	533.4	533.9	534.5	535.0	535.6

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	610.3	611.1	612.0	612.8	613.7	614.1	614.2	614.5	614.8	615.0	615.3
115°	687.6	689.0	690.4	691.7	693.1	693.8	693.9	694.2	694.5	694.7	695.0
117.5°	768.5	768.5	768.5	768.5	768.5	768.5	769.1	770.2	771.3	772.4	773.5
120°	843.3	843.0	842.7	842.4	842.1	842.0	842.4	843.3	844.1	845.0	845.8
122.5°	909.3	910.7	912.1	913.4	914.8	915.5	915.6	915.9	916.2	916.5	916.8
125°	977.8	979.7	981.7	983.6	985.5	986.5	986.5	986.5	986.5	986.5	986.5
127.5°	1043.8	1045.2	1046.6	1047.9	1049.3	1050.0	1049.9	1049.6	1049.3	1049.1	1048.8
130°	1103.6	1105.0	1106.4	1107.7	1109.1	1109.8	1109.9	1110.2	1110.5	1110.8	1111.1
132.5°	1163.4	1165.0	1166.7	1168.3	1170.0	1170.8	1170.4	1169.6	1168.7	1167.9	1167.1
135°	1219.4	1221.1	1222.7	1224.4	1226.1	1226.9	1226.6	1226.1	1225.5	1225.0	1224.4
137.5°	1271.7	1273.4	1275.0	1276.7	1278.4	1279.2	1278.9	1278.4	1277.8	1277.3	1276.7
140°	1322.8	1323.4	1323.9	1324.5	1325.0	1325.3	1325.2	1324.9	1324.6	1324.4	1324.1
142.5°	1368.9	1369.2	1369.4	1369.7	1370.0	1370.1	1370.4	1370.9	1371.5	1372.0	1372.6
145°	1413.7	1414.3	1414.8	1415.4	1415.9	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2
147.5°	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.7	1454.0	1454.3	1454.5	1454.8
150°	1491.0	1490.4	1489.9	1489.3	1488.8	1488.5	1488.8	1489.3	1489.9	1490.4	1491.0
152.5°	1527.1	1525.7	1524.3	1523.0	1521.6	1520.9	1521.2	1521.7	1522.3	1522.8	1523.4
155°	1557.0	1555.3	1553.7	1552.0	1550.3	1549.5	1549.8	1550.3	1550.9	1551.4	1552.0
157.5°	1580.6	1579.8	1579.0	1578.1	1577.3	1576.9	1576.9	1576.9	1576.9	1576.9	1576.9
160°	1605.6	1603.9	1602.3	1600.6	1598.9	1598.1	1598.2	1598.5	1598.8	1599.0	1599.3
162.5°	1625.5	1623.8	1622.2	1620.5	1618.8	1618.0	1618.1	1618.4	1618.7	1619.0	1619.3
165°	1642.9	1641.3	1639.6	1638.0	1636.3	1635.5	1635.6	1635.9	1636.2	1636.4	1636.7
167.5°	1656.6	1655.0	1653.3	1651.7	1650.0	1649.2	1649.3	1649.6	1649.9	1650.1	1650.4
170°	1667.8	1665.9	1663.9	1662.0	1660.1	1659.1	1659.2	1659.5	1659.8	1660.1	1660.4
172.5°	1675.3	1673.4	1671.4	1669.5	1667.6	1666.6	1666.9	1667.4	1668.0	1668.5	1669.1
175°	1680.3	1678.6	1677.0	1675.3	1673.6	1672.8	1672.9	1673.2	1673.5	1673.8	1674.1
177.5°	1684.0	1682.4	1680.7	1679.1	1677.4	1676.6	1676.7	1677.0	1677.3	1677.5	1677.8
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1640.1	1649.1	1656.9	1653.0	1668.5	1667.2	1669.8	1675.0	1676.2	1673.7	1668.5
5°	1729.1	1742.1	1764.0	1775.6	1773.0	1783.3	1788.5	1796.3	1804.0	1801.4	1801.4
7.5°	1828.5	1846.6	1868.5	1898.2	1902.1	1911.1	1926.6	1926.6	1935.6	1931.7	1930.5
10°	1915.0	1936.9	1971.7	1995.0	2005.3	2010.5	2025.9	2031.1	2041.4	2042.7	2042.7
12.5°	1985.9	2024.7	2047.9	2071.1	2076.3	2084.0	2095.6	2103.4	2107.2	2107.2	2103.4
15°	2023.4	2054.3	2081.4	2105.9	2120.1	2126.6	2138.2	2147.2	2152.4	2164.0	2166.6
17.5°	2038.8	2076.3	2120.1	2155.0	2179.5	2186.0	2209.2	2216.9	2227.2	2232.4	2238.9
20°	2060.8	2115.0	2167.9	2210.5	2233.7	2250.5	2275.0	2311.1	2321.4	2321.4	2317.6
22.5°	2080.1	2149.8	2222.1	2290.5	2309.8	2343.4	2388.5	2427.3	2442.7	2449.2	2444.0
25°	2103.4	2198.9	2293.1	2378.2	2431.1	2455.6	2516.3	2562.8	2580.8	2591.1	2593.7
27.5°	2143.4	2263.4	2383.4	2491.8	2546.0	2574.4	2637.6	2677.6	2699.5	2708.6	2702.1
30°	2188.5	2335.6	2475.0	2571.8	2607.9	2642.8	2684.1	2699.5	2694.4	2694.4	2713.7
32.5°	2235.0	2387.3	2511.1	2574.4	2587.3	2582.1	2565.3	2518.9	2491.8	2491.8	2508.6
35°	2260.8	2392.4	2455.6	2435.0	2384.7	2355.0	2263.4	2211.8	2153.7	2149.8	2169.2
37.5°	2246.6	2303.4	2277.6	2142.1	2073.7	2016.9	1873.7	1816.9	1774.3	1715.0	1806.6
40°	2147.2	2127.9	1993.7	1798.8	1722.7	1642.7	1529.1	1472.4	1413.0	1404.0	1425.9
42.5°	1979.5	1864.6	1668.5	1480.1	1402.7	1345.9	1259.4	1204.0	1166.5	1151.0	1176.9
45°	1770.4	1589.8	1393.6	1244.0	1158.8	1129.1	1050.4	1001.4	973.0	961.4	979.4
47.5°	1514.9	1333.0	1147.2	1020.7	970.4	940.7	887.8	845.2	820.7	813.0	820.7
50°	1286.5	1099.4	943.3	862.0	816.8	792.3	748.4	721.3	702.0	696.8	709.7
52.5°	1089.1	918.8	800.1	727.8	698.1	677.5	646.5	623.3	611.7	606.5	615.5
55°	912.3	774.2	678.8	616.8	594.9	582.0	554.9	542.0	529.1	527.8	536.8
57.5°	756.2	660.7	572.9	529.1	522.6	503.3	480.0	468.4	462.0	460.7	464.5
60°	629.7	544.6	491.6	452.9	443.9	428.4	415.5	407.8	400.0	397.4	400.0
62.5°	523.9	456.8	414.2	388.4	375.5	371.6	357.4	348.4	347.1	347.1	349.7
65°	432.3	375.5	348.4	327.8	318.7	314.9	304.5	298.1	299.4	299.4	300.7
67.5°	352.3	311.0	286.5	276.1	268.4	267.1	256.8	254.2	251.6	251.6	254.2
70°	280.0	254.2	236.1	231.0	229.7	220.7	216.8	215.5	211.6	212.9	212.9
72.5°	219.4	202.6	192.3	184.5	185.8	180.7	175.5	175.5	172.9	176.8	176.8
75°	162.6	154.8	147.1	144.5	147.1	144.5	140.7	139.4	140.7	139.4	139.4
77.5°	120.0	116.1	113.6	112.3	112.3	107.1	104.5	107.1	101.9	104.5	104.5
80°	83.9	78.7	77.4	74.8	76.1	72.3	73.6	71.0	71.0	71.0	71.0
82.5°	52.9	51.6	51.6	51.6	50.3	50.3	50.3	50.3	50.3	50.3	49.0
85°	32.3	31.0	31.0	31.0	29.7	29.7	29.7	29.7	29.7	29.7	29.7
87.5°	12.9	14.2	14.2	15.5	14.2	12.9	12.9	12.9	14.2	14.2	12.9
90°	21.3	22.7	24.1	25.5	26.2	26.6	27.4	28.3	29.1	29.9	29.1
92.5°	21.3	22.7	24.1	25.5	26.2	26.3	26.6	26.9	27.1	27.4	27.1
95°	21.3	22.7	24.1	25.5	26.2	26.2	26.2	26.2	26.2	26.2	26.2
97.5°	23.0	23.5	24.1	24.6	24.9	25.0	25.3	25.6	25.9	26.2	25.9
100°	175.5	134.2	93.0	51.7	31.1	30.6	29.5	28.4	27.3	26.2	27.3
102.5°	292.1	292.6	293.2	293.7	294.0	282.4	259.1	235.8	212.6	189.3	212.6
105°	371.2	371.2	371.2	371.2	371.2	371.1	370.8	370.5	370.2	369.9	370.2
107.5°	453.7	453.9	454.2	454.5	454.6	454.1	453.0	451.9	450.8	449.7	450.8
110°	534.8	534.0	533.1	532.3	531.9	532.0	532.3	532.6	532.8	533.1	532.8

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	614.2	613.1	612.0	610.9	610.3	610.0	609.5	608.9	608.4	607.8	608.4
115°	693.9	692.8	691.7	690.6	690.1	689.3	687.6	685.9	684.3	682.6	684.3
117.5°	771.8	770.2	768.5	766.8	766.0	765.7	765.2	764.6	764.1	763.5	764.1
120°	845.2	844.7	844.1	843.6	843.3	842.6	841.2	839.8	838.4	837.0	838.4
122.5°	916.2	915.7	915.1	914.6	914.3	913.5	911.8	910.1	908.5	906.8	908.5
125°	985.4	984.3	983.2	982.1	981.5	981.1	980.3	979.4	978.6	977.8	978.6
127.5°	1048.2	1047.7	1047.1	1046.6	1046.3	1045.2	1043.0	1040.7	1038.5	1036.3	1038.5
130°	1110.3	1109.4	1108.6	1107.7	1107.3	1106.6	1105.2	1103.9	1102.5	1101.1	1102.5
132.5°	1167.1	1167.1	1167.1	1167.1	1167.1	1166.4	1165.0	1163.7	1162.3	1160.9	1162.3
135°	1223.8	1223.3	1222.7	1222.2	1221.9	1221.1	1219.4	1217.7	1216.1	1214.4	1216.1
137.5°	1276.7	1276.7	1276.7	1276.7	1276.7	1276.0	1274.6	1273.3	1271.9	1270.5	1271.9
140°	1324.6	1325.2	1325.7	1326.2	1326.5	1325.7	1324.0	1322.4	1320.7	1319.1	1320.7
142.5°	1372.6	1372.6	1372.6	1372.6	1372.6	1371.8	1370.1	1368.5	1366.8	1365.2	1366.8
145°	1416.5	1416.8	1417.1	1417.4	1417.5	1416.7	1415.0	1413.3	1411.7	1410.0	1411.7
147.5°	1455.1	1455.4	1455.7	1456.0	1456.1	1455.1	1453.2	1451.3	1449.3	1447.4	1449.3
150°	1491.6	1492.1	1492.7	1493.2	1493.5	1492.4	1490.2	1487.9	1485.7	1483.5	1485.7
152.5°	1523.9	1524.5	1525.0	1525.5	1525.8	1524.8	1522.9	1521.0	1519.0	1517.1	1519.0
155°	1552.8	1553.6	1554.5	1555.3	1555.7	1554.6	1552.4	1550.2	1548.0	1545.8	1548.0
157.5°	1577.7	1578.5	1579.4	1580.2	1580.6	1579.5	1577.3	1575.1	1572.9	1570.7	1572.9
160°	1600.4	1601.5	1602.6	1603.7	1604.3	1603.2	1601.0	1598.7	1596.5	1594.3	1596.5
162.5°	1620.9	1622.6	1624.2	1625.9	1626.7	1625.5	1623.0	1620.5	1618.0	1615.5	1618.0
165°	1638.4	1640.0	1641.7	1643.4	1644.2	1643.1	1640.9	1638.6	1636.4	1634.2	1636.4
167.5°	1652.3	1654.3	1656.2	1658.1	1659.1	1657.9	1655.4	1652.9	1650.4	1647.9	1650.4
170°	1662.6	1664.8	1667.0	1669.2	1670.3	1669.1	1666.6	1664.1	1661.6	1659.1	1661.6
172.5°	1671.0	1673.0	1674.9	1676.8	1677.8	1676.6	1674.1	1671.6	1669.1	1666.6	1669.1
175°	1676.3	1678.5	1680.7	1682.9	1684.0	1682.8	1680.3	1677.8	1675.3	1672.8	1675.3
177.5°	1679.7	1681.7	1683.6	1685.5	1686.5	1685.4	1683.2	1681.0	1678.8	1676.6	1678.8
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1675.0	1665.9	1669.8	1665.9	1662.0	1658.2	1649.1	1636.2	1625.9	1618.2	1616.9
5°	1804.0	1792.4	1784.6	1780.8	1773.0	1762.7	1745.9	1726.6	1703.3	1694.3	1676.2
7.5°	1922.7	1918.8	1900.8	1898.2	1893.0	1873.7	1845.3	1819.5	1789.8	1765.3	1742.1
10°	2035.0	2025.9	2013.0	1995.0	1992.4	1967.9	1940.8	1904.6	1865.9	1842.7	1801.4
12.5°	2104.7	2094.3	2080.1	2068.5	2062.1	2046.6	2009.2	1973.0	1938.2	1895.6	1859.5
15°	2155.0	2142.1	2116.3	2107.2	2099.5	2078.8	2051.8	2014.3	1967.9	1938.2	1886.6
17.5°	2223.4	2207.9	2182.1	2165.3	2151.1	2118.9	2080.1	2029.8	1985.9	1952.4	1905.9
20°	2302.1	2278.9	2245.3	2223.4	2202.7	2165.3	2111.1	2051.8	1988.5	1947.2	1899.5
22.5°	2432.4	2388.5	2335.6	2304.7	2276.3	2211.8	2147.2	2073.7	2002.7	1940.8	1882.7
25°	2558.9	2515.0	2449.2	2406.6	2362.7	2287.9	2202.7	2100.8	2010.5	1938.2	1862.1
27.5°	2676.3	2631.1	2570.5	2518.9	2476.3	2364.0	2251.8	2136.9	2022.1	1922.7	1845.3
30°	2703.4	2684.1	2637.6	2592.4	2553.7	2450.5	2320.2	2174.3	2036.3	1908.5	1822.1
32.5°	2539.5	2587.3	2598.9	2592.4	2567.9	2494.4	2374.4	2220.8	2056.9	1902.1	1783.3
35°	2198.9	2285.3	2374.4	2422.1	2445.3	2455.6	2384.7	2244.0	2071.1	1891.7	1757.5
37.5°	1823.3	1907.2	2047.9	2118.9	2197.6	2300.8	2329.2	2238.9	2064.7	1884.0	1716.2
40°	1498.2	1605.3	1721.4	1785.9	1854.3	2040.1	2180.8	2170.5	2044.0	1855.6	1684.0
42.5°	1219.4	1286.5	1388.5	1459.5	1543.3	1751.1	1939.5	2032.4	1982.1	1820.8	1642.7
45°	1016.8	1068.5	1140.7	1213.0	1264.6	1453.0	1676.2	1828.5	1876.3	1758.8	1579.5
47.5°	856.8	895.5	958.8	1003.9	1059.4	1207.8	1401.4	1615.6	1716.2	1671.1	1512.4
50°	734.2	765.2	815.5	843.9	893.0	1020.7	1167.8	1392.4	1544.6	1549.8	1423.3
52.5°	627.1	658.1	700.7	725.2	754.9	841.3	989.7	1179.4	1354.9	1419.5	1321.4
55°	545.8	563.9	598.8	618.1	645.2	729.1	823.3	984.6	1167.8	1273.6	1211.7
57.5°	471.0	490.4	512.3	527.8	547.1	614.2	699.4	820.7	1002.6	1117.5	1096.8
60°	410.4	422.0	442.6	454.2	472.3	516.2	575.5	696.8	841.3	949.7	961.4
62.5°	353.6	363.9	378.1	388.4	400.0	434.9	478.7	565.2	691.7	809.1	824.6
65°	304.5	313.6	321.3	330.3	339.4	361.3	398.7	465.8	563.9	673.6	707.1
67.5°	260.7	263.2	274.9	276.1	281.3	298.1	325.2	379.4	450.4	538.1	582.0
70°	218.1	223.2	225.8	229.7	234.9	246.5	268.4	296.8	349.7	420.7	462.0
72.5°	176.8	178.1	181.9	184.5	189.7	198.7	209.0	231.0	264.5	316.2	353.6
75°	140.7	141.9	144.5	145.8	149.7	152.3	157.4	172.9	196.1	227.1	254.2
77.5°	105.8	108.4	111.0	111.0	112.3	114.8	117.4	122.6	134.2	154.8	178.1
80°	72.3	73.6	73.6	74.8	73.6	77.4	81.3	87.7	92.9	99.4	111.0
82.5°	50.3	50.3	50.3	51.6	51.6	52.9	52.9	54.2	55.5	59.4	64.5
85°	31.0	31.0	32.3	29.7	31.0	32.3	32.3	31.0	32.3	33.6	34.8
87.5°	12.9	12.9	14.2	14.2	14.2	14.2	12.9	14.2	12.9	14.2	14.2
90°	28.3	27.4	26.6	26.2	25.5	24.1	22.7	21.3	19.9	18.0	16.0
92.5°	26.9	26.6	26.3	26.2	25.5	24.1	22.7	21.3	19.9	18.3	16.6
95°	26.2	26.2	26.2	26.2	25.5	24.1	22.7	21.3	19.9	30.4	41.0
97.5°	25.6	25.3	25.0	24.9	24.6	24.1	23.5	23.0	22.4	48.7	75.0
100°	28.4	29.5	30.6	31.1	51.7	93.0	134.2	175.5	216.7	215.6	214.5
102.5°	235.8	259.1	282.4	294.0	293.7	293.2	292.6	292.1	291.5	290.9	290.4
105°	370.5	370.8	371.1	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2
107.5°	451.9	453.0	454.1	454.6	454.5	454.2	453.9	453.7	453.4	452.8	452.3
110°	532.6	532.3	532.0	531.9	532.3	533.1	534.0	534.8	535.6	535.0	534.5

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	608.9	609.5	610.0	610.3	610.9	612.0	613.1	614.2	615.3	615.0	614.8
115°	685.9	687.6	689.3	690.1	690.6	691.7	692.8	693.9	695.0	694.7	694.5
117.5°	764.6	765.2	765.7	766.0	766.8	768.5	770.2	771.8	773.5	772.4	771.3
120°	839.8	841.2	842.6	843.3	843.6	844.1	844.7	845.2	845.8	845.0	844.1
122.5°	910.1	911.8	913.5	914.3	914.6	915.1	915.7	916.2	916.8	916.5	916.2
125°	979.4	980.3	981.1	981.5	982.1	983.2	984.3	985.4	986.5	986.5	986.5
127.5°	1040.7	1043.0	1045.2	1046.3	1046.6	1047.1	1047.7	1048.2	1048.8	1049.1	1049.3
130°	1103.9	1105.2	1106.6	1107.3	1107.7	1108.6	1109.4	1110.3	1111.1	1110.8	1110.5
132.5°	1163.7	1165.0	1166.4	1167.1	1167.1	1167.1	1167.1	1167.1	1167.1	1167.9	1168.7
135°	1217.7	1219.4	1221.1	1221.9	1222.2	1222.7	1223.3	1223.8	1224.4	1225.0	1225.5
137.5°	1273.3	1274.6	1276.0	1276.7	1276.7	1276.7	1276.7	1276.7	1276.7	1277.3	1277.8
140°	1322.4	1324.0	1325.7	1326.5	1326.2	1325.7	1325.2	1324.6	1324.1	1324.4	1324.6
142.5°	1368.5	1370.1	1371.8	1372.6	1372.6	1372.6	1372.6	1372.6	1372.6	1372.0	1371.5
145°	1413.3	1415.0	1416.7	1417.5	1417.4	1417.1	1416.8	1416.5	1416.2	1416.2	1416.2
147.5°	1451.3	1453.2	1455.1	1456.1	1456.0	1455.7	1455.4	1455.1	1454.8	1454.5	1454.3
150°	1487.9	1490.2	1492.4	1493.5	1493.2	1492.7	1492.1	1491.6	1491.0	1490.4	1489.9
152.5°	1521.0	1522.9	1524.8	1525.8	1525.5	1525.0	1524.5	1523.9	1523.4	1522.8	1522.3
155°	1550.2	1552.4	1554.6	1555.7	1555.3	1554.5	1553.6	1552.8	1552.0	1551.4	1550.9
157.5°	1575.1	1577.3	1579.5	1580.6	1580.2	1579.4	1578.5	1577.7	1576.9	1576.9	1576.9
160°	1598.7	1601.0	1603.2	1604.3	1603.7	1602.6	1601.5	1600.4	1599.3	1599.0	1598.8
162.5°	1620.5	1623.0	1625.5	1626.7	1625.9	1624.2	1622.6	1620.9	1619.3	1619.0	1618.7
165°	1638.6	1640.9	1643.1	1644.2	1643.4	1641.7	1640.0	1638.4	1636.7	1636.4	1636.2
167.5°	1652.9	1655.4	1657.9	1659.1	1658.1	1656.2	1654.3	1652.3	1650.4	1650.1	1649.9
170°	1664.1	1666.6	1669.1	1670.3	1669.2	1667.0	1664.8	1662.6	1660.4	1660.1	1659.8
172.5°	1671.6	1674.1	1676.6	1677.8	1676.8	1674.9	1673.0	1671.0	1669.1	1668.5	1668.0
175°	1677.8	1680.3	1682.8	1684.0	1682.9	1680.7	1678.5	1676.3	1674.1	1673.8	1673.5
177.5°	1681.0	1683.2	1685.4	1686.5	1685.5	1683.6	1681.7	1679.7	1677.8	1677.5	1677.3
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1613.0	1605.3	1600.1	1598.8	1591.1	1584.6	1576.9	1575.6	1571.7	1561.4	1554.9
5°	1663.3	1645.3	1641.4	1629.8	1610.4	1596.2	1578.2	1567.8	1556.2	1536.9	1521.4
7.5°	1715.0	1690.4	1672.4	1655.6	1628.5	1602.7	1576.9	1556.2	1535.6	1507.2	1484.0
10°	1765.3	1727.9	1705.9	1681.4	1644.0	1605.3	1569.1	1539.5	1505.9	1472.4	1438.8
12.5°	1811.7	1764.0	1731.7	1696.9	1650.4	1602.7	1556.2	1514.9	1480.1	1434.9	1397.5
15°	1840.1	1787.2	1755.0	1721.4	1651.7	1598.8	1544.6	1491.7	1445.3	1397.5	1362.7
17.5°	1856.9	1797.5	1761.4	1730.4	1659.5	1587.2	1517.5	1460.7	1410.4	1353.6	1307.2
20°	1849.2	1791.1	1757.5	1727.9	1645.3	1573.0	1498.2	1432.4	1369.1	1311.1	1262.0
22.5°	1832.4	1771.7	1734.3	1707.2	1633.7	1548.5	1465.9	1394.9	1329.1	1271.1	1215.6
25°	1796.3	1736.9	1704.6	1671.1	1598.8	1517.5	1433.6	1357.5	1287.8	1225.9	1163.9
27.5°	1764.0	1691.7	1658.2	1628.5	1552.4	1480.1	1397.5	1313.6	1242.7	1178.1	1116.2
30°	1726.6	1645.3	1609.1	1569.1	1500.7	1432.4	1349.8	1272.3	1198.8	1130.4	1071.0
32.5°	1686.6	1592.4	1551.1	1505.9	1436.2	1371.7	1302.0	1225.9	1152.3	1085.2	1023.3
35°	1634.9	1534.3	1486.6	1444.0	1371.7	1307.2	1242.7	1179.4	1105.9	1034.9	975.5
37.5°	1585.9	1474.9	1424.6	1375.6	1299.4	1237.5	1184.6	1125.2	1054.3	985.9	929.1
40°	1530.4	1402.7	1351.1	1305.9	1227.2	1158.8	1111.0	1064.6	1002.6	936.8	874.9
42.5°	1480.1	1335.6	1281.4	1234.9	1152.3	1087.8	1042.7	1003.9	949.7	889.1	825.9
45°	1410.4	1263.3	1207.8	1158.8	1074.9	1014.3	967.8	934.3	891.7	834.9	778.1
47.5°	1345.9	1193.6	1133.0	1073.6	997.5	935.5	893.0	867.2	838.8	788.4	730.4
50°	1267.2	1113.6	1051.7	1002.6	916.2	863.3	820.7	802.6	776.8	729.1	682.6
52.5°	1182.0	1036.2	978.1	918.8	838.8	787.1	749.7	729.1	708.4	673.6	629.7
55°	1082.7	949.7	895.5	842.6	762.6	714.9	681.3	659.4	647.8	615.5	583.3
57.5°	987.2	862.0	811.7	762.6	692.9	638.8	616.8	597.5	580.7	557.5	530.4
60°	890.4	776.8	722.6	678.8	618.1	569.1	551.0	531.6	518.7	500.7	481.3
62.5°	779.4	682.6	641.3	600.0	548.4	509.7	489.1	473.6	456.8	445.2	428.4
65°	662.0	593.6	553.6	522.6	473.6	438.7	423.3	412.9	398.7	387.1	374.2
67.5°	552.3	498.1	481.3	447.8	410.4	379.4	367.8	354.9	343.2	336.8	325.2
70°	446.5	407.8	391.0	382.0	340.7	320.0	309.7	304.5	290.3	283.9	276.1
72.5°	345.8	331.6	320.0	308.4	281.3	268.4	256.8	251.6	241.3	236.1	233.6
75°	255.5	246.5	240.0	238.7	227.1	214.2	202.6	200.0	192.3	187.1	184.5
77.5°	179.4	176.8	175.5	176.8	169.0	161.3	158.7	156.1	147.1	145.8	145.8
80°	117.4	123.9	123.9	122.6	120.0	118.7	114.8	112.3	107.1	105.8	107.1
82.5°	72.3	76.1	77.4	80.0	78.7	77.4	74.8	73.6	74.8	72.3	73.6
85°	36.1	38.7	43.9	43.9	45.2	45.2	45.2	43.9	41.3	42.6	41.3
87.5°	14.2	15.5	15.5	15.5	14.2	18.1	19.4	19.4	19.4	16.8	16.8
90°	14.1	12.2	11.2	10.1	7.9	5.6	3.4	1.2	3.4	5.6	7.9
92.5°	15.0	13.3	12.5	13.7	16.2	18.7	21.2	23.7	21.2	18.7	16.2
95°	51.5	62.0	67.3	67.7	68.5	69.4	70.2	71.0	70.2	69.4	68.5
97.5°	101.3	127.6	140.8	140.0	138.3	136.6	135.0	133.3	135.0	136.6	138.3
100°	213.4	212.3	211.7	211.3	210.5	209.6	208.8	208.0	208.8	209.6	210.5
102.5°	289.8	289.3	289.0	288.4	287.3	286.2	285.1	284.0	285.1	286.2	287.3
105°	371.2	371.2	371.2	370.6	369.5	368.4	367.3	366.2	367.3	368.4	369.5
107.5°	451.7	451.2	450.9	450.9	450.9	450.9	450.9	450.9	450.9	450.9	450.9
110°	533.9	533.4	533.1	533.1	533.1	533.1	533.1	533.1	533.1	533.1	533.1

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	614.5	614.2	614.1	613.7	612.8	612.0	611.1	610.3	611.1	612.0	612.8
115°	694.2	693.9	693.8	693.1	691.7	690.4	689.0	687.6	689.0	690.4	691.7
117.5°	770.2	769.1	768.5	768.5	768.5	768.5	768.5	768.5	768.5	768.5	768.5
120°	843.3	842.4	842.0	842.1	842.4	842.7	843.0	843.3	843.0	842.7	842.4
122.5°	915.9	915.6	915.5	914.8	913.4	912.1	910.7	909.3	910.7	912.1	913.4
125°	986.5	986.5	986.5	985.5	983.6	981.7	979.7	977.8	979.7	981.7	983.6
127.5°	1049.6	1049.9	1050.0	1049.3	1047.9	1046.6	1045.2	1043.8	1045.2	1046.6	1047.9
130°	1110.2	1109.9	1109.8	1109.1	1107.7	1106.4	1105.0	1103.6	1105.0	1106.4	1107.7
132.5°	1169.6	1170.4	1170.8	1170.0	1168.3	1166.7	1165.0	1163.4	1165.0	1166.7	1168.3
135°	1226.1	1226.6	1226.9	1226.1	1224.4	1222.7	1221.1	1219.4	1221.1	1222.7	1224.4
137.5°	1278.4	1278.9	1279.2	1278.4	1276.7	1275.0	1273.4	1271.7	1273.4	1275.0	1276.7
140°	1324.9	1325.2	1325.3	1325.0	1324.5	1323.9	1323.4	1322.8	1323.4	1323.9	1324.5
142.5°	1370.9	1370.4	1370.1	1370.0	1369.7	1369.4	1369.2	1368.9	1369.2	1369.4	1369.7
145°	1416.2	1416.2	1416.2	1415.9	1415.4	1414.8	1414.3	1413.7	1414.3	1414.8	1415.4
147.5°	1454.0	1453.7	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6
150°	1489.3	1488.8	1488.5	1488.8	1489.3	1489.9	1490.4	1491.0	1490.4	1489.9	1489.3
152.5°	1521.7	1521.2	1520.9	1521.6	1523.0	1524.3	1525.7	1527.1	1525.7	1524.3	1523.0
155°	1550.3	1549.8	1549.5	1550.3	1552.0	1553.7	1555.3	1557.0	1555.3	1553.7	1552.0
157.5°	1576.9	1576.9	1576.9	1577.3	1578.1	1579.0	1579.8	1580.6	1579.8	1579.0	1578.1
160°	1598.5	1598.2	1598.1	1598.9	1600.6	1602.3	1603.9	1605.6	1603.9	1602.3	1600.6
162.5°	1618.4	1618.1	1618.0	1618.8	1620.5	1622.2	1623.8	1625.5	1623.8	1622.2	1620.5
165°	1635.9	1635.6	1635.5	1636.3	1638.0	1639.6	1641.3	1642.9	1641.3	1639.6	1638.0
167.5°	1649.6	1649.3	1649.2	1650.0	1651.7	1653.3	1655.0	1656.6	1655.0	1653.3	1651.7
170°	1659.5	1659.2	1659.1	1660.1	1662.0	1663.9	1665.9	1667.8	1665.9	1663.9	1662.0
172.5°	1667.4	1666.9	1666.6	1667.6	1669.5	1671.4	1673.4	1675.3	1673.4	1671.4	1669.5
175°	1673.2	1672.9	1672.8	1673.6	1675.3	1677.0	1678.6	1680.3	1678.6	1677.0	1675.3
177.5°	1677.0	1676.7	1676.6	1677.4	1679.1	1680.7	1682.4	1684.0	1682.4	1680.7	1679.1
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1551.1	1545.9	1542.0	1538.2	1521.4	1503.3	1500.7	1496.9	1489.1	1498.2	1494.3
5°	1511.1	1499.5	1493.0	1476.2	1455.6	1440.1	1427.2	1411.7	1405.3	1400.1	1398.8
7.5°	1462.0	1451.7	1440.1	1423.3	1397.5	1371.7	1352.3	1336.9	1324.0	1317.5	1317.5
10°	1414.3	1401.4	1385.9	1357.5	1333.0	1300.7	1280.1	1264.6	1246.5	1236.2	1227.2
12.5°	1365.3	1351.1	1336.9	1300.7	1272.3	1238.8	1209.1	1189.8	1180.7	1169.1	1153.6
15°	1316.2	1294.3	1280.1	1244.0	1207.8	1174.3	1154.9	1134.3	1113.6	1102.0	1096.8
17.5°	1264.6	1249.1	1225.9	1187.2	1147.2	1117.5	1089.1	1069.7	1045.2	1033.6	1022.0
20°	1218.1	1194.9	1171.7	1133.0	1094.3	1054.3	1025.9	1002.6	987.2	978.1	967.8
22.5°	1162.7	1140.7	1121.4	1080.1	1037.5	1000.1	969.1	954.9	939.4	925.2	914.9
25°	1114.9	1093.0	1073.6	1028.5	982.0	947.2	923.9	905.9	889.1	882.6	872.3
27.5°	1064.6	1043.9	1018.1	973.0	931.7	902.0	877.5	860.7	847.8	834.9	827.2
30°	1016.8	993.6	970.4	921.4	887.8	858.1	834.9	814.2	803.9	797.5	784.6
32.5°	970.4	940.7	921.4	876.2	843.9	815.5	796.2	778.1	765.2	753.6	743.3
35°	920.1	887.8	868.4	831.0	797.5	769.1	752.3	739.4	723.9	713.6	708.4
37.5°	872.3	845.2	825.9	787.1	753.6	730.4	712.3	695.5	689.1	674.9	672.3
40°	820.7	797.5	779.4	742.0	711.0	692.9	673.6	658.1	646.5	640.0	631.0
42.5°	774.2	754.9	735.5	700.7	671.0	649.1	634.9	620.7	610.4	600.0	593.6
45°	731.7	711.0	692.9	659.4	629.7	610.4	596.2	579.4	576.8	562.6	556.2
47.5°	686.5	668.4	652.9	618.1	591.0	571.7	554.9	543.3	531.6	526.5	517.5
50°	642.6	624.6	606.5	575.5	551.0	531.6	514.9	502.0	495.5	487.8	480.0
52.5°	594.9	580.7	566.5	534.2	509.7	492.9	478.7	462.0	455.5	449.1	443.9
55°	554.9	534.2	518.7	491.6	469.7	451.6	436.2	423.3	416.8	411.6	405.2
57.5°	500.7	487.8	474.9	450.4	429.7	411.6	396.2	385.8	378.1	374.2	375.5
60°	454.2	440.0	432.3	406.5	385.8	371.6	357.4	347.1	339.4	335.5	334.2
62.5°	405.2	394.9	380.7	362.6	342.0	329.1	318.7	311.0	298.1	296.8	292.9
65°	357.4	349.7	336.8	320.0	303.2	291.6	280.0	269.7	264.5	258.1	254.2
67.5°	311.0	303.2	291.6	277.4	265.8	254.2	243.9	233.6	224.5	219.4	216.8
70°	265.8	259.4	251.6	234.9	220.7	211.6	203.9	197.4	188.4	185.8	184.5
72.5°	222.0	215.5	211.6	197.4	184.5	176.8	169.0	162.6	158.7	157.4	153.6
75°	181.9	175.5	170.3	157.4	149.7	144.5	136.8	134.2	130.3	129.0	127.8
77.5°	141.9	135.5	134.2	125.2	116.1	113.6	111.0	105.8	105.8	105.8	103.2
80°	101.9	100.7	99.4	90.3	86.5	83.9	82.6	78.7	76.1	73.6	72.3
82.5°	68.4	67.1	65.8	61.9	58.1	56.8	55.5	52.9	52.9	54.2	51.6
85°	41.3	38.7	37.4	36.1	33.6	33.6	34.8	33.6	33.6	33.6	32.3
87.5°	15.5	15.5	15.5	15.5	16.8	14.2	15.5	15.5	14.2	14.2	12.9
90°	10.1	11.2	12.2	14.1	16.0	18.0	19.9	21.3	22.7	24.1	25.5
92.5°	13.7	12.5	13.3	15.0	16.6	18.3	19.9	21.3	22.7	24.1	25.5
95°	67.7	67.3	62.0	51.5	41.0	30.4	19.9	21.3	22.7	24.1	25.5
97.5°	140.0	140.8	127.6	101.3	75.0	48.7	22.4	23.0	23.5	24.1	24.6
100°	211.3	211.7	212.3	213.4	214.5	215.6	216.7	175.5	134.2	93.0	51.7
102.5°	288.4	289.0	289.3	289.8	290.4	290.9	291.5	292.1	292.6	293.2	293.7
105°	370.6	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2
107.5°	450.9	450.9	451.2	451.7	452.3	452.8	453.4	453.7	453.9	454.2	454.5
110°	533.1	533.1	533.4	533.9	534.5	535.0	535.6	534.8	534.0	533.1	532.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	613.7	614.1	614.2	614.5	614.8	615.0	615.3	614.2	613.1	612.0	610.9
115°	693.1	693.8	693.9	694.2	694.5	694.7	695.0	693.9	692.8	691.7	690.6
117.5°	768.5	768.5	769.1	770.2	771.3	772.4	773.5	771.8	770.2	768.5	766.8
120°	842.1	842.0	842.4	843.3	844.1	845.0	845.8	845.2	844.7	844.1	843.6
122.5°	914.8	915.5	915.6	915.9	916.2	916.5	916.8	916.2	915.7	915.1	914.6
125°	985.5	986.5	986.5	986.5	986.5	986.5	986.5	985.4	984.3	983.2	982.1
127.5°	1049.3	1050.0	1049.9	1049.6	1049.3	1049.1	1048.8	1048.2	1047.7	1047.1	1046.6
130°	1109.1	1109.8	1109.9	1110.2	1110.5	1110.8	1111.1	1110.3	1109.4	1108.6	1107.7
132.5°	1170.0	1170.8	1170.4	1169.6	1168.7	1167.9	1167.1	1167.1	1167.1	1167.1	1167.1
135°	1226.1	1226.9	1226.6	1226.1	1225.5	1225.0	1224.4	1223.8	1223.3	1222.7	1222.2
137.5°	1278.4	1279.2	1278.9	1278.4	1277.8	1277.3	1276.7	1276.7	1276.7	1276.7	1276.7
140°	1325.0	1325.3	1325.2	1324.9	1324.6	1324.4	1324.1	1324.6	1325.2	1325.7	1326.2
142.5°	1370.0	1370.1	1370.4	1370.9	1371.5	1372.0	1372.6	1372.6	1372.6	1372.6	1372.6
145°	1415.9	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.5	1416.8	1417.1	1417.4
147.5°	1453.6	1453.6	1453.7	1454.0	1454.3	1454.5	1454.8	1455.1	1455.4	1455.7	1456.0
150°	1488.8	1488.5	1488.8	1489.3	1489.9	1490.4	1491.0	1491.6	1492.1	1492.7	1493.2
152.5°	1521.6	1520.9	1521.2	1521.7	1522.3	1522.8	1523.4	1523.9	1524.5	1525.0	1525.5
155°	1550.3	1549.5	1549.8	1550.3	1550.9	1551.4	1552.0	1552.8	1553.6	1554.5	1555.3
157.5°	1577.3	1576.9	1576.9	1576.9	1576.9	1576.9	1576.9	1577.7	1578.5	1579.4	1580.2
160°	1598.9	1598.1	1598.2	1598.5	1598.8	1599.0	1599.3	1600.4	1601.5	1602.6	1603.7
162.5°	1618.8	1618.0	1618.1	1618.4	1618.7	1619.0	1619.3	1620.9	1622.6	1624.2	1625.9
165°	1636.3	1635.5	1635.6	1635.9	1636.2	1636.4	1636.7	1638.4	1640.0	1641.7	1643.4
167.5°	1650.0	1649.2	1649.3	1649.6	1649.9	1650.1	1650.4	1652.3	1654.3	1656.2	1658.1
170°	1660.1	1659.1	1659.2	1659.5	1659.8	1660.1	1660.4	1662.6	1664.8	1667.0	1669.2
172.5°	1667.6	1666.6	1666.9	1667.4	1668.0	1668.5	1669.1	1671.0	1673.0	1674.9	1676.8
175°	1673.6	1672.8	1672.9	1673.2	1673.5	1673.8	1674.1	1676.3	1678.5	1680.7	1682.9
177.5°	1677.4	1676.6	1676.7	1677.0	1677.3	1677.5	1677.8	1679.7	1681.7	1683.6	1685.5
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1487.8	1490.4	1484.0	1481.4	1476.2	1482.7	1484.0	1482.7	1494.3	1489.1	1491.7
5°	1401.4	1396.2	1392.4	1383.3	1383.3	1384.6	1388.5	1382.0	1385.9	1394.9	1393.6
7.5°	1305.9	1303.3	1304.6	1294.3	1286.5	1289.1	1286.5	1298.2	1304.6	1302.0	1307.2
10°	1219.4	1224.6	1213.0	1207.8	1202.7	1207.8	1206.5	1209.1	1216.9	1222.0	1231.1
12.5°	1149.8	1148.5	1142.0	1136.9	1127.8	1130.4	1138.1	1135.6	1136.9	1148.5	1147.2
15°	1083.9	1076.2	1071.0	1059.4	1062.0	1053.0	1060.7	1069.7	1073.6	1083.9	1090.4
17.5°	1018.1	1016.8	1010.4	1009.1	994.9	991.0	998.8	1001.4	1005.2	1010.4	1019.4
20°	962.6	961.4	952.3	949.7	938.1	945.9	943.3	948.5	951.0	961.4	965.2
22.5°	912.3	905.9	903.3	899.4	895.5	894.3	899.4	898.1	907.2	911.0	912.3
25°	865.9	860.7	859.4	853.0	850.4	846.5	850.4	854.3	864.6	868.4	873.6
27.5°	823.3	819.4	816.8	811.7	807.8	807.8	810.4	815.5	819.4	822.0	824.6
30°	784.6	782.0	774.2	771.7	767.8	767.8	767.8	770.4	776.8	784.6	788.4
32.5°	744.6	739.4	734.2	734.2	730.4	730.4	731.7	734.2	740.7	742.0	748.4
35°	705.9	700.7	696.8	694.2	695.5	690.4	692.9	696.8	704.6	707.1	711.0
37.5°	668.4	667.1	659.4	655.5	658.1	658.1	656.8	659.4	664.6	669.7	672.3
40°	627.1	624.6	624.6	620.7	622.0	616.8	620.7	623.3	625.8	631.0	634.9
42.5°	591.0	588.4	583.3	584.6	580.7	580.7	583.3	584.6	588.4	594.9	597.5
45°	552.3	552.3	549.7	545.8	547.1	543.3	545.8	547.1	552.3	558.7	556.2
47.5°	514.9	513.6	513.6	508.4	511.0	507.1	511.0	512.3	514.9	518.7	517.5
50°	478.7	474.9	476.2	474.9	473.6	473.6	476.2	476.2	478.7	478.7	482.6
52.5°	441.3	441.3	438.7	440.0	442.6	440.0	443.9	440.0	442.6	443.9	446.5
55°	407.8	405.2	406.5	405.2	410.4	406.5	410.4	407.8	410.4	409.1	411.6
57.5°	371.6	367.8	369.1	367.8	371.6	370.3	374.2	370.3	371.6	372.9	376.8
60°	330.3	330.3	330.3	327.8	331.6	331.6	330.3	330.3	335.5	338.1	336.8
62.5°	291.6	290.3	286.5	285.2	286.5	283.9	289.1	287.8	290.3	292.9	295.5
65°	249.0	246.5	245.2	242.6	242.6	241.3	242.6	247.8	249.0	250.3	256.8
67.5°	214.2	212.9	211.6	207.8	207.8	210.3	210.3	210.3	218.1	214.2	219.4
70°	183.2	180.7	178.1	176.8	176.8	178.1	179.4	180.7	179.4	184.5	185.8
72.5°	153.6	154.8	152.3	152.3	152.3	151.0	151.0	153.6	154.8	153.6	154.8
75°	127.8	127.8	126.5	127.8	127.8	126.5	126.5	129.0	129.0	127.8	131.6
77.5°	103.2	101.9	99.4	96.8	98.1	96.8	98.1	96.8	100.7	104.5	101.9
80°	72.3	71.0	71.0	71.0	72.3	71.0	73.6	71.0	72.3	72.3	73.6
82.5°	51.6	52.9	52.9	51.6	52.9	51.6	52.9	52.9	52.9	51.6	52.9
85°	33.6	33.6	33.6	33.6	32.3	33.6	33.6	33.6	34.8	33.6	34.8
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	15.5	14.2	15.5
90°	26.2	26.6	27.4	28.3	29.1	29.9	29.1	28.3	27.4	26.6	26.2
92.5°	26.2	26.3	26.6	26.9	27.1	27.4	27.1	26.9	26.6	26.3	26.2
95°	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2
97.5°	24.9	25.0	25.3	25.6	25.9	26.2	25.9	25.6	25.3	25.0	24.9
100°	31.1	30.6	29.5	28.4	27.3	26.2	27.3	28.4	29.5	30.6	31.1
102.5°	294.0	282.4	259.1	235.8	212.6	189.3	212.6	235.8	259.1	282.4	294.0
105°	371.2	371.1	370.8	370.5	370.2	369.9	370.2	370.5	370.8	371.1	371.2
107.5°	454.6	454.1	453.0	451.9	450.8	449.7	450.8	451.9	453.0	454.1	454.6
110°	531.9	532.0	532.3	532.6	532.8	533.1	532.8	532.6	532.3	532.0	531.9

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	610.3	610.0	609.5	608.9	608.4	607.8	608.4	608.9	609.5	610.0	610.3
115°	690.1	689.3	687.6	685.9	684.3	682.6	684.3	685.9	687.6	689.3	690.1
117.5°	766.0	765.7	765.2	764.6	764.1	763.5	764.1	764.6	765.2	765.7	766.0
120°	843.3	842.6	841.2	839.8	838.4	837.0	838.4	839.8	841.2	842.6	843.3
122.5°	914.3	913.5	911.8	910.1	908.5	906.8	908.5	910.1	911.8	913.5	914.3
125°	981.5	981.1	980.3	979.4	978.6	977.8	978.6	979.4	980.3	981.1	981.5
127.5°	1046.3	1045.2	1043.0	1040.7	1038.5	1036.3	1038.5	1040.7	1043.0	1045.2	1046.3
130°	1107.3	1106.6	1105.2	1103.9	1102.5	1101.1	1102.5	1103.9	1105.2	1106.6	1107.3
132.5°	1167.1	1166.4	1165.0	1163.7	1162.3	1160.9	1162.3	1163.7	1165.0	1166.4	1167.1
135°	1221.9	1221.1	1219.4	1217.7	1216.1	1214.4	1216.1	1217.7	1219.4	1221.1	1221.9
137.5°	1276.7	1276.0	1274.6	1273.3	1271.9	1270.5	1271.9	1273.3	1274.6	1276.0	1276.7
140°	1326.5	1325.7	1324.0	1322.4	1320.7	1319.1	1320.7	1322.4	1324.0	1325.7	1326.5
142.5°	1372.6	1371.8	1370.1	1368.5	1366.8	1365.2	1366.8	1368.5	1370.1	1371.8	1372.6
145°	1417.5	1416.7	1415.0	1413.3	1411.7	1410.0	1411.7	1413.3	1415.0	1416.7	1417.5
147.5°	1456.1	1455.1	1453.2	1451.3	1449.3	1447.4	1449.3	1451.3	1453.2	1455.1	1456.1
150°	1493.5	1492.4	1490.2	1487.9	1485.7	1483.5	1485.7	1487.9	1490.2	1492.4	1493.5
152.5°	1525.8	1524.8	1522.9	1521.0	1519.0	1517.1	1519.0	1521.0	1522.9	1524.8	1525.8
155°	1555.7	1554.6	1552.4	1550.2	1548.0	1545.8	1548.0	1550.2	1552.4	1554.6	1555.7
157.5°	1580.6	1579.5	1577.3	1575.1	1572.9	1570.7	1572.9	1575.1	1577.3	1579.5	1580.6
160°	1604.3	1603.2	1601.0	1598.7	1596.5	1594.3	1596.5	1598.7	1601.0	1603.2	1604.3
162.5°	1626.7	1625.5	1623.0	1620.5	1618.0	1615.5	1618.0	1620.5	1623.0	1625.5	1626.7
165°	1644.2	1643.1	1640.9	1638.6	1636.4	1634.2	1636.4	1638.6	1640.9	1643.1	1644.2
167.5°	1659.1	1657.9	1655.4	1652.9	1650.4	1647.9	1650.4	1652.9	1655.4	1657.9	1659.1
170°	1670.3	1669.1	1666.6	1664.1	1661.6	1659.1	1661.6	1664.1	1666.6	1669.1	1670.3
172.5°	1677.8	1676.6	1674.1	1671.6	1669.1	1666.6	1669.1	1671.6	1674.1	1676.6	1677.8
175°	1684.0	1682.8	1680.3	1677.8	1675.3	1672.8	1675.3	1677.8	1680.3	1682.8	1684.0
177.5°	1686.5	1685.4	1683.2	1681.0	1678.8	1676.6	1678.8	1681.0	1683.2	1685.4	1686.5
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1486.6	1493.0	1487.8	1484.0	1494.3	1499.5	1499.5	1508.5	1517.5	1525.3	1526.6
5°	1394.9	1405.3	1407.8	1406.5	1422.0	1429.8	1446.5	1455.6	1468.5	1477.5	1487.8
7.5°	1311.1	1325.3	1326.5	1329.1	1352.3	1365.3	1379.4	1402.7	1420.7	1433.6	1445.3
10°	1227.2	1236.2	1245.2	1256.9	1280.1	1302.0	1322.7	1347.2	1370.4	1383.3	1400.1
12.5°	1163.9	1170.4	1180.7	1188.5	1213.0	1232.3	1259.4	1293.0	1326.5	1336.9	1357.5
15°	1098.1	1102.0	1122.7	1130.4	1151.0	1183.3	1200.1	1232.3	1268.5	1287.8	1311.1
17.5°	1022.0	1045.2	1058.1	1067.2	1093.0	1118.8	1145.9	1179.4	1225.9	1244.0	1260.7
20°	967.8	984.6	998.8	1010.4	1033.6	1072.3	1096.8	1123.9	1167.8	1188.5	1213.0
22.5°	920.1	934.3	947.2	960.1	975.5	1010.4	1038.8	1076.2	1120.1	1139.4	1167.8
25°	874.9	889.1	896.8	912.3	933.0	957.5	991.0	1024.6	1068.5	1090.4	1117.5
27.5°	831.0	845.2	859.4	872.3	886.5	909.7	933.0	975.5	1020.7	1046.5	1069.7
30°	793.6	800.1	813.0	827.2	841.3	863.3	890.4	920.1	971.7	994.9	1023.3
32.5°	752.3	763.9	773.0	783.3	801.3	819.4	843.9	881.3	922.6	944.6	975.5
35°	713.6	723.9	730.4	748.4	760.1	779.4	803.9	837.5	872.3	896.8	923.9
37.5°	676.2	686.5	694.2	704.6	720.0	736.8	762.6	787.1	828.4	849.1	880.1
40°	637.5	646.5	655.5	667.1	681.3	702.0	717.5	748.4	782.0	805.2	828.4
42.5°	600.0	605.2	615.5	628.4	642.6	660.7	682.6	707.1	740.7	761.3	782.0
45°	560.0	569.1	580.7	589.7	602.6	620.7	640.0	662.0	695.5	716.2	738.1
47.5°	522.6	529.1	536.8	551.0	567.8	580.7	601.3	622.0	652.9	672.3	692.9
50°	483.9	490.4	502.0	511.0	523.9	540.7	560.0	582.0	611.7	624.6	645.2
52.5°	447.8	450.4	462.0	471.0	483.9	503.3	518.7	538.1	566.5	580.7	601.3
55°	411.6	414.2	420.7	429.7	443.9	459.4	476.2	498.1	522.6	535.5	554.9
57.5°	374.2	376.8	383.3	389.7	403.9	418.1	437.4	455.5	480.0	491.6	509.7
60°	336.8	336.8	343.2	352.3	362.6	375.5	392.3	414.2	432.3	446.5	459.4
62.5°	296.8	300.7	304.5	311.0	322.6	338.1	352.3	367.8	389.7	400.0	411.6
65°	256.8	260.7	268.4	274.9	283.9	294.2	312.3	325.2	342.0	353.6	363.9
67.5°	222.0	225.8	231.0	238.7	245.2	256.8	269.7	282.6	300.7	308.4	316.2
70°	185.8	189.7	193.6	203.9	210.3	219.4	228.4	241.3	256.8	262.0	268.4
72.5°	157.4	158.7	163.9	166.5	175.5	183.2	193.6	201.3	212.9	219.4	224.5
75°	132.9	132.9	134.2	136.8	141.9	147.1	154.8	162.6	172.9	176.8	183.2
77.5°	104.5	108.4	107.1	109.7	112.3	114.8	121.3	126.5	136.8	139.4	141.9
80°	74.8	76.1	80.0	83.9	83.9	87.7	91.6	92.9	99.4	103.2	103.2
82.5°	54.2	55.5	54.2	55.5	56.8	58.1	61.9	67.1	67.1	68.4	71.0
85°	33.6	33.6	34.8	36.1	36.1	34.8	37.4	36.1	37.4	40.0	40.0
87.5°	16.8	15.5	15.5	15.5	15.5	15.5	16.8	15.5	16.8	16.8	16.8
90°	25.5	24.1	22.7	21.3	19.9	18.0	16.0	14.1	12.2	11.2	10.1
92.5°	25.5	24.1	22.7	21.3	19.9	18.3	16.6	15.0	13.3	12.5	13.7
95°	25.5	24.1	22.7	21.3	19.9	30.4	41.0	51.5	62.0	67.3	67.7
97.5°	24.6	24.1	23.5	23.0	22.4	48.7	75.0	101.3	127.6	140.8	140.0
100°	51.7	93.0	134.2	175.5	216.7	215.6	214.5	213.4	212.3	211.7	211.3
102.5°	293.7	293.2	292.6	292.1	291.5	290.9	290.4	289.8	289.3	289.0	288.4
105°	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	370.6
107.5°	454.5	454.2	453.9	453.7	453.4	452.8	452.3	451.7	451.2	450.9	450.9
110°	532.3	533.1	534.0	534.8	535.6	535.0	534.5	533.9	533.4	533.1	533.1

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	610.9	612.0	613.1	614.2	615.3	615.0	614.8	614.5	614.2	614.1	613.7
115°	690.6	691.7	692.8	693.9	695.0	694.7	694.5	694.2	693.9	693.8	693.1
117.5°	766.8	768.5	770.2	771.8	773.5	772.4	771.3	770.2	769.1	768.5	768.5
120°	843.6	844.1	844.7	845.2	845.8	845.0	844.1	843.3	842.4	842.0	842.1
122.5°	914.6	915.1	915.7	916.2	916.8	916.5	916.2	915.9	915.6	915.5	914.8
125°	982.1	983.2	984.3	985.4	986.5	986.5	986.5	986.5	986.5	986.5	985.5
127.5°	1046.6	1047.1	1047.7	1048.2	1048.8	1049.1	1049.3	1049.6	1049.9	1050.0	1049.3
130°	1107.7	1108.6	1109.4	1110.3	1111.1	1110.8	1110.5	1110.2	1109.9	1109.8	1109.1
132.5°	1167.1	1167.1	1167.1	1167.1	1167.1	1167.9	1168.7	1169.6	1170.4	1170.8	1170.0
135°	1222.2	1222.7	1223.3	1223.8	1224.4	1225.0	1225.5	1226.1	1226.6	1226.9	1226.1
137.5°	1276.7	1276.7	1276.7	1276.7	1276.7	1277.3	1277.8	1278.4	1278.9	1279.2	1278.4
140°	1326.2	1325.7	1325.2	1324.6	1324.1	1324.4	1324.6	1324.9	1325.2	1325.3	1325.0
142.5°	1372.6	1372.6	1372.6	1372.6	1372.6	1372.0	1371.5	1370.9	1370.4	1370.1	1370.0
145°	1417.4	1417.1	1416.8	1416.5	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1415.9
147.5°	1456.0	1455.7	1455.4	1455.1	1454.8	1454.5	1454.3	1454.0	1453.7	1453.6	1453.6
150°	1493.2	1492.7	1492.1	1491.6	1491.0	1490.4	1489.9	1489.3	1488.8	1488.5	1488.8
152.5°	1525.5	1525.0	1524.5	1523.9	1523.4	1522.8	1522.3	1521.7	1521.2	1520.9	1521.6
155°	1555.3	1554.5	1553.6	1552.8	1552.0	1551.4	1550.9	1550.3	1549.8	1549.5	1550.3
157.5°	1580.2	1579.4	1578.5	1577.7	1576.9	1576.9	1576.9	1576.9	1576.9	1576.9	1577.3
160°	1603.7	1602.6	1601.5	1600.4	1599.3	1599.0	1598.8	1598.5	1598.2	1598.1	1598.9
162.5°	1625.9	1624.2	1622.6	1620.9	1619.3	1619.0	1618.7	1618.4	1618.1	1618.0	1618.8
165°	1643.4	1641.7	1640.0	1638.4	1636.7	1636.4	1636.2	1635.9	1635.6	1635.5	1636.3
167.5°	1658.1	1656.2	1654.3	1652.3	1650.4	1650.1	1649.9	1649.6	1649.3	1649.2	1650.0
170°	1669.2	1667.0	1664.8	1662.6	1660.4	1660.1	1659.8	1659.5	1659.2	1659.1	1660.1
172.5°	1676.8	1674.9	1673.0	1671.0	1669.1	1668.5	1668.0	1667.4	1666.9	1666.6	1667.6
175°	1682.9	1680.7	1678.5	1676.3	1674.1	1673.8	1673.5	1673.2	1672.9	1672.8	1673.6
177.5°	1685.5	1683.6	1681.7	1679.7	1677.8	1677.5	1677.3	1677.0	1676.7	1676.6	1677.4
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1535.6	1547.2	1558.8	1573.0
5°	1504.6	1525.3	1547.2	1567.8
7.5°	1471.1	1500.7	1529.1	1558.8
10°	1433.6	1471.1	1503.3	1544.6
12.5°	1392.4	1432.4	1477.5	1524.0
15°	1351.1	1401.4	1449.1	1502.0
17.5°	1312.3	1360.1	1413.0	1476.2
20°	1265.9	1318.8	1378.2	1445.3
22.5°	1216.9	1274.9	1339.4	1411.7
25°	1175.6	1234.9	1296.9	1373.0
27.5°	1130.4	1192.3	1253.0	1334.3
30°	1078.8	1145.9	1207.8	1291.7
32.5°	1029.7	1096.8	1165.2	1244.0
35°	982.0	1047.8	1116.2	1196.2
37.5°	936.8	996.2	1063.3	1135.6
40°	894.3	948.5	1007.8	1073.6
42.5°	840.1	903.3	958.8	1006.5
45°	793.6	845.2	896.8	935.5
47.5°	739.4	791.0	834.9	865.9
50°	694.2	735.5	771.7	798.8
52.5°	640.0	678.8	708.4	729.1
55°	587.1	620.7	646.5	660.7
57.5°	539.4	561.3	580.7	593.6
60°	486.5	503.3	520.0	534.2
62.5°	429.7	447.8	456.8	472.3
65°	379.4	391.0	405.2	410.4
67.5°	330.3	336.8	345.8	356.2
70°	278.7	282.6	291.6	305.8
72.5°	233.6	237.4	243.9	249.0
75°	185.8	189.7	194.9	200.0
77.5°	145.8	147.1	149.7	154.8
80°	105.8	109.7	112.3	113.6
82.5°	73.6	74.8	74.8	76.1
85°	46.5	43.9	43.9	45.2
87.5°	16.8	19.4	19.4	21.9
90°	7.9	5.6	3.4	1.2
92.5°	16.2	18.7	21.2	23.7
95°	68.5	69.4	70.2	71.0
97.5°	138.3	136.6	135.0	133.3
100°	210.5	209.6	208.8	208.0
102.5°	287.3	286.2	285.1	284.0
105°	369.5	368.4	367.3	366.2
107.5°	450.9	450.9	450.9	450.9
110°	533.1	533.1	533.1	533.1

TEST NUMBER: P1034703

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	612.8	612.0	611.1	610.3
115°	691.7	690.4	689.0	687.6
117.5°	768.5	768.5	768.5	768.5
120°	842.4	842.7	843.0	843.3
122.5°	913.4	912.1	910.7	909.3
125°	983.6	981.7	979.7	977.8
127.5°	1047.9	1046.6	1045.2	1043.8
130°	1107.7	1106.4	1105.0	1103.6
132.5°	1168.3	1166.7	1165.0	1163.4
135°	1224.4	1222.7	1221.1	1219.4
137.5°	1276.7	1275.0	1273.4	1271.7
140°	1324.5	1323.9	1323.4	1322.8
142.5°	1369.7	1369.4	1369.2	1368.9
145°	1415.4	1414.8	1414.3	1413.7
147.5°	1453.6	1453.6	1453.6	1453.6
150°	1489.3	1489.9	1490.4	1491.0
152.5°	1523.0	1524.3	1525.7	1527.1
155°	1552.0	1553.7	1555.3	1557.0
157.5°	1578.1	1579.0	1579.8	1580.6
160°	1600.6	1602.3	1603.9	1605.6
162.5°	1620.5	1622.2	1623.8	1625.5
165°	1638.0	1639.6	1641.3	1642.9
167.5°	1651.7	1653.3	1655.0	1656.6
170°	1662.0	1663.9	1665.9	1667.8
172.5°	1669.5	1671.4	1673.4	1675.3
175°	1675.3	1677.0	1678.6	1680.3
177.5°	1679.1	1680.7	1682.4	1684.0
180°	1680.3	1680.3	1680.3	1680.3

(END OF REPORT)