

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034708

Luminaire Tested: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034708
REPORT IS A COMBINATION OF REPORTS P1005982 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9200.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034708

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034708

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1034708

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	1.7
10°-20°	449.3	4.9
20°-30°	651.5	7.1
30°-40°	742.2	8.1
40°-50°	723.5	7.9
50°-60°	608.8	6.6
60°-70°	426.7	4.6
70°-80°	218.7	2.4
80°-90°	57.0	0.6
90°-100°	57.0	0.6
100°-110°	379.2	4.1
110°-120°	682.9	7.4
120°-130°	876.6	9.5
130°-140°	942.8	10.2
140°-150°	884.8	9.6
150°-160°	715.7	7.8
160°-170°	462.9	5.0
170°-180°	159.6	1.7
0°-30°	1261.6	13.7
0°-40°	2003.8	21.8
0°-60°	3336.1	36.3
0°-90°	4038.5	43.9
90°-120°	1119.2	12.2
90°-150°	3823.3	41.6
90°-180°	5162.0	56.1
0°-180°	9200.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	1	11	20	26	30	8
95°	71	67	20	26	26	87
105°	366	371	371	371	370	388
115°	688	694	695	690	683	682
125°	978	986	986	982	978	873
135°	1219	1227	1224	1222	1214	940
145°	1414	1416	1416	1418	1410	884
155°	1557	1550	1552	1556	1546	717
165°	1643	1636	1637	1644	1634	464
175°	1680	1673	1674	1684	1673	160
180°	1680	1680	1680	1680	1680	

TEST NUMBER: P1034708

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	1.2	11.2	19.9	26.2	29.9
92.5°	23.7	12.5	19.9	26.2	27.4
95°	71.0	67.3	19.9	26.2	26.2
97.5°	133.3	140.8	22.4	24.9	26.2
100°	208.0	211.7	216.7	31.1	26.2
102.5°	284.0	289.0	291.5	294.0	189.3
105°	366.2	371.2	371.2	371.2	369.9
107.5°	450.9	450.9	453.4	454.6	449.7
110°	533.1	533.1	535.6	531.9	533.1

TEST NUMBER: P1034708

CATALOG NUMBER: S125RDIW-B1090D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	610.3	614.1	615.3	610.3	607.8
115°	687.6	693.8	695.0	690.1	682.6
117.5°	768.5	768.5	773.5	766.0	763.5
120°	843.3	842.0	845.8	843.3	837.0
122.5°	909.3	915.5	916.8	914.3	906.8
125°	977.8	986.5	986.5	981.5	977.8
127.5°	1043.8	1050.0	1048.8	1046.3	1036.3
130°	1103.6	1109.8	1111.1	1107.3	1101.1
132.5°	1163.4	1170.8	1167.1	1167.1	1160.9
135°	1219.4	1226.9	1224.4	1221.9	1214.4
137.5°	1271.7	1279.2	1276.7	1276.7	1270.5
140°	1322.8	1325.3	1324.1	1326.5	1319.1
142.5°	1368.9	1370.1	1372.6	1372.6	1365.2
145°	1413.7	1416.2	1416.2	1417.5	1410.0
147.5°	1453.6	1453.6	1454.8	1456.1	1447.4
150°	1491.0	1488.5	1491.0	1493.5	1483.5
152.5°	1527.1	1520.9	1523.4	1525.8	1517.1
155°	1557.0	1549.5	1552.0	1555.7	1545.8
157.5°	1580.6	1576.9	1576.9	1580.6	1570.7
160°	1605.6	1598.1	1599.3	1604.3	1594.3
162.5°	1625.5	1618.0	1619.3	1626.7	1615.5
165°	1642.9	1635.5	1636.7	1644.2	1634.2
167.5°	1656.6	1649.2	1650.4	1659.1	1647.9
170°	1667.8	1659.1	1660.4	1670.3	1659.1
172.5°	1675.3	1666.6	1669.1	1677.8	1666.6
175°	1680.3	1672.8	1674.1	1684.0	1672.8
177.5°	1684.0	1676.6	1677.8	1686.5	1676.6
180°	1680.3	1680.3	1680.3	1680.3	1680.3

(END OF REPORT)