

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034714

Luminaire Tested: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034714
REPORT IS A COMBINATION OF REPORTS P1006020 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9316.0 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034714

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034714

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	42	37	57	47	39	34	39	34	30	32	28	25	26	23	21
7	58	45	38	32	53	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1034714

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	1.7
10°-20°	449.3	4.8
20°-30°	651.5	7.0
30°-40°	742.2	8.0
40°-50°	723.5	7.8
50°-60°	608.8	6.5
60°-70°	426.7	4.6
70°-80°	218.7	2.3
80°-90°	57.5	0.6
90°-100°	125.7	1.3
100°-110°	373.5	4.0
110°-120°	633.5	6.8
120°-130°	834.0	9.0
130°-140°	934.5	10.0
140°-150°	916.0	9.8
150°-160°	769.4	8.3
160°-170°	511.5	5.5
170°-180°	179.0	1.9
0°-30°	1261.6	13.5
0°-40°	2003.8	21.5
0°-60°	3336.1	35.8
0°-90°	4039.0	43.4
90°-120°	1132.7	12.2
90°-150°	3817.2	41.0
90°-180°	5277.0	56.6
0°-180°	9316.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	2	13	24	31	35	11
95°	96	99	113	124	126	100
105°	336	343	352	360	365	358
115°	634	640	643	642	640	627
125°	926	934	936	933	931	829
135°	1204	1212	1214	1214	1208	928
145°	1458	1464	1468	1468	1464	912
155°	1669	1669	1670	1676	1669	769
165°	1814	1811	1813	1819	1810	512
175°	1886	1880	1880	1889	1879	179
180°	1891	1891	1891	1891	1891	

TEST NUMBER: P1034714

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	1.5	13.2	23.5	30.9	35.3
92.5°	44.1	51.5	64.7	75.0	78.0
95°	95.6	98.6	113.3	123.6	126.5
97.5°	147.1	148.6	169.2	178.0	179.5
100°	206.0	206.0	225.1	238.4	241.3
102.5°	269.3	276.6	284.0	298.7	303.1
105°	335.5	342.8	351.7	360.5	364.9
107.5°	407.6	414.9	422.3	426.7	426.7
110°	482.6	490.0	494.4	498.8	497.3

TEST NUMBER: P1034714

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	559.1	562.1	568.0	569.4	566.5
115°	634.2	640.1	643.0	641.5	640.1
117.5°	710.7	712.2	715.1	716.6	710.7
120°	781.3	788.7	790.2	790.2	784.3
122.5°	857.8	859.3	863.7	862.3	857.8
125°	925.5	934.4	935.8	932.9	931.4
127.5°	1000.6	1005.0	1006.5	1005.0	1002.0
130°	1066.8	1074.1	1077.1	1075.6	1072.7
132.5°	1133.0	1146.2	1144.8	1143.3	1138.9
135°	1203.6	1212.5	1213.9	1213.9	1208.0
137.5°	1269.8	1278.7	1281.6	1283.1	1275.7
140°	1333.1	1340.5	1344.9	1347.8	1340.5
142.5°	1396.4	1402.3	1408.2	1409.6	1402.3
145°	1458.2	1464.1	1468.5	1468.5	1464.1
147.5°	1515.6	1520.0	1522.9	1527.4	1515.6
150°	1573.0	1571.5	1577.4	1577.4	1574.4
152.5°	1620.1	1623.0	1624.5	1628.9	1623.0
155°	1668.6	1668.6	1670.1	1676.0	1668.6
157.5°	1712.8	1709.8	1711.3	1717.2	1706.9
160°	1751.0	1746.6	1748.1	1754.0	1746.6
162.5°	1784.9	1781.9	1781.9	1789.3	1780.4
165°	1814.3	1811.3	1812.8	1818.7	1809.9
167.5°	1840.8	1834.9	1834.9	1843.7	1834.9
170°	1861.4	1855.5	1855.5	1864.3	1854.0
172.5°	1876.1	1870.2	1870.2	1879.0	1870.2
175°	1886.4	1880.5	1880.5	1889.3	1879.0
177.5°	1893.7	1887.9	1886.4	1895.2	1884.9
180°	1890.8	1890.8	1890.8	1890.8	1890.8

(END OF REPORT)