

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034717

Luminaire Tested: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034717
REPORT IS A COMBINATION OF REPORTS P1006024 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10576.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034717

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034717

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	96	92	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40			34
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34			29
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29			25
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25			21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22			18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19			16
7	57	45	37	32	52	41	35	30	35	29	25	28	24	21	22	19	17			14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15			13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14			12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	17	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1034717

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	1.6
10°-20°	469.3	4.4
20°-30°	680.5	6.4
30°-40°	775.3	7.3
40°-50°	755.7	7.1
50°-60°	636.0	6.0
60°-70°	445.7	4.2
70°-80°	228.5	2.2
80°-90°	60.1	0.6
90°-100°	70.2	0.7
100°-110°	467.1	4.4
110°-120°	841.1	8.0
120°-130°	1079.6	10.2
130°-140°	1161.1	11.0
140°-150°	1089.7	10.3
150°-160°	881.5	8.3
160°-170°	570.1	5.4
170°-180°	196.6	1.9
0°-30°	1317.8	12.5
0°-40°	2093.2	19.8
0°-60°	3484.9	33.0
0°-90°	4219.1	39.9
90°-120°	1378.3	13.0
90°-150°	4708.7	44.5
90°-180°	6357.0	60.1
0°-180°	10576.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	2	14	24	32	37	9
95°	87	83	24	32	32	107
105°	451	457	457	457	456	478
115°	847	854	856	850	841	839
125°	1204	1215	1215	1209	1204	1076
135°	1502	1511	1508	1505	1496	1158
145°	1741	1744	1744	1746	1737	1089
155°	1918	1908	1911	1916	1904	884
165°	2023	2014	2016	2025	2013	572
175°	2070	2060	2062	2074	2060	197
180°	2070	2070	2070	2070	2070	

TEST NUMBER: P1034717

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	1.5	13.8	24.5	32.2	36.8
92.5°	29.1	15.3	24.5	32.2	33.7
95°	87.4	82.8	24.5	32.2	32.2
97.5°	164.1	173.3	27.6	30.7	32.2
100°	256.2	260.8	266.9	38.4	32.2
102.5°	349.8	355.9	359.0	362.0	233.2
105°	451.0	457.2	457.2	457.2	455.6
107.5°	555.3	555.3	558.4	559.9	553.8
110°	656.6	656.6	659.6	655.0	656.6

TEST NUMBER: P1034717

CATALOG NUMBER: S125RDIW-B1090D1560UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	751.7	756.3	757.8	751.7	748.6
115°	846.8	854.5	856.0	849.9	840.7
117.5°	946.5	946.5	952.7	943.5	940.4
120°	1038.6	1037.0	1041.6	1038.6	1030.9
122.5°	1119.9	1127.5	1129.1	1126.0	1116.8
125°	1204.2	1215.0	1215.0	1208.8	1204.2
127.5°	1285.5	1293.2	1291.7	1288.6	1276.3
130°	1359.2	1366.9	1368.4	1363.8	1356.1
132.5°	1432.8	1442.0	1437.4	1437.4	1429.7
135°	1501.9	1511.1	1508.0	1504.9	1495.7
137.5°	1566.3	1575.5	1572.4	1572.4	1564.7
140°	1629.2	1632.2	1630.7	1633.8	1624.6
142.5°	1685.9	1687.5	1690.5	1690.5	1681.3
145°	1741.2	1744.2	1744.2	1745.8	1736.6
147.5°	1790.3	1790.3	1791.8	1793.3	1782.6
150°	1836.3	1833.2	1836.3	1839.3	1827.1
152.5°	1880.8	1873.1	1876.2	1879.2	1868.5
155°	1917.6	1908.4	1911.4	1916.0	1903.8
157.5°	1946.7	1942.1	1942.1	1946.7	1934.5
160°	1977.4	1968.2	1969.7	1975.9	1963.6
162.5°	2002.0	1992.8	1994.3	2003.5	1989.7
165°	2023.4	2014.2	2015.8	2025.0	2012.7
167.5°	2040.3	2031.1	2032.6	2043.4	2029.6
170°	2054.1	2043.4	2044.9	2057.2	2043.4
172.5°	2063.3	2052.6	2055.6	2066.4	2052.6
175°	2069.5	2060.3	2061.8	2074.1	2060.3
177.5°	2074.1	2064.9	2066.4	2077.1	2064.9
180°	2069.5	2069.5	2069.5	2069.5	2069.5

(END OF REPORT)