

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034735

Luminaire Tested: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034735
REPORT IS A COMBINATION OF REPORTS P1006110 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7260.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034735

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034735

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	84	78	72	85	78	73	68	68	64	60	58	55	53	50	47	46
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39
4	76	65	58	51	71	61	54	49	54	48	44	46	42	39	40	36	34
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21
9	52	40	32	27	48	37	30	26	33	27	24	29	25	21	25	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11287	11287	11287
5°	11288	11005	11023
10°	11178	10728	10633
15°	11019	10340	10121
20°	10824	9873	9584
25°	10599	9417	9008
30°	10325	8915	8403
35°	10044	8406	7760
40°	9777	7883	7133
45°	9456	7319	6475
50°	9130	6720	5806
55°	8753	6129	5113
60°	8367	5454	4394
65°	7907	4700	3619
70°	7369	3827	2848
75°	6627	2877	2075
80°	5591	1864	1399
85°	4185	1002	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9456 cd/sqm

TEST NUMBER: P1034735

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	2.3
10°-20°	463.3	6.4
20°-30°	671.8	9.3
30°-40°	765.4	10.5
40°-50°	746.0	10.3
50°-60°	627.8	8.6
60°-70°	440.0	6.1
70°-80°	225.6	3.1
80°-90°	57.8	0.8
90°-100°	34.2	0.5
100°-110°	227.5	3.1
110°-120°	409.7	5.6
120°-130°	525.9	7.2
130°-140°	565.6	7.8
140°-150°	530.8	7.3
150°-160°	429.4	5.9
160°-170°	277.7	3.8
170°-180°	95.8	1.3
0°-30°	1300.9	17.9
0°-40°	2066.3	28.5
0°-60°	3440.2	47.4
0°-90°	4163.5	57.3
90°-120°	671.4	9.2
90°-150°	2293.7	31.6
90°-180°	3097.0	42.7
0°-180°	7260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1762	1762	1762	1762	1762	
5°	1759	1754	1739	1752	1750	167
15°	1672	1664	1636	1635	1623	472
25°	1517	1497	1448	1430	1416	698
35°	1307	1275	1215	1176	1158	818
45°	1070	1031	958	905	885	825
55°	812	769	694	635	613	726
65°	550	504	434	380	361	544
75°	293	253	197	168	158	309
85°	73	49	43	41	40	80
90°	1	7	12	16	18	6
95°	43	40	12	16	16	52
105°	220	223	223	223	222	233
115°	412	416	417	414	410	409
125°	587	592	592	589	587	524
135°	732	736	735	733	729	564
145°	848	850	850	850	846	530
155°	934	930	931	933	927	430
165°	986	981	982	986	980	278
175°	1008	1004	1004	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1034735

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1761.6	1761.6	1761.6	1761.6	1761.6
2.5°	1765.6	1761.6	1748.3	1761.6	1760.3
5°	1758.9	1753.6	1739.0	1752.3	1749.6
7.5°	1745.6	1740.3	1723.0	1733.6	1731.0
10°	1725.7	1721.7	1703.0	1707.0	1703.0
12.5°	1703.0	1697.7	1671.1	1673.8	1667.1
15°	1672.4	1664.5	1636.5	1635.2	1623.2
17.5°	1640.5	1628.5	1595.3	1588.6	1579.3
20°	1601.9	1588.6	1546.0	1539.4	1527.4
22.5°	1559.3	1546.0	1500.8	1486.2	1476.9
25°	1516.8	1496.8	1447.6	1430.3	1415.7
27.5°	1468.9	1444.9	1393.0	1370.4	1355.8
30°	1415.7	1390.4	1334.5	1303.9	1291.9
32.5°	1363.8	1333.2	1276.0	1241.4	1225.4
35°	1306.6	1274.6	1214.7	1176.2	1157.5
37.5°	1252.0	1213.4	1152.2	1107.0	1088.4
40°	1193.5	1153.5	1089.7	1039.1	1023.2
42.5°	1132.3	1091.0	1024.5	976.6	951.3
45°	1069.7	1031.1	958.0	904.7	884.8
47.5°	1004.5	964.6	891.4	836.9	814.3
50°	943.3	899.4	823.6	767.7	747.7
52.5°	876.8	831.6	761.0	699.8	679.9
55°	811.6	769.0	694.5	634.6	613.4
57.5°	745.1	699.8	628.0	569.5	550.8
60°	681.2	634.6	562.8	504.3	484.3
62.5°	613.4	569.5	496.3	443.1	423.1
65°	549.5	504.3	433.7	380.5	360.6
67.5°	485.6	440.4	372.5	322.0	306.0
70°	420.4	375.2	308.7	267.4	251.5
72.5°	356.6	312.7	251.5	214.2	204.9
75°	292.7	252.8	196.9	167.6	158.3
77.5°	227.5	195.6	149.0	126.4	118.4
80°	173.0	141.0	103.8	91.8	89.1
82.5°	119.7	91.8	69.2	65.2	63.9
85°	73.2	49.2	42.6	41.2	39.9
87.5°	30.6	21.3	20.0	20.0	18.6
90°	0.7	6.7	12.0	15.7	17.9
92.5°	14.2	7.5	12.0	15.7	16.4
95°	42.6	40.4	12.0	15.7	15.7
97.5°	80.0	84.4	13.5	14.9	15.7
100°	124.8	127.0	130.0	18.7	15.7
102.5°	170.4	173.4	174.9	176.4	113.6
105°	219.7	222.7	222.7	222.7	221.9
107.5°	270.5	270.5	272.0	272.7	269.8
110°	319.8	319.8	321.3	319.1	319.8



TEST NUMBER: P1034735

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	366.2	368.4	369.1	366.2	364.7
115°	412.5	416.2	417.0	414.0	409.5
117.5°	461.1	461.1	464.0	459.6	458.1
120°	505.9	505.1	507.4	505.9	502.2
122.5°	545.5	549.2	550.0	548.5	544.0
125°	586.6	591.8	591.8	588.8	586.6
127.5°	626.2	629.9	629.2	627.7	621.7
130°	662.1	665.8	666.6	664.3	660.6
132.5°	697.9	702.4	700.2	700.2	696.4
135°	731.6	736.0	734.6	733.1	728.6
137.5°	762.9	767.4	765.9	765.9	762.2
140°	793.6	795.1	794.3	795.8	791.3
142.5°	821.2	822.0	823.5	823.5	819.0
145°	848.1	849.6	849.6	850.4	845.9
147.5°	872.0	872.0	872.8	873.5	868.3
150°	894.5	893.0	894.5	896.0	890.0
152.5°	916.1	912.4	913.9	915.4	910.2
155°	934.1	929.6	931.1	933.3	927.3
157.5°	948.3	946.0	946.0	948.3	942.3
160°	963.2	958.7	959.5	962.5	956.5
162.5°	975.2	970.7	971.4	975.9	969.2
165°	985.6	981.1	981.9	986.4	980.4
167.5°	993.8	989.4	990.1	995.3	988.6
170°	1000.6	995.3	996.1	1002.1	995.3
172.5°	1005.1	999.8	1001.3	1006.6	999.8
175°	1008.0	1003.6	1004.3	1010.3	1003.6
177.5°	1010.3	1005.8	1006.6	1011.8	1005.8
180°	1008.0	1008.0	1008.0	1008.0	1008.0

(END OF REPORT)