

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983197

Luminaire Tested: S124IW-B1340UB2750-4F0-XX-W2A_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1340UB2750-4F0-XX-W2A_3500K
Description: Define 4 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5395.0 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983197

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983197

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983197

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.6	0.1
90°-100°	57.8	1.1
100°-110°	380.9	7.1
110°-120°	727.3	13.5
120°-130°	923.3	17.1
130°-140°	987.7	18.3
140°-150°	923.6	17.1
150°-160°	744.8	13.8
160°-170°	480.4	8.9
170°-180°	165.5	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.6	0.1
90°-120°	1166.1	21.6
90°-150°	4000.7	74.2
90°-180°	5391.0	99.9
0°-180°	5395.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	18	29	36	39	4
95°	72	27	29	36	38	88
105°	392	400	407	418	371	411
115°	732	736	735	738	738	721
125°	1030	1035	1032	1036	1037	919
135°	1277	1276	1281	1284	1286	984
145°	1473	1476	1476	1478	1480	920
155°	1615	1616	1612	1617	1613	744
165°	1703	1697	1697	1707	1695	481
175°	1742	1734	1736	1748	1732	166
180°	1742	1742	1742	1742	1742	

TEST NUMBER: P983197

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.9	18.2	28.7	36.5	39.1
92.5°	19.5	16.9	27.4	35.2	35.2
95°	71.7	27.4	28.7	36.5	37.8
97.5°	136.8	165.5	28.7	35.2	36.5
100°	213.7	237.2	57.3	35.2	36.5
102.5°	299.7	315.4	331.0	37.8	37.8
105°	392.3	400.1	406.6	418.3	371.4
107.5°	477.0	480.9	490.0	496.5	501.7
110°	563.0	566.9	574.7	577.3	581.2

TEST NUMBER: P983197

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	646.4	654.2	656.8	655.5	660.7
115°	732.4	736.3	735.0	737.6	737.6
117.5°	809.3	814.5	818.4	817.1	817.1
120°	887.5	892.7	891.4	894.0	891.4
122.5°	960.4	963.0	965.6	967.0	964.3
125°	1029.5	1034.7	1032.1	1036.0	1037.3
127.5°	1096.0	1097.3	1103.8	1102.5	1101.2
130°	1159.8	1161.1	1165.0	1166.3	1166.3
132.5°	1218.5	1221.1	1226.3	1227.6	1226.3
135°	1277.1	1275.8	1281.0	1283.6	1286.2
137.5°	1329.2	1329.2	1335.7	1338.4	1337.1
140°	1380.1	1382.7	1385.3	1389.2	1390.5
142.5°	1425.7	1430.9	1432.2	1434.8	1434.8
145°	1472.6	1476.5	1476.5	1477.8	1480.4
147.5°	1509.1	1516.9	1515.6	1516.9	1518.2
150°	1549.5	1554.7	1553.4	1553.4	1554.7
152.5°	1583.3	1587.3	1584.7	1587.3	1586.0
155°	1614.6	1615.9	1612.0	1617.2	1613.3
157.5°	1642.0	1642.0	1636.8	1643.3	1636.8
160°	1665.4	1661.5	1660.2	1668.1	1660.2
162.5°	1686.3	1681.1	1679.8	1687.6	1678.5
165°	1703.2	1696.7	1696.7	1707.2	1695.4
167.5°	1717.6	1711.1	1709.8	1721.5	1708.5
170°	1729.3	1721.5	1722.8	1733.2	1720.2
172.5°	1737.1	1729.3	1730.6	1741.0	1726.7
175°	1742.3	1734.5	1735.8	1747.5	1731.9
177.5°	1746.2	1737.1	1739.7	1750.2	1734.5
180°	1742.3	1742.3	1742.3	1742.3	1742.3

(END OF REPORT)