

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034738

Luminaire Tested: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034738
REPORT IS A COMBINATION OF REPORTS P1006114 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7041.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034738

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034738

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	84	78	72	85	78	73	68	68	64	60	58	55	53	50	47	46
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39
4	76	65	58	51	71	61	54	49	54	48	44	46	42	39	40	36	34
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21
9	52	40	32	27	48	37	30	26	33	27	24	29	25	21	25	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1034738

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.3
10°-20°	449.3	6.4
20°-30°	651.5	9.3
30°-40°	742.2	10.5
40°-50°	723.5	10.3
50°-60°	608.8	8.6
60°-70°	426.7	6.1
70°-80°	218.7	3.1
80°-90°	56.0	0.8
90°-100°	33.2	0.5
100°-110°	220.7	3.1
110°-120°	397.4	5.6
120°-130°	510.1	7.2
130°-140°	548.6	7.8
140°-150°	514.9	7.3
150°-160°	416.5	5.9
160°-170°	269.4	3.8
170°-180°	92.9	1.3
0°-30°	1261.6	17.9
0°-40°	2003.8	28.5
0°-60°	3336.1	47.4
0°-90°	4037.5	57.3
90°-120°	651.2	9.2
90°-150°	2224.8	31.6
90°-180°	3004.0	42.7
0°-180°	7041.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	1	6	12	15	17	6
95°	41	39	12	15	15	51
105°	213	216	216	216	215	226
115°	400	404	404	402	397	397
125°	569	574	574	571	569	508
135°	710	714	712	711	707	547
145°	823	824	824	825	820	515
155°	906	902	903	905	900	417
165°	956	952	952	957	951	270
175°	978	973	974	980	973	93
180°	978	978	978	978	978	

TEST NUMBER: P1034738

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	0.7	6.5	11.6	15.2	17.4
92.5°	13.8	7.2	11.6	15.2	15.9
95°	41.3	39.1	11.6	15.2	15.2
97.5°	77.6	81.9	13.0	14.5	15.2
100°	121.0	123.2	126.1	18.1	15.2
102.5°	165.3	168.2	169.6	171.1	110.2
105°	213.1	216.0	216.0	216.0	215.3
107.5°	262.4	262.4	263.8	264.6	261.7
110°	310.2	310.2	311.7	309.5	310.2



TEST NUMBER: P1034738

CATALOG NUMBER: S125RDIW-B1090D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.2	357.3	358.1	355.2	353.7
115°	400.1	403.7	404.5	401.6	397.2
117.5°	447.2	447.2	450.1	445.8	444.3
120°	490.7	490.0	492.2	490.7	487.1
122.5°	529.1	532.7	533.5	532.0	527.7
125°	569.0	574.1	574.1	571.2	569.0
127.5°	607.4	611.0	610.3	608.9	603.1
130°	642.2	645.8	646.5	644.4	640.7
132.5°	677.0	681.3	679.2	679.2	675.5
135°	709.6	713.9	712.5	711.1	706.7
137.5°	740.0	744.4	742.9	742.9	739.3
140°	769.8	771.2	770.5	771.9	767.6
142.5°	796.6	797.3	798.8	798.8	794.4
145°	822.7	824.1	824.1	824.8	820.5
147.5°	845.9	845.9	846.6	847.3	842.2
150°	867.6	866.2	867.6	869.1	863.3
152.5°	888.6	885.0	886.5	887.9	882.8
155°	906.0	901.7	903.1	905.3	899.5
157.5°	919.8	917.6	917.6	919.8	914.0
160°	934.3	929.9	930.7	933.6	927.8
162.5°	945.9	941.5	942.3	946.6	940.1
165°	956.0	951.7	952.4	956.8	951.0
167.5°	964.0	959.7	960.4	965.5	958.9
170°	970.5	965.5	966.2	972.0	965.5
172.5°	974.9	969.8	971.3	976.3	969.8
175°	977.8	973.4	974.2	980.0	973.4
177.5°	980.0	975.6	976.3	981.4	975.6
180°	977.8	977.8	977.8	977.8	977.8

(END OF REPORT)