

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983212

Luminaire Tested: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K
Description: Define 4 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5517.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983212

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983212

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983212

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.2	0.1
90°-100°	129.5	2.3
100°-110°	387.9	7.0
110°-120°	659.0	11.9
120°-130°	869.1	15.8
130°-140°	976.1	17.7
140°-150°	959.4	17.4
150°-160°	806.9	14.6
160°-170°	536.9	9.7
170°-180°	188.0	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.2	0.1
90°-120°	1176.4	21.3
90°-150°	3981.0	72.2
90°-180°	5513.0	99.9
0°-180°	5517.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	22	34	43	46	7
95°	92	106	117	121	121	100
105°	358	360	366	370	375	380
115°	670	670	667	665	664	661
125°	976	976	974	971	968	870
135°	1258	1268	1268	1265	1260	974
145°	1529	1535	1537	1535	1530	957
155°	1752	1752	1750	1756	1750	806
165°	1907	1902	1899	1908	1902	538
175°	1984	1976	1974	1985	1974	188
180°	1987	1987	1987	1987	1987	

TEST NUMBER: P983212

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.6	21.5	33.8	43.0	46.1
92.5°	40.0	59.9	67.6	72.2	73.8
95°	92.2	106.0	116.8	121.4	121.4
97.5°	147.5	159.8	172.1	178.2	178.2
100°	215.1	221.3	235.1	238.2	238.2
102.5°	285.8	287.3	299.6	304.2	305.8
105°	358.0	359.6	365.7	370.3	374.9
107.5°	433.3	434.9	436.4	442.5	441.0
110°	510.2	513.2	511.7	508.6	513.2

TEST NUMBER: P983212

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.1	590.1	587.0	587.0	587.0
115°	670.0	670.0	666.9	665.4	663.8
117.5°	745.3	745.3	743.7	739.1	734.5
120°	820.6	826.7	822.1	814.4	817.5
122.5°	898.9	900.5	898.9	894.3	886.6
125°	975.7	975.7	974.2	971.1	968.1
127.5°	1044.9	1049.5	1046.4	1043.4	1041.8
130°	1118.7	1123.3	1123.3	1120.2	1114.0
132.5°	1193.9	1197.0	1195.5	1192.4	1190.9
135°	1258.5	1267.7	1267.7	1264.6	1260.0
137.5°	1330.7	1335.3	1338.4	1333.8	1335.3
140°	1402.9	1406.0	1406.0	1404.5	1402.9
142.5°	1469.0	1472.1	1470.5	1470.5	1470.5
145°	1528.9	1535.1	1536.6	1535.1	1530.5
147.5°	1590.4	1598.1	1596.5	1595.0	1593.5
150°	1645.7	1651.9	1651.9	1651.9	1650.3
152.5°	1698.0	1701.0	1702.6	1707.2	1702.6
155°	1751.7	1751.7	1750.2	1756.3	1750.2
157.5°	1797.8	1794.8	1794.8	1799.4	1794.8
160°	1837.8	1836.3	1834.7	1839.3	1831.6
162.5°	1874.7	1870.1	1868.5	1877.7	1870.1
165°	1906.9	1902.3	1899.3	1908.5	1902.3
167.5°	1933.1	1926.9	1926.9	1936.1	1926.9
170°	1954.6	1946.9	1948.4	1957.6	1946.9
172.5°	1969.9	1963.8	1963.8	1974.5	1963.8
175°	1983.8	1976.1	1974.5	1985.3	1974.5
177.5°	1989.9	1982.2	1982.2	1993.0	1980.7
180°	1986.8	1986.8	1986.8	1986.8	1986.8

(END OF REPORT)