

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983215

Luminaire Tested: S124IW-B1560UB2750-4F0-XX-W2A_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1560UB2750-4F0-XX-W2A_2700K
Description: Define 4 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6280.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983215

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P983215

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983215

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.2	0.1
90°-100°	67.3	1.1
100°-110°	443.4	7.1
110°-120°	846.6	13.5
120°-130°	1074.8	17.1
130°-140°	1149.8	18.3
140°-150°	1075.1	17.1
150°-160°	867.0	13.8
160°-170°	559.1	8.9
170°-180°	192.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.2	0.1
90°-120°	1357.3	21.6
90°-150°	4657.0	74.2
90°-180°	6276.0	99.9
0°-180°	6280.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	21	33	42	46	4
95°	83	32	33	42	44	103
105°	457	466	473	487	432	478
115°	852	857	856	859	859	839
125°	1198	1204	1201	1206	1208	1070
135°	1487	1485	1491	1494	1497	1145
145°	1714	1719	1719	1720	1723	1071
155°	1880	1881	1876	1882	1878	867
165°	1983	1975	1975	1987	1974	560
175°	2028	2019	2021	2034	2016	193
180°	2028	2028	2028	2028	2028	

TEST NUMBER: P983215

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.6	21.2	33.4	42.5	45.5
92.5°	22.8	19.7	31.9	41.0	41.0
95°	83.4	31.9	33.4	42.5	44.0
97.5°	159.3	192.7	33.4	41.0	42.5
100°	248.8	276.1	66.7	41.0	42.5
102.5°	348.9	367.1	385.3	44.0	44.0
105°	456.6	465.7	473.3	486.9	432.3
107.5°	555.2	559.8	570.4	578.0	584.0
110°	655.3	659.9	669.0	672.0	676.6

TEST NUMBER: P983215

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	752.4	761.5	764.5	763.0	769.1
115°	852.5	857.1	855.6	858.6	858.6
117.5°	942.0	948.1	952.6	951.1	951.1
120°	1033.0	1039.1	1037.6	1040.6	1037.6
122.5°	1118.0	1121.0	1124.1	1125.6	1122.5
125°	1198.4	1204.5	1201.4	1206.0	1207.5
127.5°	1275.7	1277.3	1284.8	1283.3	1281.8
130°	1350.1	1351.6	1356.1	1357.7	1357.7
132.5°	1418.3	1421.4	1427.4	1429.0	1427.4
135°	1486.6	1485.1	1491.2	1494.2	1497.2
137.5°	1547.3	1547.3	1554.9	1557.9	1556.4
140°	1606.4	1609.5	1612.5	1617.1	1618.6
142.5°	1659.5	1665.6	1667.1	1670.2	1670.2
145°	1714.1	1718.7	1718.7	1720.2	1723.2
147.5°	1756.6	1765.7	1764.2	1765.7	1767.2
150°	1803.6	1809.7	1808.2	1808.2	1809.7
152.5°	1843.1	1847.6	1844.6	1847.6	1846.1
155°	1879.5	1881.0	1876.5	1882.5	1878.0
157.5°	1911.3	1911.3	1905.3	1912.9	1905.3
160°	1938.7	1934.1	1932.6	1941.7	1932.6
162.5°	1962.9	1956.9	1955.3	1964.4	1953.8
165°	1982.6	1975.1	1975.1	1987.2	1973.5
167.5°	1999.3	1991.7	1990.2	2003.9	1988.7
170°	2013.0	2003.9	2005.4	2017.5	2002.4
172.5°	2022.1	2013.0	2014.5	2026.6	2009.9
175°	2028.2	2019.0	2020.6	2034.2	2016.0
177.5°	2032.7	2022.1	2025.1	2037.3	2019.0
180°	2028.2	2028.2	2028.2	2028.2	2028.2

(END OF REPORT)