

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983234

Luminaire Tested: S124IW-B470UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B470UB2750-4F0-XX-W2A-1_5000K
Description: Define 4 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1582.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983234

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P983234

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983234

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.2	0.1
90°-100°	37.1	2.3
100°-110°	111.2	7.0
110°-120°	189.0	11.9
120°-130°	249.2	15.8
130°-140°	279.9	17.7
140°-150°	275.1	17.4
150°-160°	231.4	14.6
160°-170°	153.9	9.7
170°-180°	53.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.2	0.1
90°-120°	337.3	21.3
90°-150°	1141.5	72.2
90°-180°	1581.0	99.9
0°-180°	1582.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	10	12	13	2
95°	26	30	34	35	35	29
105°	103	103	105	106	108	109
115°	192	192	191	191	190	189
125°	280	280	279	278	278	249
135°	361	364	364	363	361	279
145°	438	440	441	440	439	274
155°	502	502	502	504	502	231
165°	547	546	545	547	546	154
175°	569	567	566	569	566	54
180°	570	570	570	570	570	

TEST NUMBER: P983234

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	6.2	9.7	12.3	13.2
92.5°	11.5	17.2	19.4	20.7	21.1
95°	26.4	30.4	33.5	34.8	34.8
97.5°	42.3	45.8	49.3	51.1	51.1
100°	61.7	63.4	67.4	68.3	68.3
102.5°	82.0	82.4	85.9	87.2	87.7
105°	102.7	103.1	104.9	106.2	107.5
107.5°	124.3	124.7	125.1	126.9	126.5
110°	146.3	147.2	146.7	145.8	147.2

TEST NUMBER: P983234

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.2	169.2	168.3	168.3	168.3
115°	192.1	192.1	191.2	190.8	190.3
117.5°	213.7	213.7	213.3	211.9	210.6
120°	235.3	237.1	235.7	233.5	234.4
122.5°	257.8	258.2	257.8	256.4	254.2
125°	279.8	279.8	279.4	278.5	277.6
127.5°	299.6	300.9	300.1	299.2	298.7
130°	320.8	322.1	322.1	321.2	319.5
132.5°	342.4	343.2	342.8	341.9	341.5
135°	360.9	363.5	363.5	362.6	361.3
137.5°	381.6	382.9	383.8	382.5	382.9
140°	402.3	403.2	403.2	402.7	402.3
142.5°	421.2	422.1	421.7	421.7	421.7
145°	438.4	440.2	440.6	440.2	438.9
147.5°	456.0	458.2	457.8	457.4	456.9
150°	471.9	473.7	473.7	473.7	473.2
152.5°	486.9	487.8	488.2	489.5	488.2
155°	502.3	502.3	501.9	503.6	501.9
157.5°	515.5	514.6	514.6	516.0	514.6
160°	527.0	526.5	526.1	527.4	525.2
162.5°	537.6	536.2	535.8	538.4	536.2
165°	546.8	545.5	544.6	547.3	545.5
167.5°	554.3	552.5	552.5	555.2	552.5
170°	560.5	558.3	558.7	561.4	558.3
172.5°	564.9	563.1	563.1	566.2	563.1
175°	568.8	566.6	566.2	569.3	566.2
177.5°	570.6	568.4	568.4	571.5	568.0
180°	569.7	569.7	569.7	569.7	569.7

(END OF REPORT)