

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034768

Luminaire Tested: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034768
REPORT IS A COMBINATION OF REPORTS P1006246 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10789.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034768

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034768

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12746	12746	12746
5°	12747	12428	12448
10°	12622	12115	12008
15°	12444	11677	11429
20°	12223	11149	10823
25°	11969	10634	10172
30°	11659	10068	9489
35°	11341	9493	8763
40°	11040	8902	8054
45°	10679	8265	7313
50°	10311	7588	6556
55°	9885	6922	5773
60°	9449	6160	4962
65°	8928	5308	4087
70°	8323	4322	3216
75°	7483	3249	2344
80°	6311	2104	1581
85°	4723	1131	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10679 cd/sqm

TEST NUMBER: P1034768

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	1.7
10°-20°	523.2	4.8
20°-30°	758.7	7.0
30°-40°	864.3	8.0
40°-50°	842.5	7.8
50°-60°	709.0	6.6
60°-70°	496.8	4.6
70°-80°	254.7	2.4
80°-90°	66.5	0.6
90°-100°	67.2	0.6
100°-110°	447.2	4.1
110°-120°	805.2	7.5
120°-130°	1033.6	9.6
130°-140°	1111.6	10.3
140°-150°	1043.3	9.7
150°-160°	843.9	7.8
160°-170°	545.8	5.1
170°-180°	188.2	1.7
0°-30°	1469.1	13.6
0°-40°	2333.5	21.6
0°-60°	3884.9	36.0
0°-90°	4702.9	43.6
90°-120°	1319.6	12.2
90°-150°	4508.1	41.8
90°-180°	6086.0	56.4
0°-180°	10789.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1986	1980	1964	1979	1976	188
15°	1889	1880	1848	1847	1833	533
25°	1713	1690	1635	1615	1599	788
35°	1475	1439	1372	1328	1307	924
45°	1208	1164	1082	1022	999	932
55°	916	868	784	717	693	820
65°	620	569	490	430	407	614
75°	330	286	222	189	179	349
85°	83	56	48	47	45	90
90°	2	13	24	31	35	9
95°	84	79	24	31	31	103
105°	432	438	438	438	436	457
115°	811	818	820	814	805	804
125°	1153	1163	1163	1157	1153	1030
135°	1438	1447	1444	1441	1432	1109
145°	1667	1670	1670	1671	1663	1043
155°	1836	1827	1830	1834	1823	846
165°	1937	1928	1930	1939	1927	547
175°	1981	1972	1974	1986	1972	189
180°	1981	1981	1981	1981	1981	

TEST NUMBER: P1034768

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1989.3	1989.3	1989.3	1989.3	1989.3
2.5°	1993.8	1989.3	1974.3	1989.3	1987.8
5°	1986.3	1980.3	1963.8	1978.8	1975.8
7.5°	1971.3	1965.3	1945.7	1957.7	1954.7
10°	1948.7	1944.2	1923.2	1927.7	1923.2
12.5°	1923.2	1917.2	1887.1	1890.1	1882.6
15°	1888.6	1879.6	1848.1	1846.6	1833.0
17.5°	1852.6	1839.0	1801.5	1794.0	1783.5
20°	1809.0	1794.0	1745.9	1738.4	1724.9
22.5°	1760.9	1745.9	1694.8	1678.3	1667.8
25°	1712.8	1690.3	1634.7	1615.2	1598.6
27.5°	1658.7	1631.7	1573.1	1547.6	1531.0
30°	1598.6	1570.1	1507.0	1472.4	1458.9
32.5°	1540.1	1505.5	1440.9	1401.8	1383.8
35°	1475.4	1439.4	1371.8	1328.2	1307.2
37.5°	1413.8	1370.3	1301.2	1250.1	1229.0
40°	1347.7	1302.7	1230.5	1173.4	1155.4
42.5°	1278.6	1232.0	1156.9	1102.8	1074.3
45°	1208.0	1164.4	1081.8	1021.7	999.2
47.5°	1134.4	1089.3	1006.7	945.1	919.5
50°	1065.3	1015.7	930.0	866.9	844.4
52.5°	990.1	939.1	859.4	790.3	767.8
55°	916.5	868.4	784.3	716.7	692.6
57.5°	841.4	790.3	709.2	643.1	622.0
60°	769.3	716.7	635.6	569.4	546.9
62.5°	692.6	643.1	560.4	500.3	477.8
65°	620.5	569.4	489.8	429.7	407.2
67.5°	548.4	497.3	420.7	363.6	345.6
70°	474.8	423.7	348.6	302.0	284.0
72.5°	402.7	353.1	284.0	241.9	231.4
75°	330.5	285.5	222.4	189.3	178.8
77.5°	256.9	220.9	168.3	142.7	133.7
80°	195.3	159.3	117.2	103.7	100.7
82.5°	135.2	103.7	78.1	73.6	72.1
85°	82.6	55.6	48.1	46.6	45.1
87.5°	34.6	24.0	22.5	22.5	21.0
90°	1.5	13.2	23.5	30.8	35.2
92.5°	27.9	14.7	23.5	30.8	32.3
95°	83.7	79.3	23.5	30.8	30.8
97.5°	157.2	166.0	26.4	29.4	30.8
100°	245.3	249.7	255.6	36.7	30.8
102.5°	334.9	340.7	343.7	346.6	223.2
105°	431.8	437.7	437.7	437.7	436.2
107.5°	531.7	531.7	534.6	536.1	530.2
110°	628.6	628.6	631.5	627.1	628.6

TEST NUMBER: P1034768

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.7	724.1	725.5	719.7	716.7
115°	810.7	818.1	819.5	813.7	804.8
117.5°	906.2	906.2	912.1	903.3	900.3
120°	994.3	992.8	997.2	994.3	987.0
122.5°	1072.2	1079.5	1081.0	1078.0	1069.2
125°	1152.9	1163.2	1163.2	1157.3	1152.9
127.5°	1230.8	1238.1	1236.6	1233.7	1222.0
130°	1301.3	1308.6	1310.1	1305.7	1298.3
132.5°	1371.8	1380.6	1376.2	1376.2	1368.8
135°	1437.9	1446.7	1443.7	1440.8	1432.0
137.5°	1499.5	1508.4	1505.4	1505.4	1498.1
140°	1559.8	1562.7	1561.2	1564.2	1555.4
142.5°	1614.1	1615.6	1618.5	1618.5	1609.7
145°	1667.0	1669.9	1669.9	1671.4	1662.6
147.5°	1714.0	1714.0	1715.4	1716.9	1706.6
150°	1758.0	1755.1	1758.0	1761.0	1749.2
152.5°	1800.6	1793.3	1796.2	1799.2	1788.9
155°	1835.9	1827.1	1830.0	1834.4	1822.7
157.5°	1863.8	1859.4	1859.4	1863.8	1852.0
160°	1893.2	1884.3	1885.8	1891.7	1879.9
162.5°	1916.7	1907.8	1909.3	1918.1	1904.9
165°	1937.2	1928.4	1929.9	1938.7	1926.9
167.5°	1953.4	1944.6	1946.0	1956.3	1943.1
170°	1966.6	1956.3	1957.8	1969.5	1956.3
172.5°	1975.4	1965.1	1968.1	1978.3	1965.1
175°	1981.3	1972.5	1973.9	1985.7	1972.5
177.5°	1985.7	1976.9	1978.3	1988.6	1976.9
180°	1981.3	1981.3	1981.3	1981.3	1981.3

(END OF REPORT)