

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983236

Luminaire Tested: S124IW-B470UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B470UB2750-4F0-XX-W2A_3000K
Description: Define 4 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1897.0 lumens
Efficiency: N/A
Efficacy: 143.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983236

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983236

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983236

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.3	0.1
90°-100°	20.3	1.1
100°-110°	133.9	7.1
110°-120°	255.7	13.5
120°-130°	324.6	17.1
130°-140°	347.3	18.3
140°-150°	324.8	17.1
150°-160°	261.9	13.8
160°-170°	168.9	8.9
170°-180°	58.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.3	0.1
90°-120°	410.0	21.6
90°-150°	1406.7	74.2
90°-180°	1896.0	99.9
0°-180°	1897.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	10	13	14	1
95°	25	10	10	13	13	31
105°	138	141	143	147	131	144
115°	258	259	258	259	259	253
125°	362	364	363	364	365	323
135°	449	449	450	451	452	346
145°	518	519	519	520	520	324
155°	568	568	567	569	567	262
165°	599	597	597	600	596	169
175°	613	610	610	614	609	58
180°	613	613	613	613	613	

TEST NUMBER: P983236

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.4	6.4	10.1	12.8	13.7
92.5°	6.9	6.0	9.6	12.4	12.4
95°	25.2	9.6	10.1	12.8	13.3
97.5°	48.1	58.2	10.1	12.4	12.8
100°	75.1	83.4	20.2	12.4	12.8
102.5°	105.4	110.9	116.4	13.3	13.3
105°	137.9	140.7	143.0	147.1	130.6
107.5°	167.7	169.1	172.3	174.6	176.4
110°	198.0	199.3	202.1	203.0	204.4

TEST NUMBER: P983236

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.3	230.0	230.9	230.5	232.3
115°	257.5	258.9	258.4	259.4	259.4
117.5°	284.6	286.4	287.8	287.3	287.3
120°	312.0	313.9	313.4	314.3	313.4
122.5°	337.7	338.6	339.5	340.0	339.1
125°	362.0	363.8	362.9	364.3	364.7
127.5°	385.4	385.8	388.1	387.7	387.2
130°	407.8	408.3	409.7	410.1	410.1
132.5°	428.4	429.4	431.2	431.6	431.2
135°	449.1	448.6	450.4	451.3	452.3
137.5°	467.4	467.4	469.7	470.6	470.1
140°	485.3	486.2	487.1	488.5	488.9
142.5°	501.3	503.1	503.6	504.5	504.5
145°	517.8	519.2	519.2	519.6	520.5
147.5°	530.6	533.4	532.9	533.4	533.8
150°	544.8	546.7	546.2	546.2	546.7
152.5°	556.7	558.1	557.2	558.1	557.7
155°	567.7	568.2	566.8	568.7	567.3
157.5°	577.4	577.4	575.5	577.8	575.5
160°	585.6	584.2	583.8	586.5	583.8
162.5°	592.9	591.1	590.6	593.4	590.2
165°	598.9	596.6	596.6	600.3	596.1
167.5°	603.9	601.6	601.2	605.3	600.7
170°	608.1	605.3	605.8	609.4	604.9
172.5°	610.8	608.1	608.5	612.2	607.1
175°	612.6	609.9	610.4	614.5	609.0
177.5°	614.0	610.8	611.7	615.4	609.9
180°	612.6	612.6	612.6	612.6	612.6

(END OF REPORT)