

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983239

Luminaire Tested: S124IW-B470UB2750-4F0-XX-W2A_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B470UB2750-4F0-XX-W2A_5000K
Description: Define 4 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1824.0 lumens
Efficiency: N/A
Efficacy: 138.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983239

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P983239

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983239

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.2	0.1
90°-100°	19.6	1.1
100°-110°	128.8	7.1
110°-120°	245.9	13.5
120°-130°	312.2	17.1
130°-140°	333.9	18.3
140°-150°	312.3	17.1
150°-160°	251.8	13.8
160°-170°	162.4	8.9
170°-180°	56.0	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.2	0.1
90°-120°	394.2	21.6
90°-150°	1352.6	74.2
90°-180°	1823.0	99.9
0°-180°	1824.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	10	12	13	1
95°	24	9	10	12	13	30
105°	133	135	138	141	126	139
115°	248	249	248	249	249	244
125°	348	350	349	350	351	311
135°	432	431	433	434	435	333
145°	498	499	499	500	500	311
155°	546	546	545	547	545	252
165°	576	574	574	577	573	163
175°	589	586	587	591	586	56
180°	589	589	589	589	589	

TEST NUMBER: P983239

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	6.2	9.7	12.3	13.2
92.5°	6.6	5.7	9.3	11.9	11.9
95°	24.2	9.3	9.7	12.3	12.8
97.5°	46.3	56.0	9.7	11.9	12.3
100°	72.3	80.2	19.4	11.9	12.3
102.5°	101.3	106.6	111.9	12.8	12.8
105°	132.6	135.3	137.5	141.4	125.6
107.5°	161.3	162.6	165.7	167.9	169.6
110°	190.3	191.7	194.3	195.2	196.5

TEST NUMBER: P983239

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.5	221.2	222.1	221.6	223.4
115°	247.6	248.9	248.5	249.4	249.4
117.5°	273.6	275.4	276.7	276.2	276.2
120°	300.0	301.8	301.4	302.2	301.4
122.5°	324.7	325.6	326.5	326.9	326.0
125°	348.1	349.8	348.9	350.3	350.7
127.5°	370.5	371.0	373.2	372.7	372.3
130°	392.1	392.6	393.9	394.3	394.3
132.5°	412.0	412.8	414.6	415.0	414.6
135°	431.8	431.3	433.1	434.0	434.9
137.5°	449.4	449.4	451.6	452.5	452.0
140°	466.6	467.5	468.3	469.7	470.1
142.5°	482.0	483.8	484.2	485.1	485.1
145°	497.9	499.2	499.2	499.6	500.5
147.5°	510.2	512.8	512.4	512.8	513.3
150°	523.9	525.6	525.2	525.2	525.6
152.5°	535.3	536.6	535.8	536.6	536.2
155°	545.9	546.3	545.0	546.8	545.4
157.5°	555.1	555.1	553.4	555.6	553.4
160°	563.1	561.8	561.3	564.0	561.3
162.5°	570.1	568.4	567.9	570.6	567.5
165°	575.9	573.6	573.6	577.2	573.2
167.5°	580.7	578.5	578.1	582.0	577.6
170°	584.7	582.0	582.5	586.0	581.6
172.5°	587.3	584.7	585.1	588.6	583.8
175°	589.1	586.4	586.9	590.8	585.5
177.5°	590.4	587.3	588.2	591.7	586.4
180°	589.1	589.1	589.1	589.1	589.1

(END OF REPORT)