

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034786

Luminaire Tested: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034786
REPORT IS A COMBINATION OF REPORTS P1006331 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8013.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034786

CATALOG NUMBER: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034786

CATALOG NUMBER: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	69	67	65	59	58	57	57	57	52
2	92	84	78	73	86	79	74	69	69	65	62	61	57	55	52	50	48	48	48	44
3	84	74	67	61	78	70	63	58	62	56	52	54	50	47	47	44	41	41	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	36	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	31	31	28
6	65	53	45	39	61	50	43	37	44	39	34	39	34	31	34	31	28	28	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	28	25	25	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	22	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	20	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13256	13256	13256
5°	13257	12925	12946
10°	13128	12599	12488
15°	12942	12144	11887
20°	12712	11595	11256
25°	12448	11059	10579
30°	12125	10471	9869
35°	11796	9872	9114
40°	11482	9259	8377
45°	11106	8595	7605
50°	10724	7891	6819
55°	10281	7199	6005
60°	9826	6406	5161
65°	9285	5520	4250
70°	8656	4494	3344
75°	7785	3379	2437
80°	6563	2189	1644
85°	4911	1176	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11106 cd/sqm

TEST NUMBER: P1034786

CATALOG NUMBER: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	2.4
10°-20°	544.2	6.8
20°-30°	789.0	9.8
30°-40°	898.9	11.2
40°-50°	876.2	10.9
50°-60°	737.4	9.2
60°-70°	516.7	6.4
70°-80°	264.9	3.3
80°-90°	67.6	0.8
90°-100°	34.5	0.4
100°-110°	229.5	2.9
110°-120°	413.3	5.2
120°-130°	530.4	6.6
130°-140°	570.5	7.1
140°-150°	535.5	6.7
150°-160°	433.1	5.4
160°-170°	280.1	3.5
170°-180°	96.6	1.2
0°-30°	1527.9	19.1
0°-40°	2426.8	30.3
0°-60°	4040.3	50.4
0°-90°	4889.5	61.0
90°-120°	677.3	8.5
90°-150°	2313.7	28.9
90°-180°	3124.0	39.0
0°-180°	8013.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2066	2060	2042	2058	2055	196
15°	1964	1955	1922	1920	1906	554
25°	1781	1758	1700	1680	1663	820
35°	1534	1497	1427	1381	1360	961
45°	1256	1211	1125	1063	1039	969
55°	953	903	816	745	720	852
65°	645	592	509	447	424	639
75°	344	297	231	197	186	363
85°	86	58	50	48	47	94
90°	1	7	12	16	18	7
95°	43	41	12	16	16	53
105°	222	225	225	225	224	235
115°	416	420	421	418	413	412
125°	592	597	597	594	592	529
135°	738	742	741	739	735	569
145°	856	857	857	858	853	535
155°	942	938	939	942	935	434
165°	994	990	990	995	989	281
175°	1017	1012	1013	1019	1012	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1034786

CATALOG NUMBER: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
2.5°	2073.6	2068.9	2053.2	2068.9	2067.3
5°	2065.7	2059.5	2042.3	2057.9	2054.8
7.5°	2050.1	2043.9	2023.6	2036.1	2032.9
10°	2026.7	2022.0	2000.1	2004.8	2000.1
12.5°	2000.1	1993.9	1962.6	1965.7	1957.9
15°	1964.2	1954.8	1922.0	1920.4	1906.4
17.5°	1926.7	1912.6	1873.5	1865.7	1854.8
20°	1881.4	1865.7	1815.7	1807.9	1793.9
22.5°	1831.4	1815.7	1762.6	1745.4	1734.5
25°	1781.4	1757.9	1700.1	1679.8	1662.6
27.5°	1725.1	1697.0	1636.0	1609.5	1592.3
30°	1662.6	1632.9	1567.3	1531.3	1517.3
32.5°	1601.7	1565.7	1498.5	1457.9	1439.1
35°	1534.5	1497.0	1426.6	1381.3	1359.5
37.5°	1470.4	1425.1	1353.2	1300.1	1278.2
40°	1401.6	1354.8	1279.8	1220.4	1201.6
42.5°	1329.8	1281.3	1203.2	1146.9	1117.3
45°	1256.3	1211.0	1125.1	1062.6	1039.1
47.5°	1179.8	1132.9	1046.9	982.9	956.3
50°	1107.9	1056.3	967.2	901.6	878.2
52.5°	1029.7	976.6	893.8	821.9	798.5
55°	953.2	903.2	815.7	745.4	720.4
57.5°	875.1	821.9	737.5	668.8	646.9
60°	800.0	745.4	661.0	592.2	568.8
62.5°	720.4	668.8	582.8	520.3	496.9
65°	645.3	592.2	509.4	446.9	423.5
67.5°	570.3	517.2	437.5	378.1	359.4
70°	493.8	440.7	362.5	314.1	295.3
72.5°	418.8	367.2	295.3	251.6	240.6
75°	343.8	296.9	231.3	196.9	185.9
77.5°	267.2	229.7	175.0	148.4	139.1
80°	203.1	165.6	121.9	107.8	104.7
82.5°	140.6	107.8	81.3	76.6	75.0
85°	85.9	57.8	50.0	48.4	46.9
87.5°	35.9	25.0	23.4	23.4	21.9
90°	0.8	6.8	12.1	15.8	18.1
92.5°	14.3	7.5	12.1	15.8	16.6
95°	43.0	40.7	12.1	15.8	15.8
97.5°	80.7	85.2	13.6	15.1	15.8
100°	125.9	128.1	131.2	18.8	15.8
102.5°	171.9	174.9	176.4	177.9	114.6
105°	221.6	224.6	224.6	224.6	223.9
107.5°	272.9	272.9	274.4	275.1	272.1
110°	322.6	322.6	324.1	321.9	322.6



TEST NUMBER: P1034786

CATALOG NUMBER: S125RDIW-B1270D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	369.3	371.6	372.4	369.3	367.8
115°	416.1	419.8	420.6	417.6	413.1
117.5°	465.1	465.1	468.1	463.6	462.1
120°	510.3	509.5	511.8	510.3	506.5
122.5°	550.2	554.0	554.8	553.3	548.7
125°	591.7	597.0	597.0	594.0	591.7
127.5°	631.7	635.4	634.7	633.2	627.1
130°	667.8	671.6	672.4	670.1	666.3
132.5°	704.0	708.5	706.3	706.3	702.5
135°	737.9	742.5	741.0	739.4	734.9
137.5°	769.6	774.1	772.6	772.6	768.8
140°	800.5	802.0	801.3	802.8	798.2
142.5°	828.4	829.1	830.7	830.7	826.1
145°	855.5	857.0	857.0	857.8	853.3
147.5°	879.6	879.6	880.4	881.2	875.9
150°	902.3	900.8	902.3	903.8	897.7
152.5°	924.1	920.3	921.9	923.4	918.1
155°	942.2	937.7	939.2	941.5	935.4
157.5°	956.5	954.3	954.3	956.5	950.5
160°	971.6	967.1	967.8	970.9	964.8
162.5°	983.7	979.1	979.9	984.4	977.6
165°	994.2	989.7	990.4	995.0	988.9
167.5°	1002.5	998.0	998.7	1004.0	997.2
170°	1009.3	1004.0	1004.8	1010.8	1004.0
172.5°	1013.8	1008.5	1010.0	1015.3	1008.5
175°	1016.8	1012.3	1013.1	1019.1	1012.3
177.5°	1019.1	1014.6	1015.3	1020.6	1014.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)