

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983250

Luminaire Tested: S124IW-B770UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B770UB2750-4F0-XX-W2A-1_2700K
Description: Define 4 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2687.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983250

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P983250

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983250

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	63.1	2.3
100°-110°	188.9	7.0
110°-120°	321.0	11.9
120°-130°	423.3	15.8
130°-140°	475.4	17.7
140°-150°	467.3	17.4
150°-160°	393.0	14.6
160°-170°	261.5	9.7
170°-180°	91.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	572.9	21.3
90°-150°	1938.9	72.2
90°-180°	2685.0	99.9
0°-180°	2687.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	10	16	21	22	3
95°	45	52	57	59	59	49
105°	174	175	178	180	183	185
115°	326	326	325	324	323	322
125°	475	475	474	473	472	424
135°	613	617	617	616	614	474
145°	745	748	748	748	745	466
155°	853	853	852	855	852	393
165°	929	926	925	930	926	262
175°	966	962	962	967	962	92
180°	968	968	968	968	968	

TEST NUMBER: P983250

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.2	10.5	16.5	21.0	22.5
92.5°	19.5	29.2	32.9	35.2	35.9
95°	44.9	51.6	56.9	59.1	59.1
97.5°	71.8	77.8	83.8	86.8	86.8
100°	104.8	107.8	114.5	116.0	116.0
102.5°	139.2	139.9	145.9	148.2	148.9
105°	174.4	175.1	178.1	180.4	182.6
107.5°	211.0	211.8	212.5	215.5	214.8
110°	248.5	250.0	249.2	247.7	250.0

TEST NUMBER: P983250

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.4	287.4	285.9	285.9	285.9
115°	326.3	326.3	324.8	324.1	323.3
117.5°	363.0	363.0	362.2	360.0	357.7
120°	399.6	402.6	400.4	396.6	398.1
122.5°	437.8	438.6	437.8	435.6	431.8
125°	475.2	475.2	474.5	473.0	471.5
127.5°	508.9	511.2	509.7	508.2	507.4
130°	544.8	547.1	547.1	545.6	542.6
132.5°	581.5	583.0	582.2	580.8	580.0
135°	612.9	617.4	617.4	615.9	613.7
137.5°	648.1	650.4	651.8	649.6	650.4
140°	683.3	684.8	684.8	684.0	683.3
142.5°	715.5	717.0	716.2	716.2	716.2
145°	744.7	747.6	748.4	747.6	745.4
147.5°	774.6	778.3	777.6	776.8	776.1
150°	801.5	804.5	804.5	804.5	803.8
152.5°	827.0	828.5	829.2	831.5	829.2
155°	853.2	853.2	852.4	855.4	852.4
157.5°	875.6	874.1	874.1	876.4	874.1
160°	895.1	894.3	893.6	895.8	892.1
162.5°	913.0	910.8	910.0	914.5	910.8
165°	928.8	926.5	925.0	929.5	926.5
167.5°	941.5	938.5	938.5	943.0	938.5
170°	952.0	948.2	949.0	953.5	948.2
172.5°	959.4	956.4	956.4	961.7	956.4
175°	966.2	962.4	961.7	966.9	961.7
177.5°	969.2	965.4	965.4	970.7	964.7
180°	967.7	967.7	967.7	967.7	967.7

(END OF REPORT)