

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983253

Luminaire Tested: S124IW-B770UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B770UB2750-4F0-XX-W2A-1_4000K
Description: Define 4 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2695.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983253

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P983253

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983253

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	63.3	2.3
100°-110°	189.5	7.0
110°-120°	321.9	11.9
120°-130°	424.5	15.8
130°-140°	476.8	17.7
140°-150°	468.6	17.4
150°-160°	394.2	14.6
160°-170°	262.3	9.7
170°-180°	91.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	574.6	21.3
90°-150°	1944.7	72.2
90°-180°	2693.0	99.9
0°-180°	2695.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	10	16	21	22	3
95°	45	52	57	59	59	49
105°	175	176	179	181	183	185
115°	327	327	326	325	324	323
125°	477	477	476	474	473	425
135°	615	619	619	618	616	476
145°	747	750	751	750	748	467
155°	856	856	855	858	855	394
165°	932	929	928	932	929	263
175°	969	965	964	970	964	92
180°	971	971	971	971	971	

TEST NUMBER: P983253

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.3	10.5	16.5	21.0	22.5
92.5°	19.5	29.3	33.0	35.3	36.0
95°	45.0	51.8	57.0	59.3	59.3
97.5°	72.1	78.1	84.1	87.1	87.1
100°	105.1	108.1	114.8	116.3	116.3
102.5°	139.6	140.4	146.4	148.6	149.4
105°	174.9	175.6	178.6	180.9	183.2
107.5°	211.7	212.4	213.2	216.2	215.4
110°	249.2	250.7	250.0	248.5	250.7

TEST NUMBER: P983253

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	288.2	286.7	286.7	286.7
115°	327.3	327.3	325.8	325.0	324.3
117.5°	364.1	364.1	363.3	361.0	358.8
120°	400.8	403.8	401.6	397.8	399.3
122.5°	439.1	439.9	439.1	436.9	433.1
125°	476.6	476.6	475.9	474.4	472.9
127.5°	510.4	512.7	511.2	509.7	508.9
130°	546.5	548.7	548.7	547.2	544.2
132.5°	583.2	584.7	584.0	582.5	581.7
135°	614.8	619.3	619.3	617.8	615.5
137.5°	650.0	652.3	653.8	651.5	652.3
140°	685.3	686.8	686.8	686.1	685.3
142.5°	717.6	719.1	718.3	718.3	718.3
145°	746.9	749.9	750.6	749.9	747.6
147.5°	776.9	780.6	779.9	779.1	778.4
150°	803.9	806.9	806.9	806.9	806.2
152.5°	829.4	830.9	831.7	833.9	831.7
155°	855.7	855.7	855.0	858.0	855.0
157.5°	878.2	876.7	876.7	879.0	876.7
160°	897.7	897.0	896.2	898.5	894.7
162.5°	915.8	913.5	912.8	917.3	913.5
165°	931.5	929.3	927.8	932.3	929.3
167.5°	944.3	941.3	941.3	945.8	941.3
170°	954.8	951.0	951.8	956.3	951.0
172.5°	962.3	959.3	959.3	964.5	959.3
175°	969.1	965.3	964.5	969.8	964.5
177.5°	972.1	968.3	968.3	973.6	967.5
180°	970.6	970.6	970.6	970.6	970.6

(END OF REPORT)