

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983254

Luminaire Tested: S124IW-B770UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B770UB2750-4F0-XX-W2A-1_5000K
Description: Define 4 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2606.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983254

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P983254

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983254

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	61.2	2.3
100°-110°	183.2	7.0
110°-120°	311.3	11.9
120°-130°	410.5	15.8
130°-140°	461.1	17.7
140°-150°	453.2	17.4
150°-160°	381.1	14.6
160°-170°	253.6	9.7
170°-180°	88.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	555.7	21.3
90°-150°	1880.4	72.2
90°-180°	2604.0	99.9
0°-180°	2606.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	10	16	20	22	3
95°	44	50	55	57	57	47
105°	169	170	173	175	177	179
115°	316	316	315	314	314	312
125°	461	461	460	459	457	411
135°	594	599	599	597	595	460
145°	722	725	726	725	723	452
155°	827	827	827	830	827	381
165°	901	899	897	902	899	254
175°	937	933	933	938	933	89
180°	938	938	938	938	938	

TEST NUMBER: P983254

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.2	10.2	16.0	20.3	21.8
92.5°	18.9	28.3	31.9	34.1	34.8
95°	43.5	50.1	55.2	57.3	57.3
97.5°	69.7	75.5	81.3	84.2	84.2
100°	101.6	104.5	111.1	112.5	112.5
102.5°	135.0	135.7	141.5	143.7	144.4
105°	169.1	169.8	172.7	174.9	177.1
107.5°	204.7	205.4	206.1	209.0	208.3
110°	241.0	242.4	241.7	240.3	242.4

TEST NUMBER: P983254

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.7	278.7	277.3	277.3	277.3
115°	316.5	316.5	315.0	314.3	313.6
117.5°	352.0	352.0	351.3	349.1	346.9
120°	387.6	390.5	388.3	384.7	386.1
122.5°	424.6	425.3	424.6	422.4	418.8
125°	460.9	460.9	460.2	458.7	457.3
127.5°	493.6	495.7	494.3	492.8	492.1
130°	528.4	530.6	530.6	529.1	526.2
132.5°	564.0	565.4	564.7	563.2	562.5
135°	594.5	598.8	598.8	597.4	595.2
137.5°	628.6	630.7	632.2	630.0	630.7
140°	662.7	664.1	664.1	663.4	662.7
142.5°	693.9	695.3	694.6	694.6	694.6
145°	722.2	725.1	725.8	725.1	722.9
147.5°	751.2	754.9	754.1	753.4	752.7
150°	777.4	780.3	780.3	780.3	779.5
152.5°	802.0	803.5	804.2	806.4	804.2
155°	827.4	827.4	826.7	829.6	826.7
157.5°	849.2	847.8	847.8	849.9	847.8
160°	868.1	867.4	866.6	868.8	865.2
162.5°	885.5	883.3	882.6	887.0	883.3
165°	900.8	898.6	897.1	901.5	898.6
167.5°	913.1	910.2	910.2	914.5	910.2
170°	923.3	919.6	920.4	924.7	919.6
172.5°	930.5	927.6	927.6	932.7	927.6
175°	937.0	933.4	932.7	937.8	932.7
177.5°	940.0	936.3	936.3	941.4	935.6
180°	938.5	938.5	938.5	938.5	938.5

(END OF REPORT)