

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034824

Luminaire Tested: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034824
REPORT IS A COMBINATION OF REPORTS P1006504 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2934.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034824

CATALOG NUMBER: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034824

CATALOG NUMBER: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53			46
1	97	93	89	86	89	85	82	79	71	69	67	59	57	56	47	46	45			39
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	40	38			33
3	81	72	64	59	74	66	60	55	56	51	47	46	43	40	37	35	33			28
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28			24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25			21
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17			15
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3669	3669	3669
5°	3670	3578	3584
10°	3634	3487	3457
15°	3582	3361	3290
20°	3519	3210	3115
25°	3446	3061	2928
30°	3356	2898	2732
35°	3265	2733	2523
40°	3179	2562	2319
45°	3075	2379	2105
50°	2969	2184	1888
55°	2845	1993	1662
60°	2721	1774	1428
65°	2570	1528	1176
70°	2396	1243	925
75°	2156	935	675
80°	1816	605	455
85°	1361	324	257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3075 cd/sqm

TEST NUMBER: P1034824

CATALOG NUMBER: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.8
10°-20°	150.6	5.1
20°-30°	218.4	7.4
30°-40°	248.8	8.5
40°-50°	242.5	8.3
50°-60°	204.1	7.0
60°-70°	143.0	4.9
70°-80°	73.3	2.5
80°-90°	19.2	0.7
90°-100°	37.7	1.3
100°-110°	111.8	3.8
110°-120°	189.7	6.5
120°-130°	249.7	8.5
130°-140°	279.8	9.5
140°-150°	274.3	9.3
150°-160°	230.4	7.9
160°-170°	153.1	5.2
170°-180°	53.6	1.8
0°-30°	422.9	14.4
0°-40°	671.7	22.9
0°-60°	1118.4	38.1
0°-90°	1353.9	46.1
90°-120°	339.2	11.6
90°-150°	1143.0	39.0
90°-180°	1580.0	53.9
0°-180°	2934.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	573	573	573	573	573	
5°	572	570	565	570	569	54
15°	544	541	532	532	528	153
25°	493	487	471	465	460	227
35°	425	414	395	382	376	266
45°	348	335	311	294	288	268
55°	264	250	226	206	199	236
65°	179	164	141	124	117	177
75°	95	82	64	54	52	101
85°	24	16	14	13	13	26
90°	0	4	7	9	11	3
95°	29	30	34	37	38	30
105°	100	103	105	108	109	107
115°	190	192	192	192	192	188
125°	277	280	280	279	279	248
135°	360	363	364	364	362	278
145°	437	438	440	440	438	273
155°	500	500	500	502	500	230
165°	543	542	543	545	542	153
175°	565	563	563	566	563	54
180°	566	566	566	566	566	

TEST NUMBER: P1034824

CATALOG NUMBER: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	572.7	572.7	572.7	572.7	572.7
2.5°	574.0	572.7	568.3	572.7	572.2
5°	571.8	570.1	565.3	569.6	568.8
7.5°	567.5	565.7	560.1	563.6	562.7
10°	561.0	559.7	553.6	554.9	553.6
12.5°	553.6	551.9	543.3	544.1	542.0
15°	543.7	541.1	532.0	531.6	527.7
17.5°	533.3	529.4	518.6	516.4	513.4
20°	520.8	516.4	502.6	500.4	496.5
22.5°	506.9	502.6	487.9	483.1	480.1
25°	493.1	486.6	470.6	465.0	460.2
27.5°	477.5	469.7	452.9	445.5	440.7
30°	460.2	452.0	433.8	423.9	420.0
32.5°	443.3	433.4	414.8	403.5	398.4
35°	424.7	414.4	394.9	382.4	376.3
37.5°	407.0	394.5	374.6	359.9	353.8
40°	388.0	375.0	354.2	337.8	332.6
42.5°	368.1	354.7	333.0	317.5	309.3
45°	347.8	335.2	311.4	294.1	287.6
47.5°	326.6	313.6	289.8	272.1	264.7
50°	306.7	292.4	267.7	249.6	243.1
52.5°	285.0	270.3	247.4	227.5	221.0
55°	263.8	250.0	225.8	206.3	199.4
57.5°	242.2	227.5	204.2	185.1	179.1
60°	221.5	206.3	183.0	163.9	157.4
62.5°	199.4	185.1	161.3	144.0	137.5
65°	178.6	163.9	141.0	123.7	117.2
67.5°	157.9	143.2	121.1	104.7	99.5
70°	136.7	122.0	100.3	86.9	81.7
72.5°	115.9	101.6	81.7	69.6	66.6
75°	95.2	82.2	64.0	54.5	51.5
77.5°	74.0	63.6	48.4	41.1	38.5
80°	56.2	45.8	33.7	29.8	29.0
82.5°	38.9	29.8	22.5	21.2	20.8
85°	23.8	16.0	13.8	13.4	13.0
87.5°	9.9	6.9	6.5	6.5	6.1
90°	0.4	4.0	7.0	9.3	10.6
92.5°	13.2	15.4	19.4	22.5	23.4
95°	28.6	29.5	33.9	37.0	37.9
97.5°	44.1	44.5	50.7	53.3	53.8
100°	61.7	61.7	67.4	71.4	72.3
102.5°	80.6	82.8	85.0	89.4	90.8
105°	100.5	102.7	105.3	107.9	109.3
107.5°	122.0	124.2	126.5	127.8	127.8
110°	144.5	146.7	148.0	149.4	148.9

TEST NUMBER: P1034824

CATALOG NUMBER: S125RDIW-B375D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.4	168.3	170.1	170.5	169.6
115°	189.9	191.7	192.5	192.1	191.7
117.5°	212.8	213.2	214.1	214.6	212.8
120°	234.0	236.2	236.6	236.6	234.8
122.5°	256.9	257.3	258.6	258.2	256.9
125°	277.1	279.8	280.2	279.3	278.9
127.5°	299.6	300.9	301.4	300.9	300.0
130°	319.4	321.6	322.5	322.1	321.2
132.5°	339.3	343.2	342.8	342.3	341.0
135°	360.4	363.1	363.5	363.5	361.7
137.5°	380.2	382.9	383.8	384.2	382.0
140°	399.2	401.4	402.7	403.6	401.4
142.5°	418.1	419.9	421.6	422.1	419.9
145°	436.6	438.4	439.7	439.7	438.4
147.5°	453.8	455.1	456.0	457.3	453.8
150°	471.0	470.6	472.3	472.3	471.4
152.5°	485.1	486.0	486.4	487.7	486.0
155°	499.6	499.6	500.1	501.8	499.6
157.5°	512.9	512.0	512.4	514.2	511.1
160°	524.3	523.0	523.4	525.2	523.0
162.5°	534.4	533.6	533.6	535.8	533.1
165°	543.3	542.4	542.8	544.6	541.9
167.5°	551.2	549.4	549.4	552.1	549.4
170°	557.4	555.6	555.6	558.2	555.1
172.5°	561.8	560.0	560.0	562.6	560.0
175°	564.8	563.1	563.1	565.7	562.6
177.5°	567.0	565.3	564.8	567.5	564.4
180°	566.2	566.2	566.2	566.2	566.2

(END OF REPORT)