

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034838

Luminaire Tested: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034838
REPORT IS A COMBINATION OF REPORTS P1006554 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4358.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034838

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034838

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	90	86	82	84	81	78	75	64	62	60	49	47	46	34	34	33
2	85	78	72	68	77	71	66	61	56	53	50	43	41	39	30	29	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3669	3669	3669
5°	3670	3578	3584
10°	3634	3487	3457
15°	3582	3361	3290
20°	3519	3210	3115
25°	3446	3061	2928
30°	3356	2898	2732
35°	3265	2733	2523
40°	3179	2562	2319
45°	3075	2379	2105
50°	2969	2184	1888
55°	2845	1993	1662
60°	2721	1774	1428
65°	2570	1528	1176
70°	2396	1243	925
75°	2156	935	675
80°	1816	605	455
85°	1361	324	257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3075 cd/sqm

TEST NUMBER: P1034838

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.2
10°-20°	150.6	3.5
20°-30°	218.4	5.0
30°-40°	248.8	5.7
40°-50°	242.5	5.6
50°-60°	204.1	4.7
60°-70°	143.0	3.3
70°-80°	73.3	1.7
80°-90°	19.7	0.5
90°-100°	33.2	0.8
100°-110°	220.7	5.1
110°-120°	397.4	9.1
120°-130°	510.1	11.7
130°-140°	548.6	12.6
140°-150°	514.9	11.8
150°-160°	416.5	9.6
160°-170°	269.4	6.2
170°-180°	92.9	2.1
0°-30°	422.9	9.7
0°-40°	671.7	15.4
0°-60°	1118.4	25.7
0°-90°	1354.4	31.1
90°-120°	651.2	14.9
90°-150°	2224.8	51.1
90°-180°	3004.0	68.9
0°-180°	4358.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	573	573	573	573	573	
5°	572	570	565	570	569	54
15°	544	541	532	532	528	153
25°	493	487	471	465	460	227
35°	425	414	395	382	376	266
45°	348	335	311	294	288	268
55°	264	250	226	206	199	236
65°	179	164	141	124	117	177
75°	95	82	64	54	52	101
85°	24	16	14	13	13	26
90°	1	6	12	15	17	3
95°	41	39	12	15	15	51
105°	213	216	216	216	215	226
115°	400	404	404	402	397	397
125°	569	574	574	571	569	508
135°	710	714	712	711	707	547
145°	823	824	824	825	820	515
155°	906	902	903	905	900	417
165°	956	952	952	957	951	270
175°	978	973	974	980	973	93
180°	978	978	978	978	978	

TEST NUMBER: P1034838

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	572.7	572.7	572.7	572.7	572.7
2.5°	574.0	572.7	568.3	572.7	572.2
5°	571.8	570.1	565.3	569.6	568.8
7.5°	567.5	565.7	560.1	563.6	562.7
10°	561.0	559.7	553.6	554.9	553.6
12.5°	553.6	551.9	543.3	544.1	542.0
15°	543.7	541.1	532.0	531.6	527.7
17.5°	533.3	529.4	518.6	516.4	513.4
20°	520.8	516.4	502.6	500.4	496.5
22.5°	506.9	502.6	487.9	483.1	480.1
25°	493.1	486.6	470.6	465.0	460.2
27.5°	477.5	469.7	452.9	445.5	440.7
30°	460.2	452.0	433.8	423.9	420.0
32.5°	443.3	433.4	414.8	403.5	398.4
35°	424.7	414.4	394.9	382.4	376.3
37.5°	407.0	394.5	374.6	359.9	353.8
40°	388.0	375.0	354.2	337.8	332.6
42.5°	368.1	354.7	333.0	317.5	309.3
45°	347.8	335.2	311.4	294.1	287.6
47.5°	326.6	313.6	289.8	272.1	264.7
50°	306.7	292.4	267.7	249.6	243.1
52.5°	285.0	270.3	247.4	227.5	221.0
55°	263.8	250.0	225.8	206.3	199.4
57.5°	242.2	227.5	204.2	185.1	179.1
60°	221.5	206.3	183.0	163.9	157.4
62.5°	199.4	185.1	161.3	144.0	137.5
65°	178.6	163.9	141.0	123.7	117.2
67.5°	157.9	143.2	121.1	104.7	99.5
70°	136.7	122.0	100.3	86.9	81.7
72.5°	115.9	101.6	81.7	69.6	66.6
75°	95.2	82.2	64.0	54.5	51.5
77.5°	74.0	63.6	48.4	41.1	38.5
80°	56.2	45.8	33.7	29.8	29.0
82.5°	38.9	29.8	22.5	21.2	20.8
85°	23.8	16.0	13.8	13.4	13.0
87.5°	9.9	6.9	6.5	6.5	6.1
90°	0.7	6.5	11.6	15.2	17.4
92.5°	13.8	7.2	11.6	15.2	15.9
95°	41.3	39.1	11.6	15.2	15.2
97.5°	77.6	81.9	13.0	14.5	15.2
100°	121.0	123.2	126.1	18.1	15.2
102.5°	165.3	168.2	169.6	171.1	110.2
105°	213.1	216.0	216.0	216.0	215.3
107.5°	262.4	262.4	263.8	264.6	261.7
110°	310.2	310.2	311.7	309.5	310.2

TEST NUMBER: P1034838

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.2	357.3	358.1	355.2	353.7
115°	400.1	403.7	404.5	401.6	397.2
117.5°	447.2	447.2	450.1	445.8	444.3
120°	490.7	490.0	492.2	490.7	487.1
122.5°	529.1	532.7	533.5	532.0	527.7
125°	569.0	574.1	574.1	571.2	569.0
127.5°	607.4	611.0	610.3	608.9	603.1
130°	642.2	645.8	646.5	644.4	640.7
132.5°	677.0	681.3	679.2	679.2	675.5
135°	709.6	713.9	712.5	711.1	706.7
137.5°	740.0	744.4	742.9	742.9	739.3
140°	769.8	771.2	770.5	771.9	767.6
142.5°	796.6	797.3	798.8	798.8	794.4
145°	822.7	824.1	824.1	824.8	820.5
147.5°	845.9	845.9	846.6	847.3	842.2
150°	867.6	866.2	867.6	869.1	863.3
152.5°	888.6	885.0	886.5	887.9	882.8
155°	906.0	901.7	903.1	905.3	899.5
157.5°	919.8	917.6	917.6	919.8	914.0
160°	934.3	929.9	930.7	933.6	927.8
162.5°	945.9	941.5	942.3	946.6	940.1
165°	956.0	951.7	952.4	956.8	951.0
167.5°	964.0	959.7	960.4	965.5	958.9
170°	970.5	965.5	966.2	972.0	965.5
172.5°	974.9	969.8	971.3	976.3	969.8
175°	977.8	973.4	974.2	980.0	973.4
177.5°	980.0	975.6	976.3	981.4	975.6
180°	977.8	977.8	977.8	977.8	977.8

(END OF REPORT)